

# 3M™ Solus™ 2000 Series

The 3M™ Solus™ 2000 Series features adjustable ratchet temples that allow the wearer to customize fit—a first for our Solus lineup. Choose from several lens coating options, including 3M™ Scotchgard™ Anti-Fog, multiple lens colors and features like a removable foam gasket to create a protective eyewear solution for YOU.

**Adjustable Ratchet Temples**  
Multiple position ratchet allows user to adjust lens for facial features and eyeglass position.

**Removable Foam-lined Gasket**  
Helps limit eye exposure to dirt and debris while providing added comfort and cushioning.\* (Select Models)

**Reader Models**  
Models available with reading diopters +1.5, +2.0, +2.5

**Polycarbonate Lenses**  
▶ Absorb 99.9% of UVA and UVB rays.  
▶ Meet the requirements of ANSI Z87.1-2015 Standard as an Impact Rated Spectacle.

**Same Protection, New IR Lens Color**  
Unlike green IR shade lenses, gray IR lenses provide wearers with better color recognition. (Select Models)

**Choose Your Coating**  
▶ Scotchgard™ Anti-Fog Coating provides fog and abrasion resistance. (Select Models)  
▶ Resists fogging longer than traditional anti-fog coatings, up to 25 washings with water.\*  
▶ Helps provide durable scratch resistance in tough work environments.

\*Does not meet ANSI Z87.1 D4 dust or D5 fine dust rating. Users must determine if eyewear is suitable for the application prior to use.  
\*\*3M internal testing per EN168 test method when compared with traditional anti-fog coatings.

## Available Models:

**S2001SGAF-RED**  
Lens: Clear  
Frame Color: Gray/Red

**S2002SGAF-RED**  
Lens: Gray  
Frame Color: Gray/Red

**S2024AS-RED**  
Lens: Red Mirror  
Frame Color: Gray/Red

**S2001SGAF-BGR**  
Lens: Clear  
Frame Color: Gray/Teal

**S2002SGAF-BGR**  
Lens: Gray  
Frame Color: Gray/Teal

**S2003SGAF-BGR**  
Lens: Amber  
Frame Color: Gray/Teal

**S2005SGAF-BGR**  
Lens: Brown  
Frame Color: Gray/Teal

**S2007SGAF-BGR**  
Lens: I/O Gray  
Frame Color: Gray/Teal

**S2001SGAF-BGR-F**  
Lens: Clear  
Frame Color: Gray/Teal  
*Foam gasket*

**S2001AF-BLU**  
**S2001AS-BLU**  
Lens: Clear  
Frame Color: Blue/Gray

### READER MODELS

**S2008AS-CLR**  
Lens: Blue Mirror  
Frame Color: Clear/Blue

**S2001SGAF-CLR**  
Lens: Clear  
Frame Color: Clear/Blue

**S2015AF-BLU**  
Lens: Clear +1.5  
Frame Color: Blue/Gray

**S2020AF-BLU**  
Lens: Clear +2.0  
Frame Color: Blue/Gray

**S2025AF-BLU**  
Lens: Clear +2.5  
Frame Color: Blue/Gray

### IR SHADE MODELS

**S2017AS-BLK**  
Lens: IR 1.7 Gray  
Frame Color: Black/Green

**S2030AS-BLK**  
Lens: IR 3.0 Gray  
Frame Color: Black/Green

**S2050AS-BLK**  
Lens: IR 5.0 Gray  
Frame Color: Black/Green

# Ordering Information

Product I.D.	3M I.D.	Description	Frame Color	Lens Color	Coating	Units per Case	Foam Gasket
S2001SGAF-RED	70-0717-3285-6	3M™ Solus™ 2000 Series, S2001SGAF-RED, Gray/Red Temples, Scotchgard™ Anti-Fog Coating, Clear AF-AS Lens	Gray/Red	Clear	SGAF AF/AS	20	-
S2002SGAF-RED	70-0717-3286-4	3M™ Solus™ 2000 Series, S2002SGAF-RED, Gray/Red Temples, Scotchgard™ Anti-Fog Coating, Gray AF-AS Lens	Gray/Red	Gray	SGAF AF/AS	20	-
S2024AS-RED	70-0717-3287-2	3M™ Solus™ 2000 Series, S2024AS-RED, Gray/Red Temples, Red Mirror Anti-Scratch Lens	Gray/Red	Red Mirror	AS	20	-
S2001SGAF-BGR	70-0717-3288-0	3M™ Solus™ 2000 Series, S2001SGAF-BGR, Gray/Blue-Green Temples, Scotchgard™ Anti-Fog Coating, Clear AF-AS Lens	Gray/Teal	Clear	SGAF AF/AS	20	-
S2002SGAF-BGR	70-0717-3289-8	3M™ Solus™ 2000 Series, S2002SGAF-BGR, Gray/Blue-Green Temples, Scotchgard™ Anti-Fog Coating, Gray AF-AS Lens	Gray/Teal	Gray	SGAF AF/AS	20	-
S2003SGAF-BGR	70-0717-3290-6	3M™ Solus™ 2000 Series, S2003SGAF-BGR, Gray/Blue-Green Temples, Scotchgard™ Anti-Fog Coating, Amber AF-AS Lens	Gray/Teal	Amber	SGAF AF/AS	20	-
S2005SGAF-BGR	70-0717-3292-2	3M™ Solus™ 2000 Series, S2005SGAF-BGR, Gray/Blue-Green Temples, Scotchgard™ Anti-Fog Coating, Brown AF-AS Lens	Gray/Teal	Brown	SGAF AF/AS	20	-
S2007SGAF-BGR	70-0717-3293-0	3M™ Solus™ 2000 Series, S2007SGAF-BGR, Gray/Blue-Green Temples, Scotchgard™ Anti-Fog Coating, I/O Gray AF-AS Lens	Gray/Teal	I/O Gray	SGAF AF/AS	20	-
S2001S-GAF-BGR-F	70-0717-3295-5	3M™ Solus™ 2000 Series, S2001SGAF-BGR-F, Gray/Blue-Green Temples, Scotchgard™ Anti-Fog Coating, Clear AF-AS Lens, Foam Gasket	Gray/Teal	Clear	SGAF AF/AS	20	✓
S2001AS-BLU	70-0717-3296-3	3M™ Solus™ 2000 Series, S2001AS-BLU, Blue/Gray Temples, Clear Anti-Scratch Lens	Blue/Gray	Clear	AS	20	-
S2001AF-BLU	70-0717-3297-1	3M™ Solus™ 2000 Series, S2001AF-BLU, Blue/Gray Temples, Clear AF-AS Lens	Blue/Gray	Clear	AF/AS	20	-
S2008AS-CLR	70-0717-3380-5	3M™ Solus™ 2000 Series, S2008AS-CLR, Clear/Blue Temples, Blue Mirror Anti-Scratch Lens	Clear/Blue	Blue Mirror	AS	20	-
S2001SGAF-CLR	70-0717-3398-7	3M™ Solus™ 2000 Series, S2001SGAF-CLR, Clear/Blue Temples, Scotchgard™ Anti-Fog Coating, Clear AF-AS Lens	Clear/Blue	Clear	SGAF AF/AS	20	-
<b>Readers Models</b>							
S2015AF-BLU	70-0717-3377-1	3M™ Solus™ 2000 Series, S2015AF-BLU, Blue/Gray Temples, Clear Reader +1.5 Anti-Fog/Anti-Scratch lens	Blue/Gray	Clear +1.5	AF/AS	20	-
S2020AF-BLU	70-0717-3378-9	3M™ Solus™ 2000 Series, S2020AF-BLU, Blue/Gray Temples, Clear Reader +2.0 Anti-Fog/Anti-Scratch lens	Blue/Gray	Clear +2.0	AF/AS	20	-
S2025AF-BLU	70-0717-3379-7	3M™ Solus™ 2000 Series, S2025AF-BLU, Blue/Gray Temples, Clear Reader +2.5 Anti-Fog/Anti-Scratch lens	Blue/Gray	Clear +2.5	AF/AS	20	-
<b>IR Shade Models</b>							
S2017AS-BLK	70-0717-3298-9	3M™ Solus™ 2000 Series, S2017AS-BLK, Black/Green Temples, IR 1.7 Gray Anti-Scratch Lens	Black/Green	IR 1.7 Gray	AS	20	-
S2030AS-BLK	70-0717-3301-1	3M™ Solus™ 2000 Series, S2030AS-BLK, Black/Green Temples, IR 3.0 Gray Anti-Scratch Lens	Black/Green	IR 3.0 Gray	AS	20	-
S2050AS-BLK	70-0717-3302-9	3M™ Solus™ 2000 Series, S2050AS-BLK, Black/Green Temples, IR 5.0 Gray Anti-Scratch Lens	Black/Green	IR 5.0 Gray	AS	20	-
<b>Accessories</b>							
S2000-FOAM	70-0717-3381-3	3M™ Solus™ 2000 Series, S2000-FOAM, Replacement Foam Gasket	-	-	-	10ea/bag	-

Explore more protective eyewear at [3M.com/ProtectiveEyewear](https://www.3m.com/ProtectiveEyewear).

#3MScienceofSafety

**WARNING:** These eye and face protection products help provide limited eye and face protection. Misuse or failure to follow warnings and User Instructions may result in serious potential injury, including blindness or death. For proper use, selection and applications against flying particles, optical radiation and/or splash, see supervisor, read User Instructions and warnings on the package or call 3M PSD Technical Service in the USA at 800-243-4630. In Canada, call Technical Service at 800-267-4114.



Personal Safety Division  
3M Center, Building 235-2W-70  
St. Paul, MN 55144-1000

Technical Assistance 1-800-243-4630  
Customer Service 1-800-328-1667  
[3M.com/ProtectiveEyewear](https://www.3m.com/ProtectiveEyewear)

3M PSD products are for occupational use only.

© 3M 2019. All rights reserved. 3M, Solus and Scotchgard are trademarks of 3M. Used under license by 3M subsidiaries and affiliates. Please recycle. Printed in USA. Issued: 11/19 14677HB70-0716-9775-2