

3M Science.
Applied to Life.™

Personalize your OTG.

Over-the-glass eye protection that is comfortable and lets you focus on your work instead of uncomfortable and poor fitting eyewear.



[3M.com/SecureFit](https://www.3m.com/SecureFit)

3M™ SecureFit™
3700 OTG Series

Designed with self-adjusting temple technology for all day wearability and comfort.

3M™ SecureFit™ 3700 OTG Series

Workers that wear regular prescription glasses often complain about the nature of traditional over-the-glass spectacles. Too heavy. Uncomfortable. Easily scratch. Damage my personal glasses.


That's why we created the 3M™ SecureFit™ 3700 OTG Series. We achieve improved fit and performance with patented self-adjusting Pressure Diffusion Temple (PDT) technology, designed to help our protective eyewear feel secure and comfortable for extended periods of time.

It's time to protect your prescription eyewear with the 3M™ SecureFit™ 3700 OTG Series.



Adjustable Ratchet Temples
Multiple position ratchet allows user to adjust lens for facial features and eyeglass position.

Pressure Diffusion Temple (PDT) Technology
3M patented technology that helps diffuse pressure over the ear for a secure, comfortable fit.



Brow Guard
Contoured brow guard rests comfortably against forehead and helps provide additional coverage from particles. (Select Models)

Alternate Fit
Adjusted lens angle and soft nose bridge designed to help accommodate tall cheekbone structure and low nose bridge height. (Select Models)

Polycarbonate Lenses

- ▶ Absorb 99.9% of UVA and UVB rays.
- ▶ Meet the requirements of ANSI Z87.1-2015 Standard as an Impact Rated Spectacle.



Two Coating Options (Model Dependent):

Anit-Scratch Coating

- ▶ Many prescription eyeglasses do not have anti-fog coating on the lenses, therefore some workers may prefer our less expensive standard anti-scratch coating.

3M™ Scotchgard™ Anti-Fog Coating

- ▶ Scotchgard™ Anti-Fog Coating resists fogging longer than traditional anti-fog coatings, up to 25 washings with water.*
- ▶ Helps provide durable scratch resistance in tough work environments.

Designed with you in mind.

Models featuring the brow guard offer users additional coverage from particles. In addition, the brow guard is designed to position the OTG lens further from the face to help accommodate a wider range of eyeglass positions on the nose.



Alternate Fit

Workers with low nose bridges can utilize the adjusted nose piece to help achieve a more comfortable fit. Popular with Asian, African American and American Indigenous users.

Designed with options.



SF3701SGAF-BLU
SF3701AS-BLU
Lens: Clear
Frame Color: Blue/Blue



SF3702SGAF-BLU
SF3702AS-BLU
Lens: Gray
Frame Color: Blue/Blue



SF3707SGAF-BLU
SF3707AS-BLU
Lens: I/O Gray
Frame Color: Blue/Blue



SF3701SGAF-GRN
SF3701AS-GRN
Lens: Clear
Frame Color: Gray/Lime Green



SF3703SGAF-GRN
Lens: Amber
Frame Color: Gray/Lime Green



SF3701SGAF-ORG
SF3701AS-ORG
Lens: Clear
Frame Color: Gray/Orange

BROW GUARD



SF3701XSGAF-BLU
SF3701XAS-BLU
Lens: Clear
Frame Color: Gray/Blue



SF3702XSGAF-BLU
Lens: Gray
Frame Color: Gray/Blue



SF3707XSGAF-BLU
Lens: I/O Gray
Frame Color: Gray/Blue



SF3701XSGAF-RED
Lens: Clear
Frame Color: Gray/Gray

ALTERNATE FIT



SF3701ASGAF-BLU
Lens: Clear
Frame Color: Blue/Blue



SF3701XASGAF-BLU
Lens: Gray
Frame Color: Gray/Blue

3M™ SecureFit™ 3700 OTG Series

Product I.D.	3M I.D.	Description	Frame Color	Lens Color	Coating	Units per Case
SF3701SGAF-BLU	70-0717-3196-5	3M™ SecureFit™ 3700 Series, SF3701SGAF-BLU, Blue Temple, Scotchgard™ Anti-Fog Coating, Clear OTG AF-AS Lens	Blue/Blue	Clear	SGAF AF/AS	10
SF3701AS-BLU	70-0717-3197-3	3M™ SecureFit™ 3700 Series, SF3701AS-BLU, Blue Temple, Clear OTG Anti-Scratch Lens	Blue/Blue	Clear	AS	10
SF3702SGAF-BLU	70-0717-3198-1	3M™ SecureFit™ 3700 Series, SF3702SGAF-BLU, Blue Temple, Scotchgard™ Anti-Fog Coating, Gray OTG AF-AS Lens	Blue/Blue	Gray	SGAF AF/AS	10
SF3702AS-BLU	70-0717-3199-9	3M™ SecureFit™ 3700 Series, SF3702AS-BLU, Blue Temple, Gray OTG Anti-Scratch Lens	Blue/Blue	Gray	AS	10
SF3707SGAF-BLU	70-0717-3206-2	3M™ SecureFit™ 3700 Series, SF3707SGAF-BLU, Blue Temple, Scotchgard™ Anti-Fog Coating, Indoor/Outdoor Gray OTG AF-AS Lens	Blue/Blue	I/O Gray	SGAF AF/AS	10
SF3707AS-BLU	70-0717-3207-0	3M™ SecureFit™ 3700 Series, SF3707AS-BLU, Blue Temple, Indoor/Outdoor Gray OTG Anti-Scratch Lens	Blue/Blue	I/O Gray	AS	10
SF3701SGAF-GRN	70-0717-3208-8	3M™ SecureFit™ 3700 Series, SF3701SGAF-GRN, Lime Green Temple, Scotchgard™ Anti-Fog Coating, Clear OTG AF-AS Lens	Gray/Lime Green	Clear	SGAF AF/AS	10
SF3701AS-GRN	70-0717-3209-6	3M™ SecureFit™ 3700 Series, SF3701AS-GRN, Lime Green Temple, Clear OTG Anti-Scratch Lens	Gray/Lime Green	Clear	AS	10
SF3703SGAF-GRN	70-0717-3210-4	3M™ SecureFit™ 3700 Series, SF3703SGAF-GRN, Green Temple, Scotchgard™ Anti-Fog Coating, Amber OTG AF-AS Lens	Gray/Lime Green	Amber	SGAF AF/AS	10
SF3701SGAF-ORG	70-0717-3294-8	3M™ SecureFit™ 3700 Series, SF3701SGAF-ORG, Orange Temple, Scotchgard™ Anti-Fog Coating, Clear OTG AF-AS Lens	Gray/Orange	Clear	SGAF AF/AS	10
SF3701AS-ORG	70-0717-3299-7	3M™ SecureFit™ 3700 Series, SF3701AS-ORG, Orange Temple, Clear OTG Anti-scratch Lens	Gray/Orange	Clear	AS	10
BROW GUARD						
SF3701XSGAF-BLU	70-0717-3203-9	3M™ SecureFit™ 3700 Series, SF3701XSGAF-BLU, Blue Temple, Brow guard, Scotchgard™ Anti-Fog Coating, Clear OTG AF-AS Lens	Gray/Blue	Clear	SGAF AF/AS	10
SF3701XAS-BLU	70-0717-3204-7	3M™ SecureFit™ 3700 Series, SF3701XAS-BLU, Blue Temple, Brow guard, Clear OTG Anti-Scratch Lens	Gray/Blue	Clear	AS	10
SF3702XSGAF-BLU	70-0717-3205-4	3M™ SecureFit™ 3700 Series, SF3702XSGAF-BLU, Blue Temple, Brow guard, Scotchgard™ Anti-Fog Coating, Gray OTG AF-AS Lens	Gray/Blue	Gray	SGAF AF/AS	10
SF3707XSGAF-BLU	70-0717-3217-9	3M™ SecureFit™ 3700 Series, SF3707XSGAF-BLU, Blue Temple, Brow guard, Scotchgard™ Anti-Fog Coating, I/O Gray OTG AF-AS Lens	Gray/Blue	I/O Gray	SGAF AF/AS	10
SF3701XSGAF-RED	70-0717-3300-3	3M™ SecureFit™ 3700 Series, SF3701XSGAF-RED, Gray Temple, Brow guard, Scotchgard™ Anti-Fog, Clear OTG AF-AS Lens	Gray/Gray	Clear	SGAF AF/AS	10
ALTERNATE FIT						
SF3701ASGAF-BLU	70-0717-3215-3	3M™ SecureFit™ 3700 Series, SF3701ASGAF-BLU, Alternate Fit, Blue, Scotchgard™ Anti-Fog Coating, Clear OTG AF-AS Lens	Blue/Blue	Clear	SGAF AF/AS	10
SF3701XASGAF-BLU	70-0717-3291-4	3M™ SecureFit™ 3700 Series, SF3701XASGAF-BLU, Alternate Fit, Blue, Brow guard, Scotchgard™ Anti-Fog, Clear OTG AF-AS Lens	Gray/Blue	Clear	SGAF AF/AS	10

Give them a try—request a sample at [3M.com/SecureFit](https://www.3M.com/SecureFit)

#3MScienceofSafety

WARNING: These eye and face protection products help provide limited eye and face protection. Misuse or failure to follow warnings and User Instructions may result in serious potential injury, including blindness or death. For proper use, selection and applications against flying particles, optical radiation and/or splash, see supervisor, read User Instructions and warnings on the package or call 3M PSD Technical Service in the USA at 800-243-4630. In Canada, call Technical Service at 800-267-4114.



Personal Safety Division
3M Center, Building 235-2W-70
St. Paul, MN 55144-1000

Technical Assistance 1-800-243-4630
Customer Service 1-800-328-1667
[3M.com/SecureFit](https://www.3M.com/SecureFit)

3M PSD products are for occupational use only.
3M, SecureFit and Scotchgard are trademarks of 3M. Used under license by 3M subsidiaries and affiliates. Please recycle. Printed in USA.
© 3M 2019. All rights reserved. Issued: 2/19 14677HB70-0716-9775-2