



Fall Protection

Introducing the new 3M™ DBI-SALA®  
Nano-Lok™ Personal Self-Retracting Lifeline

**Light on  
weight.  
Heavy on  
features.**



# Less is more.

30% smaller and 4X more durable

Introducing the new 3M™ DBI-SALA® Nano-Lok™ Personal Self-Retracting Lifeline. Trusted for its reliability and durability, the Nano-Lok has long been the workhorse personal SRL of the industry. Our latest version doesn't just match the performance of the outgoing model—it surpasses it and then some. It's sleeker with a more compact design. It's tougher with a longer lasting cover. It's easier and faster to connect.\* All whilst complying with CE EN 360:2002.





## Next generation features:

### Saves time


- ▶ Installs 60% faster\*
- ▶ Inspect easily and quickly

### Built to last

- ▶ Nitrile rubber cover lasts 4X longer than outgoing model\*

### Tie-off versatility

- ▶ Foot-level tie off with 140 kg capacity



#### Fast connection system

Simple, light-weight connector allows backward compatibility

#### Optional twin pin connector

Easily add or remove Nano-Lok legs without removing the connector from the harness



#### Compact housing

#### Built-in RFID tag

Sleek, durable nitrile rubber energy absorber

Length: 2 m\*\*













\*Compared to previous generation.

\*\*Most models 2m, variations in top and bottom connectors mean some models measure between 1.9 m or 2.1 m.





## 3M™ DBI-SALA® Nano-Lok™ Single-leg range

Top connector (Housing side) Specific feature / application	Bottom connector (Lanyard end) Specific feature / application	Part number	↔	
 <b>Aluminium Carabiner 19 mm (3/4") opening</b> <ul style="list-style-type: none"> <li>Connects to a D-Ring attachment point on a fall arrest harness</li> </ul>	 <b>Aluminium Hook 57 mm (2-1/4") opening</b> <ul style="list-style-type: none"> <li>Popular model</li> </ul>	<b>3101208</b>	2.0 m	
	 <b>Aluminium Carabiner 19 mm (3/4") opening</b> <ul style="list-style-type: none"> <li>Lightweight</li> </ul>	<b>3101264</b>	1.9 m	
	 <b>Aluminium Hook 57 mm (2-1/4") opening</b> <ul style="list-style-type: none"> <li>Heavy-duty gate</li> </ul>	<b>3101263</b>	2.0 m	
	 <b>Aluminium Hook Comfort Grip 63.5 mm (2-1/2") opening</b> <ul style="list-style-type: none"> <li>Helps protect users hand</li> <li>Heavy-duty</li> <li>Ideal for cross-loading</li> </ul>	<b>3101709</b>	2.1 m	
 <b>Triple Action Steel Carabiner 19 mm (3/4") opening</b> <ul style="list-style-type: none"> <li>Allows the addition of a second device to convert to a twin-leg unit</li> </ul>	 <b>Steel Snap Hook 19 mm (3/4") opening</b> <ul style="list-style-type: none"> <li>Economical solution</li> </ul>	<b>3101265</b>	2.0 m	
	 <b>Aluminium Hook 57 mm (2-1/4") opening</b> <ul style="list-style-type: none"> <li>Popular model</li> </ul>	<b>3101461</b>	2.0 m	
 <b>Steel Fast Connection System</b> <ul style="list-style-type: none"> <li>Connects through the harness dorsal web - leaving the dorsal D-ring free for rescue operation</li> </ul>	 <b>Aluminium Hook 57 mm (2-1/4") opening</b> <ul style="list-style-type: none"> <li>Popular model</li> </ul>	<b>3101207</b>	2.0 m	
	 <b>Aluminium Hook 57 mm (2-1/4") opening</b> <ul style="list-style-type: none"> <li>Heavy-duty gate</li> </ul>	<b>3101261</b>	2.0 m	
	 <b>Aluminium Hook 63.5 mm (2-1/2") opening</b> <ul style="list-style-type: none"> <li>Heavy-duty</li> </ul>	<b>3101730</b>	2.0 m	

## 3M™ DBI-SALA® Nano-Lok™ Twin-leg range

Top connector (Housing side) Specific feature / application	Bottom connector (Lanyard end) Specific feature / application	Part number	←.....→	
 <p><b>Triple Action Steel Carabiner</b> 19 mm (3/4") opening</p> <ul style="list-style-type: none"> <li>To be connected through the harness dorsal web or on the dorsal fall arrest D-ring</li> </ul>	 <p><b>Aluminium Hook</b> 57 mm (2-1/4") opening</p> <ul style="list-style-type: none"> <li>Popular model</li> </ul>	<b>3101316</b>	2.0 m	
 <p><b>Steel Fast Connection System</b></p> <ul style="list-style-type: none"> <li>Connects through the harness dorsal web - leaving the dorsal D-ring free for rescue operation</li> </ul>	 <p><b>Aluminium Hook</b> 57 mm (2-1/4") opening</p> <ul style="list-style-type: none"> <li>Popular model</li> </ul>	<b>3101298</b>	2.0 m	
	 <p><b>Aluminium Hook</b> 57 mm (2-1/4") opening</p> <ul style="list-style-type: none"> <li>Heavy-duty gate</li> </ul>	<b>3101270</b>	2.0 m	
	 <p><b>Aluminium Hook Comfort Grip 63.5 mm (2-1/2") opening</b></p> <ul style="list-style-type: none"> <li>Helps protect users hand</li> <li>Heavy-duty</li> <li>Ideal for cross-loading</li> </ul>	<b>3101718</b>	2.0 m	
	 <p><b>Aluminium Hook</b> 63.5 mm (2-1/2") opening</p> <ul style="list-style-type: none"> <li>Heavy-duty</li> </ul>	<b>3101719</b>	2.0 m	

Top connectors can be ordered separately using the following references

Part number		Description	Part number		Description
2000025		Aluminium Carabiner 19mm(3/4") opening	3100481		Fast Connection System (For use only with 3M™ DBI-SALA® Nano-Lok™)
3100128		Triple Action Steel Carabiner 19 mm (3/4") opening	3100484		Twin Pin Connector (For use only with Nano-Lok™)



Fall Protection

#### 3M Fall Protection

**Capital Safety (Northern Europe) Limited**  
3M Centre, Cain Road  
Bracknell, Berkshire, RG12 8HT, UK

**Capital Safety Group (EMEA)**  
Le Broc Center, Bâtiment A, Z.1. 1re Avenue – BP15  
06511 Carros Le Broc, Cedex, FRANCE

Phone +33(0)4 83 58 08 08 Email [informationfallprotection@mmm.com](mailto:informationfallprotection@mmm.com) Web [3M.com/FallProtection](http://3M.com/FallProtection)

3M, DBI-SALA and Nano-Lok are trademarks of 3M Company and its affiliates.

Please recycle. Printed in the U.K.  
©3M 2021. All rights reserved.  
Ref: CC23206