

Next-generation comfort, breathability and simplicity.

Introducing the 3M[™] Secure Click[™] Half Mask Reusable Respirator HF-800 Series.

Designed with smart and intuitive features 3M[™] Secure Click[™] Half Mask Reusable Respirator is simple, comfortable and reliable.

Experience the breathability and comfort provided by the world's first quad-flow cartridge system.

Introducing the

3M[™] Secure Click[™] Half Mask Reusable Respirator HF-800 Series.

Designed with smart and intuitive features, the 3M Secure Click Half Facepiece Reusable Respirator HF-800 Series helps protect workers from particulates and a wide variety of gases and vapours when used with approved 3M Secure Click filters.



3M™ Secure Click™ Half Mask Reusable Respirator HF-800 Series

Product: HF-801SD/HF-802SD/HF-803SD

Size: Small/medium/large



3M™ Secure Click™ connection helps provide confidence that filters are installed properly. Simply align the connections and push into place.





Help increase worker confidence that the respirator is being worn properly with the easy, one-touch, user seal check.





Feel it:

Experience the breathability and comfort provided by the world's first quad-flow gas and vapour filter/combination filter systems.





Say it:

Utilise the speaking diaphragm to help provide easy communication.



Half Masks	
Product	Description
HF-801SD	3M™ Secure Click™ Half Mask Reusable Respirator, Small, HF-801SD
HF-802SD	3M™ Secure Click™ Half Mask Reusable Respirator, Medium, HF-802SD
HF-803SD	3M™ Secure Click™ Half Mask Reusable Respirator, Large, HF-803SD

Particulate filters		
Product	Description	
D3125	3M™ Secure Click™ Particulate Filter, P2 R, D3125	
D3135	3M™ Secure Click™ Particulate Filter, P3 R, D3135	
D3128	3M [™] Secure Click [™] Particulate Filter with Nuisance Level Organic Vapour and Acid Gas Relief, and Ozone up to 10 x WEL, P2 R, D3128	
D3138	3M [™] Secure Click [™] Particulate Filter with Nuisance Level Organic Vapour and Acid Gas Relief, and Ozone up to 10 x WEL, P3 R, D3138	

Gas and vapour filters		
Product	Description	
D8059	3M [™] Secure Click [™] Gas and Vapour Filter, A1B1E1K1, with Dual Flow, D8059	
D8057	3M [™] Secure Click [™] Gas and Vapour Filter, A1B1E1, with Dual Flow, D8057	
D8055	3M [™] Secure Click [™] Gas and Vapour Filter, A2, with Dual Flow, D8055	
D8051	3M [™] Secure Click [™] Gas and Vapour Filter, A1, with Dual Flow, D8051	

Particulate filters – compatible with gas and vapour filters		
Product	Description	
D701	3M™ Secure Click™ Reusable Respirator Filter Retainer, D701	
D7915	3M™ Secure Click™ Particulate Filter, P1 R, D7915	
D7925	3M™ Secure Click™ Particulate Filter, P2 R, D7925	
D7935	3M™ Secure Click™ Particulate Filter, P3 R, D7935	

Combination filters		
Product	Description	
D8097	3M™ Secure Click™ Gas, Vapour and Particulate Filter, A1B1E1K1+Hg P3 R, with Dual Flow, D8097	
D8095	3M™ Secure Click™ Gas, Vapour and Particulate Filter, A2 P3 R, with Dual Flow, D8095	
D8094	3M™ Secure Click™ Gas, Vapour and Particulate Filter, A1B1E1K1 P3 R, with Dual Flow, D8094	

Fit test adapters		
Product	Description	
HF-800-03	3M [™] Secure Click [™] Quantitative Fit Test Adapter Kit, for 3M [™] Secure Click [™] Half Mask HF-800 Series, HF- 800-03	
Spare parts and accessories		
Product	Description	
HF-800-01	3M™ Secure Click™ Reusable Respirator Head Harness Assembly, for 3M™ Secure Click™ Half Mask HF-800 Series, HF-800-01	
HF-800-04	3M [™] Secure Click [™] Reusable Respirator Head Harness Assembly, for 3M [™] Secure Click [™] Half Mask HF-800 Series with Speaking Diaphragm, HF- 800-04	

Mask HF-800, HF-800-05

800 Series, HF-800-02

HF-800-05

HF-800-02

3M[™] Secure Click Reusable Respirator Speaking

Diaphragm Assembly, for 3M[™] Secure Click[™] Half

3M[™] Secure Click[™] Reusable Respirator Inhale & Exhale Valve, for 3M[™] Secure Click[™] Half Mask HF-

^{*}Nuisance levels refers to concentrations not exceeding applicable government occupational exposure limits.