

3M™ Scott™ ELSA – Emergency Life Support Apparatus



Anti-static bag

Description

The 3M™ Scott™ ELSA (Emergency Life Support Apparatus) is an escape breathing apparatus which provides a constant supply of air for rapid escape from hazardous industrial and marine environments. The 3M™ Scott™ ELSA is designed to be simple and quick to operate, reliable and robust in use, ensuring maximum protection in an escape situation.

The ELSA is available in durations of 10 or 15 minutes in high visibility PVC or black anti-static polyurethane materials. The ELSA apparatus consists of a cylinder with combined cylinder valve and reducer, supply hose to constant flow hood and stowage bag. The ELSA is activated upon opening the bag whereby a pin which is attached to the ELSA hood is released.

Applications

The ELSA is suitable for use in marine or industrial escape settings for escape use only.

Carrying bag

The carrying bag is made of PVC coated nylon. This is coloured for high visibility and is both flame retardant and chemical splash resistant. There is an anti-static option for working in potentially explosive atmospheres and this is made of polyurethane. The bag can be worn across the chest as a bandolier.

Hood

The constant flow hood is manufactured from PVC coated materials. This is flame retardant and coloured for high visibility. This provides a stretch material for a comfortable fit combined with an elastomeric neck seal giving ease of donning over spectacles, beards and long hair. The optically clear visor is made from polyurethane. The hood has an exhale valve for increased performance and a compact orinasal inner mask for reduced rebreathed CO₂ levels.

Maintenance/cleaning/servicing

Cleaning should only be carried out as specified in the user instructions. Maintenance and servicing must only be performed by trained personnel following the procedures in the service and maintenance manual.

Specification

Approvals

CE marked in accordance with EN 1146

MED shipswheel approved

Materials

Pressure reducing valve	Nickel plated brass
Rust tube	Brass
Reducing valve seat	Polyamide (nylon)
O-rings	Nitrile, silicone, EPDM, viton
Reducing valve springs	Stainless steel
HP pressure gauge	Stainless steel, polycarbonate lens
HP pressure gauge cover	Neoprene
MP air supply hose fittings	Nickel plated brass
Air hood	PVC coated viscose with clear PU visor
MP air supply hose	Chlorinated polyethylene, fabric braid reinforcement, nitrile liner
Carrying bag	PVC coated nylon
Anti-static carrying bag	Polyurethane
Strap buckles	Polyamide
Cylinder	Steel or composite

Hoses

Stainless steel swivel hose fittings

Medium pressure hose

Maximum working pressure 16 bar

Minimum burst pressure 80 bar

Packing specifications (with steel cylinder)

10 minute bag version 52×30×15cm, 6.0kg

15 minute bag version 52×30×25cm, 6.5kg

Weight/dimensions (with steel cylinder)

10 minute bag version

Weight	4.8kg
Length	510mm
Width	340mm
Depth	135mm

15 minute bag version

Weight	5.6kg
Length	520mm
Width	340mm
Depth	135mm

3M Scott Fire & Safety

Pimbo Road
Skelmersdale
Lancashire, WN8 9RA
United Kingdom

Phone +44 (0)1695 711711
E-Mail skelmenq@mmm.com
Web www.3Mscott.com

ISO 9001 Registered. Please recycle.
Printed in the UK. © 3M 2023.
All rights reserved. 3M and Scott are
trademarks of 3M Company. OMG561030

