






Trust 3M Products to help keep your facility clean and safe.



- 1 3M™ Easy Trap Duster – sweep & dust sheets
- 2 3M™ Easy Scrub Flat Mop System
- 3 Scotch-Brite™ High Performance Microfibre Cloths
- 4 3M™ Stainless Steel Cleaner and Protector 
- 5 Scotch-Brite™ Easy Erasing Hand Pad 4004
- 6 3M™ Safety-Walk™ Anti-Slip Tapes and Treads 

- 7 3M™ Clean Walk Mat
- 8 3M™ High Capacity Maintenance Sorbent Roll
- 9 Scotch-Brite™ Power Pad 2000 
- 10 Scotch-Brite™ Medium Duty Scouring Pad 97 
- 11 Scotch-Brite™ Light Duty Scrubbing Pad 9030 

Maintain the high standards of your food processing facilities with 3M™ Professional Cleaning Solutions.



1 3M™ Easy Trap Duster – sweep & dust sheets

Traps up to 8 times more dirt, dust and sand than conventional flat-fringed cotton dust mops or a competitive sweeping dust cloth brand. Can be used with your existing flat mop or high duster.*

* Based on a study conducted by 3M



2 3M™ Easy Scrub Flat Mop System

Excellent for daily cleaning activities and ease of manoeuvring around furniture. Help cut chemical waste by 80% compared to a mop and bucket, with the operator-controlled dispensing mechanism.*

* Based on a study conducted by 3M



3 Scotch-Brite™ High Performance Microfibre Cleaning Cloths

Ideal for cleaning stainless steel, chrome, wood and enamel, Scotch-Brite™ High Performance Cleaning Cloths are reusable and perfect for delicate surfaces such as glass and plastic.

4 3M™ Stainless Steel Cleaner & Protector

Leaves an invisible layer of protection on stainless steel surfaces, making them easier to clean and more resistant to fingerprinting and smudging. This water-based, oil-free formula allows for quick-drying, streak-free spot cleaning, which can help reduce labour and lower product consumption.



5 Scotch-Brite™ Easy Erasing Hand Pad 4004

Ideal for removing stains, marks, ink and more. Just use water — no chemicals or sprays needed.



6 3M™ Safety-Walk™ Anti-Slip Tapes and Treads

Offers a low-profile design and helps reduce trip hazards. This mineral-coated, slip-resistant material is adhered by a durable resin to a pressure-sensitive adhesive backed plastic film.



7 3M™ Clean Walk Mat

3M™ Clean-Walk Mat is an adhesive-coated mat used to remove dirt from the bottom of shoes, wheels or any passing objects. To expose the adhesive surface, just peel the top sheet back.



8 3M™ High Capacity Maintenance Sorbent Roll

3M™ High Capacity Maintenance Sorbent Roll offers a pad that has a scrim on one side to increase the strength and help eliminate lifting. This material is perfect for lining drawers, covering workbenches or masking larger areas from mist and overspray.



9 Scotch-Brite™ Power Pad 2000

Scours 2 - 4 times faster than conventional commercial scouring pads, and is 6 - 10 times less abrasive than other medium-duty commercial scouring products to reduce scratching.*

* Based on a study conducted by 3M



10 Scotch-Brite™ Medium Duty Scouring Pad 97

Use it on everyday equipment. This pad replaces steel wool and won't leave metal slivers in hands. Long-lasting, non-rusting and resilient.



11 Scotch-Brite™ Light Duty Scrubbing Pad 9030

The Scotch-Brite™ Light Duty Scrubbing Pad 9030 is a convenient, thick, hand-sized pad designed for gentle, no-scratch cleaning of the most delicate surfaces.



3M Commercial Solutions Division
3M Canada
P.O. Box 5757
London, Ontario
N6A 4T1
3M.ca/CommercialCleaning

For more information, please contact
your distribution representative or visit
3M.ca/CommercialCleaning.

3M, 3M Science. Applied to Life., Scotch-Brite, Safety-Walk and Scotchgard are trademarks of 3M. Used under license in Canada. All other trademarks are property of their respective owners. © 2019, 3M. All rights reserved. 1902-13951 E