

**3M** Science.  
Applied to Life.™



# A family of pads to fit every size repair.

## More is better!

Our redesigned foam buff pads now have TWICE as many convolutes (peaks and valleys) as our previous generation pads. Our 100% Low Lint wool pads reduce the amount of floating fibers with great cut and a better finish for easier polishing. And what benefits does that provide?

- Smoother gliding with less chatter and drag
- Uniformly spreads compound with less smearing
- Less spatter and sling = less cleanup = less work

4 inch pad inset protects sharp edge of the backing plate



| Part No.  | Product Description  |       |   |
|---|--|-------|---|
| <b>3M™ Perfect-It™ Paint Finishing System Compounding</b>       |  |       |   |
| 05706   | 3M™ Perfect-It™ Foam Compound Pad Quick Connect, 8 in, 1/Bag, 6 per case                                     | 33287 | 3M™ Perfect-It™ 100% Wool Compounding Pad 6 in, 1/Bag 6 per case  |
| 33284   | 3M™ Perfect-It™ Foam Compound Pad Quick Connect, 6 in, 1/Bag, 6 per case                                     | 33288 | 3M™ Perfect-It™ Low Linting Wool Compounding Pad 6 in, 1/Bag, 6 per case  |
| 05737   | 3M™ Perfect-It™ Foam Compounding Pad, Single Sided, Inset, 8 in, 1/Bag, 6 per case                           | 33279 | 3M™ Perfect-It™ Low Linting 100% Wool Compounding Pad 9 in, 1/Bag, 6 per case                                     |
| 05753   | 3M™ Perfect-It™ 100% Wool Compounding Pad 9 in, 1/Bag, 6 per case  |       |   |
| <b>3M™ Perfect-It™ Paint Finishing System Polish</b>            |  |       |   |
| 05707   | 3M™ Perfect-It™ Foam Polishing Pad Quick Connect, 8 in, 1/Bag, 6 per case                                    | 33035 | 3M™ Perfect-It™ 1-Step Foam Finishing Pad, 8 in, 1/Bag, Quick Connect, 6 per case                                 |
| 33285   | 3M™ Perfect-It™ Foam Polishing Pad Quick Connect, 6 in, 1/Bag, 6 per case                                    | 33036 | 3M™ Perfect-It™ 1-Step Foam Finishing Pad, 8 in, Hook-it, 2 pads per bag, 12 bags per case                        |
| 05738   | 3M™ Perfect-It™ Foam Polishing Pad, Single Sided, Inset, 8 in, 1/Bag, 6 per case                             | 33037 | 3M™ Perfect-It™ 1-Step Foam Finishing Pad, 8 in, 1/Bag, Inset, 6 per case   |
| 33033   | 3M™ Perfect-it™ 1-Step Foam Finishing Pad, 4 in, Hook-it, 2 pads per bag, 6 bags per case                    | 33042 | 3M™ Perfect-It™ 1-Step Foam Finishing Pad, 6 in, Hook-it, 2 pads per bag, 12 bags per case                        |
| 33034   | 3M™ Perfect-It™ 1-Step Foam Finishing Pad, 6 in, 1/Bag, Quick Connect, 6 per case                            |       |   |
| <b>3M™ Perfect-It™ Paint Finishing System Swirl Elimination</b> |  |       |   |
| 05708   | 3M™ Perfect-It™ Ultrafine Foam Polishing Pad Quick Connect, 8 in, 1/Bag, 1/Bag per case                      | 05733 | 3M™ Perfect-It™ Ultrafine Foam Polishing Pad, Single Sided, Inset, 8 in, 1/Bag, 6 Bags per case                   |
| 33286   | 3M™ Perfect-It™ Ultrafine Foam Polishing Pad Quick Connect, 6 in, 1/Bag, 1/Bag per case                      |       |   |
| <b>3M™ Perfect-It™ Buffing Pads</b>                             |  |       |   |
| 05723   | 3M™ Perfect-It™ Foam Compounding Pad, Single Sided, Flat Back, 8 in, 2/Bag, 12 per case                      | 30042 | 3M™ Perfect-It™ Foam Polishing Pad, 4 in, single sided with inset, Hookit™ 4 in, 2/Bag, 6 Bags per case           |
| 05725   | 3M™ Perfect-It™ Foam Polishing Pad, Single Sided, Flat Back, 8 in, 2/Bag, 12 per case                        | 30043 | 3M™ Perfect-It™ Ultrafine Foam Polishing Pad, 4 in, single sided with inset, Hookit™ 4 in, 2/Bag, 6 Bags per case |
| 05751   | 3M™ Perfect-It™ Ultrafine Foam Polishing Pad, Single Sided, Flat Back, 8 in, 2/Bag, 12 per case              | 30044 | 3M™ Perfect-It™ Foam Finishing Pad, 4 in, single sided with inset, Hookit™ 4 in, 2/Bag, 6 Bags per case           |
| 30040   | 3M™ Perfect-It™ Low Lint Wool Compounding Pad, single sided with inset, Hookit™ 4 in, 2/Bag, 6 bags per case | 30045 | 3M™ Perfect-It™ Paint Finishing Pad Kit, 4 in, single sided with inset, Hookit™ 4 in, 4/Box, 6 Boxes per case     |
| 30041   | 3M™ Perfect-It™ Foam Compound Pad, 4 in, single sided with inset, Hookit™ 4 in, 2/Bag, 6 Bags per case       |       |   |
| <b>Accessories</b>  |  |       |   |
| 05752   | 3M™ Quick Connect Adaptor, 5/8 in, 10 per case   | 33270 | 3M™ Quick Connect Adaptor, 16 mm, 10 per case   |
| 33271   | 3M™ Quick Connect Adaptor, 14 mm, 10 per case  |       |   |

Visit [3mcollision.com/performancepads](http://3mcollision.com/performancepads) for more SOPs & videos



**Automotive Aftermarket Division**  
**3M Center, Building 223-6N-01**  
**St. Paul, MN 55144 USA**

Phone 1-877-666-2277  
 Web [3MCollision.com](http://3MCollision.com)

**Warranty and Limited Remedy:** 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER EXPRESS OR IMPLIED WARRANTIES OR CONDITIONS, INCLUDING ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. If the 3M product does not conform to this warranty, the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

**Limitation of Liability:** Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted.

3M, Accuspray, Cubitron, Hookit, PPS, Perfect-It, Platinum, Roloc, Scotch, Speedglas, Stikit and Trizact are trademarks of 3M Company. Please recycle. Printed in USA. © 3M 2019. All rights reserved. 60-4402-7852-5 (Rev. 08/19)