



SALA Detachable, steel, screw gate Karabiner for use with fall arrest equipment.

Description

Sala connectors ensure there are no weak links in the worlds premier safety systems.

This detachable karabiner can be attached to spliced or webbing lanyards, and other PPE products.

The screw gate is ideal working situations where opening is occasional during the working day. For quick installation of items such as fall arrest blocks the screw gate is ideal, as the gate can be opened by the action of pushing it onto the anchorage point, the gate can then be manual locked once the karabiner holds the weight of the device.

Main features

- High tensile alloy steel gate and body
- Very high strength karabiner minimum breaking strength 50kN
- Gate opening 25mm
- Automatic closing with manual screw locking
- Double action security
- Quick and easy to open with one hand
- Easily used by left and right handed persons
- Marked with Batch reference for easier quality assurance traceability.

Applications

A high strength karabiner, suitable for work in most areas of height safety:

- General Height safety
- Anchorage points



Associated Products

Can be used in association with:-

KE5175R Splices rope lanyard

KE5125W, KE5175W Webbing lanyard

KE5125X, KE5175X Expander lanyard

KD1TALONHN

Talon webbing retractable fall arrest device 3m.

KD100/2

Lightweight webbing retractable fall arrest device 2.5m.

KJ5107


(R-107)



SALA Detachable, steel, screw gate Karabiner for use with fall arrest equipment.

Technical specification

- Material – Heat treated, high tensile alloy steel
- Surface finish – Zinc plated with yellow passivation
- Gate opening – 25mm
- Height – 112mm
- Width – 64mm
- Net Weight - 220g
- CE marked – Yes
- Conforms to standard – EN362
- Breaking Strength – 50kN



Options

KJ5105S

Detachable steel karabiner with 17mm opening. Breaking strength 22kN

KJ5106

Detachable steel Karabiner with 33mm opening. High Breaking strength 45kN

KJ5024

Detachable aluminium Karabiner with 21mm opening. Breaking strength 25kN