

## Specifications for 3M™ Sun Control Window Film Prestige Series

### 1.0 Scope

This specification is for an abrasion resistant solar control window film which when applied to the interior window surface will reduce the gain of solar heat energy through the window. The film shall contain no metals. The film shall be called 3M™ Prestige Sun Control Window Film \_\_\_\_\_ [Series or Product Number].

### 2.0 Applicable Documents

The publications listed below form a part of this specification to the extent referenced. The publications are referred to in the text by the basic designation only.

The 1997 American Society for Heating, Refrigeration, and Air Conditioning Engineers (ASHRAE) Handbook of Fundamentals.

The American Society for Testing and Materials (ASTM) publication:

- ASTM E-308 Standard Recommended Practice for Spectrophotometry and Description of Color in CIE 1931 System
- NFRC 100/200/304 (FORMERLY ASTM E-903) Standard Methods of Test for Solar Absorbance, Reflectance and Transmittance of Materials Using Integrating Spheres
- ASTM D-1044 Standard Method of Test for Resistance of Transparent Plastics to Surface Abrasion (Taber Abrader Test)
- ASTM G-26 Standard Practice for Performing Accelerated Outdoor Weatherizing for Non-metallic Materials Using Concentrated Natural Sunlight
- ASTM E-84 Standard Method of Test for Surface Burning Characteristics of Building Materials

Window, A Computer Tool for Analyzing Window Thermal Performance, Lawrence Berkeley Laboratory

### 3.0 Requirements of the Film

**3.1 Film Material:** The film shall be an optically clear polyester film containing at least 220 layers and incorporating an acrylic pressure sensitive adhesive on one side and an acrylic abrasion resistant coating on the other. The film shall also incorporate Infrared absorbing carbon and/or metal oxide particles. The film shall be uniform without noticeable pin holes, streaks, thin spots, scratches, banding or other optical defects. The variation in total transmission across the width, at any portion along the length, shall conform to NFRC certification requirements. The film shall have a nominal thickness of 2.0 mils (0.002 inches). There shall be no evidence of coating voids. The film shall be identified as to Manufacturer of Origin (hereafter to be called Manufacturer).

**3.2 Emissivity:** The emissivity of the non-adhesive surface of the film shall be 0.78 nominal when measured using a Devices & Services Emissometer Model AE at or near room temperature. The Manufacturer shall provide laboratory data of emissivity and calculated window "U" Values for various outdoor temperatures based upon established calculation procedure defined by the 1997 ASHRAE Handbook of Fundamentals, ch. 29, or Lawrence Berkeley Laboratory Window Computer Program available from:

<http://windows.lbl.gov/software/window/window.html>

**3.3 U Value:** The U Value of the film applied to 1/4" (6mm) clear glass shall be 1.0 nominal when measured in accordance with test procedures described in 3.2 for Emissivity.

**3.4 Transmission - Visible:** When applied to 1/4" (6mm) clear glass, the luminous transmittance shall be \_\_\_\_\_ nominal when measured with an integrating sphere spectrophotometer as referenced by NFRC 100/200/304 (Formerly ASTM E-903) and calculated per ASTM E-308 using Standard Source "C" for average daylight.

### Commercial Solutions Division

3M Center, Building 220-12E-04 St. Paul, MN 55144  
3M.com/windowfilm

© 3M 2019. All rights reserved.

3M is a trademark of 3M. Used under license in Canada.

All other trademarks are property of their respective owners. Revision A, April 2019. Please recycle.



**3.5 Reflection – Visible, Exterior:** When applied to 1/4" (6mm) clear glass, the total luminous reflection from the glass surface shall be \_\_\_\_\_ nominal when measured with an integrating sphere spectrophotometer as referenced by NFRC 100/200/304 (Formerly ASTM E-903) and calculated per ASTM E-308 using Standard CIE Source "C" for average daylight.

**3.6 Reflection – Visible, Interior:** When applied to 1/4" (6mm) clear glass, the total luminous reflection from the glass surface shall be \_\_\_\_\_ nominal when measured with an integrating sphere spectrophotometer as referenced by NFRC 100/200/304 (FORMERLY ASTM E-903) and calculated per ASTM E-308 using Standard CIE Source "C" for average daylight.

**3.7 Rejected – Ultraviolet Light:** When applied to 1/4" (6mm) clear glass, the total rejection of solar ultraviolet radiation of air mass = 2 over the spectral range of 3000 to 3800 angstroms shall be 99.9% minimum when measured with an integrating sphere spectrophotometer as referenced by NFRC 100/200/304 (FORMERLY ASTM E-903).

**3.8 Light to Solar Heat Gain:** When applied to 1/4" (6mm) clear glass, the Light to Solar Heat Gain (Defined as the ratio of visible light transmission to shading coefficient) shall be \_\_\_\_\_ Nominal.

**3.9 Shading Coefficient:** When applied to 1/4" (6mm) clear glass, the shading coefficient shall be \_\_\_\_\_ nominal (\_\_\_\_\_ at 60 Degrees) as measured per NFRC 100/200/304 (FORMERLY ASTM E-903) and computed in accordance with the established procedures defined by The ASHRAE Handbook of Fundamentals.

**3.10 Total Solar Energy Rejected:** – 90 Degree Angle – nominal incidence

**3.10.1 Total Solar Energy Rejected:** – 60 Degree Angle

**3.11 Adhesive System:** The film shall be supplied with an optically clear pressure sensitive weather able acrylic adhesive applied uniformly over the surface opposite the abrasion resistant coating.

**3.12 Flammability:** The Manufacturer shall provide independent test data showing that the window film shall meet the requirements of a Class A Interior Finish for Building Materials for both Flame Spread Index and Smoke Development Values per ASTM E-84.

**3.13 Abrasion Resistance:** The Manufacturer shall provide independent test data showing that the film shall have a surface coating that is resistant to abrasion such that, less than 5% increase of transmitted light haze will result in accordance with ASTM D-1044 using 50 cycles, 500 grams weight, and the CS10F Calibrase Wheel.

#### 4.0 Requirements of the Authorized Dealer/Applicator (ADA)

**4.1** The ADA shall provide documentation that the ADA is authorized by the Manufacturer to install window film as per the Manufacturer's specifications and in accordance with specific requests as to be determined and agreed to by the customer.

**4.2** Authorization of dealership may be verified through the company's ADA Identification Number.

**4.3** The ADA will provide a commercial building reference list of \_\_\_\_\_ (#) properties where the ADA has installed window film. This list will include the following information:

- \* Name of building
- \* The name and telephone number of a management contact
- \* Type of glass
- \* Type of film
- \* Amount of film installed
- \* Date of completion

**4.4** Upon request, the ADA will provide a Glass Stress Analysis of the existing glass and proposed glass/film combination as recommended by the film Manufacturer.

**4.5** Upon request, the ADA will provide an application analysis to determine available energy cost reduction and savings.

#### Commercial Solutions Division

3M Center, Building 220-12E-04 St. Paul, MN 55144  
3M.com/windowfilm

© 3M 2019. All rights reserved.

3M is a trademark of 3M. Used under license in Canada.

All other trademarks are property of their respective owners. Revision A, April 2019. Please recycle.



## 5.0 Requirements of the Manufacturer

5.1 The Manufacturer will ensure proper quality control during production, shipping and inventory, clearly identify and label each film core with the product designation and run number.

### 5.2 Materials shall be manufactured by:

3M Commercial Solutions Division  
3M Center Building 280  
St. Paul, MN 55144-1000

### 5.3 3M CSD Point of Contact:

Jennifer Daly 651-737-1281

## 6.0 Application

6.1 **Examination:** Examine glass surfaces to receive new film and verify that they are free from defects and imperfections which will affect the final appearance. Correct and/or note all such deficiencies to the owner prior to commencing film application.

### 6.2 Preparation:

- a. The use of protective tarps and/or drop cloths to cover office interior furnishing near the window is recommended.
- b. The window and window framing will be cleaned thoroughly with a neutral cleaning solution. The inside surface of the window glass shall be bladed with industrial razors to ensure the removal of any foreign contaminants.
- c. Toweling or other absorbent material shall be placed on the window sill or sash to absorb moisture generated by the film application process.

6.3 **Installation:** The film shall be applied as to the specifications of the Manufacturer by an ADA.

- a. Materials will be delivered to the job site with the manufacturer's labels intact and legible.
- b. Film edges shall be cut neatly and square at a uniform distance of 1/8" (3mm) to 1/16" (1,5mm) of the window sealing device.
- c. Edge Seal – None required. 3M Sun Control Window Film Prestige Series do not contain metals.
- d. Water and film slip solution shall be used on the window glass and adhesive to facilitate the proper positioning of the film.
- e. To ensure efficient removal of excess water from the underside of the film and to maximize bonding of the pressure sensitive adhesive, polyplastic bladed squeegees shall be used.
- f. Upon completion, the film may have a dimpled appearance from residual moisture. Said moisture shall, under reasonable weather conditions, dry flat with no moisture dimples within a period of 30 calendar days when viewed under normal viewing conditions.

After installation, any left over material and/or debris will be removed and the work area will be returned to original condition. ADA will protect the film before, during and after the installation.

## 7.0 Cleaning

The film may be washed using common window cleaning solutions, including ammonia solutions, 30 days after application. Abrasive type cleaning agents and bristle brushes which could scratch the film must not be used. Synthetic sponges or soft cloths are recommended.

## 8.0 Warranty

Films Covered: Prestige 20, Prestige 40, Prestige 50, Prestige 60 & Prestige 70.

8.1 The application shall be warranted by the film manufacturer (3M) for a period of Fifteen (15) years in that the film will maintain solar reflective properties without cracking, crazing, delaminating, bubbling, peeling or discoloration. In the event that the product is found to be defective under warranty, the seller will replace such quantity of the film proved to be defective and will additionally provide the removal and reapplication labor free of charge.

### Commercial Solutions Division

3M Center, Building 220-12E-04 St. Paul, MN 55144  
3M.com/windowfilm

© 3M 2019. All rights reserved.

3M is a trademark of 3M. Used under license in Canada.

All other trademarks are property of their respective owners. Revision A, April 2019. Please recycle.



8.2 The film manufacturer (3M) also warrants against glass failure (maximum value \$500 per window) due to thermal shock fracture of glass provided the film is applied to recommended types of glass and the failure occurs within sixty (60) months from the start of application. Any glass failure must be reviewed by the film manufacturer (3M) prior to replacement.

| Section | Title  | 3M Window Films |        |        |        |        |
|---------|--|-----------------|--------|--------|--------|--------|
|         |  | PR20            | PR40   | PR50   | PR60   | PR70   |
| 1       | Film   |                 |        |        |        |        |
| 3.1     | Thickness (mils)   | >2.0            | >2.0   | >2.0   | >2.0   | >2.0   |
|         | (inches)   | 0.002           | 0.002  | 0.002  | 0.002  | 0.002  |
| 3.3     | U value  | 1.03            | 0.99   | 0.99   | 0.99   | 0.99   |
| 3.4     | Visible Light Transmission                                 | 21%             | 39%    | 50%    | 60%    | 69%    |
| 3.5     | Visible Light Reflection - Exterior                        | 6%              | 7%     | 8%     | 8%     | 9%     |
| 3.6     | Visible Light Reflection - Interior                        | 5%              | 7%     | 7%     | 8%     | 9%     |
| 3.7     | Ultraviolet Rejection                                      | 99.90%          | 99.90% | 99.90% | 99.90% | 99.90% |
| 3.8     | Light to Solar Heat Gain                                   | 0.5             | 1      | 1.1    | 1.3    | 1.4    |
| 3.9     | Shading Coefficient - 90 degrees (normal incidence)        | 0.44            | 0.46   | 0.5    | 0.54   | 0.58   |
| 3.10.1  | Total Solar Energy Rejected -90 degrees (normal incidence) | 62%             | 60%    | 56%    | 53%    | 50%    |
| 3.10.2  | TSER - 60 Degree Angle                                     | 66%             | 66%    | 63%    | 61%    | 59%    |

Note: Performance based upon ¼ clear glass \*IR rejection measured from 900-1000nm

**Commercial Solutions Division**

3M Center, Building 220-12E-04 St. Paul, MN 55144  
 3M.com/windowfilm

© 3M 2019. All rights reserved.

3M is a trademark of 3M. Used under license in Canada.

All other trademarks are property of their respective owners. Revision A, April 2019. Please recycle.



## Health and Safety

When handling any chemical products, read the manufacturers' container labels and the Safety Data Sheets (SDS) for important health, safety and environmental information. To obtain SDS sheets for 3M products go to [3M.com/SDS](http://3M.com/SDS), or by mail or in case of an emergency, call 1-888-364-3577 or 1-651-737-6501. When using any equipment, always follow the manufacturers' instructions for safe operation.

## Technical Information

Technical information and data, recommendations, and other statements provided by 3M are based on information, tests, or experience which 3M believes to be reliable, but the accuracy or completeness of such information is not guaranteed. Such technical information and data are intended for persons with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. The typical values shown should not be used for the purpose of specification limits. If you have questions about this Product, contact the Customer Service Department at 1-800-852-9722.

## Product Use

Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. Given the variety of factors that can affect the use and performance of a 3M product, user is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application.

## Warranty

3M warrants that each 3M product will be free from defects in material and manufacture for the length of the product warranty. 3M MAKES NO OTHER EXPRESS OR IMPLIED WARRANTIES, INCLUDING ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.

### Limited Remedy

If a 3M product does not conform to this warranty, the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

### No Extension of Warranty

In the case of an approved warranty claim, the replacement Product will carry only the remaining term of the original warranty period.

### Limitation of Liability

Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted.

## Commercial Solutions Division

3M Center, Building 220-12E-04 St. Paul, MN 55144  
[3M.com/windowfilm](http://3M.com/windowfilm)

© 3M 2019. All rights reserved.

3M is a trademark of 3M. Used under license in Canada.

All other trademarks are property of their respective owners. Revision A, April 2019. Please recycle.

