

## Specifications for 3M™ Scotchshield™ Safety & Security Window Film Ultra S800

### 1.0 Scope

This product is an optically clear, glass shatter resistant and abrasion resistant 8-mil window film that, when applied as instructed to the glass surface of interior windows or doors, helps hold broken glass together and significantly reduces the ultra-violet light that normally would enter through the glass. This easily applied, tear-resistant safety and security window film is engineered for the following applications:

- Helps prevent flying glass shards in the following applications:
  - Spontaneous Glass Breakage
  - Break and Entry Incidents
  - Seismic Events
  - Intentional and Accidental Explosions
  - Windstorms
- Helps delay intruders in break and entry incidents
- Helps protect against ultraviolet (UV) fading
- Helps meet many industry performance standards for glass fragment retention

Product **must** be installed with the 3M™ Impact Protection Attachment (IPA) Sealant for all windstorm, break and entry, and explosion mitigation applications and for all spontaneous glass breakage applications on single pane tempered glass. The product is not bulletproof and is not designed to stop intruders.

Product **must** be installed strictly in accordance with these specifications and 3M instruction guidelines.

### 2.0 Applicable Documents

The publications listed below form a part of this specification to the extent referenced.

The 1985 American Society for Heating, Refrigeration, and Air Conditioning Engineers (ASHRAE) Handbook of Fundamentals.

The American National Standards Institute (ANSI):

ANSI Z97.1 – 2015 Specification for Safety Glazing Material used in Buildings<sup>1</sup>

The American Society for Testing and Materials (ASTM):

- ASTM E-308 Standard Recommended Practice for Spectrophotometry and Description of Color in CIE 1931 System
- ASTM E-903 Standard Methods of Test for Solar Absorbance, Reflectance and Transmittance of Materials Using Integrating Spheres
- ASTM D-882 Standard Test Method for Tensile Properties of Thin Plastic Sheet
- ASTM D-1044 Standard Method of Test for Resistance of Transparent Plastics to Surface Abrasion (Taber Abrader Test)
- ASTM D-2582 Standard Test Method for Puncture-Propagation Tear Resistance of Plastic Film and Thin Sheet
- ASTM D-4830 Standard Test Methods for Characterizing Thermoplastic Fabrics Used in Roofing and Waterproofing
- ASTM G-90 Standard Practice for Performing Accelerated Outdoor Weathering for Non-metallic Materials Using Concentrated Natural Sunlight
- ASTM G 26 Standard Practice for Performing Accelerated Outdoor Weathering for Non-metallic Materials Using Concentrated Natural Sunlight
- ASTM E-84 Standard Method of Test for Surface Burning Characteristics of Building Materials
- ASTM D-1004 Standard Method of Test for Resistance of Transparent Plastics to Tearing (Graves Tear Test)
- ASTM E-1886 Standard Test Method for Performance of Exterior Windows, Curtain Walls, Doors, and Impact Protective Systems Impacted by Missile(s) and Exposed to Cyclic Pressure Differentials<sup>1</sup>
- ASTM E-1996 Standard Specification for Performance of Exterior Windows, Curtain Walls, Doors and Impact Protective Systems Impacted by Windborne Debris in Hurricanes<sup>1</sup>
- ASTM F-1642 Standard Method of Test for Glazing and Glazing Systems Subject to Airblast Loadings, as adapted by the U.S. Government GSA Test Standard Protocols<sup>1</sup>
- ASTM F-2912 Standard Specification for Glazing and Glazing Systems Subjected to Airblast Loadings<sup>1</sup>

GSA-TS01-2003 General Services Administration Standard Test for Glazing and Glazing Systems Subject to Airblast Loadings<sup>1</sup>

Berkeley Lab WINDOW - A Computer Tool for Analyzing Window Thermal Performance, Lawrence Berkeley Laboratory

<sup>1</sup> Window film can be applied to glass using a dry or a wet application process. For purposes of testing for conformance to these standards, 3M may utilize dry lamination for single-pane glass and wet lamination for double-pane glass.

### 3.0 Requirements of the Film

3.1 **Film Material:** The film material consists of an optically clear polyester film, composed of co-extruded micro-layers, with a durable acrylic abrasion resistant coating over one surface, and a UV stabilized pressure sensitive adhesive on the other. The film color is clear and does not contain dyed polyester. The film has a nominal thickness of 8 mils (0.008 inches), with a total construction including adhesive of 9 mils (0.009 inches). There are no observed adhesive coating voids.

**3.2 Film Properties (typical):**

- a) Tensile Strength (ASTM D882): Coated Film: 33,000 psi (MD) / 30,000 psi (TD)
- b) Break Strength (ASTM D882): Coated Film: 265 lb/in (MD) / 240 lb/in (TD)
- c) Percent Elongation at Break (ASTM D882): Coated Film: 140 % (MD) / 130% (TD)
- d) Yield Strength: Coated Film: 15,000 psi (MD)
- e) Percent Elongation at Yield (ASTM D882): Coated Film: 8% (MD)
- f) Graves Tear Resistance (ASTM D1004):
  - Maximum Force (lbs): Coated Film: 37 (MD) / 37 (TD)
  - Maximum Extension (in): Coated Film: 0.50 (MD) / 0.51 (TD)
  - Graves Area Tear Resistance (lbs%): Coated Film: 1,100 (MD) / 1,050 (TD)
- g) Puncture Propagation Tear Resistance (ASTM D2582): Coated Film: 10 lbf (MD) / 12 lbf (TD)
- h) Puncture Strength (ASTM D4830): Coated Film: 183 lbf.

**3.3 Solar Performance Properties:** Film applied to ¼” thick clear glass.

- a) Visible Light Transmission (ASTM E 903): 88%
- b) Visible Reflection (ASTM E 903): not more than 10%
- c) Ultraviolet Transmission (ASTM E 903): less than 1% (300-380 nm)
- d) Solar Heat Gain Coefficient (ASTM E 903): 0.80

**3.4 Flammability:** Upon request from a 3M Authorized Window Film Dealer, 3M will provide independent test data showing that the window film meets the requirements of a Class A Interior Finish for Building Materials for both Flame Spread Index and Smoked Development Values per ASTM E-84.

- a) Flame Spread Index (FDI): 5
- b) Smoke Developed Index (SDI): 25

**3.5 Abrasion Resistance:** Upon request from a 3M Authorized Window Film Dealer, 3M will provide test data showing that the film has a surface coating that is resistant to abrasion such that less than 5% increase of transmitted light haze will result in accordance with ASTM D-1044 using 100 cycles, 500 grams weight, and the CS10F Calibrase Wheel.

**3.6 Adhesion to Glass:** Upon request from a 3M Authorized Window Film Dealer, 3M will provide test data showing that the film has a 180-degree peel strength (adhesion to glass) according to ASTM D-1044 of 6 lbs/in (typical).

**3.7 Adhesive System:** The film is supplied with a high mass pressure sensitive weatherable acrylate adhesive applied uniformly over the surface opposite the abrasion resistant coated surface. The adhesive is pressure sensitive (not water activated) and physically bonded (not chemically bonded) to the glass. The adhesive is essentially optically flat and meets the following criteria:

- a) Viewing the film from a distance of ten feet at angles up to 45 degrees perpendicular from either side of the glass, the film itself will not appear distorted.
- b) It is not necessary to seal around the edges of the applied film system with a lacquer or other substance in order to prevent moisture or free water from penetrating under the film system.

**3.8 Impact Resistance for Safety Glazing:** Upon request from a 3M Authorized Window Film Dealer, 3M will provide independent test data showing that the film, when applied to either side of the window glass, meets the 400 ft-lb impact requirements of ANSI Z97.1 (Class A, Unlimited). Testing is done with film applied both on 1/8” and 1/4” annealed glass.

**3.9 Impact Protection:** Upon request from 3M Authorized Window Film Dealer, 3M will provide independent test data showing the following:

- a) Film passes impact of Large Missile “C” and withstands subsequent pressure cycling (per ASTMs E1996 and E1886) at +/- 75 psf Design Pressure with use of 3M™ Impact Protection Attachment (IPA) Sealant.

**3.10 Blast Mitigation:** Upon request from 3M Authorized Window Film Dealer, 3M will provide independent test data showing the following:

- a) GSA Rating of “3a” / ASTM F1642 “Minimal Hazard” with target blast pressure of 6 psi and 42 psi-msec blast impulse, on ¼” annealed single pane glass with 3M™ Impact Protection Attachment (IPA) Sealant
- b) GSA Rating of “3a” / ASTM F1642 “Low Hazard” with blast pressure of 7.5 psi and 55 psi-msec blast impulse, on ¼” annealed single pane glass with 3M™ Impact Protection Attachment (IPA) Sealant
- c) GSA Rating of “2” / ASTM F1642 “Minimal Hazard” with target blast pressure of 6 psi and 42 psi-msec blast impulse, on 1” annealed double pane glass with 3M™ Impact Protection Attachment (IPA) Sealant
- d) GSA Rating of “3b” / ASTM F1642 “Low Hazard” with target blast pressure of 9 psi and 70 psi-msec blast impulse, on 1” annealed double pane glass with 3M™ Impact Protection Attachment (IPA) Sealant
- e) GSA Rating of “2” / ASTM F1642 “Minimal Hazard” with target blast pressure of 9 psi and 70 psi-msec blast impulse, on 1” tempered double pane glass with 3M™ Impact Protection Attachment (IPA) Sealant
- f) GSA Rating of “2” / ASTM F1642 “Minimal Hazard” with target blast pressure of 10 psi and 75 psi-msec blast impulse, on 1” tempered double pane glass with 3M™ Impact Protection Attachment (IPA) Sealant
- g) GSA Rating of “3a” / ASTM F1642 “Very Low Hazard” with target blast pressure of 6.8 psi and 47 psi-msec blast impulse, on 1” tempered double pane glass with 3M™ Impact Protection Attachment (IPA) Sealant (on 2 sides only)
- h) GSA Rating of “3a” / ASTM F1642 “Very Low Hazard” with blast pressure of 6.5 psi and 40 psi-msec blast impulse, on ¼” tempered single pane glass with 3M™ Impact Protection Attachment (IPA) Sealant (on 2 sides only)

GSA Rating only:

- i) GSA Rating of “2” with blast pressure of 7.6 psi and 51 psi-msec blast impulse, on ¼” tempered single pane glass with 3M™ Impact Protection Attachment (IPA) Sealant
- j) GSA Rating of “3b” with blast pressure of 6.84 psi and 45 psi-msec blast impulse, on 1” annealed double pane glass with 3M™ Impact Protection Attachment (IPA) Sealant (on 2 sides only)

## 4.0 Requirements of the 3M Authorized Window Film Dealer

4.1 **Documentation.** The 3M Authorized Window Film Dealer shall provide documentation that the dealer is authorized by 3M to install said window film as per 3M's specifications and instructions, as well as in accordance with specific requests as to be determined and agreed to by the customer (to the extent not inconsistent with 3M's specifications and instructions).

4.2 **Verification.** Authorization of 3M Authorized Window Film Dealer may be verified through the company's 3M ID Number.

4.3 **References.** The 3M Authorized Window Film Dealer will provide a commercial building reference list of at least ten (10) properties where the dealer has installed the window film. This list will include the following information:

- \* Name of building
- \* The name and telephone number of a management contact
- \* Type of glass
- \* Type of film
- \* Amount of film installed
- \* Date of completion

The foregoing information will be collected and stored in accordance with [3M's Global Privacy Policy](#).

## 5.0 Requirements of the Manufacturer

5.1 **Core Labeling.** 3M will clearly identify and label each film core with the product designation and run number.

5.2 **Manufacturer.** Materials are manufactured by:  
3M Commercial Branding and Transportation Division  
3M Center, Building 280  
St. Paul, MN 55144-1000

## 6.0 Application

6.1 **Examination:** Examine glass surfaces intended to receive new film and verify that they are free from defects and imperfections, which will affect the final appearance and potentially the as-installed performance. Correct all deficiencies before starting film application.

6.2 **Preparation:**

- a) A clean and dust-free work area should be provided when the films are installed, paying attention to ventilation systems which may deposit contamination from other work areas.
- b) The window and window framing must be cleaned thoroughly with a neutral cleaning solution. The inside surface of the window glass may need to be scraped with stainless steel razor blades with clean, sharp edges to ensure the removal of any foreign contaminants without damaging the glass surface.
- c) Drop cloths or other absorbent material are to be placed on the windowsill or sash to absorb moisture accumulation generated by the film application.

6.3 **Installation:** The film must be applied strictly in accordance with 3M specifications and 3M instructions by a 3M Authorized Window Film Dealer.

- a) Materials will be delivered to the job site with the manufacturer's labels intact and legible.
- b) To minimize waste, the film may be cut to specification utilizing a vertical dispenser designed for that purpose. Film edges must be cut neatly and square at a uniform distance of 1/8" (3 mm) to 1/16" (1.6 mm) of the window-sealing device.
- c) Film is wet-applied using clean water and slip solution to facilitate positioning of the film onto glass.
- d) To help ensure efficient removal of excess water from the underside of the film and to maximize bonding of the pressure sensitive adhesive, plastic bladed squeegees are to be used.
- e) After installation, any leftover material will be removed, and the work area returned to its original condition. Use all necessary means to protect the film before, during and after the installation.

## 7.0 Guidelines for 3M Window Film Inspections, Cleaning, and Maintenance

Please refer to Technical Bulletin "Guidelines for 3M Window Film Inspections, Cleaning, And Care" for important information on how to inspect, clean, and maintain the installed window film application. IMPORTANT: Do NOT wash windows for the first thirty (30) days after installation.

## 8.0 Health & Safety



**WARNING.** To help reduce the risk of personal injury and/or property damage associated with glass breakage, when working on or near glass surfaces, always use appropriate personal protective equipment and follow the Technical Bulletin "3M™ Window Film Glass Checklist" to identify the risk of glass breakage associated with the application of window film to glass surfaces.



**CAUTION.** When using any equipment, tools, or cleaning solutions in connection with the processing and application of this Product, always follow the manufacturer's container labels and/or instructions for safe operation.

## 9.0 Important Product Notices

**IMPORTANT PRODUCT AND APPLICATION LIMITATIONS:** Many factors can contribute to potential hazards and damages arising from wind, impact, seismic, explosion, or break and entry incidents, including the window film selected, type and thickness of glass, building construction, exterior pressure, proximity of impact occurrence, quality of window or door frames, intruder size and strength, and type of tools used to gain entry. Certain 3M™ Window Films require the use of 3M™ Impact Protection Attachment (IPA) Sealant on glass window and door frames for windstorm, break & entry, and explosion mitigation applications and for spontaneous glass breakage applications on single pane tempered glass. The sealant may also be recommended for certain other spontaneous glass breakage, safety glazing, and seismic applications. Always refer to the 3M Technical Data Sheets and 3M Technical Specifications to determine whether these combinations are required. **CAUTION: While 3M™ Window Films, when applied in accordance with 3M instructions, may help reduce the impact of flying glass shards under certain conditions and potentially delay intruders, these films do not prevent property damage, personal injury, or death. CAUTION: Window films are not bulletproof and not designed to stop intruders.** Always consult with security professionals and a 3M Authorized Window Film Dealer prior to selecting any window films to determine suitability for the intended application.

**IMPORTANT STATE OF FLORIDA NOTICE:** This product is not approved in the State of Florida for use as hurricane, windstorm, or impact protection from wind-borne debris from a hurricane or windstorm. In compliance with Florida Statute 553.842, this product may not be advertised, sold, offered, provided, distributed, or marketed in the State of Florida as hurricane, windstorm, or impact protection from wind-borne debris from a hurricane or windstorm.

## 10. Warranty Information

**Technical Information:** Technical information, guidance, and other statements provided by 3M are based upon records, tests, or experience that 3M believes to be reliable, but the accuracy, completeness, and representative nature of such information is not guaranteed. Such information is intended for people with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license to any intellectual property rights is granted or implied with respect to this technical information.

**Product Selection and Use:** Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. Customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment, reviewing all applicable regulations and standards, and reviewing the product label and use instructions. Failure to properly evaluate, select, and use a 3M product in accordance with instructions or to meet all applicable safety regulations may result in injury, sickness, death, and/or harm to property.

**Warranty, Limited Remedy, and Disclaimer:** Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. Please refer to the Warranty Bulletin for 3M™ Window Films (Flat Glass Applications) and 3M™ Impact Protection Attachment (IPA) Sealant for complete details on warranty coverage, which can be obtained by contacting your 3M Authorized Window Film Dealer or your local 3M sales representative. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

**Limitation of Liability:** Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.

### Commercial Branding and Transportation

3M Center, Building 223-3N-30 St. Paul, MN 55144

3M.com/windowfilm

© 3M 2024. All rights reserved.

3M and Scotchshield are trademarks of 3M. Used under license in Canada.

All other trademarks are the property of their respective owners.

