

3M™ Versaflo™ Systems for
Powered and Supplied Air Respirators

Helping you take on your workplace hazards.

Did you know?

Powered Air Purifying Respirators (PAPR) systems can offer respiratory protection with integrated head, eye and face protection that can help provide a more comfortable environment for the worker.



Respiratory	Head	Eye and face	Hearing
-------------	------	--------------	---------

More reasons to consider a 3M™ Versaflo™ Belt-Mounted PAPR System

--	--	--

With the ANSI standard in mind, 3M designed certain headtops with integrated face shields to help reduce the risk of exposure to eye injuries.***

200 eye injuries occur every day in Canadian workplaces.

Which PAPR is right for you?

3M™ Versaflo™ TR-300+ PAPR	3M™ Versaflo™ TR-600 PAPR	3M™ Versaflo™ TR-800 PAPR
----------------------------	---------------------------	---------------------------

3M™ Versaflo™ TR-300+ PAPR

particulate protection

- Heavy industrial and infrastructure
- Construction
- Pharmaceutical
- Healthcare
- General Manufacturing
- Food safety

Constant airflow
Even as the battery discharges, or the filter becomes loaded with particulates, the unit delivers a steady flow of air.

3M™ Versaflo™ TR-600 PAPR

particulate, gas and vapour protection

- Heavy industrial and infrastructure
- Construction and demolition
- Pharmaceutical
- Healthcare
- General Manufacturing
- Food safety and dry foods
- Nuclear energy
- Metal working

an expanded range of NIOSH-approved filters for protection against hazards such as **particulates, organic vapours and acid gases**

3M™ Versaflo™ TR-800 PAPR

particulate and gas protection for intrinsically safe requirements

- Oil and gas
- Pharmaceutical
- Paint spraying
- Chemical handling
- Food production

High level of protection from both **respiratory and fire/explosion hazards**

Choosing a headtop

All 3M™ Versaflo™ PAPRs are compatible with all M- and S-series headtops, but different jobs call for different kinds of headtops to protect workers from hazardous environments. From hoods to helmets, choosing the right headtop requires putting on your own thinking cap.

Find your application and match it to the right headtop

PH Powder Handling	PS Paint spraying	G Grinding	B Buffing	HC Healthcare
GM General manufacturing	PM Pharmaceutical manufacturing	SH Liquid splash hazards		

Heavy-duty protection in a lightweight design.

M-Series Faceshields, Hard Hats and Helmets

M-200 Series • use when head impact protection is not required Recommended for most: PH PS G B GM	M-300 Series • use when hard hat protection is required or desired Recommended for most: PH PS GM	M-400 Series • use when hard hat protection is required or desired Recommended for most: PH PS GM
--	--	--

Hard work. Soft headcovers.

S-Series Hoods and Headcovers

S-133 • Suitable for applications where frequent replacement of the head gear assembly is required Recommended for most: PM PS HC	S-403	S-657 • Premium reusable suspension hoods can be a cost-effective choice for some high disposal rate environments – just the soiled hood fabric is replaced, while the suspension and air ducting can be reused Recommended for most: SH	S-857
--	--------------	---	--------------

[Click here to see our full line of products.](#)