

What's in your toolbox?

General Industrial



3M™ Dual Lock™ Reclosable Fasteners

3M™ Dual Lock™ Reclosable Fasteners are a heavy duty, reliable reclosable fastener which can easily attach two substrates together, replacing screws, clips and other traditional fastening methods. Switching to 3M Dual Lock Reclosable Fasteners can improve productivity on the production floor and offers designers new flexibility in design.



Eliminate rework.

- No pre-drilled holes
- Perfect positioning every time
- Confidence in assembly..."snap!"
- Reduce reliance on high maintenance tools



Improve productivity.

- Instant attachment
- Immediate handling strength
- Pre-apply for downstream assembly or use as a third hand
- Bonding power of 3M™ VHB™ Tape Technology




Enhance designs.

- No exposed mechanical fasteners
- Attach dissimilar materials without holes
- Create a sleeker design
- Lightweight

Designing with 3M™ Dual Lock™ Reclosable Fasteners


Typical Applications

Interior panel attachments




Ceiling panels, floor panels, side panels, covers/lids for easy serviceability, assembly, refurbishment or decorations.

Removable access panels




Hide electronics, controls, machinery, lighting for easy maintenance, repairs or refurbishment.

Mobile mounting



GPS, RFID tracking, sensors, transponders, device or instrument attachment for easy and secure attachment and replaceability.

Signage and display



Point-of-sale displays, trade shows, interior retail signage for ease of assembly, strength and replaceability.

Product selection

3M™ Dual Lock™ Reclosable Fastener portfolio offers a variety of strengths, adhesives, thicknesses, and colors. Start any evaluation with black, mid-strength SJ3550, good on most high surface energy and medium surface energy substrates. Your 3M Representative can offer alternate suggestions to meet your application needs.

SJ3550CF



Medium strength
when attached to itself

SJ3551CF



High strength when
attached to SJ3550CF

SJ3552CF



High strength when
attached to SJ3550CF

SJ3560



Clear

SJ4570



Thin / low profile

For more information on assembly options to achieve your desired strength and design, please work with your 3M Representative or 3M Tech Service.



Industrial Adhesives and Tapes Division
3M Center, Building 225-3S-06
St. Paul, MN 55144-100
800-362-3550 877-369-2923 (Fax)
3M.com/converter

© 3M 2022. All rights reserved.
3M Dual Lock Reclosable Fastener, 3M and 3M Science
Applied to Life are trademarks of 3M Company.