









Product	Description	Part #	Size	Rolls/ Case
<b>Scotch® Performance Masking Tape 233+</b>				
 <ul style="list-style-type: none"> <li>• Premium paper backing resists breaking, lifting, and edge curl</li> <li>• High conformability with clean removal and sharp paint lines</li> <li>• Superior resistance to UV, moisture, and solvents compared to other paper tapes</li> <li>• Release coating minimizes unwind force, reducing wrinkling and paint blow-by</li> </ul>	26334	3/4 in. x 60 yds. (18 mm x 55 m)	48	
	26336	1 in. x 60 yds. (24 mm x 55 m)	24	
	26338	1-1/2 in. x 60 yds. (36 mm x 55 m)	16	
	26340	2 in. x 60 yds. (48 mm x 55 m)	12	
	26341	3 in. x 60 yds. (72 mm x 55 m)	8	
<b>3M™ Highland™ Masking Tape 2727</b>				
 <ul style="list-style-type: none"> <li>• Engineered as our highest adhesion masking tape with superior performance in hot and humid environments</li> <li>• Balanced construction for consistent unwind and easy tear</li> <li>• Rubber-based adhesive provides quick stick for fast application</li> <li>• Smooth crepe paper backing with classic feel and reliable performance</li> </ul>	06541	3/4 in. x 60 yds. (18 mm x 55 m)	48	
	06542	1-1/2 in. x 60 yds. (36 mm x 55 m)	24	
	06543	2 in. x 60 yds. (48 mm x 55 m)	24	
<b>3M™ Automotive Refinish Masking Tape 388N</b>				
 <ul style="list-style-type: none"> <li>• Robust crepe paper backing that resists solvents and moisture</li> <li>• Proprietary rubber-based adhesive formula allows the tape to stick and stay on a variety of surfaces</li> <li>• Great usability - fits contours and curves</li> <li>• Excels in all general masking applications</li> </ul>	06652	3/4 in. x 60 yds. (18 mm x 55 m)	48	
	06654	1-1/2 in. x 60 yds. (36 mm x 55 m)	24	
	06656	2 in. x 60 yds. (48 mm x 55 m)	24	
<b>3M™ Automotive Masking Tape 2308</b>				
 <ul style="list-style-type: none"> <li>• Cost-effective general purpose masking tape developed for a variety of applications</li> <li>• Reliable crepe paper backing with good conformability and easy application</li> <li>• Designed for minimal adhesive transfer and effortless unmasking</li> <li>• Proprietary solvent-free adhesive formula that sticks with confidence</li> </ul>	06545	3/4 in. x 60 yds. (18 mm x 55 m)	48	
	06547	1-1/2 in. x 60 yds. (36 mm x 55 m)	24	
	06548	2 in. x 60 yds. (48 mm x 55 m)	24	

# 3M Automotive Aftermarket Masking Solutions: Fine Line Tape

Product	Description	Part #	Size	Rolls/ Case
<b>3M™ Vinyl Tape 471+</b>				
	<ul style="list-style-type: none"> <li>• Excels in masking applications to create sharp, fine paint lines for striping, color separation and complex designs</li> <li>• Unique stretch properties enable tape to remain stretched to conform to uneven surfaces without lifting, thus avoiding paint bleed</li> <li>• Rubber adhesive provides quick stick with excellent holding strength on most surfaces</li> </ul>	06404	1/8 in. x 36 yds. (3 mm x 33 m)	12
		06405	1/4 in. x 36 yds. (6 mm x 33 m)	12
		06408	1/2 in. x 36 yds. (12 mm x 33 m)	12
<b>3M™ Precision Masking Tape</b>				
	<ul style="list-style-type: none"> <li>• Thinnest 3M tape for automotive applications won't leave high paint edges, great for two-tone jobs</li> <li>• Prevents seepage and edge bleed with waterborne and solvent paints</li> <li>• Semitransparent for better visibility</li> <li>• Acrylic adhesive provides excellent UV resistance</li> </ul>	06525	1/4 in. x 60 yds. (6 mm x 55 m)	12
<b>Scotch® Performance Masking Tape 233+</b>				
	<ul style="list-style-type: none"> <li>• Premium paper backing resists breaking, lifting, and edge curl</li> <li>• High conformability with clean removal and sharp paint lines</li> <li>• Superior resistance to UV, moisture, and solvents compared to other paper tapes</li> <li>• Release coating minimizes unwind force, reducing wrinkling and paint blow-by</li> </ul>	26343	1/8 in. x 60 yds. (3 mm x 55 m)	12
		26344	1/4 in. x 60 yds. (6 mm x 55 m)	12
		26332	1/2 in. x 60 yds. (12 mm x 55 m)	48
<b>Scotch® Fine Line Tape 218</b>				
	<ul style="list-style-type: none"> <li>• Thin tape provides excellent color line separation</li> <li>• Proven excellent for painting long straight lines and smooth curves</li> <li>• Resistant to most solvents and moisture</li> </ul>	06306	1/16 in. x 60 yds. ( 1.6 mm x 55m)	12
		06308	3/32 in. x 60 yds. (2 mm x 55 m)	12
		06300	1/8 in. x 60 yds. (3 mm x 55 m)	12
		06307	3/16 in. x 60 yds. (5 mm x 55 m)	12
		06301	1/4 in. x 60 yds. (6 mm x 55 m)	12
		06302	3/8 in. x 60 yds. (9mm x 55 m)	12
		06303	1/2 in. x 60 yds. (12 mm x 55 m)	12

Limited Warranty & Limitation of Liability: 3M warrants this product will meet 3M specifications at the time of 3M shipment. Except as required by law, 3M MAKES NO OTHER WARRANTIES OR CONDITIONS INCLUDING ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. If there is a breach of this warranty, your exclusive remedy shall be product replacement or refund of purchase price. 3M will not be liable for any direct, indirect, special, incidental, or consequential damage related to the product.



Automotive Aftermarket Division  
3M Center, Building 223-06S-07  
St. Paul, MN 55144-1000  
1-877-666-2277

Please recycle. Printed in USA.  
3M, Scotch and Highland are trademarks of 3M. ©  
3M 2021. All rights reserved.  
60-4402-8011-7