





Commercial Espresso Machine Filter Sizing

Find the right filter to fit your commercial espresso equipment needs based on water hardness and capacity.

ScaleGard™ Pro Series Products (SGP124BN-T, SGP165BN-T and SGP195BN-T) reduce hardness from water to help reduce scale, but also feature built-in non-adjustable blend mechanisms to allow some hardness to remain in the product water, deemed important for flavor of the espresso.

ESP Series Products do not feature a built-in blend mechanism.

Commercial Espresso Machines

ESP Series Softening and ScaleGard™ Pro Series Products				
Inlet Hardness (ppm/gpg)	Capacity Gallons (Liters)			
				
	ESP124-T	SGP124BN-T	SGP165BN-T	SGP195BN-T
50 (3)	367 (1,388)	1,525 (5,773)	2,157 (8,164)	3,595 (13,607)
60 (4)	275 (1,041)	1,271 (4,811)	1,798 (6,804)	2,996 (11,339)
100 (6)	183 (694)	763 (2,886)	1,079 (4,082)	1,798 (6,804)
140 (8)	138 (520)	545 (2,062)	770 (2,916)	1,284 (4,860)
180 (11)	100 (379)	424 (1,604)	599 (2,268)	999 (3,780)
200 (12)	92 (347)	381 (1,443)	539 (2,041)	899 (3,402)
240 (14)	79 (297)	318 (1,203)	449 (1,701)	749 (2,835)
280 (16)	69 (260)	272 (1,031)	385 (1,458)	642 (2,430)
320 (19)	58 (219)	238 (902)	337 (1,276)	562 (2,126)
360 (21)	52 (198)	212 (802)	300 (1,134)	499 (1,890)
400 (23)	48 (181)	191 (722)	270 (1,021)	449 (1,701)



3M Purification Inc.
3M Separation and Purification Sciences Division
400 Research Parkway
Meriden, CT 06450

Phone 1-866-990-9785
WW 1-203-237-5541
Web 3Mfoodservice.com

Clear things up at 3MFoodService.com

3M is a trademark of 3M Company.
© 3M 2019. All rights reserved.