



3M™ Scott™ EPIC 3 Voice Amplifier



Feature	Benefit
Clear voice communication	Enhances mask voice intelligibility and loudness
Simple operation	Preprogrammed acoustics and single button operation provides simple use with any compatible mask
Rugged and reliable	Robust, high-heat resistant design and construction provides reliable, long term operation and performance
Compatible with a variety of masks	Designed for use with Vision 3, Promask, Vision AMS and AV-3000 HT
Supports mask top-down-convertibility	Compatible for use with a wide range of SCBA, Supplied Air, APR and PAPR full face masks
Advanced power management	Extends run time up to 50 hours while reducing battery replacement costs
Easy to use programming tools	Allows devices to be easily adjusted to meet specific use case requirements

3M Scott Fire & Safety

Pimbo Road
Skelmersdale
Lancashire, WN8 9RA
United Kingdom

Phone +44 (0)1695 711711
E-Mail skelmenq@mmm.com
Web www.3Mscott.com

ISO 9001 Registered. Please recycle. Printed in the UK. © 3M 2019. All rights reserved. 3M and Scott are trademarks of 3M Company. J460395

