



# PSD Marketing Content Review Summary

**Project Title:** PSD HEF SecureFit Protective Eyewear Catalog

**Details of Request:** Product, 3M ID, and image updates/refresh

Marketing Content Contact:	Heather Delaney
Today's Date:	9/13/2023
Date Needed:	9/25/2023
Requestor:	Adam Beck
Canada Use Pre-Approval:	No
Collaborative Review:	Katie Aune
Management Review:	Katie Hacker
Legal Review:	Lisa Brihn

## Content Summary:

Portfolio:	Head, Eye & Face
Region:	Global
Audience:	End Users, Customers
Asset Type:	Catalog/Brochure
Translations Needed:	No - will be localized by area as needed

## Additional Comments:

[Requestor Comments]

**3M** Science.  
Applied to Life.™



**Safety backed  
by science.**



**3M™ SecureFit™  
Protective Eyewear**

# Performance. Style. Comfort.

## 3M™ SecureFit™ Protective Eyewear

Protecting your vision on the job is important. But it doesn't have to mean sacrificing style or comfort. Get eyewear that performs — and looks good doing it. Featuring a comfortable fit and a sleek profile designed to work with other personal protective equipment, 3M™ SecureFit™ Protective Eyewear helps keep you safe and comfortable on the job.





## The science of comfort.

We collected data on head and face shapes around the world to develop a patented design that self-adjusts to individual head sizes. This design provides the same level of comfort to individuals across a diverse workforce.

Regardless of head size, from small heads to large heads, our 3M™ SecureFit™ Pressure Diffusion Temple Technology is designed to provide a secure and comfortable fit for an extended period of wear time.



## Designed to perform.



### Curved temples for enhanced security

Our design applies pressure on the less sensitive back of the head instead of the temples, achieving a comfortable fit even during rapid head movement.



### 3M™ Pressure Diffusion Temple Technology

3M's innovative temple design features slotted ribs that provide comfortable pressure equalization, allowing the temples to flex and self-adjust to the size of the wearer's head.

## The benefits are clear.

Fogged lenses can be frustrating and dangerous. But 3M™ SecureFit™ Protective Eyewear models featuring 3M™ Scotchgard™ Protector Anti-Fog Coating can help workers see clearly for longer, thanks to an active ingredient that bonds the coating to the lens.



**Uncoated**



Microscopic water droplets bead up, forming condensation and fog, which obscure vision.

**3M™ Scotchgard™ Protector Anti-Fog Coating**



Reduced contact angle flattens water beads into a thin, transparent film that allows light to pass through.



### 3M™ Scotchgard™ Protector Anti-Fog Coating

- Resists 11x longer than traditional anti-fog coatings, and up to 25 washings with water.\*
- Provides 7x better anti-scratch performance vs traditional 3M anti-fog coating for tough work environments.
- Designed for working in challenging situations, such as hot and humid conditions, indoor/outdoor work, physically demanding tasks and climate-controlled areas.
- Workers can feel confident wearing 3M eye protection that meets both the Impact-Rated Protector and Anti-Fog Performance (X) requirements of the ANSI/ISEA Z87.1-2020 Standard.



# 3M™ SecureFit™

Family of Protective Eyewear

There's a lot of variety to choose from in the 3M™ SecureFit™ family, all with the comfort, safety and style your workforce demands. Find the series with the right mix of features and value for you.


100 Series



200 Series



300 Series



400 Series



400X Series




500 Series



600 Series



3700 Series



# 100 Series




Sleek, comfortable eye protection  
at an economical price.



# 100 Series

3M™ SecureFit™ 100 Series Protective Eyewear features a sleek, sporty lens shape and self-adjusting temples, providing a stylish yet comfortable fit for an extended period of time.



Workers can feel confident wearing 3M eye protection that meets the Impact-Rated Protector requirement of the ANSI/ISEA Z87.1-2020 Standard.

Bulk package available  
(100 per case)



Product ID: **SF101AF**  
Lens: **Clear**  
Frame: **Black**  
Coating: **Anti-Fog/Anti-Scratch**



Product ID: **SF101AS**  
Lens: **Clear**  
Frame: **Black**  
Coating: **Anti-Scratch**



Product ID: **SF102AF**  
Lens: **Gray**  
Frame: **Black**  
Coating: **Anti-Fog/Anti-Scratch**



Product ID: **SF103AF**  
Lens: **Amber**  
Frame: **Black**  
Coating: **Anti-Fog/Anti-Scratch**



Product ID: **SF107AF**  
Lens: **Indoor/Outdoor**  
Frame: **Black**  
Coating: **Anti-Fog/Anti-Scratch**

## Available SKUs

## 100 Series

Product I.D.	3M I.D.	Description	Frame Color	Lens Color	Coating Performance	Each/Case
SF101AF	7100238174	3M™ SecureFit™ 100 Series SF101AF, Black, Clear Anti-Fog/Anti-Scratch Lens	Black	Clear	AF/AS	20
SF101AS	7100238173	3M™ SecureFit™ 100 Series SF101AS, Black, Clear Anti-Scratch Lens	Black	Clear	AS	20
SF102AF	7100238172	3M™ SecureFit™ 100 Series SF102AF, Black, Gray Anti-Fog/Anti-Scratch Lens	Black	Gray	AF/AS	20
SF103AF	7100238183	3M™ SecureFit™ 100 Series SF103AF, Black, Amber Anti-Fog/Anti-Scratch Lens	Black	Amber	AF/AS	20
SF107AF	7100238257	3M™ SecureFit™ 100 Series SF107AF, Black, Indoor/Outdoor Anti-Fog Coating/Anti-Scratch Lens	Black	I/O	AF/AS	20
BULK PACKAGING						
SF101AF	7100238175	3M™ SecureFit™ 100 Series SF101AF, Black, Clear Anti-Fog/Anti-Scratch Lens	Black	Clear	AF/AS	100
SF101AS	7100238171	3M™ SecureFit™ 100 Series SF101AS, Black, Clear Anti-Scratch Lens	Black	Clear	AS	100

# 200 Series

Lightweight comfort at  
an affordable price.



# 200 Series

The right fit changes everything. 3M™ SecureFit™ 200 Series Protective Eyewear features temples that automatically self-adjust to help provide a secure, comfortable fit every time.

Lightweight design  
weighs less than 1 oz.

Molded nose bridge  
no loose parts

U6-rated polycarbonate lenses  
absorb 99.9% of UVA, UVB and  
UVC rays between 200 nm  
and 380 nm

Exclusively features 3M™ Anti-Fog  
Plus Coating. Resists fog up to 11x  
longer than traditional anti-fog  
coatings\*, and through up to 10  
washings with water.

Choose from models with  
3M™ Anti-fog Plus or  
3M™ Scotchgard™ Anti-Fog Coatings

3M™ Pressure Diffusion  
Temple Technology

Models with blue accents  
help make eyewear more  
visible in food preparation/  
processing areas

Workers can feel confident  
wearing 3M eye protection that  
meets the Impact-Rated Protector  
requirement of the ANSI/ISEA  
Z87.1-2020 Standard.

\*Based on 60 second test. 3M internal testing per EN168 test method when compared with traditional anti-fog coatings.

# 200 Series



Product ID: **SF201AFP**  
Lens: **Clear**  
Frame: **Clear**  
Coating: **Anti-Fog Plus/Anti-Scratch**



Product ID: **SF202AFP**  
Lens: **Gray**  
Frame: **Gray**  
Coating: **Anti-Fog/Anti-Scratch**



Product ID: **SF203AFP**  
Lens: **Amber**  
Frame: **Amber**  
Coating: **Anti-Fog Plus/Anti-Scratch**



Product ID: **SF201SGAF-BLU**  
Lens: **Clear**  
Frame: **Blue**  
Coating: **Scotchgard™ Anti-Fog/Anti-Scratch**



Product ID: **SF204SGAF-BLU**  
Lens: **Blue**  
Frame: **Blue**  
Coating: **Scotchgard™ Anti-Fog/Anti-Scratch**

Available SKUs

200 Series

Product I.D.	3M I.D.	Description	Frame Color	Lens Color	Coating Performance	Each/Case
3M™ ANTI-FOG PLUS COATING						
SF201AFP	7100090435	3M™ SecureFit™ 200 Series SF201AFP, Clear Anti-Fog Plus/Anti-Scratch Lens	Clear	Clear	AFP/AS	20
SF202AFP	7100090616	3M™ SecureFit™ 200 Series SF202AFP, Gray Anti-Fog Plus/Anti-Scratch Lens	Gray	Gray	AFP/AS	20
SF203AFP	7100090617	3M™ SecureFit™ 200 Series SF203AFP, Amber Anti-Fog Plus/Anti-Scratch Lens	Amber	Amber	AFP/AS	20
3M™ SCOTCHGARD™ PROTECTOR ANTI-FOG COATING						
SF201SGAF-BLU	7100180044	3M™ SecureFit™ 200 Series SF201SGAF-BLU, Blue, Clear Scotchgard™ Protector Anti-Fog Coating/Anti-Scratch Lens	Blue	Clear	SGAF/AS	20
SF204SGAF-BLU	7100180046	3M™ SecureFit™ 200 Series SF204SGAF-BLU, Blue, Blue Scotchgard™ Protector Anti-Fog Coating/Anti-Scratch Lens	Blue	Blue	SGAF/AS	20


# 300 Series

Designed to help accommodate high cheekbone structure and low nose bridge.



# 300 Series

3M™ SecureFit™ 300 Series Protective Eyewear is designed with Asian facial features in mind and features an adjusted lens angle and soft nose bridge.



Workers can feel confident wearing 3M eye protection that meets the Impact-Rated Protector requirement of the ANSI/ISEA Z87.1-2020 Standard.


# 300 Series



Product ID: **SF301AF**  
Lens: **Clear**  
Frame: **Black**  
Coating: **Anti-Fog/Anti-Scratch**



Product ID: **SF302AF**  
Lens: **Gray**  
Frame: **Black**  
Coating: **Anti-Fog/Anti-Scratch**



Product ID: **SF301SGAF-LBL**  
Lens: **Clear**  
Frame: **Ice Blue**  
Coating: **Scotchgard™ Anti-Fog/Anti-Scratch**



Product ID: **SF302SGAF-LBL**  
Lens: **Gray**  
Frame: **Ice Blue**  
Coating: **Scotchgard™ Anti-Fog/Anti-Scratch**

Available SKUs

300 Series

Product I.D.	3M I.D.	Description	Frame Color	Lens Color	Coating Performance	Each/Case
SF301AF	7010315373	3M™ SecureFit™ 300 Series, SF301AF, Black, Clear Anti-Fog/Anti-Scratch Lens	Black	Clear	AF/AS	20
SF302AF	7010342616	3M™ SecureFit™ 300 Series, SF302AF, Black, Gray Anti-Fog/Anti-Scratch Lens	Black	Gray	AF/AS	20
3M™ SCOTCHGARD™ PROTECTOR ANTI-FOG COATING						
SF301SGAF-LBL	7100202277	3M™ SecureFit™ 300 Series, SF301SGAF-LBL, Ice Blue, Clear Scotchgard™ Protector Anti-Fog Coating/Anti-Scratch Lens	Ice Blue	Clear	SGAF/AS	20
SF302SGAF-LBL	7100202278	3M™ SecureFit™ 300 Series, SF302SGAF-LBL, Ice Blue, Gray Scotchgard™ Protector Anti-Fog Coating/Anti-Scratch Lens	Ice Blue	Gray	SGAF/AS	20


# 400 Series

Enhanced comfort and sleek design available in a variety of contemporary colors.



# 400 Series

Take the next step in comfort with 3M™ SecureFit™ 400 Series Protective Eyewear, featuring 3M™ Pressure Diffusion Temple Technology, a soft one-piece nose bridge, dual-injected temples and a range of options, including lens colors, premium coatings, readers and more.



Workers can feel confident wearing 3M eye protection that meets the Impact-Rated Protector requirement of the ANSI/ISEA Z87.1-2020 Standard.

# 400 Series



Product ID: **SF401AF**  
Lens: **Clear**  
Frame: **Green/Black**  
Coating: **Anti-Fog/Anti-Scratch**



Product ID: **SF401AF-FM**  
Lens: **Clear w/Foam Gasket**  
Frame: **Green/Black**  
Coating: **Anti-Fog/Anti-Scratch**



Product ID: **SF402AF**  
Lens: **Gray**  
Frame: **Green/Black**  
Coating: **Anti-Fog/Anti-Scratch**



Product ID: **SF402AF-FM**  
Lens: **Gray w/Foam Gasket**  
Frame: **Green/Black**  
Coating: **Anti-Fog/Anti-Scratch**



Product ID: **SF410AS**  
Lens: **Indoor/Outdoor Mirror**  
Frame: **Green/Black**  
Coating: **Anti-Scratch**



Product ID: **SF410AS-FM**  
Lens: **Indoor/Outdoor Mirror w/Foam Gasket**  
Frame: **Green/Black**  
Coating: **Anti-Scratch**



Product ID: **SF415AF**  
Lens: **Clear Readers +1.5**  
Frame: **Green/Black**  
Coating: **Anti-Fog/Anti-Scratch**



Product ID: **SF420AF**  
Lens: **Clear Readers +2.0**  
Frame: **Green/Black**  
Coating: **Anti-Fog/Anti-Scratch**



Product ID: **SF425AF**  
Lens: **Clear Readers +2.5**  
Frame: **Green/Black**  
Coating: **Anti-Fog/Anti-Scratch**

# 400 Series

with 3M™ Scotchgard™ Protector  
Anti-Fog Coating

Advanced coating technology  
for premium performance.




Product ID: **SF401SGAF-BLU**  
Lens: **Clear**  
Frame: **Blue/Gray**  
Coating: **Scotchgard™ Anti-Fog/Anti-Scratch**



Product ID: **SF401SGAF-BLU-F**  
Lens: **Clear w/Foam Gasket**  
Frame: **Blue/Gray**  
Coating: **Scotchgard™ Anti-Fog/Anti-Scratch**



Product ID: **SF401SGAF-RED**  
Lens: **Clear**  
Frame: **Red/Gray**  
Coating: **Scotchgard™ Anti-Fog/Anti-Scratch**



Product ID: **SF402SGAF-BLU**  
Lens: **Gray**  
Frame: **Blue/Gray**  
Coating: **Scotchgard™ Anti-Fog/Anti-Scratch**



Product ID: **SF402SGAF-BLU-F**  
Lens: **Gray w/Foam Gasket**  
Frame: **Blue/Gray**  
Coating: **Scotchgard™ Anti-Fog/Anti-Scratch**



Product ID: **SF403SGAF-YEL**  
Lens: **Amber**  
Frame: **Yellow/Black**  
Coating: **Scotchgard™ Anti-Fog/Anti-Scratch**



Product ID: **SF405SGAF-BLA**  
Lens: **Brown**  
Frame: **Brown/Black**  
Coating: **Scotchgard™ Anti-Fog/Anti-Scratch**



Product ID: **SF406SGAF-BLA**  
Lens: **Orange**  
Frame: **Brown/Black**  
Coating: **Scotchgard™ Anti-Fog/Anti-Scratch**



Product ID: **SF407SGAF-BLU**  
Lens: **Indoor/Outdoor Gray**  
Frame: **Blue/Gray**  
Coating: **Scotchgard™ Anti-Fog/Anti-Scratch**


# 400X Series

with Brow Guard

Helps provide additional coverage  
from particles.



Product ID: **SF401XAF-GRN**  
Lens: **Clear**  
Frame: **Green/Black**  
Coating: **Anti-Fog/Anti-Scratch**



Product ID: **SF401XSGAF-BLU**  
Lens: **Clear**  
Frame: **Blue/Gray**  
Coating: **Scotchgard™ Anti-Fog/Anti-Scratch**




Product ID: **SF402XAF-GRN**  
Lens: **Gray**  
Frame: **Green/Black**  
Coating: **Anti-Fog/Anti-Scratch**



Product ID: **SF402XSGAF-BLU**  
Lens: **Gray**  
Frame: **Blue/Gray**  
Coating: **Scotchgard™ Anti-Fog/Anti-Scratch**



Product ID: **SF403XSGAF-YEL**  
Lens: **Amber**  
Frame: **Yellow/Black**  
Coating: **Scotchgard™ Anti-Fog/Anti-Scratch**



Product ID: **SF407XSGAF-BLU**  
Lens: **Indoor/Outdoor Gray**  
Frame: **Blue/Gray**  
Coating: **Scotchgard™ Anti-Fog/Anti-Scratch**

# Available SKUs

# 400

## Series

Product I.D.	3M I.D.	Description	Frame Color	Lens Color	Coating Performance	Each/Case
SF401AF	7100112435	3M™ SecureFit™ 400 Series, SF401AF, Green/Black, Clear Anti-Fog/Anti-Scratch Lens	Green/Black	Clear	AF/AS	20
SF401AF-FM	7100112131	3M™ SecureFit™ 400 Series, SF401AF-FM, Green/Black, Clear Anti-Fog/Anti-Scratch Lens, Foam Gasket	Green/Black	Clear	AF/AS	20
SF402AF	7100112433	3M™ SecureFit™ 400 Series, SF402AF, Green/Black, Gray Anti-Fog/Anti-Scratch Lens	Green/Black	Gray	AF/AS	20
SF402AF-FM	7100112244	3M™ SecureFit™ 400 Series, SF402AF-FM, Green/Black, Gray Anti-Fog/Anti-Scratch Lens, Foam Gasket	Green/Black	Gray	AF/AS	20
SF410AS	7100112436	3M™ SecureFit™ 400 Series, SF410AS, Green/Black, Indoor/Outdoor Mirror Anti-Scratch Lens	Green/Black	I/O Mirror	AS	20
SF410AS-FM	7100112223	3M™ SecureFit™ 400 Series, SF410AS-FM, Green/Black, Indoor/Outdoor Mirror Anti-Scratch Lens, Foam Gasket	Green/Black	I/O Mirror	AS	20
SF415AF	7100115326	3M™ SecureFit™ 400 Series, SF415AF, Green/Black, Clear Anti-Fog/Anti-Scratch Lens, +1.5 Diopter	Green/Black	Clear	AF/AS	20
SF420AF	7100115325	3M™ SecureFit™ 400 Series, SF420AF, Green/Black, Clear Anti-Fog/Anti-Scratch Lens, +2.0 Diopter	Green/Black	Clear	AF/AS	20
SF425AF	7100115329	3M™ SecureFit™ 400 Series, SF425AF, Green/Black, Clear Anti-Fog/Anti-Scratch Lens, +2.5 Diopter	Green/Black	Clear	AF/AS	20
<b>3M™ SCOTCHGARD™ PROTECTOR ANTI-FOG COATING</b>						
SF401SGAF-BLU	7100150838	3M™ SecureFit™ 400 Series, SF401SGAF-BLU, Blue/Gray, Clear Scotchgard™ Protector Anti-Fog Coating/Anti-Scratch Lens	Blue/Gray	Clear	SGAF/AS	20
SF401SGAF-BLU-F	7100156104	3M™ SecureFit™ 400 Series, SF401SGAF-BLU-F, Blue/Gray, Clear Scotchgard™ Protector Anti-Fog Coating/Anti-Scratch Lens, Foam Gasket	Blue/Gray	Clear	SGAF/AS	20
SF401SGAF-RED	7100158218	3M™ SecureFit™ 400 Series, SF401SGAF-RED, Red/Gray, Clear Scotchgard™ Protector Anti-Fog Coating/Anti-Scratch Lens	Red/Gray	Clear	SGAF/AS	20
SF402SGAF-BLU	7100156101	3M™ SecureFit™ 400 Series, SF402SGAF-BLU, Blue/Gray, Gray Scotchgard™ Protector Anti-Fog Coating/Anti-Scratch Lens	Blue/Gray	Gray	SGAF/AS	20
SF402SGAF-BLU-F	7100156137	3M™ SecureFit™ 400 Series, SF402SGAF-BLU-F, Blue/Gray, Gray Scotchgard™ Protector Anti-Fog Coating/Anti-Scratch Lens, Foam Gasket	Blue/Gray	Gray	SGAF/AS	20
SF403SGAF-YEL	7100179972	3M™ SecureFit™ 400 Series, SF403SGAF-YEL, Yellow/Black, Amber Scotchgard™ Protector Anti-Fog Coating/Anti-Scratch Lens	Yellow/Black	Amber	SGAF/AS	20
SF405SGAF-BLA	7100155940	3M™ SecureFit™ 400 Series, SF405SGAF-BLA, Brown/Black, Brown Scotchgard™ Protector Anti-Fog Coating/Anti-Scratch Lens	Brown/Black	Brown	SGAF/AS	20
SF406SGAF-BLA	7100158220	3M™ SecureFit™ 400 Series, SF406SGAF-BLA, Brown/Black, Orange Scotchgard™ Protector Anti-Fog Coating/Anti-Scratch Lens	Brown/Black	Orange	SGAF/AS	20
SF407SGAF-BLU	7100156103	3M™ SecureFit™ 400 Series, SecureFit™ SF407SGAF-BLU, Blue/Gray, Indoor/Outdoor Gray Scotchgard™ Protector Anti-Fog Coating/Anti-Scratch Lens	Blue/Gray	I/O Gray	SGAF/AS	20
<b>ACCESSORIES</b>						
RX-SF400	7010528331	3M™ Protective Eyewear Prescription Insert for SecureFit™ 200, 300, 400 Series, RX-SF400	N/A	Clear	N/A	10

## Available SKUs

# 400X

Series

with Brow Guard

Product I.D.	3M I.D.	Description	Frame Color	Lens Color	Coating Performance	Each/Case
SF401XAF-GRN	7100180045	3M™ SecureFit™ 400 Series, SF401XAF-GRN, Green/Black, Clear Anti-Fog/Anti-Scratch Lens	Green/Black	Clear	AF/AS	20
SF402XAF-GRN	7100180047	3M™ SecureFit™ 400 Series, SF402XAF-GRN, Green/Black, Gray Anti-Fog/Anti-Scratch Lens	Green/Black	Gray	AF/AS	20
3M™ SCOTCHGARD™ PROTECTOR ANTI-FOG COATING						
SF401XSGAF-BLU	7100180049	3M™ SecureFit™ 400 Series, SF401XSGAF-BLU, Blue/Gray, Clear Scotchgard™ Protector Anti-Fog Coating/Anti-Scratch Lens	Blue/Gray	Clear	SGAF/AS	20
SF402XSGAF-BLU	7100180050	3M™ SecureFit™ 400 Series, SF402XSGAF-BLU, Blue/Gray, Gray Scotchgard™ Protector Anti-Fog Coating/Anti-Scratch Lens	Blue/Gray	Gray	SGAF/AS	20
SF403XSGAF-YEL	7100179972	3M™ SecureFit™ 400 Series, SF403XSGAF-YEL, Yellow/Black, Amber Scotchgard™ Protector Anti-Fog Coating/Anti-Scratch Lens	Yellow/Black	Amber	SGAF/AS	20
SF407XSGAF-BLU	7100180051	3M™ SecureFit™ 400 Series, SF407XSGAF-BLU, Blue/Gray, Indoor/Outdoor Gray Scotchgard™ Protector Anti-Fog Coating/Anti-Scratch Lens	Blue/Gray	I/O Gray	SGAF/AS	20

# 500 Series



Contemporary safety glasses featuring a sporty, streamlined lens shape.



## PPE Compatibility

Sporty design with contemporary lens shape and a sleek profile of safety glasses that can combine well with other personal protective equipment.


SecureFit's flat and flexible temple design combines well with 3M™ Protective Earmuffs



The adjustable ratcheting temples of the SecureFit™ 500 Series are designed to help improve the positioning of the eyewear when worn with half-facepiece respirators


# 500 Series

3M™ SecureFit™ 500 Series features a contemporary lens design coupled with adjustable ratchet temples and 3M™ Pressure Diffusion Temple (PDT) technology to help provide a more personalized fit. This sporty eyewear also offers self-adjusting colored temples, a variety of lens tints and models with Scotchgard™ Protector Anti-Fog Coating.




Workers can feel confident wearing 3M eye protection that meets the Impact-Rated Protector requirement of the ANSI/ISEA Z87.1-2020 Standard.


# 500 Series



Product ID: **SF501AF-BLK**  
Lens: **Clear**  
Frame: **Black**  
Coating: **Anti-Fog/Anti-Scratch**



Product ID: **SF502AF-BLK**  
Lens: **Gray**  
Frame: **Black**  
Coating: **Anti-Fog/Anti-Scratch**




Product ID: **SF507AF-BLK**  
Lens: **Indoor/Outdoor Gray**  
Frame: **Black**  
Coating: **Anti-Fog/Anti-Scratch**



Product ID: **SF509AF-BLK**  
Lens: **Silver Mirror**  
Frame: **Black**  
Coating: **Anti-Fog/Anti-Scratch**



Product ID: **SF517AF-GRN**  
Lens: **IR 1.7 Gray**  
Frame: **Green/Black**  
Coating: **Anti-Fog/Anti-Scratch**



Product ID: **SF530AF-GRN**  
Lens: **IR 3.0 Gray**  
Frame: **Green/Black**  
Coating: **Anti-Fog/Anti-Scratch**




Product ID: **SF550AF-GRN**  
Lens: **IR 5.0 Gray**  
Frame: **Green/Black**  
Coating: **Anti-Fog/Anti-Scratch**

# 500 Series



Product ID: **SF501SGAF-BLK**  
Lens: **Clear**  
Frame: **Black**  
Coating: **Scotchgard™ Anti-Fog/Anti-Scratch**



Product ID: **SF501SGAF-BLK-FM**  
Lens: **Clear w/Foam Gasket**  
Frame: **Black**  
Coating: **Scotchgard™ Anti-Fog/Anti-Scratch**



Product ID: **SF502SGAF-BLK**  
Lens: **Gray**  
Frame: **Black**  
Coating: **Scotchgard™ Anti-Fog/Anti-Scratch**



Product ID: **SF502SGAF-BLK-FM**  
Lens: **Gray w/Foam Gasket**  
Frame: **Black**  
Coating: **Scotchgard™ Anti-Fog/Anti-Scratch**



Product ID: **SF503SGAF-BLK**  
Lens: **Amber**  
Frame: **Black**  
Coating: **Scotchgard™ Anti-Fog/Anti-Scratch**



Product ID: **SF505SGAF-DGR**  
Lens: **Brown**  
Frame: **Olive Green**  
Coating: **Scotchgard™ Anti-Fog/Anti-Scratch**



Product ID: **SF507SGAF-BLK**  
Lens: **Indoor/Outdoor Gray**  
Frame: **Black**  
Coating: **Scotchgard™ Anti-Fog/Anti-Scratch**



Product ID: **SF507SGAF-BLK-FM**  
Lens: **Indoor/Outdoor Gray w/Foam Gasket**  
Frame: **Black**  
Coating: **Scotchgard™ Anti-Fog/Anti-Scratch**



Product ID: **SF528SGAF-DGR**  
Lens: **Light Brown**  
Frame: **Olive Green**  
Coating: **Scotchgard™ Anti-Fog/Anti-Scratch**

## Available SKUs

## 500 Series

Product I.D.	3M I.D.	Description	Frame Color	Lens Color	Coating Performance	Each/Case
SF501AF-BLK	7100228736	3M™ SecureFit™ 500 Series, SF501AF, Black, Clear Anti-Fog/Anti-Scratch Lens	Black	Clear	AF/AS	20
SF502AF-BLK	7100228722	3M™ SecureFit™ 500 Series, SF502AF, Black, Gray Anti-Fog/Anti-Scratch Lens	Black	Gray	AF/AS	20
SF507AF-BLK	7100228721	3M™ SecureFit™ 500 Series, SF507AF, Black, Indoor/Outdoor Anti-Fog/Anti-Scratch Lens	Black	I/O	AF/AS	20
SF509AF-BLK	7100239203	3M™ SecureFit™ 500 Series, SF509AF, Black, Silver Mirror Anti-Fog/Anti-Scratch Lens	Black	Silver Mirror	AF/AS	20
SF517AF-GRN	7100239204	3M™ SecureFit™ 500 Series, SF517AF, Green/Black, Gray IR 1.7, Anti-Fog/Anti-Scratch Lens	Green/Black	Gray IR 1.7	AF/AS	20
SF530AF-GRN	7100239086	3M™ SecureFit™ 500 Series, SF530AF, Green/Black, Gray IR 3.0, Anti-Fog/Anti-Scratch Lens	Green/Black	Gray IR 3.0	AF/AS	20
SF550AF-GRN	7100239205	3M™ SecureFit™ 500 Series, SF550AF, Green/Black, Gray IR 5.0, Anti-Fog/Anti-Scratch Lens	Green/Black	Gray IR 5.0	AF/AS	20
ACCESSORIES						
SF500-FOAM	7100239114	3M™ SecureFit™ 500 Series, SF500-FOAM Replacement Foam Gasket, 10 pk	N/A	N/A	N/A	12

## Available SKUs

500 Series

Product I.D.	3M I.D.	Description	Frame Color	Lens Color	Coating Performance	Each/Case
<b>3M™ SCOTCHGARD™ PROTECTOR ANTI-FOG COATING</b>						
SF501SGAF-BLK	7100238910	3M™ SecureFit™ 500 Series, SF501SGAF-BLK, Black, Clear Scotchgard™ Protector Anti-Fog Coating/Anti-Scratch Lens	Black	Clear	SGAF/AS	20
SF501SGAF-BLK-FM	7100238909	3M™ SecureFit™ 500 Series, SF4501SGAF-BLK-F, Black, Clear Scotchgard™ Protector Anti-Fog Coating/Anti-Scratch Lens, Foam Gasket	Black	Clear	SGAF/AS	20
SF502SGAF-BLK	7100239089	3M™ SecureFit™ 500 Series, SF502SGAF-BLK, Black, Gray Scotchgard™ Protector Anti-Fog Coating/Anti-Scratch Lens	Black	Gray	SGAF/AS	20
SF502SGAF-BLK-FM	7100239195	3M™ SecureFit™ 500 Series, SF502SGAF-BLK-F, Black, Gray Scotchgard™ Protector Anti-Fog Coating/Anti-Scratch Lens, Foam Gasket	Black	Gray	SGAF/AS	20
SF503SGAF-BLK	7100239090	3M™ SecureFit™ 500 Series, SF503SGAF-BLK, Black, Amber Scotchgard™ Protector Anti-Fog Coating/Anti-Scratch Lens	Black	Amber	SGAF/AS	20
SF505SGAF-DGR	7100239088	3M™ SecureFit™ 500 Series, SF505SGAF-DGR, Olive Green/Brown Scotchgard™ Protector Anti-Fog Coating/Anti-Scratch Lens	Olive Green	Brown	SGAF/AS	20
SF507SGAF-BLK	7100239091	3M™ SecureFit™ 500 Series, SF528SGAF-BLK, Black/Indoor/Outdoor Gray, Scotchgard™ Protector Anti-Fog Coating/Anti-Scratch Lens	Black	I/O Gray	SGAF/AS	20
SF507SGAF-BLK-FM	7100239092	3M™ SecureFit™ 500 Series, SF528SGAF-BLK, Black/Indoor/Outdoor Gray, Scotchgard™ Protector Anti-Fog Coating/Anti-Scratch Lens, Foam Gasket	Black	I/O Gray	SGAF/AS	20
SF528SGAF-DGR	7100239191	3M™ SecureFit™ 500 Series, SF528SGAF-DGR, Olive Green/Light Brown Scotchgard™ Protector Anti-Fog Coating/Anti-Scratch Lens	Olive Green	Light Brown	SGAF/AS	20
<b>ACCESSORIES</b>						
SF500-FOAM	7100239114	3M™ SecureFit™ 500 Series, SF500-FOAM Replacement Foam Gasket, 10 pk	N/A	N/A	N/A	12

# 600 Series

Stylish dual-lens frame with  
a variety of lens options.



# 600 Series

Get quality, durability and versatility all in one with 3M™ SecureFit™ 600 Series Protective Eyewear. Choose from a variety of features, including 3M™ Scotchgard™ Protector Anti-Fog Coating, multiple lens colors and a removable foam-lined gasket.

Stylish yet sturdy frame

Available in multiple lens color options

U6-rated polycarbonate lenses absorb 99.9% of UVA, UVB and UVC rays between 200 nm and 380 nm

Optional foam gasket

All models available with 3M™ Scotchgard™ Anti-Fog Coatings

3M™ Pressure Diffusion Temple Technology

Optional readers in a range of diopters

Workers can feel confident wearing 3M eye protection that meets the Impact-Rated Protector requirement of the ANSI/ISEA Z87.1-2020 Standard.



# 600 Series



Product ID: **SF601SGAF**  
Lens: **Clear**  
Frame: **Gray**  
Coating: **Scotchgard™ Anti-Fog/Anti-Scratch**



Product ID: **SF601SGAF-FM**  
Lens: **Clear w/Foam Gasket**  
Frame: **Gray**  
Coating: **Scotchgard™ Anti-Fog/Anti-Scratch**



Product ID: **SF602SGAF**  
Lens: **Gray**  
Frame: **Gray**  
Coating: **Scotchgard™ Anti-Fog/Anti-Scratch**



Product ID: **SF602SGAF-FM**  
Lens: **Gray w/Foam Gasket**  
Frame: **Gray**  
Coating: **Scotchgard™ Anti-Fog/Anti-Scratch**



Product ID: **SF603SGAF**  
Lens: **Amber**  
Frame: **Gray**  
Coating: **Scotchgard™ Anti-Fog/Anti-Scratch**



Product ID: **SF607SGAF**  
Lens: **Indoor/Outdoor Gray**  
Frame: **Gray**  
Coating: **Scotchgard™ Anti-Fog/Anti-Scratch**



Product ID: **SF615SGAF**  
Lens: **Clear Readers +1.5**  
Frame: **Gray**  
Coating: **Scotchgard™ Anti-Fog/Anti-Scratch**



Product ID: **SF620SGAF**  
Lens: **Clear Readers +2.0**  
Frame: **Gray**  
Coating: **Scotchgard™ Anti-Fog/Anti-Scratch**



Product ID: **SF625SGAF**  
Lens: **Clear Readers +2.5**  
Frame: **Gray**  
Coating: **Scotchgard™ Anti-Fog/Anti-Scratch**

# Available SKUs

# 600

## Series

Product I.D.	3M I.D.	Description	Frame Color	Lens Color	Coating Performance	Each/Case
3M™ SCOTCHGARD™ PROTECTOR ANTI-FOG COATING						
SF601SGAF	7100128689	3M™ SecureFit™ 600 Series, SF601SGAF, Gray, Clear Scotchgard™ Protector Anti-Fog Coating/Anti-Scratch Lens	Gray	Clear	SGAF/AS	20
SF601SGAF-FM	7100132350	3M™ SecureFit™ 600 Series, SF601SGAF-FM, Gray, Clear Scotchgard™ Protector Anti-Fog Coating/Anti-Scratch Lens, Foam Gasket	Gray	Clear	SGAF/AS	20
SF602SGAF	7100128690	3M™ SecureFit™ 600 Series, SF602SGAF, Gray, Gray Scotchgard™ Protector Anti-Fog Coating/Anti-Scratch Lens	Gray	Gray	SGAF/AS	20
SF602SGAF-FM	7100132350	3M™ SecureFit™ 600 Series, SF602SGAF-FM, Gray, Gray Scotchgard™ Protector Anti-Fog Coating/Anti-Scratch Lens, Foam Gasket	Gray	Gray	SGAF/AS	20
SF603SGAF	7100141599	3M™ SecureFit™ 600 Series, SF603SGAF, Gray, Amber Scotchgard™ Protector Anti-Fog Coating/Anti-Scratch Lens	Gray	Amber	SGAF/AS	20
SF607SGAF	7100132351	3M™ SecureFit™ 600 Series, SF607SGAF, Gray, Indoor/Outdoor Gray Scotchgard™ Protector Anti-Fog Coating/Anti-Scratch Lens	Gray	I/O Gray	SGAF/AS	20
SF615SGAF	7100132357	3M™ SecureFit™ 600 Series, SF615SGAF, Gray, Clear Scotchgard™ Protector Anti-Fog Coating/Anti-Scratch Lens, +1.5 Diopter	Gray	Clear	SGAF/AS	20
SF620SGAF	7100132359	3M™ SecureFit™ 600 Series, SF620SGAF, Gray, Clear Scotchgard™ Protector Anti-Fog Coating/Anti-Scratch Lens, +2.0 Diopter	Gray	Clear	SGAF/AS	20
SF625SGAF	7100132360	3M™ SecureFit™ 600 Series, SF625SGAF, Gray, Clear Scotchgard™ Protector Anti-Fog Coating/Anti-Scratch Lens, +2.5 Diopter	Gray	Clear	SGAF/AS	20
ACCESSORIES						
SF600FI	7100132738	3M™ SecureFit™ SF600FI, Replacement Foam Gasket	N/A	N/A	N/A	20


# 3700 Series

Over-the-glass protection designed with self-adjusting temple technology for all-day wearability.




# 3700 Series

3M™ SecureFit™ 3700 Series is designed to offer eye protection with all-day wearability for workers with prescription eyeglasses. Since prescription glasses may not be anti-fog coated, you can choose between a standard anti-scratch coating or 3M™ Scotchgard™ Protector Anti-Fog Coating.




Workers can feel confident wearing 3M eye protection that meets the Impact-Rated Protector requirement of the ANSI/ISEA Z87.1-2020 Standard.

# 3700 Series



Product ID: **SF3701AS-BLU**  
Lens: **Clear**  
Frame: **Blue/Blue**  
Coating: **Anti-Scratch**



Product ID: **SF3701SGAF-BLU**  
Lens: **Clear**  
Frame: **Blue/Blue**  
Coating: **Scotchgard™ Anti-Fog/Anti-Scratch**



Product ID: **SF3702AS-BLU**  
Lens: **Gray**  
Frame: **Blue/Blue**  
Coating: **Anti-Scratch**



Product ID: **SF3702SGAF-BLU**  
Lens: **Gray**  
Frame: **Blue/Blue**  
Coating: **Scotchgard™ Anti-Fog/Anti-Scratch**



Product ID: **SF3703SGAF-GRN**  
Lens: **Amber**  
Frame: **Gray/Lime Green**  
Coating: **Scotchgard™ Anti-Fog/Anti-Scratch**




Product ID: **SF3704SGAF-BLU**  
Lens: **Clear**  
Frame: **Blue/Blue**  
Coating: **Anti-Scratch**



Product ID: **SF3706AS**  
Lens: **Clear**  
Frame: **Blue/Blue**  
Coating: **Scotchgard™ Anti-Fog/Anti-Scratch**



Product ID: **SF3707AS-BLU**  
Lens: **Indoor/Outdoor Gray**  
Frame: **Blue/Blue**  
Coating: **Anti-Scratch**



Product ID: **SF3707SGAF-BLU**  
Lens: **Indoor/Outdoor Gray**  
Frame: **Blue/Blue**  
Coating: **Scotchgard™ Anti-Fog/Anti-Scratch**



Product ID: **SF3717AS-BLK**  
Lens: **Clear**  
Frame: **Blue/Blue**  
Coating: **Scotchgard™ Anti-Fog/Anti-Scratch**




Product ID: **SF3730AS-BLK**  
Lens: **Clear**  
Frame: **Blue/Blue**  
Coating: **Scotchgard™ Anti-Fog/Anti-Scratch**



Product ID: **SF3750AS\_BLK**  
Lens: **Clear**  
Frame: **Blue/Blue**  
Coating: **Scotchgard™ Anti-Fog/Anti-Scratch**

# 3700X Series

with Brow Guard




Product ID: **SF3701XAS-BLU**

Lens: **Clear**

Frame: **Gray/Blue**

Coating: **Anti-Scratch**



Product ID: **SF3701XSGAF-BLU**

Lens: **Clear**

Frame: **Gray/Blue**

Coating: **Scotchgard™ Anti-Fog/Anti-Scratch**

## Available SKUs

## 3700 Series

Product I.D.	3M I.D.	Description	Frame Color	Lens Color	Coating Performance	Each/Case
SF3701AS-BLU	7100203180	3M™ SecureFit™ 3700 Series, SF3701AS-BLU, Blue/Blue, Clear OTG Anti-Scratch Lens	Blue/Blue	Clear	AS	10
SF3701SGAF-BLU	7100203179	3M™ SecureFit™ 3700 Series, SF3701SGAF-BLU, Blue/Blue, Clear OTG Scotchgard™ Protector Anti-Fog Coating/Anti-Scratch Lens	Blue/Blue	Clear	SGAF/AS	10
SF3702AS-BLU	7100203175	3M™ SecureFit™ 3700 Series, SF3702AS-BLU, Blue/Blue, Gray OTG Anti-Scratch Lens	Blue/Blue	Gray	AS	10
SF3702SGAF-BLU	7100203203	3M™ SecureFit™ 3700 Series, SF3702SGAF-BLU, Blue/Blue, Gray OTG Scotchgard™ Protector Anti-Fog Coating/Anti-Scratch Lens	Blue/Blue	Gray	SGAF/AS	10
SF3703SGAF-GRN	7100203192	3M™ SecureFit™ 3700 Series, SF3703SGAF-GRN, Gray/Lime Green, Amber OTG Scotchgard™ Protector Anti-Fog Coating/Anti-Scratch Lens	Gray/ Lime Green	Amber	SGAF/AS	10
SF3704SGAF-BLU	7100220603	3M™ SecureFit™ 3700 Series, SF3704SGAF-BLU, Blue/Blue, Gray OTG Scotchgard™ Protector Anti-Fog Coating/Anti-Scratch Lens	Blue/Blue	Gray	SGAF/AS	10
SF3706AS-GRY	7100221021	3M™ SecureFit™ 3700 Series, SF3706AS, Orange/Orange, Indoor/Outdoor Gray OTG Anti-Scratch Lens	Orange/ Orange	Gray	AS	10
SF3707AS-BLU	7100203195	3M™ SecureFit™ 3700 Series, SF3707AS-BLU, Blue/Blue, Indoor/Outdoor Gray OTG Anti-Scratch Lens	Blue/Blue	I/O Gray	AS	10
SF3707SGAF-BLU	7100203165	3M™ SecureFit™ 3700 Series, SF3707SGAF-BLU, Blue/Blue, Indoor/Outdoor Gray OTG Scotchgard™ Protector Anti-Fog Coating/Anti-Scratch Lens	Blue/Blue	I/O Gray	SGAF/AS	10
SF3717AS-BLK	7100222922	3M™ SecureFit™ 3700 Series, SF3717AS-BLK, Black/Black, Indoor/Outdoor Gray OTG Scotchgard™ Protector Anti-Scratch Lens	Black/ Black	I/O Gray	AS	10
SF3730AS-BLK	7100220175	3M™ SecureFit™ 3700 Series, SF3730AS-BLK, Black/Black, Indoor/Outdoor Gray OTG Scotchgard™ Protector Anti-Scratch Lens	Black/ Black	I/O Gray	AS	10
SF3750AS-BLK	7100220603	3M™ SecureFit™ 3700 Series, SF3750AS-BLK, Black/Black, Indoor/Outdoor Gray OTG Scotchgard™ Protector Anti-Scratch Lens	Black/ Black	I/O Gray	AS	10
BROW GUARD						
SF3701XAS-BLU	7100203197	3M™ SecureFit™ 3700 Series, SF3701XAS-BLU, Gray/Blue, Brow Guard, Clear OTG Anti-Scratch Lens	Gray/Blue	Clear	AS	10
SF3701XSGAF-BLU	7100203198	3M™ SecureFit™ 3700 Series, SF3701XSGAF-BLU, Gray/Blue, Brow Guard, Clear OTG Scotchgard™ Protector Anti-Fog Coating/Anti-Scratch Lens	Gray/Blue	Clear	SGAF/AS	10




## Additional resources

### Fit testing

Eye injuries can occur even while wearing eye protection if the safety glasses do not fit properly. When fitted properly, eyewear should cover the soft tissue around the eye. Small spectacles on larger heads can leave exposed areas. Spectacles that are too large for a person can leave gaps. Selecting the proper eye protection for the task and ensuring proper-fitting eyewear can help to reduce worker eye injuries.

3M has developed a step-by-step method to ensure you can find your best-fitting protective eyewear, and can help you to validate properly fitting eyewear.

▶ **Download 3M™ Eyewear Fit System FS200 brochure**





## **A difference you can see and feel.**

Eyewear that's lightweight and comfortable — believe it. Contact your 3M sales rep to request trial wear samples of 3M™ SecureFit™ Protective Eyewear and feel the difference the instant you put them on. See for yourself.

▶ **Visit [3M.com/SecureFit](https://www.3m.com/SecureFit)**