



Automotive Aftermarket Division

3M™ PPS™ Paint Preparation System

1) Part Numbers

| 3M Part Number | 3M Part Descriptor |
|----------------|--|
| 16024 | 3M™ PPS™ Spray Cup System Large Kit (850 ml) with 200u filter |
| 16740 | 3M™ PPS™ Spray Cup System Large Kit (850 ml) with 125u filter |
| 16000 | 3M™ PPS™ Spray Cup System Standard Kit (650 ml) with 200u filter |
| 16026 | 3M™ PPS™ Spray Cup System Standard Kit (650 ml) with 125u filter |
| 16112 | 3M™ PPS™ Spray Cup System Midi Kit (400 ml) with 200u filter |
| 16312 | 3M™ PPS™ Spray Cup System Midi Kit (400 ml) with 125u filter |
| 16114 | 3M™ PPS™ Spray Cup System Mini Kit (200 ml) with 200u filter |
| 16752 | 3M™ PPS™ Spray Cup System Mini Kit (200 ml) with 125u filter |
| 16023 | 3M™ PPS™ Large mixing cup (850ml) |
| 16001 | 3M™ PPS™ Standard mixing cup (650ml) |
| 16112 | 3M™ PPS™ Midi mixing cup (400ml) |
| 16115 | 3M™ PPS™ Mini mixing cup (170ml) |
| 16124 | 3M™ PPS™ 828ml pressurised H/O cup |
| 16121 | 3M™ PPS™ 177ml pressurised H/O cup |
| 16010 | 3M™ PPS™ 6 cup carrier |
| 16299 | 3M™ PPS™ Lid dispenser for standard, midi and large |
| 16219 | 3M™ PPS™ Liner dispenser for standard, midi and large |
| 16298 | 3M™ PPS™ Lid and Liner dispenser for mini |
| 16022 | 3M™ PPS™ mini mixing sticks |
| 16755 | 3M™ PPS™ standard mixing sticks |



Technical Data Sheet

Effective: 19/08/2020 Supersedes: 01/01/2000

2) Description and end uses

3M™ PPS™ Spray Cups are a disposable lid and liner system for the application of a variety of coatings. The system is designed for use with solvent based and/or water-based coatings. It is a closed paint system which eliminates the need for separate mixing cups and filters. Specifically, designed adapters allow operators to use the PPS™ system with nearly any spray gun

3) Physical Properties

| Element | Material of construction |
|---------|---------------------------------|
| Liner | LDPE (Low density polyethylene) |
| Lid | PP (polypropylene) |
| Filter | Nylon 6 |

4) Directions for Use

- Insert a disposable liner in the cup
- Mix paint inside the 3M™ PPS™ Cup and Liner
- Place lid carefully on top of cup and push down – you will hear a click when the lid is correctly engaged. Attach the collar and carefully tighten onto the outer cup.
- Choose the right adapter for your spray gun - push down and twist until adapter locks into lid
- When finished spraying, disconnect air-line, invert gun and pull trigger to return excess paint to cup, allowing any excess paint to drain back into the liner before detaching the gun.
- Use the 3M™ PPS™ Cup Sealing plug to seal and protect coatings not in use, in accordance with local regulations or authorities

Consult paint or solvent Safety Data Sheets (SDS) in addition to local regulations or authorities for safe use and proper disposal.



Technical Data Sheet

Effective: 19/08/2020 Supersedes: 01/01/2000

5) Storage

- Use the red 3M™ PPS™ Dispensers - work with all 3M™ PPS™ Lids and Liners
- For storage paints and coatings, please consult paint or solvent Safety Data Sheets (SDS) for storage conditions and shelf life information
- If paint and coatings will be storage in 3M™ PPS™, you may need to use a new lid when spraying if the paint has dried out. Always follow manufacturers' guidelines for storage of any coatings.

6) Safety

Personal Protective Equipment (PPE) helps reduce exposure to certain workplace hazards. It is ultimately the responsibility of the employer to select the most appropriate PPE based on a full risk assessment. Always read the product performance, warnings and limitations from coating manufacturer before selection and use.

3M™ PPS™ Paint Preparation System is designed FOR PROFESSIONAL INDUSTRIAL USE ONLY.

7) Disclaimer

All statements, technical information and recommendations are based on tests we believe to be reliable as at the date of hereof, but the accuracy or completeness thereof is not guaranteed. Please ensure before using the product that it is suitable for your intended use. Since the conditions and methods of use of the product and of the information referred to herein are beyond our control, other than for fraudulent misrepresentation, 3M expressly disclaims any and all liability as to any results obtained or arising from any use of the product or reliance on such information.



Technical Data Sheet

Effective: 19/08/2020 Supersedes: 01/01/2000

For Additional Health and Safety Information

| | | |
|--|--|---|
| <p>3M United Kingdom plc Automotive Aftermarket 3M Centre, Cain Road, Bracknell, RG12 8HT Tel: +44 (0)161 237 6391 aadukenquiries@mmm.com www.3Mbodyshop.co.uk</p> | <p>3M Ireland Limited Automotive Aftermarket The Iveagh Building Carrickmines Park Carrickmines , Dublin 18 Tel: +353 12160301 aadukenquiries@mmm.com www.3Mbodyshop.co.uk</p> | <p>3M Denmark a/s Automotive Aftermarket Hannemanns Allé 53 2300 København S Tel: +45 43480100 aadukenquiries@mmm.com www.3MAuto.dk</p> |
| <p>3M Finland, Suomen 3M Oy Automotive Aftermarket Keilaranta 6 02150 Espoo Tel: 09 5252 1 aadukenquiries@mmm.com www.3M.fi/autotuotteet</p> | <p>3M Svenska AB Automotive Aftermarket Herrjärva torg 4 170 67 Solna Tel: 08-922100 aadukenquiries@mmm.com www.3M.se/bileftermarkad</p> | <p>3M Norge AS Automotive Aftermarket Kanalveien 2 2004 Lillestrøm Tel: 06384 aadukenquiries@mmm.com www.3m.no/auto</p> |
| <p>3M Latvija K.Ulmana 5 Riga, LV-1004 Tel: +371 67066120 aadukenquiries@mmm.com www.3m.lv</p> | <p>3M Eesti OU Pärnu mnt. 158 11317 Tallinn Tel: +372 6 115 902 aadukenquiries@mmm.com www.3m.ee</p> | <p>3M Lietuva A.Goštauto str. 40 A LT-01112 Vilnius Tel: +370 5 2160780 aadukenquiries@mmm.com www.3m.lt</p> |

© 3M 2020. 3M is a trademark of the 3M company. All rights reserved