

3M Science.
Applied to Life.™

3M™ PPS™ Series 2.0 UV Kit Standard 650ml



3M™ Series 2.0 UV Kit, Standard, 650ml

3M™ PPS™ Series 2.0 UV Kit is a black, non transparent version of 3M™ PPS™ Series 2.0 Standard Kit, designed for UV light curing materials.

For UV light curing materials use 3M™ PPS™ Series 2.0 UV Kit. Our innovative kit protects your daylight sensitive materials like primers, sealers, base and clear coats, and helps you measure, mix, filter and spray with ease. Our

PPS™ Series 2.0 UV Kit contains black lids with 125 micron filters, black liners and black sealing plugs. It's designed to save time and money by eliminating the need for traditional mixing cups and paint strainers, reduces also solvent usage and cleaning time.

- ▶ Block UV light from sensitive materials.
- ▶ Measure, mix, filter and spray with ease.
- ▶ Ideal for UV cure primer applications.



Part no.	Item	Units per pack	Units per case
20730UV	Standard 650ml Lids and Liners	5	5
26710UV			

Learn more about our complete system of body repair solutions at:
www.3M.co.uk/paint-preparation-system/2.0

Automotive Aftermarket Division

3M United Kingdom PLC
0845 603 9714
aadukenquiries@mmm.com
www.3M.co.uk/bodyshop

3M Ireland
Tel: (00) 353 1 216 0301
Fax: (00) 353 1 280 3509

Please recycle. Printed in the UK. © 3M 2017.
3M is a trademark of the 3M company.
All rights reserved. AB001/19

