




# Comfort and confidence in your safety harness



We know that feeling comfortable and confident in your safety harness makes a huge impact on the way you work. That’s why we’re proud to offer the widest variety of specialty harnesses for the widest variety of segments, from construction, wind energy, utilities and everything in between. But choosing the right harness for your specific application can be tough. These are our four most popular harnesses and we are sharing some of the key features that differentiate them from other harnesses on the market.



## 3M™ DBI-SALA® ExoFit™ STRATA™ Full-Body Harness

Our premium harness is stacked with features that set it apart from the competition. This harness was built with a first-of-its-kind **LIFTech™ Load Distribution System** that literally takes the weight off your shoulders, and redistributes the weight the harnesses to your centre of gravity to help reduce fatigue and give you a more comfortable fit. Our **PolarMesh™ Padding** keeps your back cool throughout your day by allowing greater airflow.

**Ideal for:** General use, construction, tower climbing



## 3M™ DBI-SALA® ExoFit™ NEX Plus Full-Body Harness

We redesigned this family of harnesses to keep its most-loved features and add even more. This harness has **Tech-Lite™ Aluminum D-rings** that are made from an extremely lightweight alloy that’s commonly used in military and aerospace applications. The integrated **easy-link SRL adapter** is unlike any other on the market, allowing for quick and easy connecting and disconnecting to personal SRLs. And unlike a lot of harnesses on the market, this one has reflective trim on the legs, chest, shoulders and back to help ensure greater visibility in low light situations.

**Ideal for:** General use, construction, rescue, ladder and tower climbing



## 3M™ DBI-SALA® Delta™ Full-Body Harness

Dubbed the “industry workhorse” because it’s as tough as those who wear it, Delta™ Harnesses are constructed with a unique, **tangle-free design**. This means that even when you toss the harness, you can pick it up for quick, hassle-free donning because it retains its original shape. The **REPEL Technology Webbing** features a water repellent to help reduce mould and dirt build-up, and is also more resistant to abrasion. As with some of our premium harnesses, Delta™ Harnesses are made with **Revolver™ Vertical Torso Adjusters** to help ensure elimination of loose ends and locks into place, preventing slippage.

**Ideal for:** General use, construction, rescue, ladder and tower climbing



## 3M™ Protecta® Full-Body Harnesses

We redesigned the Protecta® Harnesses to upgrade performance while maintaining **the great value** our customers have come to expect. **Auto-resetting lanyard keepers** help make this family of harnesses safer than ever, while the comfort padding with a U-shaped neck pad helps prevent chafing and allows greater comfort through a long shift. Unlike many value-priced harnesses, this family of harnesses features the same **protected, waterproof labels** that all 3M™ Harnesses have, helping to ensure easy inspection and referencing.

**Ideal for:** General use, construction



[3M.ca/FallProtection](https://3M.ca/FallProtection)