



# *Double Coated Polyethylene Foam Tapes*

## **1600T series**

*Technical Data*

*revised on March. 14th, 2007*

### **Product Description:**

Product 1600T series double-coated polyethylene foam tape combines a conformable closed cell foam with a high strength acrylic adhesive that provide good initial tack and offer high ultimate adhesion to a wide variety of surfaces, including many plastics. In addition, it also possesses good shear property that provides long term holding power, even under elevated temperature and environmental conditions.

### **Construction:**

<b>Product Number</b>	<b>Adhesive type<sup>1</sup> / Tape Thickness/ Tolerance</b>	<b>Adhesive carrier/ Color</b>	<b>Release liner Thickness, Color, Type, Print</b>	<b>Approximate density (foam only)</b>
1600T-05	Acrylic, 0.024" (0.62mm) ±15%	Closed cell PE <sup>2</sup> foam, White	0.0027" (0.07 mm) White, Glassine paper, <b>3M PE FOAM</b> logo print in light blue color	12 lb/ft <sup>3</sup> (200 Kg/m <sup>3</sup> )
1600TG-05	Acrylic, 0.024" (0.62mm) ±15%	Closed cell PE <sup>2</sup> foam, Gray	0.0027" (0.07 mm) White, Glassine paper, <b>3M PE FOAM</b> logo print in light blue color	12 lb/ft <sup>3</sup> (200 Kg/m <sup>3</sup> )

1600TB-05	Acrylic, 0.024" (0.62mm) ±15%	Closed cell PE <sup>2</sup> foam, Black	0.0027" (0.07 mm) White, Glassine paper, <b>3M PE FOAM</b> logo print in light blue color	12 lb/ft <sup>3</sup> (200 Kg/m <sup>3</sup> )
1600T-10	Acrylic, 0.044" (1.12 mm) ±10%	Closed cell PE <sup>2</sup> foam, White	0.0027" (0.07 mm) White, Glassine paper, <b>3M PE FOAM</b> logo print in light blue color	8 lb/ft <sup>3</sup> (128 Kg/m <sup>3</sup> )
1600TG-10	Acrylic, 0.044" (1.12 mm) ±10%	Closed cell PE <sup>2</sup> foam, Gray	0.0027" (0.07 mm) White, Glassine paper, <b>3M PE FOAM</b> logo print in light blue color	8 lb/ft <sup>3</sup> (128 Kg/m <sup>3</sup> )
1600TB-10	Acrylic, 0.044" (1.12 mm) ±10%	Closed cell PE <sup>2</sup> foam, Black	0.0027" (0.07 mm) White, Glassine paper, <b>3M PE FOAM</b> logo print in light blue color	8 lb/ft <sup>3</sup> (128 Kg/m <sup>3</sup> )
1600T-15	Acrylic, 0.063" (1.62 mm) ±10%	Closed cell PE <sup>2</sup> foam, White	0.0027" (0.07 mm) White, Glassine paper, <b>3M PE FOAM</b> logo print in light blue color	6 lb/ft <sup>3</sup> (96 Kg/m <sup>3</sup> )
1600TG-15	Acrylic, 0.063" (1.62 mm) ±10%	Closed cell PE <sup>2</sup> foam, Gray	0.0027" (0.07 mm) White, Glassine paper, <b>3M PE FOAM</b> logo print in light blue color	6 lb/ft <sup>3</sup> (96 Kg/m <sup>3</sup> )
1600TB-15	Acrylic, 0.063" (1.62 mm) ±10%	Closed cell PE <sup>2</sup> foam, Black	0.0027" (0.07 mm) White, Glassine paper, <b>3M PE FOAM</b> logo print in light blue color	6 lb/ft <sup>3</sup> (96 Kg/m <sup>3</sup> )
1600T-20	Acrylic, 0.083" (2.12 mm) ±10%	Closed cell PE <sup>2</sup> foam, White	0.0027" (0.07 mm) White, Glassine paper, <b>3M PE FOAM</b> logo print in light blue color	6 lb/ft <sup>3</sup> (96 Kg/m <sup>3</sup> )

1600TG-20	Acrylic, 0.083" (2.12 mm) ±10%	Closed cell PE <sup>2</sup> foam, Gray	0.0027" (0.07 mm) White, Glassine paper, <b>3M PE FOAM</b> logo print in light blue color	6 lb/ft <sup>3</sup> (96 Kg/m <sup>3</sup> )
1600TB-20	Acrylic, 0.083" (2.12 mm) ±10%	Closed cell PE <sup>2</sup> foam, Black	0.0027" (0.07 mm) White, Glassine paper, <b>3M PE FOAM</b> logo print in light blue color	6 lb/ft <sup>3</sup> (96 Kg/m <sup>3</sup> )
1600T-25	Acrylic, 0.103" (2.62 mm) ±10%	Closed cell PE <sup>2</sup> foam, White	0.0027" (0.07 mm) White, Glassine paper, <b>3M PE FOAM</b> logo print in light blue color	6 lb/ft <sup>3</sup> (96 Kg/m <sup>3</sup> )
1600TG-25	Acrylic, 0.103" (2.62 mm) ±10%	Closed cell PE <sup>2</sup> foam, Gray	0.0027" (0.07 mm) White, Glassine paper, <b>3M PE FOAM</b> logo print in light blue color	6 lb/ft <sup>3</sup> (96 Kg/m <sup>3</sup> )
1600TB-25	Acrylic, 0.103" (2.62 mm) ±10%	Closed cell PE <sup>2</sup> foam, Black	0.0027" (0.07 mm) White, Glassine paper, <b>3M PE FOAM</b> logo print in light blue color	6 lb/ft <sup>3</sup> (96 Kg/m <sup>3</sup> )

Note 1: Pressure Sensitive Acrylic Adhesive provides excellent initial tack and adhesion to a wide variety surface including many low surface energy plastics.

Note 2: PE (Polyethylene)

## Feature

1. 3M 1600T series feature a medium-soft acrylic pressure sensitive adhesive system. The key characteristics of this adhesive include a combination of high initial adhesion and good shear and holding power to a wide variety of materials, including many plastics.
2. 3M 1600T series feature good structural polyethylene foam strength to withstand heavy loading and harsh peeling.
3. Glassine paper liner features good converting characteristics.

## Typical Physical Properties and Performance Characteristics

Note: The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

Product	Color	Adhesion to stainless steel ASTM D3330 — 90 °angle peel, jaw speed 12 in/min, 72 hour dwell time, 5 mil Al foil backed, at 22°C, 50%RH	Relative High temperature Operating Ranges	
			Long Term (days, weeks)	Short Term (minutes, hours)
1600T-05	White	5 Kg/in (11 lb/in)	70°C (158°F)	82°C (180°F)
1600TG-05	Gray	5 Kg/in (11 lb/in)	70°C (158°F)	82°C (180°F)
1600TB-05	Black	5 Kg/in (11 lb/in)	70°C (158°F)	82°C (180°F)
1600T-10	White	5 Kg/in (11 lb/in)	70°C (158°F)	82°C (180°F)
1600TG-10	Gray	5 Kg/in (11 lb/in)	70°C (158°F)	82°C (180°F)
1600TB-10	Black	5 Kg/in (11 lb/in)	70°C (158°F)	82°C (180°F)
1600T-15	White	5 Kg/in (11 lb/in)	70°C (158°F)	82°C (180°F)
1600TG-15	Gray	5 Kg/in (11 lb/in)	70°C (158°F)	82°C (180°F)
1600TB-15	Black	5 Kg/in (11 lb/in)	70°C (158°F)	82°C (180°F)
1600T-20	White	5 Kg/in (11 lb/in)	70°C (158°F)	82°C (180°F)
1600TG-20	Gray	5 Kg/in (11 lb/in)	70°C (158°F)	82°C (180°F)
1600TB-20	Black	5 Kg/in (11 lb/in)	70°C (158°F)	82°C (180°F)
1600T-25	White	5 Kg/in (11 lb/in)	70°C (158°F)	82°C (180°F)
1600TG-25	Gray	5 Kg/in (11 lb/in)	70°C (158°F)	82°C (180°F)
1600TB-25	Black	5 Kg/in (11 lb/in)	70°C (158°F)	82°C (180°F)

### **Application Techniques:**

Bond strength is dependent upon the amount of adhesive-to-surface contact developed. Firm application pressure helps develop better adhesive contact and improves bond strength.

To obtain optimum adhesion, the bonding surfaces must be clean, dry and well unified. Some typical surface cleaning solvents are isopropyl alcohol or n-heptane. Note: Carefully read and follow the manufacturer's precautions and directions for use when working with solvents.

Ideal tape application temperature range is 70° F to 100° F (21° C to 38° C). Initial tape application to surfaces at temperatures below 50° F (10° C) is not recommended because the adhesive becomes too firm to adhere readily. However, once properly applied, low temperature holding is generally satisfactory.

### **Application Ideas**

- The foam construction makes these products ideal for many joining, mounting, gasketing, and sealing application involving irregular surface.
- 1600T series tapes are specially formulated for many indoor/outdoor high performance purpose mounting and joining applications, including bonding to many Plastics, where moderate temperature and shear performance are required.
- For secure joining/mounting, 2 kilograms is the maximum static loading for 1 square inch tape application. Due to the consideration of less than 100% contact with the surface, variations in surface preparation, extreme/environmental conditions, customer evaluation and testing are required for every specific application.
- Application ideas for these tapes include
  - **Plastic Hooks, Racks and Dispensers**
  - **Sign, Nameplates and Plaques**
  - **Wire and Cable Clips**
  - **Appliance, Display Case and Electronic Equipment Trim**
  - **Automotive trim**
  - **Point of Purchase and other Displays**
  - **General purpose Joining/Mounting**

**Important Notice**

3M MAKES NO WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. User is responsible for determining whether the 3M product is fit for a particular purpose and suitable for user's method of application. Please remember that many factors can affect the use and performance of a 3M product in a particular application. The materials to be bonded with the product, the surface preparation of those materials, the product selected for use, the conditions in which the product is used, and the time and environmental conditions in which the product is expected to perform are among the many factors that can affect the use and performance of a 3M product. Given the variety of factors that can affect the use and performance of a 3M product, some of which are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular purpose and suitable for the user's method of application.

**Limitation of Remedies and Liability**

If the 3M product is proved to be defective, THE EXCLUSIVE REMEDY, AT 3M'S OPTION, SHALL BE TO REFUND THE PURCHASE PRICE OF OR TO REPAIR OR REPLACE THE DEFECTIVE 3M PRODUCT. 3M shall not otherwise be liable for loss or damages, whether direct, indirect, special, incidental, or consequential, regardless of the legal theory asserted, including negligence, warranty, or strict liability.

**3M 1600T series was manufactured under a 3M's quality system registered to ISO 9002 standards; and environmental protection system registered to ISO 14000 standards.**