

3M™ Scotch-Weld™ Epoxy Adhesive

EC-1838 B/A Green, EC-1838L B/A Translucent

Technical Data Sheet

Product Description

- 3M™ Scotch-weld™ Epoxy Adhesive EC-1838 B/A Green is a controlled flow product; Scotch-Weld EC-1838L B/A Translucent Adhesive is flowable.
- These epoxy adhesives are two-part, room temperature curing structural adhesives with high shear strengths and excellent environmental resistance.
- Excellent for bonding many metals, woods, rubbers and some plastics.

Typical Uncured Physical Properties

Note: The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

Product		Scotch-Weld EC-1838 B/A Green Adhesive	Scotch-Weld EC-1838L B/A Translucent Adhesive
Viscosity (approx). @ 80°F (27°C)	Base Accelerator	70,000-600,000 cps 300,000-1,000,000 cps	11,000-15,000 cps 6,000-12,000 cps
Base	Base Accelerator	Modified Epoxy Polyamide	Synthetic Resin Modified Amine
Color	Base Accelerator	White Green	Clear Amber
Net Weight lbs./gal.	Base Accelerator	11.0-11.6 8.9-9.3	9.4-9.8 8.1-8.5
Mix Ratio (B:A)	By Weight By Volume	1:1 4:5	6:5 1:1
Worklife 73°F (23°C)	Mixed 100 gms	60 minutes	60 minutes

3M™ Scotch-Weld™ Epoxy Adhesive EC-1838 B/A Green, EC-1838L B/A Translucent

Typical Cured Physical Properties

Note: The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

Product	Scotch-Weld 1838 B/A Green Adhesive	Scotch-Weld 1838-L B/A Translucent Adhesive
Color	Green	Clear/Amber
Shore D Hardness (Approx.)	80-85	80-85
Elongation (Approx.)	2-3%	3-7%
Ultimate Tensile	4290 psi	—
Modulus of Elasticity	344,000 psi	—

Typical Cured Thermal Properties

Product	Scotch-Weld 1838 B/A Green Adhesive	Scotch-Weld 1838-L B/A Translucent Adhesive
Thermal Conductivity (Btu/Hr/Ft ² /°F/Ft)	.169	.116
Coefficient of Thermal Expansion (in/in/°C)	79 x 10 ⁻⁶ Between 32-40°F (0-40°C)	301 x 10 ⁻⁶ Between 68-184°F (20-120°C)
Glass Transition Temp.	131°F (55°C)	90°F (32°C)

Typical Cured Electrical Properties

Product	Scotch-Weld 1838 B/A Green Adhesive	Scotch-Weld 1838-L B/A Translucent Adhesive
Dielectric Strength (Volts/MIL)	585	600
Volume Resistivity @ 75°F (24°C) (ohms-cm)	1.5 x 10 ¹⁵	5.0 x 10 ¹²
Dissipation Factor 1 Khz @ 75°F (24°C)	.012	.088
Dielectric Constant 1 Khz @ 75°F (24°C)	6.06	6.1

Handling/Curing Information

Directions for Use

1. For high strength structural bonds, paint, oxide films, oils, dust, mold release agents and all other surface contaminants must be completely removed. The amount of surface preparation directly depends on the user's required bond strength and environmental aging resistance. For suggested surface preparations on common substrates, see the

3M™ Scotch-Weld™ Epoxy Adhesive EC-1838 B/A Green, EC-1838L B/A Translucent

section on Surface Preparation.

2. These products consist of two parts. Mix thoroughly by weight or volume in proportions specified on product label or in Typical Uncured Physical Properties section below. Resulting color should be uniform. Properly reseal containers.
3. For maximum bond strength apply product evenly to both surfaces to be joined.
4. Application to the substrates should be made within 1 hour for 3M™ Scotch- Weld™ Epoxy Adhesives EC-1838 B/A Green 90 minutes for Scotch- Weld EC-1838L B/A adhesive. Larger quantities and/or higher temperatures will reduce this working time.
5. Join the adhesive coated surfaces and allow to cure until completely firm. Overnight curing @75°F (24°C) is usually sufficient. Heat, up to 200°F (93°C), will speed curing.
6. The following times and temperatures will result in handling strength for these products:

<u>Temperature</u>	<u>Time</u>
RT	6-10 hrs.
150°F (65°C)	15-20 mins.

7. The following times and temperatures will result in a full cure of these products:

<u>Temperature</u>	<u>Time</u>
75°F (24°C)	7 days
150°F (65°C)	2 hours
200°F (93°C)	30 minutes

8. Keep parts from moving during cure. Contact pressure is necessary. Maximum shear strength is obtained with a 3-5 mil bond line.

Surface Preparation

The following cleaning methods are suggested for common surfaces.

Steel:

1. Wipe free of dust with oil-free solvent such as Methyl Ethyl Ketone (MEK).*
2. Sandblast or abrade using clean fine grit abrasives.
3. Wipe again with solvents to remove loose particles.

Aluminum:

1. The best performance will be achieved with the surface preparation by alkaline degreasing, then FPL etching according to ASTM D2674
2. If primer is to be used, it should be applied within 4 hours after surface preparation.

Plastics:

1. Solvent wipe with Isopropyl Alcohol.*
2. Abrade using clean fine grit abrasives.
3. Solvent wipe with Isopropyl Alcohol.*

Rubbers:

1. Solvent wipe with MEK.*
2. Abrade using clean fine grit abrasives.
3. Solvent wipe with MEK.*

Glass:

1. Solvent wipe with acetone or MEK.*
For glass applications which will be subjected to high moisture/humidity conditions, EC-3901 primer or equivalent should be used to prime the glass.

*Note: When using solvents or chemicals, be sure to extinguish all ignition sources and follow the manufacturer's precautions and directions for use when handling such materials.

3M™ Scotch-Weld™ Epoxy Adhesive EC-1838 B/A Green, EC-1838L B/A Translucent

Application and Equipment Suggestions

These products may be applied with spatula, trowel, or flow equipment.

Two part mixing/proportioning/dispensing equipment is available for intermittent or production line use. These systems are ideal because of their variable shot size and flow rate characteristics and are adaptable to most applications.

Typical Performance Characteristics

Note: The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

A. Aluminum Overlap Shear

Overlap shear strength was measured on FPL etched 1 in. wide by 1/2 in. overlap specimens. The bonds were made from 2 panels of 4 in. x 7 in. x .063 in., 2024 T3 clad aluminum bonded together and cut into 1 in. wide specimens. The separation rate of the testing jaws was .1 in./minute. Tests similar to ASTM D-1002.

Test Temperature	Scotch-Weld EC-1838 B/A Green Adhesive	Scotch-Weld EC-1838L B/A Translucent Adhesive
-67°F (-55°C)	1500	2000
75°F (24°C)	3000	2500
180°F (82°C)	500	300

B. Aluminum T-Peel

T-Peel bonds were measured on 1 in. wide specimens cut from two FPL etched 8 in. x 8 in. x .032 in., 2024 T3 clad aluminum panels bonded together. The separation rate of the testing jaws was 20 in./minute. Tests similar to ASTM D-1876.

Test Temperature	Scotch-Weld EC-1838 B/A Green Adhesive	Scotch-Weld EC-1838L B/A Translucent Adhesive
-67°F (-55°C)	2	5
75°F (24°C)	4	4
180°F (82°C)	4	4

3M™ Scotch-Weld™ Epoxy Adhesive EC-1838 B/A Green, EC-1838L B/A Translucent

C. Cold Rolled Steel Overlap Shear

Note: The following data have been developed for 3M™ Scotch-Weld™ Epoxy Adhesive EC-1838 B/A Green; similar results would be expected for Scotch-Weld EC-1838L B/A Translucent Adhesive.

Data are overlap shear on cold rolled steel (20 gauge), 302 stainless steel (50 mils thick), and 2024 T3 clad aluminum (63 mils thick) in various environments after 365 days aging. All substrates were sand blasted prior to bonding. Data are in psi and tested at 75°F (24°C)

	Cold Rolled Steel	Stainless Steel	Aluminum
Control – Scotch-Weld 1838 B/A Green Adhesive	2000-2200	3400-3800	2400-2500
Tap Water @ 75°F (24°C)	1950	2750	2250
100% Relative Humidity at 120°F (49°C)	2200	1250	1050
Hydraulic Oil (Mil-O-5606) @ 75°F (24°C)	2250	3600	2900
White Gas @ 75°F (24°C)	1100	3250	2150

Shelf Life and Storage Conditions

3M™ Scotch-Weld™ Epoxy Adhesive EC-1838 B/A Green and EC-1838L shelf life is 24 months from the date of shipment from 3M when stored at 80°F (27°C) or below in the original unopened container.

Authorization to Use

Ensure products meet all applicable specifications, standards, and maintenance manual requirements for the platform being worked on and validate all aircraft approvals against current technical documentation.

Precautionary Information

Refer to Product Label and Safety Data Sheet for health and safety information before using this product. For additional health and safety information, call 1-800-364-3577 or (651) 737-6501, and visit www.3m.com/3M/en_US/company-us/SDS-search/

For Additional information

In the U.S., call toll free 1-800-235-2376, or fax 1-800-435-3082 or 651-737-2171. For U.S. Military, call 1-866-556-5714. If you are outside of the U.S., please contact your nearest 3M office or one of the following branches:

**These products were manufacture under a 3M Quality Management System registered to the AS9100 standard*

Technical Information: The technical information, recommendations and other statements contained in this document are based upon tests or experience that 3M believes are reliable, but the accuracy or completeness of such information is not guaranteed. **Product Use:** Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. Given the variety of factors that can affect the use and performance of a 3M product, user is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application. **Warranty, Limited Remedy, and Disclaimer:** Unless an additional warranty is specifically stated on the applicable 3M product packaging or product literature, 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE. If the 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price. **Limitation of Liability:** Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.



Automotive & Aerospace Solutions Division
3M Center
St. Paul, MN 55144-1000
Phone 1-800-328-1684
Web www.3M.com/aerospace

EC-1838
Issue date: 10/2019

3M and Scotch-Weld are trademarks
of 3M Company
© 3M 2019. All rights reserved.