

3M™ Industrial Safety Helmet G22

Technical datasheet



Description

The 3M™ Industrial Safety Helmet G22 is designed to offer you head protection from small falling objects in accordance with the European Standard EN 397:2012+A1:2012.

It is available in a variety of configurations so that the product can be tailored to meet the needs of your application.

It is also a platform for a range of hearing, eye and face protection products.

Testing and approval

The 3M™ Industrial Safety Helmet G22 meets the requirements of the PPE Regulation (EU) 2016/425 and is thus CE marked.

The products have been tested and approved by RISE Research Institutes of Sweden AB, Box 857, SE-50115 Borås, Sweden, Notified Body No. 0402.

The product has been tested and approved in accordance with EN 397:2012+A1:2012.

Key features

- ▶ Compatible with pinlock head suspensions for adjustability
- ▶ Ventilated for increased airflow within the shell
- ▶ Branding and logo printing options available
- ▶ Replaceable leather or plastic sweatband
- ▶ Approved for use at -30°C
- ▶ Available in 3 standard colours (white, yellow, orange)
- ▶ Mining lamp holder option available

Typical applications

- ▶ Construction
- ▶ Forestry
- ▶ Industry

Accessories

The 3M™ G22 is compatible with a range of eye, face and hearing protection products offering flexible and compatible protection.

- ▶ GH1 2-Point Chinstrap
- ▶ HYG3 Sweatband plastic (standard)
- ▶ HYG4 Sweatband leather
- ▶ GR3C Rain shield
- ▶ V9 Integrated eyewear
- ▶ P3E Adaptor for visor attachment
- ▶ All 3M™ PELTOR™ Hearing Solutions with helmet mounted option
- ▶ 3M™ V4 Faceshields in combination with faceshield holders V43 (with peak) and V46 (without peak)
- ▶ 3M™ V5 Faceshields in combination with faceshield holder V5

Use limitation

- ▶ Never modify or alter the safety helmet
- ▶ Do not use this safety helmet against hazards other than those specified in the user instruction
- ▶ Use, store and maintain the safety helmet in accordance with the user instruction

Materials

Component	Material
Shell	UV Stabilised ABS
Headband	HDPE
Cradle	Polyester
Sweatband	Leather or plastic (PVC coated foam)

Use and storage

Temperature range for usage	-30°C to +50°C
Recommended storage conditions	+3°C to +40°C <85% humidity

Maximum recommended product life	Up to 5 years from date of manufacture*
----------------------------------	---

*The product life as defined above is indicative data. The product life is subject to many external and non-controllable factors and should not be interpreted as a warranty

Product configuration

Fitting sizes

Pinlock harness	54-62cm
-----------------	---------

Suspension

G2C	4 point pinlock headband with plastic sweatband
G2D	4 point pinlock headband with leather sweatband

Weight

G22 including G2C pinlock suspension = 380g

Product classification

Additional protection characteristics (according to EN 397:2012+A1:2012)

Low temperatures			High temperatures			Electrical properties		Lateral deformation
-10°C	-20°C	-30°C	+50°C	+150°C	Molten metal	440Vac	1000Vac/ 1500Vdc	LD
✓	✓	✓	✓	✗	✓	✗	✗	✗

Important notice

The use of the 3M product described within this document assumes that the user has previous experience of this type of product and that it will be used by a competent professional. Before any use of this product it is recommended to complete some trials to validate the performance of the product within its expected application.

All information and specification details contained within this document are inherent to this specific 3M product and would not be applied to other products or environment. Any action or usage of this product made in violation of this document is at the risk of the user.

Compliance to the information and specification relative to the 3M product contained within this document does not exempt the user from compliance with additional guidelines (safety rules, procedures). Compliance to operational requirements especially in respect to the environment and usage of tools with this product must be observed. The 3M group (which cannot verify or control those elements) would not be held responsible for the consequences of any violation of these rules which remain external to its decision and control.

Warranty conditions for 3M products are determined with the sales contract documents and with the mandatory and applicable clause, excluding any other warranty or compensation.

Personal Protective Equipment is only effective if it is correctly selected, fitted and worn throughout the time when the wearer is exposed to Physical Hazards. 3M offers advice on the selection of products, and training in the correct fitting and usage.

For more information on 3M products and services please contact 3M.

3M Personal Safety Division

3M United Kingdom PLC
3M Centre Cain Road
Bracknell, Berkshire, RG12 8HT
0870 60 800 60
www.3M.eu/safety

3M Ireland Limited
The Iveagh Building,
The Park, Carrickmines
Dublin 18
1 800 320 500

Please recycle. Printed in the UK. © 3M 2019.
All rights reserved. 3M and PELTOR are
trademarks of 3M Company. J468246

