



# VHB™ Tape LSE Series

## Product Data Sheet

October 2019

Supersedes: August 2019

### Product Description

3M™ VHB™ Tape LSE family are white conformable double coated acrylic foam tapes with a high initial tack and a soft foam. Its design enables bonding of many low surface energy substrates/materials. 3M VHB LSE white tapes are available in three different thicknesses with a 3M branded red siliconised polyethylene film liner.

### Key Features

- Double-coated acrylic foam tape
- 100% closed cell acrylic foam
- Multi material bonding for high, medium or low surface energy substrates including many metals (e.g. stainless steel) , composites and plastics (e.g. PP, PA)
- Enables bonding of many LSE substrates without primer
- Good Low temperature tack
- Soft foam enables stress relaxation & an easy application
- High initial tack
- For indoor and outdoor applications

### Applications & Benefits

- Capability to bond to many LSE substrates without primer makes it a good fit for applications in many industries such as plastics processing, transportation, appliances and signage

### Physical Properties

	LSE-060WF	LSE-110WF	LSE-160WF
<b>Adhesive &amp; Carrier</b>	Modified Acrylic on Conformable Acrylic Foam (closed cell)		
<b>Thickness</b> acc. to ASTM D-3652	0.60 mm	1.10 mm	1.60 mm
<b>Density</b>	715 kg/m <sup>3</sup>		
<b>Release Liner</b>	3M branded red siliconised polyethylene film		
<b>Tape Colour</b>	White		

**Performance Characteristics**

Type	LSE-060WF	LSE-110WF	LSE-160WF
90 ° Peel adhesion to Stainless Steel acc. to ASTM D3330, 90° peel angle @ RT, after 72h @ RT dwell	30 N/cm	44 N/cm	54 N/cm
90 ° Peel adhesion to Polypropylene acc. to ASTM D3330, 90° peel angle @ RT, after 72h @ RT dwell	24 N/cm	42 N/cm	51 N/cm
90 ° Peel adhesion to Glass acc. to ASTM D3330, 90° peel angle @ RT, after 72h @ RT dwell	29 N/cm	43 N/cm	51 N/cm
90 ° Peel adhesion to ABS acc. to ASTM D3330, 90° peel angle @ RT, after 72h @ RT dwell	24 N/cm	40 N/cm	47 N/cm
Static Shear Strength on Stainless Steel acc. to ASTM D3654, after 72h @ RT dwell (Weight held for 10.000 minutes, 3.22cm <sup>2</sup> (0.5in <sup>2</sup> ), vertical test direction	23 ° C - 1000 g 70 ° C – 500 g 90 ° C – 250 g		
Static Shear Strength on Polypropylene acc. to ASTM D3654, after 72h @ RT dwell (Weight held for 10.000 minutes, 3.22cm <sup>2</sup> (0.5in <sup>2</sup> ), vertical test direction Limited by substrate	23 ° C - 1000 g 70 ° C – 500 g 90 ° C - 500 g		
Dynamic Shear acc. to ASTM D1002 on stainless steel, after 72h @ RT dwell	525 N /6.54cm <sup>2</sup>	382 N /6.54cm <sup>2</sup>	347 N /6.54cm <sup>2</sup>
Normal Tensile (T-Block) acc. to ASTM D897 to Aluminium @ RT, after 72h @ RT dwell, test speed 50 mm/min	365 N /6.54cm <sup>2</sup>	309 N /6.54cm <sup>2</sup>	290 N /6.54cm <sup>2</sup>
Temperature Performance	Short term (minutes, hours): 150 °C Long term (days, weeks): 90 °C		

**Application Temperature**

Ideal application temperature range 10 °C to 38 °C. For certain applications and substrates 3M™ VHB™ LSE can be applied at temperatures as low as 0 °C if the surface is frost free. Testing on application-specific substrates is recommended to confirm adhesion at temperatures <10°C.

Pressure sensitive adhesives use viscous flow to achieve substrate contact area. To obtain good performance, it is important to ensure that the surfaces are clean, dry and free of condensed moisture.

---

**Shelf Life**

18 months from date of production when stored at 16 °C – 25 °C and 40-65 % relative humidity.

Performance of tapes is not projected to change even after shelf life expires; however, 3M does suggest that 3M™ VHB™ Tapes are used prior to the shelf life date whenever possible.

---

**Important Notice**

All statements, technical information and recommendations contained in this document are based upon tests or experience that 3M believes are reliable. However, many factors beyond 3M's control can affect the use and performance of a 3M product in a particular application, including the conditions under which the product is used and the time and environmental conditions in which the product is expected to perform. Since these factors are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular purpose and suitable for the user's method or application. All questions of liability relating to this product are governed by the terms of the sale subject, where applicable, to the prevailing law.

---

Values presented have been determined by standard test methods and are average values not to be used for specification purposes. Our recommendations on the use of our products are based on tests believed to be reliable but we would ask that you conduct your own tests to determine their suitability for your applications.

This is because 3M cannot accept any responsibility or liability direct or consequential for loss or damage caused as a result of our recommendations.

---

3M and VHB are trademarks of the 3M Company

**3M** Science.  
Applied to Life.™

**3M Svenska AB  
Industri**  
Bollstanäsvägen 3  
192 78 Sollentuna  
Tel: 08-92 21 00

[www.3M.se/tejp](http://www.3M.se/tejp)

**3M Norge AS  
Avd. Industri**  
Tærudgata 16  
2004 Lillestrøm  
Tlf.: 06384

[www.3M.no/tape](http://www.3M.no/tape)

**3M a/s  
Industri**  
Hannemanns Allé 53  
DK-2300 København S  
Tlf.: 43 48 01 00

[www.3MIndustri.dk](http://www.3MIndustri.dk)

**Suomen 3M Oy  
Teollisuustuottett**  
Keilaranta 6  
02150 Espoo  
Puh: 09 525 21

[www.3M.fi/teollisuus](http://www.3M.fi/teollisuus)