

3M Display Materials & Systems Division

#### **Technical Data 2019**

# 3M™ Contrast Enhancement Film CEF36XX Series

- Low modulus over a broad temperature range
- Higher adhesion to polarizer and clear polyimide (CPI)
- Elasticity for quick recovery after folding

# **Product Description**

3M™ Contrast Enhancement Films CEF36XX offers higher adhesion, especially at elevated temperatures, with a low modulus over a broad temperature range, to enable shear decoupling. It is elastic to aid quick recovery after folding. CEF36XX can be laminated via conventional film Optically Clear Adhesive (OCA) lamination process. No UV curing required.



### Construction

Product	3M CEF3601	3M CEF3602	3M CEF3603	3M CEF3604
Adhesive Type:	Acrylic	Acrylic	Acrylic	Acrylic
Adhesive Carrier:	None	None	None	None
Approximate Thickness:				
Release Liner:	50 um (2.0 mils) Clear Polyester			
Adhesive:	25 um (1.0 mil)	50 um (2.0 mils)	75 um (3.0 mils)	100 um (4.0 mils)
Release Liner:	75 um (3.0 mils) Clear Polyester			

The 3M family of optically clear adhesives for electronic displays are usually available in two forms. 3M OCA come in roll good form. 3M Contrast Enhancement Films (CEF) are available in die-cut form.

# Typical Physical Properties and Performance Characteristics

**Note:** The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

#### **Performance to Environmental Conditions:**

The following environmental tests were conducted in the 3M laboratory under the conditions specified without any appreciable deterioration in visible appearance (no bubbles, delamination, etc.). Sample construction is cover glass/3M CEF36XX/LCD glass.

	Condition	Duration
High Temperature	+95°C	800 hours
Low Temperature	-40°C	800 hours
High Temp/Humidity-1	+65°C/90%RH	800 hours
High Temp/Humidty-2	+85°C/85%RH	800 hours
Thermal Shock	-40°C and +85°C (1 hour dwell, <1 min ramp time)	100 cycles

#### **Peel Adhesion:**

ASTM D3330 modified, 180 degree peel from glass, 1 cm wide peel strips, 12 in/min (305 mm/min), 2.0 mil polyester backing, 3M CEF36XX.

	Float Glass		PI	ΕT	Polyi	mide
Dwell Time	20 min dwell at 25°C/50%RH	1 day dwell at 25°C/50%RH	20 min dwell at 25°C/50%RH	1 day dwell at 25°C/50%RH	20 min dwell at 25°C/50%RH	1 day dwell at 25°C/50%RH
Units	N/cm	N/cm	N/cm	N/cm	N/cm	N/cm
3M CEF3601	3	5				
3M CEF3602	3	6	3	3	<4	<6
3M CEF3604	4	TBD				

#### Color:

Ultra Scan Pro (Hunter Lab), ASTM E308, D65/10° 3M CEF3601 on LCD glass.

3M CEF3601	3M CEF3602	3M CEF3604
L* > 96.9	L* > 96.9	L* > 96.9
-0.1 < a* < 0.1	-0.1 < a* < 0.1	-0.1 < a* < 0.1
b* < 0.5	b* < 0.5	b* < 0.5

#### **Refractive Index:**

(+ 0.0005 from standard deviation of ellipsometry)

3M CEF36XX			
405 nm	532 nm	633 nm	1000 nm
1.4842	1.4704	1.4650	1.4570

#### Haze:


Haze is measured according to ASTM D1003-92, 3M CEF36XX on LCD glass.

3M CEF3601	3M CEF3602	3M CEF3604
< 0.3%	< 0.4%	< 0.4%

#### **Transmission Curve:**

3M™ Contrast Enhancement Film CEF36XX





# **Typical Electrical Properties at Room Temperature:**

ASTM-D150-92. 3M CEF36XX

#### **Dielectric Constant:**

3M CEF36XX			
Frequency (kHz)	Dielectric Constant		
100	5.52		
300	5.38		
500	5.28		

# **Suggested Lamination Process**


Step 1: Remove secondary liner, and then laminate 3M CEF36XX to first adherent substrate by roller at room temperature

Recommendation: roller pressure 0.1 – 0.2 MPa, roller speed 0.5 – 1 m/min

Step 2: Remove primary liner, and then laminate 3M CEF36XX/first adherent to second adherent by vacuum lamination (if rigid-to-rigid bonding)

Recommendation: Vacuum condition < 50 Pa, pressure around 0.1 – 0.2 MPa

Step 3: Autoclave process recommendation: 30-60°C/3-5kgf/cm²/20-30min



#### **Storage**

- Avoid applying pressure or resting objects on the product to prevent marking, denting, or deforming the surface.
- Wear gloves to prevent fingerprints or nail marks when handling.
- Product needs to be unpacked and handled in a clean-room facility.
- Store in sealed bag at 25°C or below.

# Regulatory

For regulatory information about this product, please contact your 3M representative.

# **Technical Information**

The technical information, recommendations and other statements contained in this document are based upon tests or experience that 3M believes reliable, but the accuracy or completeness of such information is not guaranteed.

#### **Product Use**

Many factors beyond 3M's control and uniquely within the user's knowledge and control can affect the use and performance of a 3M product in a particular application. Given the variety of factors that can affect the use and performance of a 3M product, user is solely responsible for determining if the product is fit for a particular purpose and suitable for user's method of application.

#### Warranty. Limited Remedy, and Disclaimer

Unless an additional warranty is specifically stated on the applicable 3M product packaging or product literature, 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE. If the 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

#### **Limitation of Liability**

Except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted.



**3M Display Materials & Systems Division** 3M Center, Building 235-1E-54 St. Paul, MN 55144-1000 U.S.A.

Phone 1-800-3M HELPS Web 3M.com/displayfilms