

## 3M™ Contrast Enhancement Film (CEF36XX/OCA 8F36-X Series)

- 3M film CEF36006/3M OCA 8F36-0.6
- 3M film CEF3601/3M OCA 8F36-1
- 3M film CEF36014/3M OCA 8F36-1.4
- 3M film CEF3602/3M OCA 8F36-2
- 3M film CEF3603/3M OCA 8F36-3
- 3M film CEF3604/3M OCA 8F36-4



### Product Description

3M™ Contrast Enhancement Films (CEF36XX/OCA 8F36-X Series) offer higher adhesion, especially at elevated temperatures, with a low modulus over a broad temperature range to enable shear decoupling. It is elastic to aid quick recovery after folding. 3M film CEF36XX can be laminated via the conventional film Optically Clear Adhesive (OCA) lamination process. No Ultraviolet (UV) curing required.

### Key Features

- Low modulus over a broad temperature range
- Higher adhesion to polarizer and clear polyimide (CPI)
- Elasticity for quick recovery after folding
- 3M film CEF36XX Series products are die cuts of film
- 3M OCA 8F36-X Series products are available in roll good form

### Product Construction

Product	3M™ film CEF36006 (OCA 8F36-0.6)	3M™ film CEF3601 (OCA 8F36-1)	3M™ film CEF36014 (OCA 8F36-1.4)	3M™ film CEF3602 (OCA 8F36-2)	3M™ film CEF3603 (OCA 8F36-3)	3M™ film CEF3604 (OCA 8F36-4)
<b>Adhesive Type:</b>	Acrylic	Acrylic	Acrylic	Acrylic	Acrylic	Acrylic
<b>Adhesive Carrier:</b>	None	None	None	None	None	None
<b>Approximate Thickness:</b>						
<b>Release Liner:</b>	75 µm (3.0 mils) Clear Polyester	75 µm (3.0 mils) Clear Polyester	75 µm (3.0 mils) Clear Polyester	75 µm (3.0 mils) Clear Polyester	75 µm (3.0 mils) Clear Polyester	75 µm (3.0 mils) Clear Polyester
<b>Adhesive:</b>	15 µm (0.6 mils)	25 µm (1.0 mils)	35 µm (1.4 mils)	50 µm (2.0 mils)	75 µm (3.0 mils)	100 µm (4.0 mils)
<b>Release Liner:</b>	75 µm (3.0 mils) Clear Polyester	75 µm (3.0 mils) Clear Polyester	75 µm (3.0 mils) Clear Polyester	75 µm (3.0 mils) Clear Polyester	75 µm (3.0 mils) Clear Polyester	75 µm (3.0 mils) Clear Polyester

The 3M family of optically clear adhesives for electronic displays are usually available in two forms. 3M OCA come in roll good form. 3M Contrast Enhancement Films (CEF) are available in die-cut form.

## 3M™ Contrast Enhancement Film (CEF36XX/OCA 8F36-X Series)

### Typical Physical Properties and Performance Characteristics

**Note:** The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

#### Environmental Testing:

The following environmental tests were conducted in the 3M laboratory under the conditions specified without any appreciable deterioration in visible appearance (no bubbles, delamination, etc.). Sample construction is optical glass/3M film CEF36XX/optical glass.

	Condition	Duration
High Temperature	+95°C	800 hours
Low Temperature	-40°C	800 hours
High Temp/Humidity-1	+65°C/90%RH	800 hours
High Temp/Humidity-2	+85°C/85%RH	800 hours
Thermal Shock	-40°C and +85°C (1 hour dwell, <1 min ramp time)	100 cycles

#### Peel Adhesion:

ASTM D3330 modified, 180 degree peel from glass, 1 cm wide peel strips, 12in/min (305 mm/min), 2.0 mil polyester backing, 3M film CEF36XX.

	Float Glass		PET		Polyimide	
Dwell Time	20 min dwell at 25°C/50%RH	1 day dwell at 25°C/50%RH	20 min dwell at 25°C/50%RH	1 day dwell at 25°C/50%RH	20 min dwell at 25°C/50%RH	1 day dwell at 25°C/50%RH
Units	N/cm	N/cm	N/cm	N/cm	N/cm	N/cm
3M film CEF36006	3	4				
3M film CEF3601	3	5				
3M film CEF36014	3	5				
3M film CEF3602	3	6	3	3	<4	<6
3M film CEF3604	4	8				

#### Color:

Ultra Scan Pro (Hunter Lab), ASTM E308, D65/10° 3M film CEF36XX on optical glass.

3M™ film CEF36XX Series			
3M film CEF36006	L* = 96.9	-0.1 < a* < 0.1	b* < 0.5
3M film CEF3601	L* = 96.9	-0.1 < a* < 0.1	b* < 0.5
3M film CEF36014	L* = 96.9	-0.1 < a* < 0.1	b* < 0.5
3M film CEF3602	L* = 96.9	-0.1 < a* < 0.1	b* < 0.5
3M film CEF3604	L* = 96.9	-0.1 < a* < 0.1	b* < 0.5

## 3M™ Contrast Enhancement Film (CEF36XX/OCA 8F36-X Series)

### Refractive Index:

(+ 0.0005 from standard deviation of ellipsometry) 3M film CEF36XX.

3M™ film CEF3601			
405 nm	532 nm	633 nm	1000 nm
1.4842	1.4704	1.4650	1.4570


### Haze:

Haze is measured according to ASTM D1003-92, 3M film CEF36XX on optical glass.

3M™ film CEF36006	3M™ film CEF3601	3M™ film CEF36014	3M™ film CEF3602	3M™ film CEF3604
< 0.3%	< 0.3%	< 0.3%	< 0.4%	< 0.4%

### Transmission Curve:

Transmission vs. Wavelength (Corrected for Reflection Loss) for 3M film CEF36XX on Glass



### Typical Electrical Properties at Room Temperature:

ASTM-D150-92. 3M film CEF36XX Series

### Dielectric Constant:

3M™ film CEF36XX Series	
Frequency (kHz)	Dielectric Constant
100	5.52
300	5.38
500	5.28

## 3M™ Contrast Enhancement Film (CEF36XX/OCA 8F36-X Series)

### Suggested Lamination Process


**Step 1:** Remove secondary liner, and then laminate 3M film CEF36XX Series to first adherent substrate by roller at room temperature

Recommendation: roller pressure 0.1 – 0.2 MPa, roller speed 0.5 – 1 m/min

**Step 2:** Remove primary liner, and then laminate 3M film CEF36XX/first adherent to second adherent by vacuum lamination (if rigid-to-rigid bonding)

Recommendation: Vacuum condition < 50 Pa, pressure around 0.1 – 0.2 MPa

**Step 3:** Autoclave process recommendation: 30-60°C/3-5kgf/cm<sup>2</sup>/20-30min



### Storage

- Avoid applying pressure or resting objects on the product to prevent marking, denting, or deforming the surface.
- Wear gloves to prevent fingerprints or nail marks when handling.
- Product needs to be unpacked and handled in a clean-room facility.
- Store in sealed bag at 25°C or below.

**Regulatory:** For regulatory information about this product, contact your 3M representative.

## 3M™ Contrast Enhancement Film (CEF36XX/OCA 8F36-X Series)

**Technical Information:** The technical information, guidance, and other statements contained in this document or otherwise provided by 3M are based upon records, tests, or experience that 3M believes to be reliable, but the accuracy, completeness, and representative nature of such information is not guaranteed. Such information is intended for people with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license under any 3M or third party intellectual property rights is granted or implied with this information.

**Product Use:** Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product in accordance with all applicable instructions and with appropriate safety equipment, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.

**Warranty, Limited Remedy, and Disclaimer:** Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specifications on the Certificate of Analysis, which is established when the product is manufactured and deemed commercially available and is provided at the time 3M ships the product. **3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE.** If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement or repair of the 3M product or refund of the purchase price.

**Limitation of Liability:** Except for the limited remedy stated above, and except to the extent prohibited by applicable law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.

**Disclaimer:** For industrial use only. Not intended, labeled or packaged for consumer sale or use.



**3M Display & Electronics**  
3M Center, Building 223-3S-32  
St. Paul, MN 55144-1000 U.S.A.

Phone 1-800-3M HELPS  
Web 3M.com/oca

3M is a trademark of 3M Company.  
All other trademarks herein are the  
property of their respective owners.  
©3M 2026. All rights reserved.  
60-5005-0627-8