




# Help keep your facility clean and safe with 3M products.



- 1** 3M™ Easy Trap Duster – sweep & dust sheets
- 2** 3M™ Easy Scrub Flat Mop System
- 3** Scotch-Brite™ High Performance Microfibre Cloths
- 4** 3M™ Stainless Steel Cleaner and Protector 
- 5** Scotch-Brite™ Easy Erasing Hand Pad 4004
- 6** 3M™ Safety-Walk™ Anti-Slip Tapes 

- 7** 3M™ Clean-Walk Mat
- 8** 3M™ High Capacity Maintenance Sorbent Roll
- 9** Scotch-Brite™ Power Pad 2000 
- 10** Scotch-Brite™ Medium Duty Scouring Pad 97 
- 11** Scotch-Brite™ Light Duty Scrubbing Pad 9030 

# Maintain the high standards of your manufacturing facilities with 3M™ Professional Cleaning Solutions.



## 1 3M™ Easy Trap Duster – sweep & dust sheets

Trap up to 8 times more dirt, dust and sand than with conventional flat-fringed cotton dust mops or a competitive sweeping dust cloth brand.\* Can be used with your existing flat mop or high duster.

\* Based on a study conducted by 3M



## 2 3M™ Easy Scrub Flat Mop System

Excellent for daily cleaning activities and ease of manoeuvring around furniture. Helps cut chemical waste by 80% compared to a mop and bucket, with the operator-controlled dispensing mechanism.\*

\* Based on a study conducted by 3M




## 3 Scotch-Brite™ High Performance Microfibre Cleaning Cloths

Ideal for cleaning stainless steel, chrome, wood and enamel, as well as delicate surfaces like glass and plastic.



## 4 3M™ Stainless Steel Cleaner & Protector

Builds an invisible layer of protection on stainless steel surfaces, making them easier to clean and more resistant to fingerprinting and smudging. This water-based, oil-free formula allows for quick-drying, streak-free spot cleaning, which can help reduce labour and lower product consumption.



## 5 Scotch-Brite™ Easy Erasing Hand Pad 4004

Ideal for removing stains, marks, ink and more. Just use water — no chemicals or sprays needed.



## 6 3M™ Safety-Walk™ Anti-Slip Tapes

Help reduce trip hazards with a low-profile design. This mineral-coated, slip-resistant material is adhered by a durable resin to a pressure-sensitive, adhesive-backed plastic film.



## 7 3M™ Clean-Walk Mat

An adhesive-coated mat used to remove dirt from the bottom of shoes, wheels or any passing objects. To expose the adhesive surface, just peel the top sheet back.



## 8 3M™ High Capacity Maintenance Sorbent Roll


This material is perfect for lining drawers, covering workbenches or masking larger areas from mist and overspray. It's also good to have on hand in case there is a spill.



## 9 Scotch-Brite™ Power Pad 2000

Scours 2 – 4 times faster than conventional commercial scouring pads, and is 6 – 10 times less abrasive than other medium-duty commercial scouring products to reduce scratching.\*

\* Based on a study conducted by 3M



## 10 Scotch-Brite™ Medium Duty Scouring Pad 97

Use it on everyday equipment. This pad replaces steel wool and won't leave metal slivers in hands. Long-lasting, non-rusting and resilient.



## 11 Scotch-Brite™ Light Duty Scrubbing Pad 9030

A convenient, thick, hand-sized pad designed for gentle, no-scratch cleaning of the most delicate surfaces.



3M Commercial Solutions Division  
3M Canada  
P.O. Box 5757  
London, Ontario N6A 4T1  
[3M.ca/CommercialCleaning](http://3M.ca/CommercialCleaning)

For more information, please contact  
your distribution representative or visit  
[3M.ca/CommercialCleaning](http://3M.ca/CommercialCleaning).

3M, 3M Science. Applied to Life., Scotch-Brite, Safety-Walk and Scotchgard are trademarks of 3M. Used under license in Canada. All other trademarks are property of their respective owners.  
© 2019, 3M. All rights reserved. 1910-15991 E