

IJ680-10

Product Description

- For Solvent, UV, and Latex Inkjet printing
- 7-mil, flexible, enclosed lens, retroreflective film

Product Features

- Available in white only
- Similar daytime and nighttime appearance that retains most of its reflectivity when wet
- Excellent angularity
- Pressure-activated adhesive for easy sliding and tacking
- For vertical, flat surfaces with and without rivets
- Unprocessed film resists fuel vapors or occasional spills
- Permanent
- Expected Performance Life of 9 years (unwarranted period for unprinted film with no graphic protection, applied to a flat, vertical, outdoor surface)

Recommended Types of Graphics and End Uses

- Commercial straight trucks, semi-trucks and semi-trailers
- Buses, vans, passenger vehicles, delivery and pickup trucks and enclosed trailers
- Rail and lead cars of trains
- Non-regulated, indoor and outdoor signage, emblems and striping
- Indoor and outdoor graphics and signs
- Small format original equipment manufacturer's (OEM) decorative and identification graphics, cautionary and safety labeling

When constructed and used as described in this Bulletin, these types of graphics and end uses may be warranted by the 3M™ MCS™ Warranty or the 3M Performance Guarantee. Please read the entire Bulletin for details.

IMPORTANT NOTE

Some substrates such as under-cured polyurethane paint, fiberglass, and some paint systems may continue to outgas for some time. Two-part polyurethane paints and screen print clears may stop curing when the air and surface temperature are lower than 75 °F (24 °C). This film is not recommended for use on stainless steel.

Recommended Compatible Products

See 3Mgraphics.com/warranties for a complete list of compatible products that are approved by 3M for use with the base film covered in this Bulletin and used for the creation of a graphic that may be eligible for the 3M™ MCS™ Warranty or 3M Performance Guarantee.

OEM Inkjet Inks and Printers for the 3M Performance Guarantee

See the [3M Performance Guarantee Matrix](#) for a complete list of compatible OEM Inkjet Inks and Printers that are approved by 3M for use with the base film covered in the Bulletin and used for the creation of a graphic that may be eligible for the 3M Performance Guarantee.

Quick Links

- [3M Graphics Warranties](#)
- [Technical Information Selector](#)
- [Safety Data Sheets \(SDS\)](#)
- [Flammability \(ASTM E84 Reports\)](#)
- [Videos](#)

Some of these links lead to web-based resources that are not product-specific.

Graphic Protection

- [3M™ Scotchcal™ Gloss Overlaminates 8518](#)
- [3M™ Scotchcal™ Luster Overlaminates 8519](#)
- [3M™ Screen Print Gloss Clear 1920DR](#)
- [3M™ Screen Print UV Gloss Clear 9740i](#)

Application Tapes

See [3M Instruction Bulletin AT-1](#) to determine what application tape is recommended for your film or finished graphic.

Other Products

- [3M™ Edge Sealer 3950](#)

Certificate of 3M™ MCS™ Warranty

Graphic manufacturers who produce digitally printed graphics made with all 3M Graphics Products, including 3M Ink purchased through a qualified 3M Distributor or 3M Printing Partner, may register to be recognized with a Certificate of 3M™ MCS™ Warranty. Only graphic manufacturers having a current Certificate of 3M™ MCS™ Warranty are eligible to extend this warranty to their customers.

NOTE: For non-digitally printed Finished Graphics, check your eligibility for the 3M™ MCS™ Warranty by viewing the Warranty Period found within the Product Bulletin or using the warranty selector at www.3mgraphics.com/warranties.

Characteristics

These are typical values for unprocessed product. Processing may change the values.

Physical Characteristics

| Characteristic | Value |
|---|--|
| Material | Vinyl |
| Film Color | Color: White Typical Coefficient of Retroreflection: 100 |
| Retroreflection Definition | The typical coefficient of retroreflection defined is measured at a -4° entrance angle and a 0.2° observation angle. It is expressed in candlepower per foot-candle per square foot (candela/lux/square meter) per ASTM E810. The entrance angle is formed by a light beam striking the surface at a point and a line that is perpendicular to the surface at the same point. An observation angle is formed by the light beam striking the reflective surface and returning to the observer. From 800 feet (249 meters), a motorist normally views a graphic at a 0.2° angle. |
| Thickness | With adhesive: 7–8 mil (0.18–0.20 mm) |
| Adhesive | Pressure-activated, slideability |
| Adhesive Color | Clear with silver underneath |
| Liner | Polyethylene-coated paper |
| Adhesion, Typical 24 hours after application | Aluminum 6.0 pounds/inch (1.1 kg/cm) FRP (Fiberglass Reinforced Plywood) 3.0 pounds/inch (0.5 kg/cm) Painted aluminum panels 4.5 pounds/inch (0.8 kg/cm) |
| Safety Standards | See "Health and Safety" on page 6 for ASTM, NFPA® and AAR information |
| Chemical Resistance | <ul style="list-style-type: none"> • Resists mild alkalis, mild acids, and salt • Excellent resistance to water (<i>does not include immersion</i>) • Resists occasional fuel spills |

| Characteristic | Value |
|----------------|---------------------|
| Flammability | Call 1-800-328-3908 |

Application Characteristics

| Characteristic | Value |
|---|---|
| Finished Graphic Application Recommendation | <p>Surface type: flat, with and without rivets, moderate curves, and corrugations</p> <p>Substrate type: aluminum, Fiberglass Reinforced Plywood (FRP), paint</p> <p>Application method: Dry</p> <p>Application temperature: air and substrate</p> <ul style="list-style-type: none"> Flat without rivets: 50–100 °F (10–38 °C) Flat, curved or corrugated surfaces with rivets: 55–100 °F (13–38 °C) |
| Temperature Range After Application | -30 to +200 °F (-34 to +93 °C) (not for extended periods of time at the extremes) |

Warranty Information

Warranty Coverage Overview

The warranty coverage for eligible graphics is based on the user both reading and following all applicable and current 3M Graphics Product and Instruction Bulletins. The warranty period for eligible graphics is as stated in the 3M Graphics Warranties Matrices, found at 3Mgraphics.com/warranties, at the time that the film was purchased. The warranty period may be reduced and stipulations may apply for certain constructions and applications, as covered in this Bulletin.

The warranties set forth in this Bulletin are made in lieu of all other express or implied warranties, including any implied warranty of merchantability, fitness for a particular purpose, or arising out of a course of dealing, custom, or usage of trade.

3M Basic Product Warranty

3M Graphics Products are warranted to be free of defects in materials and manufacture at the time of shipment and to meet the specifications stated in its applicable 3M Graphics Product Bulletin and as further set forth in the [3M Graphics Warranties Bulletin](#).

Limited Remedy

The limited remedy applicable to each warranty is addressed in the 3M Graphics Warranties Bulletin found at 3MGraphics.com/warranties.

Limitation of Liability

Except to the extent prohibited by law, 3M SHALL NOT UNDER ANY CIRCUMSTANCES BE LIABLE TO PURCHASER OR USER FOR ANY DIRECT (EXCEPT FOR THE LIMITED REMEDY PROVIDED HEREIN), INDIRECT, SPECIAL, INCIDENTAL, OR CONSEQUENTIAL DAMAGES (INCLUDING, BUT NOT LIMITED TO, LABOR, NON-3M MATERIAL CHARGES, LOSS OF PROFITS, REVENUE, BUSINESS, OPPORTUNITY, OR GOODWILL) RESULTING FROM OR IN ANY WAY RELATED TO 3M'S GRAPHICS PRODUCTS, SERVICES, OR THIS BULLETIN. This limitation of liability applies regardless of the legal or equitable theory under which such losses or damages are sought.

Warranty Period Matrices - Inkjet

See the ink/printer platform warranty matrices at 3MGraphics.com/warranties, for vertical warranty period information specific to your inkjet film.

Warranty Period Matrices - Unprinted Film

Table A. Unprinted Film Warranty Period (in years) for Film Series 5100R Finished Graphics with no Graphic Protection in a Standard U.S. Vertical Exposure (see [3M Graphics Warranties Bulletin](#) for Graphic Type Definitions).

| | Ink and Graphic Protection | VEH | OUT |
|--|----------------------------|-----|-----|
| 3M™ MCS™ Warranty | None | 7 | 7 |
| *Expected Performance Life (Unwarranted period of time) | None | 9 | 9 |

*Expected Performance Life is a good faith estimate of how long unprinted product may perform satisfactorily based on 3M testing. There is no warranty for performance or durability.

Reduced Warranty Period for Other Graphic Exposures

For other graphic exposures, determine the applicable reduced warranty period by multiplying the standard warranty period (in years) for your graphic construction as shown in the applicable warranty period tables by the percentage shown for the intended graphic exposure. See "Exposure Types" on page 3 of the 3M Graphics Warranties Bulletin for graphic exposure definitions.

Table B. Reduced Warranty Period for Other Graphic Exposures

| If the Graphic Exposure is: | Use this Percentage of Vertical Exposure, Warranty Period | Calculation Examples |
|----------------------------------|---|---------------------------|
| Desert Southwest Vertical | 70% | 0.7 x 7 years = 4.9 years |
| U.S. Horizontal | 0% | 0 x 4 years = 0 years |

Factors that Affect Graphic Performance Life

The actual performance life of a graphic is affected by:

- the combinations of graphics materials used.
- complete ink drying or curing.
- selection, condition and preparation of the substrate.
- surface texture.
- application methods.
- angle and direction of sun exposure.
- environmental conditions.
- cleaning or maintenance methods.

Graphics Manufacturing



CAUTION

Before using any equipment, always read the manufacturer's instructions for safe operation.

Inkjet Printing

Always read and follow the ink manufacturer's written instructions on usage.

Total Ink Coverage

The maximum recommended total ink coverage for this film is:

- **250%** is the maximum recommended total ink coverage for this film for all solvent, latex and UV inks.

Do not exceed the recommended total ink coverage for the ink series used on this product. Having too high a total physical ink amount on the product results in media characteristic changes, incomplete drying, overlamine lifting, and/or poor graphic performance. For additional details about total ink coverage, refer to the 3M Product and Instruction Bulletin for 3M inks or the [3M Performance Guarantee Matrix](#) for OEM inks.

IMPORTANT NOTE

Be sure to check the consistency of color on reflective film as it may appear different in daytime and nighttime lighting.

Completely Dry Graphics

IMPORTANT NOTE

Incomplete drying or curing can result in graphic failure including curling, increased shrinkage and adhesion failure, which are not covered under any 3M Graphic Warranty.

See the ink's 3M Product and Instruction Bulletin for more details.

Cutting

See [3M Instruction Bulletin 4.1](#) for Sheeting, Scoring and Film Cutting details.

Graphic Protection

Graphic protection may improve the appearance, performance and durability of the graphic. Click on the graphic protection options listed in Product Bulletin or see the [3M Graphics Market Product Catalog](#), for more information.

Application Tapes

There are two types of application tapes. See [3M Instruction Bulletin AT-1](#) to determine what application tape is recommended for your film or finished graphic.

Premasking Tape

Increases stiffness during application while preventing stretching and damage. Use when little or no liner is exposed. See [3M Instruction Bulletin 4.3](#) for complete details.

Prespacing Tape

Holds cut and weeded letters or graphics in place during application and after removing the film liner, while preventing stretching and damage. Use when large amounts of liner are exposed. See [3M Instruction Bulletin 4.3](#) for complete details.

IMPORTANT NOTE

Do not attempt to exchange the liner. This will compromise the slideability of the film, and could negatively impact adhesion or appearance of the applied graphic, which is not covered by any 3M warranty.

Application and Installation

IMPORTANT NOTE

This film is not recommended for use on low surface energy substrates such as some plastics, powder-coated paint, etc. The user must assume responsibility for testing and approving these substrates.

This film can be applied over other recommended 3M graphic systems. Graphics printed with clear 1920DR must be weathered for at least one year before applying this film over it. See [3M Instruction Bulletin 5.1](#) for details.

In addition to other 3M Bulletins specified in this document, the following Bulletins provide details that you may need to successfully apply a graphic.

- [3M Instruction Bulletin 5.36](#). Application Techniques for Automobiles, Vans and Buses. Complete the 3M Pre-Installation Inspection Record found in this Instruction Bulletin prior to manufacturing or applying a graphic to an automobile, van, or bus.
- [3M Instruction Bulletin 5.4](#). Application, Fleet Trucks.
- [3M Instruction Bulletin 5.5](#). Application, General Procedures for Interior and Exterior Dry Application

IMPORTANT NOTE

UV inkjet inks may crack if too much heat is used during graphic application to complex curves and deep contours as well as around rivets. When using heat during application, make sure the film surface temperature does not exceed 212° F (100° C). For best results, **always do a test application** of a printed graphic to determine how much heat can be used without damaging the image.

IMPORTANT NOTE

3M recommends using additional heat in the post-application process for vehicle graphics. During this process, 3M only recommends using a heat gun to make sure the film surface temperature reaches a minimum of 200° F (93° C) and does not exceed 225° F (107° C).

Pressure-activated Adhesive

The pressure activated adhesive on this film offers:

- smooth sliding into position on a substrate;
- fast finger tacking to check position; and

The **slideability feature is lost:**

- when firm pressure with a squeegee or other application tool is applied.
- at application temperatures above 100° F (38° C) even if only light finger pressure was used for tacking.
- if any part of the film is removed from the original liner and reapplied to the same or another liner.
- solvent from inkjet ink has not completely dried or cured.

Maintenance and Cleaning

Use a cleaner designed for high-quality painted surfaces. The cleaner must be wet, non-abrasive, without solvents, and have a pH value between 3 and 11 (neither strongly acidic nor strongly alkaline). See [3M Instruction Bulletin 6.5](#) for details.

Removal

This film uses a permanent adhesive. This film is not easily or cleanly removable. See [3M Instruction Bulletin 6.5](#) for details.

Shelf Life, Storage and Shipping

Shelf Life

The shelf life is **never more than 3 years** from the date of manufacture on the original box.

If you process the film, the shelf life is changed to **1 year** from the processing date, but not later than the 3 year maximum from the manufacturing date.

Storage Conditions

- 40° to 100 °F (4° to 38 °C)
- Out of sunlight
- Clean, dry area
- Original container
- Bring the film to room temperature before use

Shipping Finished Graphics

Flat, or rolled printed side out on 6 inch (15 cm) or larger core. This helps prevent the application tape, if used, from popping off.

Health and Safety



CAUTION

When handling any chemical products, read the manufacturer's container labels and the Safety Data Sheets (SDS) for important health, safety and environmental information. To obtain SDS sheets for 3M products go to 3M.com/SDS, or by mail or in case of an emergency, call 1-800-364-3577 or 1-651-737-6501.

When using any equipment, always follow the manufacturer's instructions for safe operation.

Standards

This information is important for applications that are regulated by ASTM or NFPA® standards, for example, traffic control signs, emergency vehicles and certain railroad graphics. The user is solely responsible for determining and complying with all current and applicable local, state and federal regulations regarding the use and application of graphics materials.

ASTM D-4956: Standard Specification for Retroreflective Sheeting for Traffic Control

ASTM D-4956 covers flexible, non-exposed glass bead lens and microprismatic, retroreflective sheeting designed for use on traffic control signs, delineators, barricades, and other devices. For Type I sheeting, it specifically covers the following colors: White, Yellow, Orange, Green, Red, Blue, and Brown. As defined in ASTM D-4956, IJ680-10 is classified as Type I sheeting with a Class 3 adhesive. IJ680-10 meets the requirements specified in section 6.1.1.

NFPA ® 1901: Standard for Automotive Fire Apparatus (2009 Edition)

According to NFPA® 1901, section 15.9.3.3 specifies that all retroreflective materials required by section 15.9.3.1 and 15.9.3.2 shall conform to the requirements of ASTM D4956, *Standard Specification for Retroreflective Sheeting for Traffic Control*, Section 6.1.1 for Type I sheeting. The film (white) meets the requirements for NFPA® 1901, Section 15.9.3.1 (Front and Sides).

AAR: Standard and Recommended Practices

This product is approved for use by the Association of American Railroads (AAR), Safety and Operations, as listed in the Manual of Standards and Recommended Practices, Section L - Lettering and Marking of Cars, Specification M-947, Adhesive-Backed Films.

Bulletin Change Summary

Release S APR-2016:

- Updated ASTM D-4956 statement. See “ASTM D-4956: Standard Specification for Retroreflective Sheeting for Traffic Control” on page 7.

Release R DEC-2015:

- Added section for "Warranty Period Matrices - Unprinted Film" on page 3. This information can now be found using the Warranty Selector, found at www.3Mgraphics.com/Warranties

3M Commercial Solutions

3M Center
Building 220-12E-04
St. Paul, MN 55144-1000
1-800-328-3908
Fax 651-736-4233
3M.com/GRAPHICS

3M Canada

PO Box 5757
London, ON N6A 4T1
1-800-265-1840
Fax 519-452-6245

3M México S.A. de C.V.

Av. Santa Fe No. 55
Col. Santa Fe, Del. Alvaro Obregón
México D.F. 01210
General 5255-5270-0400
Fax 5255-5270-2277

3M Puerto Rico, Inc.

350 Chardon Avenue
Suite 1100
San Juan, PR 00918
General 787-620-3000
Fax 787-620-3018

3M, MCS, Scotchlite and Scotchlite are trademarks of 3M Company. NFPA is a registered trademark of National Fire Protection Association, Inc. All other trademarks are the property of their respective owners.

