

IJ160 IJ160C with Comply™ Adhesive

Product Description

- For Solvent, UV and Latex Inkjet Printing Only
- 4-mil, opaque white, vinyl film with a matte finish

Product Features

- Pressure-activated adhesive for easy sliding, tacking, snap-up and repositioning
- Film IJ160C-10 also has Comply™ Adhesive air release channels for fast, easy, bubble-free graphic installations
- Excellent hiding power
- Removable with heat
- Outstanding resistance to dirt and other environmental factors and wear from high foot traffic when protected by the recommended overlamine
- Expected Performance Life of 7 years (unwarranted period for unprinted film with no graphic protection, applied to a flat, vertical, outdoor surface)
 - **Indoor Floor Graphics:** 1 year when used in a horizontal indoor exposure with typical usage and protected by:
 - [3M™ Scotchcal™ Luster Overlamine 3645](#)
 - [3M™ Envision™ Matte Overlamine 8050M](#)
 - [3M™ Scotchcal™ Luster Overlamine 8509](#)

Quick Links

- [3M Graphics Warranties](#)
- [Technical Information Selector](#)
- [Safety Data Sheets \(SDS\)](#)
- [Flammability \(ASTM E84 Reports\)](#)
- [Videos](#)

Some of these links lead to web-based resources that are not product-specific.

Recommended Types of Graphics and End Uses

- Commercial vehicle, transit or fleet graphics, emblems or striping
- Outdoor and indoor graphics and signs
- Vending or dispensing machine and cooler graphics
- Floor graphics on most indoor hard surface flooring

When constructed and used as described in this Bulletin, these types of graphics and end uses may be warranted by the 3M™ MCS™ Warranty or the 3M Performance Guarantee. Please read the entire Bulletin for details.

Recommended Compatible Products

See 3M.com/graphicswarranties for a complete list of compatible products that are approved by 3M for use with the base film covered in this Bulletin and used for the creation of a graphic that may be eligible for the 3M™ MCS™ Warranty or 3M Performance Guarantee.

OEM Inkjet Inks and Printers for the 3M Performance Guarantee

See the [3M Performance Guarantee Matrix](#) for a complete list of compatible OEM Inkjet Inks and Printers that are approved by 3M for use with the base film described in this Bulletin and used for the creation of a completed graphic that may be eligible for the 3M Performance Guarantee.

Graphic Protection

Graphic protection can improve the appearance, performance and durability of your graphic. Always use only the graphic protection options recommended in this Bulletin for this film.

- [3M™ Screen Print Gloss Clear 1920DR](#)
- [3M™ Scotchcal™ Luster Overlamine 3645](#)
- [3M™ Envision™ Matte Overlamine 8050M](#)
- [3M™ Scotchcal™ Luster Overlamine 8509](#)
- [3M™ Scotchcal™ Gloss Overlamine 8518](#)
- [3M™ Scotchcal™ Luster Overlamine 8519](#)
- [3M™ Scotchcal™ Matte Overlamine 8520](#)
- [3M™ Scotchcal™ Ultra Matte Overlamine 8915](#)
- [3M™ Screen Print UV Gloss Clear 9740i](#)
- [3M™ Screen Print UV Gloss Clear 9760LX](#)



Indoor Floor Graphics

- [3M™ Scotchcal™ Luster Overlamine 3645](#)
- [3M™ Envision™ Matte Overlamine 8050M](#)
- [3M™ Scotchcal™ Luster Overlamine 8509](#)

Other Products

- [3M™ Edge Sealer 3950](#)

Certificate of 3M™ MCS™ Warranty

Graphics manufacturers who produce graphics made with all 3M Graphics Products, including 3M Ink purchased through a qualified 3M Distributor or 3M Printing Partner, may register to be recognized with a Certificate of 3M™ MCS™ Warranty. Only graphics manufacturers having a current Certificate of 3M™ MCS™ Warranty are eligible to extend this warranty to their customers.

Characteristics

These are typical values for unprocessed product. Processing may change the values.

Physical Characteristics

Characteristic	Value
Material	Vinyl
Film Color	White, opaque
Thickness	Without adhesive: 4 mils (0.10 mm) With adhesive: 4.5 – 5 mils (0.11 – 0.13 mm)
Adhesive	IJ160C: Pressure-activated (slide, tack, snap-up, reposition) with air release channels IJ160: Pressure-activated (slide, tack, snap-up, reposition)
Adhesive Color	Gray
Liner	Polyethylene-coated paper
Adhesion, Typical 24 hours after application	ABS: IJ160: 3–4 pounds/inch (0.65–0.71 kg/cm) IJ160C: 3–4 pounds/inch (0.78 kg/cm) Fruehauf pre-painted panels: IJ160: 1.0 pounds/inch (0.18 kg/cm) IJ160C: 0.5-1 pounds/inch (0.09–0.16 kg/cm)
Tensile Strength	13 pounds/inch at 73 °F (2.3 kg/cm at 23 °C), minimum
Chemical Resistance	Resists mild alkalis, mild acids, and salt Excellent resistance to water (does not include immersion)
Flammability	ASTM E84 reports: IJ160/IJ160C , or go to the On-line Product Catalog at 3Mgraphics.com

Warranty Period Matrices

See the 3M Graphics Warranties Matrices at [3M.com/graphicswarranties](#), for vertical warranty period information specific to your film.

Additional Limitations

See the 3M Graphics Warranties Bulletin at [3MGraphics.com/warranties](#), for terms, additional limitations of your warranty, if any, and limitations of liability.

Application Characteristics

Characteristic	Value
Finished Graphic Application Recommendation	<p>Surface type: Flat, with and without rivets (expect tenting)</p> <p>Substrate type: Acrylic, aluminum, glass (uncoated), painted metal, polycarbonate, and painted wood (smooth), most indoor floors, including sealed concrete, marble, terrazzo, ceramic, finished wood</p> <p>Application temperature: 40° – 100°F (4.4° – 38°C) air and substrate</p> <p>Application method: Dry</p>
Applied Shrinkage	0.032 inch (0.8 mm)
Temperature Range After Application	-30 °F to +200 °F (-34 °C to +93 °C) (not for extended periods of time at the extremes)
Graphic Removal	Removable with heat at a minimum ambient and substrate temperature of 40°F (4°C)

Warranty Information

Warranty Coverage Overview

The warranty coverage for eligible graphics is based on the user both reading and following all applicable and current 3M Graphics Product and Instruction Bulletins. The warranty period for eligible graphics is as stated in the 3M Graphics Warranties Matrices at the time that the film was purchased. Information found at 3M.com/graphicswarranties includes:

- [3M Graphics Warranties Bulletin](#)
 - This bulletin contains information on limitations and exceptions, and warranty period reductions for 3M Graphics Warranties. The warranty period may be reduced and stipulations may apply for certain constructions, applications, and graphic exposures as covered in this Bulletin.
- [3M Graphics Warranties Selector](#)
 - Use this selector to search for your vertical warranty period by product type, ink type, film name, and/or ink/printer platform.
- [U.S. Desert Southwest Region Map](#)
 - Use this map of hot, arid desert areas to determine if you are subject to reduced warranted durabilities.

The warranties set forth in this Bulletin are made in lieu of all other express or implied warranties, including any implied warranty of merchantability, fitness for a particular purpose, or arising out of a course of dealing, custom, or usage of trade.

3M Basic Product Warranty

3M Graphics Products are warranted to be free of defects in materials and manufacture at the time of shipment and to meet the specifications stated in its applicable 3M Graphics Product Bulletin and as further set forth in the [3M Graphics Warranties Bulletin](#).

Limited Remedy

The limited remedy applicable to each warranty is addressed in the 3M Graphics Warranties Bulletin found at 3M.com/graphicswarranties.

Limitation of Liability

Except where prohibited by law, 3M SHALL NOT UNDER ANY CIRCUMSTANCES BE LIABLE TO PURCHASER OR USER FOR ANY DIRECT (EXCEPT FOR THE LIMITED REMEDY PROVIDED IN THE 3M GRAPHICS WARRANTIES BULLETIN), INDIRECT, SPECIAL, INCIDENTAL, OR CONSEQUENTIAL DAMAGES (INCLUDING, BUT NOT LIMITED TO, LABOR, NON-3M MATERIAL CHARGES, LOSS OF PROFITS, REVENUE, BUSINESS, OPPORTUNITY, OR GOODWILL) RESULTING FROM OR IN ANY WAY RELATED TO 3M'S GRAPHICS PRODUCTS, SERVICES, or THIS BULLETIN. This limitation of liability applies regardless of the legal or equitable theory under which such losses or damages are sought.

Warranty Period Matrices

3M™ MCS™ Warranty for Approved Printers & Inks in Appendix A									
Zone	Zone 1			Zone 2			Zone 3		
Graphic Protection	VEH	OUT	IN	VEH	OUT	IN	VEH	OUT	IN
8518, 8519, 8520, 8915, 8528	3	3	6	2	2	4	1	1	3
9740i (UV only)	3	3	6	2	2	4	1	1	3
1920DR (latex only)	3	3	6	2	2	4	1	1	3
3M™ MCS™ Warranty for Approved Printers & Inks in Appendix B									
8518, 8519, 8520, 8915, 8528	4	4	7	3	3	5	2	2	3
9740i*	4	4	7	3	3	5	2	2	3
3M™ MCS™ Warranty for Approved Printers & Inks in Appendix C									
8518, 8519, 8520, 8915**, 8528	4	4	7	3	3	5	2	2	3
9740i	4	3	7	3	2	5	2	1	3

* 9740i not warranted for use with Mimaki LF-200 inks.

** 8915 not warranted for use with Oki GX inks

The warranty period for eligible graphics is as stated in the 3M Warranty Period Tables for IJ160/IJ160C-10 in effect at the time that the film was purchased.

Application Tapes

See [3M Instruction Bulletin AT-1](#) to determine what application tape is recommended for the film or finished graphic.

Factors that Affect Graphic Performance Life

The actual performance life of a graphic is affected by:

- the combinations of graphics materials used.
- complete ink drying or curing.
- selection, condition and preparation of the substrate.
- surface texture.
- application methods.
- angle and direction of sun exposure.
- environmental conditions.
- cleaning or maintenance methods.

Graphics Manufacturing

CAUTION

Before using any equipment, always read the manufacturer's instructions for safe operation.

Inkjet Printing

Always read and follow the ink manufacturer's written instructions on usage.

Total Ink Coverage

The maximum recommended total ink coverage for this film is:

- **270%** when printed with all approved 3M solvent inkjet inks.
- **280%** when printed with all approved 3M UV inkjet inks.
- **280%** when printed with all approved 3M latex inkjet inks.
- **250%** when printed on the Mimaki JV5 Series printer with HS ink series ([3M Performance Guarantee](#)).

Do not exceed the recommended total ink coverage for the ink series used on this product. Having too high a total physical ink amount on the product results in media characteristic changes, incomplete drying, overlamine lifting, and/or poor graphic performance. For additional details about total ink coverage, refer to the 3M Product and Instruction Bulletin for 3M inks or the [3M Performance Guarantee Matrix](#) for OEM inks.

Completely Dry Graphics

IMPORTANT NOTE

Incomplete drying or curing can result in graphic failure including curling, increased shrinkage and adhesion failure, which are not covered under any 3M Graphic Warranty.

See the specific ink's 3M Product and Instruction Bulletin for more details.

Cutting

See [3M Instruction Bulletin 4.1](#) for Sheeting, Scoring and Film Cutting details.

Graphic Protection

Graphic protection may improve the appearance, performance and durability of the graphic. Click on the graphic protection options listed in Product Bulletin or see the [3M Graphics Market Product Catalog](#), for more information.

IMPORTANT NOTE

During installation, scratches may occur on films without graphic protection.

Application Tapes

There are two types of application tapes. See [3M Instruction Bulletin AT-1](#) to determine what application tape is recommended for the film or finished graphic.

Premasking Tape

Increases stiffness during application while preventing stretching and damage. Use when little or no liner is exposed. See [3M Instruction Bulletin 4.3](#) for complete details.

Prespacing Tape

Holds cut and weeded letters or graphics in place during application and after removing the film liner, while preventing stretching and damage. Use when large amounts of liner are exposed. See [3M Instruction Bulletin 4.3](#) for complete details.

Application and Installation

In addition to other 3M Bulletins specified in this document, the following Bulletins provide details that you may need to successfully apply a graphic.

- [3M Instruction Bulletin 3.12](#). Screen Printing. 3M™ Screen Printing Ink Series 1900 Line Color and Screen Print Clear VI0402.
- [3M Instruction Bulletin 4.22](#) Lamination Basics for Inkjet Printed Graphics
- [3M Instruction Bulletin 5.4](#). Application, Fleet Trucks.
- [3M Instruction Bulletin 5.5](#) Application, General Procedures for Interior and Exterior Dry Application

IMPORTANT NOTE

UV inkjet inks may crack if too much heat is used during graphic application to complex curves and deep contours as well as around rivets. When using heat during application, make sure the film surface temperature does not exceed 212° F (100° C). For best results, **always do a test application** of a printed graphic to determine how much heat can be used without damaging the image.

Pressure-activated Adhesive

The pressure activated adhesive on this film offers:

- Smooth sliding into position on a substrate;
- Fast finger tacking to check position; and
- Easy snap-up and repositioning when you need it.

The **snap-up and reposition feature is lost:**

- When firm pressure with a squeegee or other application tool is applied.
- At application temperatures above 100° F (38° C) even if only light finger pressure was used for tacking.
- If any part of the film is removed from the original liner and reapplied to the same or another liner.
- Solvent from inkjet ink has not completely dried or cured, which affects both slideability and snap-up.

Working with Air Release Channels

Air release channels are a characteristic of films with Comply™ adhesive that allow trapped air to exit through the edges of the graphic.

- The channels will be damaged and effective air removal affected if you remove and attempt to change liners or reapply the same liner.
- For the best results, always work from the center out to the edges of the graphic to allow trapped air to exit through the air release channels. If the channels are closed off by firm pressure and air is trapped, use an air release tool to aid in removing air bubbles. See [3M Instruction Bulletin 5.4](#) for details.

Video

Click [here](#) to see how 3M's Comply™ adhesive technology works.

Working with Rivets

- This film will tent when applied over rivets.
- If the rivets are closely spaced, the film will bridge between rivets.
- Tented or bridged film may fail prematurely.
- For the best appearance and durability, 3M recommends cutting around the rivet, removing the circle of film, and then re-squeegeeing around the rivet

3M™ Tape Primer 94

3M recommends that where the film will be stretched, use primer to maximize a graphic's bond to its substrate.

Maintenance and Cleaning

Use a cleaner designed for high-quality painted surfaces. The cleaner must be wet, non-abrasive, without solvents, and have a pH value between 3 and 11 (neither strongly acidic nor strongly alkaline). See [3M Instruction Bulletin 6.5](#) for details.

Removal

Removal requires heat and/or chemicals. 3M makes no claims as to the ease or speed of removal. This product may not remove similarly to other products in the same category. See [3M Instruction Bulletin 6.5](#) for details.

Shelf Life, Storage and Shipping

Shelf Life

The shelf life is **never more than 3 years** from the date of manufacture on the original box.

If the film is processed, the shelf life is changed to **1 year** from the processing date, but not later than the 3 year maximum from the manufacturing date.

Storage Conditions

- 40° to 100 °F (4° to 38 °C)
- Out of direct sunlight
- Clean, dry area
- Original container
- Bring the film to room temperature before use

Shipping Finished Graphics

Flat, or rolled printed side out on 6 inch (15 cm) or larger core. This helps prevent the liner, and, if used, the application tape from popping off.

Health and Safety

CAUTION

When handling any chemical products, read the manufacturers' container labels and the Safety Data Sheets (SDS) for important health, safety and environmental information. To obtain SDS sheets for 3M products go to [3M.com/SDS](https://www.3m.com/SDS), or by mail or in case of an emergency, call 1-800-364-3577 or 1-651-737-6501.

When using any equipment, always follow the manufacturer's instructions for safe operation.

Commercial Solutions

3M Center, Building 220-12E-04
St. Paul, MN 55144

1-800-328-3908
[3M.com/Graphics](https://www.3m.com/Graphics)

© 3M 2019. All rights reserved.

3M, Scotchcal, Envision, Controltac, Comply, and MCS are trademarks of 3M.

Used under license in Canada.

All other trademarks are property of their respective owners.
Revision O, November 2019 Please recycle.



Appendix A: 3M™ MCS™ Warranty Approved Printers & Inks

Printer	Ink
HP Latex R1000 Plus R2000 Plus	HP 872 / 882 / 886 Latex Inks, a 3M™ MCS™ Warranty Component
HP Latex 3200 3100 3000	HP 881 Latex Inks, a 3M™ MCS™ Warranty Component
HP Latex 3800 3600 3500	HP 3M 891 Latex Inks
HP Latex 1500	HP 881 Latex Inks, a 3M™ MCS™ Warranty Component
HP Latex 570 560 375 370 365 360	HP 831 871 Latex Inks, a 3M™ MCS™ Warranty Component
HP Designjet L28500 26500 / Latex 280 260 210	HP 792 Latex Ink, a 3M™ MCS™ Warranty Component
EFI™ Quantum® 5 3	EFI™ 3M™ SuperRange XF Ink
EFI™ VUTEK® 5r 3r	EFI™ 3M™ SuperRange XF Ink
EFI™ VUTEK® H1625 LED	EFI™ H1625 LED Series 3M™ Inks/ EFI™ Prographics UV-3M™
EFI™ Pro 16h	EFI™ Pro 16h - 3M Ink / EFI™ Prographics UV-3M™
EFI™ VUTEK® GS5500 5250 3250 LXr (incl. Pro/UD Series)	EFI VUTEk GSLX 3M SuperFlex UV Ink
EFI™ VUTEK® GS3250 2000 LX (incl. Pro/UD Series)	EFI™ VUTEK® GSLXr 3M™ SuperFlex UV Ink
EFI™ VUTEK® GS5500 5250 3250 LXr (incl. Pro/UD Series)	EFI™ 3M™ SuperRange Ink
EFI™ VUTEK® GS3250 2000 LX (incl. Pro/UD Series)	EFI™ 3M™ SuperRange Ink
EFI™ VUTEK® LX3 Pro	EFI™ 3M™ SuperRange Ink

Appendix B: 3M™ MCS™ Warranty Approved Printers & Inks

Printer	Ink
EFI™ VUTEK® QS3220 3200 2000 220	3M™ Piezo Inkjet Ink Series 2800UV
EFI™ VUTEK® PV200	3M™ Piezo Inkjet Ink Series 2200UV
EFI™ VUTEK® GS3250 3200 2000 (incl. Pro Series)	EFI™ VUTEK® GS 3M™ Premium UV ink
EFI™ VUTEK® GS5000r 3250r	EFI™ VUTEK® GSr 3M™ Premium UV ink
EFI™ R3225	EFI™ R3225 3M™ UV Inks
EFI™ VUTEK® 5300 5000 3360 3300 3000 2360 150	3M™ Piezo Inkjet Ink Series 1500v2
HP Scitex TJ8350 8300	3M™ Piezo Inkjet Ink Series 4800
Mimaki UJV500-160	MIMAKI UV Piezo Inkjet Ink Series LUS-200 Manufactured by 3M
Mimaki UCJV-300	MIMAKI UV Piezo Inkjet Ink Series LUS-200 Manufactured by 3M
Mimaki UJV160 / JFX-1631 1615R	MIMAKI UV Piezo Inkjet Ink Series LF-200 Manufactured by 3M

Appendix C: 3M™ MCS™ Warranty Approved Printers & Inks

Printer	Ink
Epson SureColor® S80600 S80610 S80650 S80670 S80680	Epson® - 3M™ UltraChrome® GS3 Ink with Red
Epson SureColor® S60600 S60610 S60650 S60670 S60680	Epson® - 3M™ UltraChrome® GS3 Ink
Epson SureColor® S40600 S40610 S40650 S40670 S40680	Epson® - 3M™ UltraChrome® GS3 Ink
OKI data ColorPainter™ M-64s	3M™ SX Ink series from OKI
OKI data ColorPainter™ H3-104s	3M™ SX Ink series from OKI
OKI data ColorPainter™ E-64s	3M™ SX Ink series from OKI
OKI data ColorPainter™ H-74s 104s / H2-74s 104s / W-54s 64s	3M™ GX Ink series from OKI
Roland TrueVIS VG2-540 640	TrueVIS TR2 Inks, a 3M™ MCS™ Warranty Component