



**3M™ Cubitron™ II
Clean Sanding Film Disc 775L**



Game-changing composite sanding performance.

Market Spotlight: RV Paint Preparation

3M Abrasives delivered game-changing performance for an RV manufacturer's paint adhesion prep. By using 3M™ Cubitron™ II Clean Sanding Film Disc 775L to sand their fiberglass composites, they were able to achieve a 2:1 performance increase over their previous disc.

2:1

RV paint shop experienced a performance increase of 2:1 over their previous disc.

Performance Highlights:



High cut-rate



Consistent finish



Dust extraction


After 1 week, operators were asking for the “purple disc.”

Product Test Data:

When testing grade 240+, 3M™ Cubitron™ II Clean Sand Film Disc 775L outperformed the competition 2:1 in cut-rate.*

Switch to revolutionary 3M™ Cubitron™ II 775L Sanding Discs for increased throughput and a more consistent finish in your sanding process.

Sanding Performance Test



* Based on internal 3M testing conducted on composite sheet using 3M™ Random Orbital Sander

Request a sample at [3M.com/775L](https://www.3m.com/775L)