

3M Science.
Applied to Life.™

A legend
reborn.

Precision optics. A comfortable,
slim fit. Premium quality at a
great price.

The 3M™ Speedglas™ Welding Helmet 9002NC.
Reengineered in a brand new light.

3M.ca/LegendReborn

 **Speedglas**™
Brand

**The 3M™ Speedglas™
Welding Helmet
9002NC – reengineered
for a better view, and
more comfort.**

legend

Now you get advanced optics,
less weight and a great new look.

For over 20 years, the 3M™ Speedglas™ Welding Helmet 9000 set the standard for rugged, dependable protection. Now we've incorporated the best features of this pioneering helmet into the 3M™ Speedglas™ Welding Helmet 9002NC—giving a new generation of welders superior performance at a price that won't break the bank.

This helmet is a classic, and now incorporates the newest technology from the 3M Speedglas brand. Advanced auto-darkening optics are easily adjusted to meet your working conditions for a lighter, brighter and more detailed view of your welds. And a lighter weight, slim profile means less constriction in tight spaces.



Reengineered with the features you want and need.

Comfort

Ergonomically designed suspension, for a precise fit, and a smooth ratchet for easy tightening, even with gloves on!

Advanced Optics

Improved optics in the Speedglas™ welding filter 9002NC helps you see your welds in a new light, providing more contrast and natural-looking colour as shown in these photos.



9002NC ADF Shade 3



Sample Competitor



Shield width
9.29 in/23.6 cm



Freedom of Movement

Slim helmet – less than 500 g (1.1 lbs), with a shield that's just 23.6 cm (9.29") wide, protects even in cramped spaces.

Design

A signature sleek, modern and professional look.

Clarity

Built-in exhaust vents help reduce fogging.





Affordability

State-of-the-art auto-darkening optics are within the reach of every welder, from apprentices to seasoned veterans.

Customize your 3M™ Speedglas™ Welding Helmet 9002NC

with accessories including magnifying lenses, ear and neck covers, flame retardant hoods and 3M™ Disposable Respirators.



| Part No. | Description |
|-----------------|---|
| 04-0100-20NC-CA | 3M™ Speedglas™ Welding Helmet 9002NC |
| 04-0112-00NC | 3M™ Speedglas™ Welding Helmet 9000 without ADF welding filter |
| 04-0000-21NC-CA | 3M™ Speedglas™ Welding Filter |
| 04-0212-02NC | 3M™ Speedglas™ Front Panel |
| 04-0270-01 | Outside protection plate, 10/case |
| 04-0270-03 | Outside protection plate, scratch resistant, 10/case |
| 04-0270-04 | Outside protection plate, high temperature, 10/case |
| 04-0280-00 | Inside protection plate, 5/case |
| 04-0320-00 | Battery, 2/case |
| 04-0380-00 | Battery holders blue, 2/case |
| 05-0655-00 | Headband with assembly parts |
| 05-0660-00 | Assembly parts for headband |
| 06-0700-83 | Full hood black/grey |
| 07-0024-02 | Sweatband fleece, 2/case |
| 18-0099-68 | Throat and side protector, leather |
| 07-0014-00NR | Hard Hat Adaptor 1/case |
| | |
| | |
| | |

3M™ Disposable Respirators for welding and metal pouring

| Model | NIOSH Class | Qty/Box | Boxes/Case | Case Qty |
|-------|-------------|---------|------------|----------|
| 8212 | N95 | 10 | 8 | 80 |
| 8214 | N95 | 10 | 8 | 80 |
| 8512 | N95 | 10 | 8 | 80 |
| 8514 | N95 | 10 | 8 | 80 |
| 8515 | N95 | 10 | 8 | 80 |

3M.ca/LegendReborn



3M Personal Safety Division
3M Canada
P.O. Box 5757
London, ON N6A 4T1

Technical Assistance 1-800-267-4414

3M PSD products are for occupational use only.

WARNING

These respirators help reduce exposures to certain airborne particulates. Before use, the wearer must read and understand the *User Instructions* provided as a part of the product packaging. A written respiratory protection program must be implemented meeting all the requirements of OSHA 1910.134 including training, fit testing and medical evaluation. In Canada, CSA standards Z94.4 requirements must be met and/or requirements of the applicable jurisdiction, as appropriate. Misuse may result in sickness or death. For proper use, see package instructions, supervisor, or call 3M PSD Technical Service in Canada at 1-800-267-4414.