



## Automotive Aftermarket Division

### 3M™ Scotch™ Tape 2328 Masking Tape

---

#### 1) Part Numbers

06034 – 18mm x 50m  
06309 – 24mm x 50m  
06311 – 36mm x 50m  
51286 – 48mm x 50m  
51287 – 72mm x 50m

#### 2) Description and end uses'

Scotch™ Tape 2328 is a beige coloured masking tape developed specifically for the vehicle refinish industry, whilst being suitable for a wide variety of applications. It is compatible with a variety of substrates and all current refinish paint systems. Made from a crepe paper it offers excellent conformability and hold around corners, a secure grip and clean easy removal.

Sizes available:

Width (mm): 18, 24, 36, 48, 72.

Length (m): 50.

Features	Advantages	Benefits
Latex saturated creped	Conformability Thinness Solvent resistance  Easy hand tear Good paint anchorage  Sliver resistance	Good curve masking Good paint line Prevents paint bleed through Good handling Good paint flaking resistance Easy removal
Crosslinked rubber resin	Instant adhesion Good holding power	Sticks easily Resists lifting

#### 3) Physical Properties

Thickness:	0.135 mm	AFERA 4006
Adhesion to steel:	6.5 N/25 mm	AFERA 4001
Tensile strength:	88 N/25 mm	AFERA 4004



# Technical Data Sheet

Effective: 01/03/2022    Supersedes: 03/03/2020

## 4) Directions for Use

1. Ensure that the area/substrates to be masked is clean and dry prior to the application of the tape.
2. Window rubbers and plastic mouldings should be cleaned using a silicon remover / mild solvent to ensure they are free from contamination to improve the tapes adhesion.
3. If the tape has been baked and left overnight allowing it to go cold and damp, we recommend the vehicle be warmed prior to the tape removal. Failure to do so may result in adhesive residue being left on the vehicle.

Satisfactory performance and clean removal of Scotch™ Tape 2328 will be achieved at varying temperatures/time exposure on many substrates. Tests should be conducted to establish Scotch™ Tape 2328 performance parameters in your process conditions. The optimum level for product performance and easy removal is at 80 °C for 60 min.

## 5) Storage

Store product in the original carton under normal conditions of 21°C and 50% relative humidity. When stored at the recommended conditions in original, unopened containers, this product has a shelf life of 12 months.

## 6) Safety

**3M™ Automotive Aftermarket Products are designed FOR PROFESSIONAL USE ONLY.**

Always use the product in the manner in which it is designed to be used.

When using solvents etc. for cleaning the surface prior to the SEMFT application, care must be taken to avoid contact with the skin and eyes. The correct PPE must be worn at all times

When removing the masking tape after use from the vehicle it should be disposed of following local authority/ country guidelines.



# Technical Data Sheet

Effective: 01/03/2022 Supersedes: 03/03/2020

## 7) Disclaimer

All statements, technical information and recommendations are based on tests we believe to be reliable, but the accuracy or completeness thereof is not guaranteed. Please ensure before using our product that it is suitable for your intended use. All questions of reliability relating to this product are governed by the Terms of Sale subject, where applicable, to the prevailing law.

### For Additional Health and Safety Information

3M South Africa & Sub-Saharan Africa, 146A Kelvin Drive, Woodmead, Sandton, South Africa, Tel: (0861) 225536
3M (East) AG Representation Office Tirane, Rruga Sami Frasherri, Pallati i Ri Perxhola Kati 2 Ap2, 1000 Albania
3M Arabia, LLC, Building 24-25 3M Saudi Arabia Zone C, Business Gate, Airport Road, Riyadh, Saudi Arabia
3M Bulgaria, Mladost 4, Business Park, bl.4, 2nd floor, Sofia 1766, Bulgaria
3M Česko, spol. s r.o., V Parku 2343/24, 148 00 - Praha 4, Czech Republic
3M (East) AG, Branch office Croatia, Avenija Većeslava Holjevca 40, 10 000 Zagreb, Croatia, Tel: +385 1 2499750, www.3m.com.hr
3M Egypt, Finance Center , New Cairo , Plot 140 , Banking Sector , 5th settlement , Cairo , Egypt
3M Hellas MEPE, Automotive Aftermarket Division, 20 Kifisias Avenue, 151 25 Marousi, Greece, Phone: +30 210 68 85 300, innovation.gr@mmm.com, www.3M.gr
3M Hungária Kft, Neumann János u. 1/E, 1117 Budapest, Hungary
3M Israel, 91 Medinat Hayehudim St., Herzliya, Israel
3M Kenya Ltd, Victoria Towers, 3rd Floor, Kilimanjaro Av, Upperhill, Kenya
3M Gulf Limited, Ein El Mreisseh, Saint Charles City Center, 4th. Floor, P.O.Box: 11-5025, Riad el Solh, Beirut 1107 2180 Lebanon
3M Minnesota Mining & Manufacturing Nigeria Limited, No 2 Sheraton Opebi Link Road, Ikeja, Lagos Nigeria
3M Pakistan, Islamic Chamber of Commerce Building, ST-2/A, Block 9, KDA Scheme 5, Clifton, Karachi, Pakistan
3M Poland, Al. Katowicka 117, Kajetany, 05-830 Nadarzyn, Poland, Telefon: +48 22 739 60 00, www.3m.pl/kontakt
3M Gulf (Representation Office), Suhaim Bin Hamad St., Al Mana Towers Tower B, 2nd Floor, Office No.4, Doha Qatar, P.O.Box 14685
3M Romania, 12 Meneuțului St., Bucharest Business Park, Building D, District 1 013713 Bucharest, Romania
3M (East) AG, Representation Office Serbia, Airport City, Omladinskih brigada 90B, 11070 Belgrade, Serbia, Tel: +381 11 2209 400, www.3m.co.rs/3M/sr_RS/3m-south-east-europe/
3M Slovensko s.r.o., Polus Tower 2, Vajnorská 100/B, 83104 Bratislava
3M (East) AG, Branch office Slovenia, Cesta v Gorice 8, 1000, Ljubljana, Slovenia, Tel: +386 1 2003 630, www.3m.com/3M/sl_SI/3m-south-east-europe/
3M Sanayi ve Ticaret As, Barbaros Mah., Mor Sümbül Sok., No:7/3F, 27-51, Nidakule Ataşehir Güney, 34746 Ataşehir, İstanbul, Turkey
3M Gulf Limited, Dubai Internet City, Building No. 11, 3rd Floor, U.A.E

© 3M 2022. 3M and Scotch are trademarks of the 3M company. All rights reserved