

Intermediate Warranty Table EMEA

Digital Print Films

3M™ MCS™ Warranty Warranty is stated in years, differentiated in 3 geographical zones. Vertical applications only! Release: Aug 21

Please review the notes below the table and the list of qualified printer-ink combinations on the next page of this document for limitations. Product offering may vary from country to country. Local availability of selected graphics constructions should be clarified with your local 3M subsidiary.			#N/A			#N/A			#N/A		
			Vehicle, Bus, Fleet Box, Truck, Trailer			Exterior Sign			Interior Sign		
Zone:			1	2	3	1	2	3	1	2	3
IJ160, 160C	white , matte; removable	8518, 8520	5	4	3	4	3,5	2,5	6	6	6
48, 48C**	white, matte permanent & removable	8048G, 8050M	4	3.5	2.5	3	3	2	5	5	5
		*SG8993	4	3.5	2.5	3	3	2	5	5	5
		SG8995-124	-	-	-	-	-	-	5	5	5
IJ40, 40C	white gloss & matte permanent & removable	8038G, 8040M	4	3.5	2.5	3	3	2	5	5	5
IJ40, 40C	transparent gloss & matte permanent & removable	8508G, 8510M	3	3	2	3	2.5	1.5	5	5	5

Only graphics manufacturers having a current Certificate of 3M™ MCS™ Warranty are eligible to extend this Warranty to their customers.

To find the best combination of protection and film for your graphic application including conformability, gloss, adhesion to substrate and other attributes, please review product and instruction bulletins.

* No warranty with SG8993 for HP 831/871/881/891 Latex inks

Notes

- For additional warranty information, follow the link to 3M Graphics Warranty Bulletin.
- All statements based on the recommended types of graphics and end uses of the product. See the product bulletin for limitations of end use.
- Graphics used on the exterior of any type of vehicle or subjected to abrasion or chemical require a 3M Graphic Protection (overlaminated or clear).

Geographical Zones

Zone 1:

Austria, Belarus, Belgium, Bosnia, Croatia, Czech Republic, Denmark, Estonia, Finland, France (except Corsica), Germany, Greenland, Hungary, Iceland, Ireland, Italy (north of Rome), Kazakhstan, Latvia, Liechensein, Lithuania, Luxembourg, Moldova, Mongolia , Montenegro, Netherlands, Norway, Poland, Romania, Russia, Serbia, Slovakia, Slovenia, Sweden, Switzerland, UK, Ukraine

Zone 2:

Albania, Armenia, Azerbaijan, Benin, Brunei, Bulgaria, Burundi, Cambodia, Central African Republic, Congo, Cote, Crete, Djibouti, France (Corsica), Gabon, Georgia, Ghana, Gibraltar, Greece (except Crete), Italy (south of Rome and Sardinia), Ivory Coast, Kenya, Kyrgyzstan, Lesotho , Liberia, Macedonia, Malawi, Malta, Mozambique, Nigeria, Portugal, Rwanda, Sierra Leone, Somalia, South Africa (except of Kalahari desert and Namib dessert area), Spain (except Canary Islands), Tajikistan, Tanzania, Tasmania, Togo, Tonga, Turkey, Turkmenistan, Uganda, Uzbekistan, Zaire

Zone 3:

Afghanistan, Algeria, Angola, Bahrain, Bhutan, Botswana, Cameroon, Chad, Cyprus, Dubai, Egypt, Equatorial Guinea, Eritrea, Ethiopia, Gambia, Greece (Crete), Iran, Iraq, Israel, Jordan, Kuwait, Lebanon, Libya, Madagascar, Mali, Mauritania, Mauritius , Morocco, Namibia, Niger, Oman, Pakistan, Qatar, Saudi Arabia, Senegal, Spain (Canary Islands), Sri Lanka, Sudan, Swaziland, Syria, Tunisia, United Arab Emirates, Uruguay, Western Sahara, Yemen, Zambia,

Definitions

Transportation: Application to any kind of vehicle that is in regular use (no static exposure of graphic).


Exterior: Application with a static geographic direction without exposure to any adjacent reflecting surface

Interior: Application inside a building without direct exposure to the elements.

Warranty and Limited Liability

The following is made in lieu of all other express or implied warranties, including any implied warranty of merchantability or fitness for a particular purpose. All 3M products are warranted to be free of defects in materials and manufacture at the time of shipment and to meet the specifications stated in the film or media's Product Bulletin. All questions of warranty and liability relating to this product are governed by the terms and conditions of the sale, subject, where applicable, to the prevailing law.

DISCLAIMER: With the exception of 3M branded products, 3M does not represent that any printer or printer accessory recommended in 3M literature will meet customer requirements, any federal, state or local regulations, or any applicable safety standards. Such determination is the responsibility of the printer owner.



Types of exposure

Vertical: The face of the graphic is ±15° from vertical. Unless otherwise noted this type of exposure is the base for the mentioned warranty periods.

Intermediate Warranty Table EMEA

Digital Print Films

Warranted printer - ink combinations

EFI™ Quantum® 5, 5+ 3, 3+ with EFI™ 3M™ SuperRange XF Ink	EFI™ VUTEk® 3r+, 5r+ with EFI™ 3M™ SuperFlex UV XF Ink
EFI™ with Pro 32r Pro 32r+ with EFI™ 3M™ SuperRange XF Ink	EFI™ VUTEk® Pro 32r Pro 32r+ with EFI™ 3M™ SuperFlex UV XF Ink
EFI™ VUTEk® D3r D5r with EFI™ 3M™ SuperRange XF Ink	EFI™ VUTEk® D3r D5r with EFI™ 3M™ SuperFlex UV XF Ink
EFI™ VUTEk® 5r, 5r+ 3r, 3r+ with EFI™ 3M™ SuperRange XF Ink	EFI™ VUTEk® Q3r Q5r with EFI™ 3M™ SuperFlex UV XF Ink
EFI™ VUTEk® Q3r Q5r with EFI™ 3M™ SuperRange XF Ink	EFI™ VUTEk® GS3250 3200 2000 (incl. Pro Series) with EFI™ VUTEk® GS 3M™ Premium UV ink ** Series 48 not suitable for E-Cut Graphics
EFI™ H1625 LED with EFI™ H1625 LED Series 3M™ Inks/ EFI™ Prographics UV-3M™ Ink	EFI™ VUTEk® EFI™ VUTEk® GS5000r 3250r) with EFI™ VUTEk® GSr 3M™ Premium UV ink ** Series 48 not suitable for E-Cut Graphics
EFI™ Pro 16h with EFI™ Pro 16h - 3M™ Inks/ EFI™ Prographics UV-3M™ Ink	
EFI™ VUTEk® GS5500 5250 3250 LXr (incl. Pro/UD Series)with EFI™ 3M™ SuperRange Ink	Epson SureColor® with Epson® - 3M™ UltraChrome® GS3 Ink with Red
EFI™ VUTEk® GS3250 2000 LX (incl. Pro/UD Series) with EFI™ 3M™ SuperRange Ink	Epson SureColor® with Epson® - 3M™ UltraChrome® GS3 Ink
EFI™ VUTEk® LX3 Pro with EFI™ 3M™ SuperRange Ink	Epson SureColor® with Epson® - 3M™ UltraChrome® GS3 Ink
EFI™ VUTEk® 32h with EFI™ 3M™ SuperRange Ink	
EFI™ VUTEk® H3 H5 with EFI™ 3M™ SuperRange Ink	
EFI™ VUTEk® GS5000r 3250r with EFI™ VUTEk® GSLXr 3M™ SuperFlex UV Ink	
EFI™ VUTEk® GS3250 3200 2000 (incl. Pro Series) with EFI™ VUTEk® GSLX 3M™ SuperFlex UV Ink	

Intermediate Warranty Table EMEA
Digital Print Films

Warranted printer - ink combinations

EFI™ Quantum® 5, 5+ 3, 3+ with EFI™ 3M™ SuperRange XF Ink	OKI data ColorPainter™ M-64s with 3M™ SX Ink series from OKI
HP Latex R1000 Plus R2000 Plus with HP 872 / 882 / 886 Latex Inks, a 3M™ MCS™ Warranty Component	OKI data ColorPainter™ H3-104s with 3M™ SX Ink series from OKI
HP Latex 700 700W / 800 800W with HP 832 / 872 Latex Inks, a 3M™ MCS™ Warranty Component	OKI data ColorPainter™ E-64s with 3M™ GX Ink series from OKI
HP Latex 3200 3100 3000 with HP 881 Latex Inks, a 3M™ MCS™ Warranty Component	OKI data ColorPainter™ H-74s 104s / H2-74s 104s with 3M™ GX Ink series from OKI
HP Latex HP Latex 3800 3600 3500 with HP 3M 891 Latex Inks	OKI data ColorPainter™ W-54s 64s with 3M™ GX Ink series from OKI
HP Latex HP Latex 1500 HP 881 Latex Inks, a 3M™ MCS™ Warranty Component	
HP Latex 570 560 375 370 365 360 with HP 831 871 Latex Inks, a 3M™ MCS™ Warranty Component	
	Roland TrueVis Series SG/SG2/VG/VG2/VF2 with TrueVIS TR2 Inks, a 3M™ MCS™ Warranty Component
Mimaki UJV500-160 with MIMAKI UV Piezo Inkjet Ink Series LUS-200 Manufactured by 3M	
Mimaki UCJV-300 with MIMAKI UV Piezo Inkjet Ink Series LUS-200 Manufactured by 3M	