



Double sided adhesive tape GPT-020F

Product Data Sheet

September 2022
Supersedes: December 2019

Product Description

Double sided adhesive tape with polyester carrier
Modified acrylic adhesive Film Liner

Key Features

- High adhesion to a variety of high and low surface energy substrate
- High initial tack
- All-purpose tape
- High shear and temperature resistance
- Easy handling and converting due to polyester carrier
- Film Liner for clean handling and automatic unwinding activities

Application ideas

- Self-adhesive mounting of furniture trim, sealing profiles and cable ducts.
- Bonding and mounting of sales displays and billboards.
- Fixing of decorative trims and emblems.

Construction

Adhesive	Modified Acrylic
Adhesive side open face ¹	0,095 mm
Carrier	PET 0,012 mm, transparent
Adhesive back side ²	0,095 mm
Total thickness without liner	0,202 mm
Liner	Polypropylene film liner, white (0,100 ± 0,010 mm)

¹The open face side is visible, when unwinding the roll.

²The back side is visible after removal of the liner.

Calipers are average values.

Calculation of the adhesive caliper based on an average density of 1.012 g/ cm³.

Performance Characteristics

Adhesion to Stainless Steel acc. to Finat FTM1 (after 72 h at RT, angle: 180°, Haul-off speed: 300 mm/min., (0,05 mm PET-Film)	11,30 N/cm
Adhesion to ABS acc. to Finat FTM1 (after 72 h at RT, angle: 180°, Haul-off speed: 300 mm/min., (0,05 mm PET-Film)	10,86 N/cm
Adhesion to Polycarbonate acc. to Finat FTM1 (after 72 h at RT, angle: 180°, Haul-off speed: 300 mm/min., (0,05 mm PET-Film)	12,32 N/cm
Adhesion to Polypropylene acc. to Finat FTM1 (after 72 h at RT, angle: 180°, Haul-off speed: 300 mm/min., (0,05 mm PET-Film)	12,26 N/cm
Adhesion to Glass acc. to Finat FTM1 (after 72 h at RT, angle: 180°, Haul-off speed: 300 mm/min., (0,05 mm PET-Film)	11,79 N/cm
Static shear resistance to stainless steel acc. to Finat FTM8, 1 kg/ 1"x1", at RT	> 10.000 min
Static shear resistance to stainless steel acc. to Finat FTM8; 500 g /0.5"x1" at 90 °C	>10.000 min
Temperature Performance (SAFT, PSTC 17, 40 °C to 205 °C, 0.5 °C / min), 500 g / 1"x1"	> 190 °C
Temperature Performance (SAFT, PSTC 17, 40 °C to 205 °C, 0.5 °C / min), 1000 g / 1"x1"	> 160 °C

Storage & Shelf Life

Store at 16 °C–25 °C and 40-65 % relative humidity in its original box.
The product can be stored up to 18 months after date of manufacturing.

Note: The shelf life may be shortened if the original packaging is not properly sealed or stored in an environment with high temperatures or humidity

Precautionary Information

For information please contact your local 3M Office at www.3M.nl/tapes

For Additional Information

To request additional product information or to arrange for sales assistance, write us at: CustomerserviceBNL@mmm.com

Automotive Disclaimer

Automotive Applications: This product is an industrial product and has not been designed or tested for use in certain automotive applications, including, but not limited to, automotive electric powertrain battery or high voltage applications. This product does not fully adhere to typical automotive design or quality system requirements, such as IATF 16949 or VDA 6.3. This product may not be manufactured in an IATF certified facility and may not meet a Ppk of 1.33 for all properties. The product may not undergo an automotive production part approval process (PPAP). Customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's automotive application and for conducting incoming inspections before use of the product. Failure to do so may result in injury, death, and/or harm to property. No written or verbal statement, report, data or recommendation by 3M related to automotive use of the product shall have any force or effect unless in an agreement signed by the Technical Director of 3M's Automotive Division. Customer assumes all responsibility and risk if customer chooses to use this product in an automotive electric powertrain battery or high voltage application, and 3M will not be liable for any loss or damage arising from or related to the 3M product or customer's use of the product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity or recall costs), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability. In no event shall 3M be liable for any damages in excess of the purchase price paid for the product.

To request addition NOTWITHSTANDING ANY OTHER STATEMENT TO THE CONTRARY, 3M MAKES NO REPRESENTATIONS, WARRANTIES OR CONDITIONS WHATSOEVER, EXPRESS OR IMPLIED, REGARDING THE PRODUCT IF USED IN AN AUTOMOTIVE ELECTRIC POWERTRAIN BATTERY OR HIGH VOLTAGE APPLICATION, INCLUDING, BUT NOT LIMITED TO, ANY WARRANTY ON PERFORMANCE, LONGEVITY, SUITABILITY, COMPATIBILITY, OR INTEROPERABILITY, OR ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. For product information or to arrange for sales assistance, write us at: CustomerserviceBNL@mmm.com

Important Notice

All statements, technical information and recommendations contained in this document are based upon tests or experience that 3M believes are reliable. However, many factors beyond 3M's control can affect the use and performance of a 3M product in a particular application, including the conditions under which the product is used and the time and environmental conditions in which the product is expected to perform. Since these factors are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular purpose and suitable for the user's method or application. All questions of liability relating to this product are governed by the terms of the sale subject, where applicable, to the prevailing law

Values presented have been determined by standard test methods and are average values not to be used for specification purposes. Our recommendations on the use of our products are based on tests believed to be reliable but we would ask that you conduct your own tests to determine their suitability for your applications. This is because 3M cannot accept any responsibility or liability direct or consequential for loss or damage caused as a result of our recommendations

3M is a trademark the 3M Company.



**Industriële tapes, lijmstoffen
en markeringssystemen**

3M Nederland B.V.
Molengraaffsingel 29
NL-2629 JD Delft

3M Belgium bvba/sprl
Hermeslaan 7
B-1831 Diegem

Email: CustomerserviceBNL@mmm.com
Website: www.3M.nl/tapes

Email: CustomerserviceBNL@mmm.com
Website: www.3M.nl/tapes