

3M Science.
Applied to Life.™

3M Automotive Aftermarket Division

3M™ Flexible Foam Abrasive Discs

Versatility at its finest.

- ▶ Flexible foam backed abrasive which conforms to irregular surfaces
- ▶ Universal product can be used wet or dry and by hand or machine for preparation and primer sanding applications
- ▶ Excellent dust and water control to ensure a clean sanding environment

NEW
P400
P600



3M™ Flexible Foam Abrasive Disc range


Part number	Product description	Grade	Discs/box	Boxes/case
Size 150mm				
33538	3M™ Hookit™ Flexible Abrasive Foam Disc 150mm, P400, PN33538	P400	20	4
33539	3M™ Hookit™ Flexible Abrasive Foam Disc 150mm, P600, PN33539	P600	20	4
33540	3M™ Hookit™ Flexible Foam Abrasive Disc, 150mm, P800, PN33540	P800	20	4
33541	3M™ Hookit™ Flexible Foam Abrasive Disc, 150mm, P1000, PN33541	P1000	20	4
33542	3M™ Hookit™ Flexible Foam Abrasive Disc, 150mm, P1200, PN33542	P1200	20	4
33543	3M™ Hookit™ Flexible Foam Abrasive Disc, 150mm, P1500, PN33543	P1500	20	4
33544	3M™ Hookit™ Flexible Foam Abrasive Disc, 150mm, P2000, PN33544	P2000	20	4
Size 125mm				
33545	3M™ Hookit™ Flexible Foam Abrasive Disc, 125 mm, P800, PN33545	P800	20	4
33546	3M™ Hookit™ Flexible Foam Abrasive Disc, 125mm, P1000, PN33546	P1000	20	4
33547	3M™ Hookit™ Flexible Foam Abrasive Disc, 125mm, P1200, PN33547	P1200	20	4
33548	3M™ Hookit™ Flexible Foam Abrasive Disc, 125mm, P1500, PN33548	P1500	20	4
33549	3M™ Hookit™ Flexible Foam Abrasive Disc, 125mm, P2000, PN33549	P2000	20	4
Size 77mm				
33550	3M™ Hookit™ Flexible Foam Abrasive Disc, 77mm, P800, PN33550	P800	20	4
33551	3M™ Hookit™ Flexible Foam Abrasive Disc, 77mm, P1000, PN33551	P1000	20	4
33552	3M™ Hookit™ Flexible Foam Abrasive Disc, 77mm, P1200, PN33552	P1200	20	4
33553	3M™ Hookit™ Flexible Foam Abrasive Disc, 77mm, P1500, PN33553	P1500	20	4
33554	3M™ Hookit™ Flexible Foam Abrasive Disc, 77mm, P2000, PN33554	P2000	20	4

3M's Flexible Foam Abrasive Discs combine a flexible aluminium oxide abrasive with a soft foam to create a high performing, versatile blending abrasive.

Hundreds of laser perforated holes mean excellent dust and water control when used wet or dry creating a clean sanding environment.

**Flexible and long lasting,
delivering a superior finish.**

Versatility at its finest.



Automotive Aftermarket Division

3M United Kingdom PLC

Tel: 0845 603 9714
aadukenquiries@mmm.com
www.3M.co.uk/bodyshop

3M Ireland

Tel: (00) 353 1 216 0301
Fax: (00) 353 1 280 3509

Please recycle. Printed in the UK. © 3M 2020.
All rights reserved. 3M and Hookit are trademarks
of the 3M company. J388370. AB009/20

