

3M™ Hook and Loop Reclosable Fasteners

Backed with proprietary 3M Adhesives, 3M™ Hook and Loop Fasteners offer secure, repeated closures for a wide variety of applications.

- Easy Release Liner and Easy Peel Edge
- Nylon Hook and Loop
- Rubber or Acrylic Adhesives or Plain Back
- Available sizes: 5/8", 3/4", 1", 1-1/2", 2", 4"
- All rolls are 50 yd long

Common use colors depicted on back.



3M™ Hook and Loop Reclosable Fasteners


Go To Portfolio

The Go To Portfolio is available in 50 yd rolls in the following widths: 5/8", 3/4", 1", 1-1/2", 2" and 4".

Volume Discounts
available for most products.

Inquire at 10, 20 and
30 case intervals.

Some exclusions apply. See your
3M Sales Specialist for more information.

Category	Product	Type	Adhesive	Color	Description
General Use	SJ3526N	Hook	High performance rubber		Long-term adhesion to a wide variety of substrates; good for indoor applications.
	SJ3527N	Loop			
Extreme Conditions	SJ3572	Hook	High performance acrylic		Long-term adhesion; good for outdoor applications.
	SJ3571	Loop			
Good Value	SJ3530	Hook	General performance rubber		Value-option, competitive priced, backed by 3M adhesives, for multi-use applications.
	SJ3531	Loop			
No Adhesive	SJ3402	Hook	None		For sew-on or other attachment methods.
	SJ3401	Loop			
Flame Resistant	SJ3519FR	Hook	Flame resistant		 <p>Provide flame resistance when tested per FAR 25.853. (a)(1)(ii) 12 Second Vertical</p>
	SJ3518FR	Loop			
	SJ3419FR	Hook	None		
	SJ3418FR	Loop			



3M Industrial Adhesives & Tapes
3M Center, Bldg 225-3S-06
St. Paul, MN 55144-1000 USA

Phone 1-800-362-3550
Web 3M.com/fasteners

The information on this page should not be used for specification purposes. Customer is responsible for in-use testing on intended substrates. Samples (1") in black, white and beige are available for testing. For samples of other colors, please contact Technical Service.

3M™ Hook and Loop is available in cut-to-length strips, circles/coins or in other shapes from our partners: HALCO USA, Fastenation, Gleicher and Lockfast.

For availability of lengths, widths or colors outside of 3M's Go To Portfolio, please contact your local 3M representative or one of the converting experts listed above. For a list of additional converters in your area, visit 3M.com/converter.

3M is a trademark of 3M Company.
All other trademarks are property of their respective owners. © 3M 2020.
All rights reserved. 70-0713-4696-2

