



Performance Guarantee for Graphic Manufacturer

Print Media

IJ180 (All versions), SV480, LX480, IJ170, IJ175Cv3, IJ3552C, IJ3555, IJ380, IJ3690LF, IJ680, IJ680CR, 780mC, IJ8150, IJ3650, IJ3630, IJ3730, 8170-P40, 8170-P50, 40C, 48C, IJ160

Sept 2020

**Graphic Protection & Media Options

Some printer/ink platforms may not have all media or protection approved. 3M recommends graphic protection for all graphics. Refer to media Product Bulletin before selecting a graphic protection option.

This is not a finished graphics warranty. The only remedy available is replacement of 3M product used in the construction.

Graphic Protection

8518, 8519, 8520, 8915, 8150, 8914, 8040M, 8048G, 8548G, 8549L, 8550M, 8528, 3619, 3620, 3658G, 3660M, 8588G, 8590M, 1920DR, 9740i, 9760LX

Manufacturer	Printer	Inks	Ink Type	Tested by 3M	**Graphic Protection or Print Media Exceptions
AGFA	Jeti Ceres RTR3200 LED	Anuvia 1550 RTR & 1050 UV	UV	✓	9760LX, 1920DR
AGFA	Jeti Mira LED	Anuvia 1500 & 1050 UV	UV	✓	9760LX, 1920DR
Durst	Rho 500R	Rho Roll v3 UV	UV	✓	9760LX, 1920DR
Durst	Rho 312R, 512R, 520R	Rho Roll UV ink	UV	✓	9760LX, 1920DR
Canon	Colorado 1650	UVgel 460 ink	UVgel	✓	9760LX, 1920DR
EPSON	Stylus® Pro GS6000	UltraChrome® GS	Solvent	✓	9740i, 9760LX, LX480
EPSON	SureColor® S30670, S50670, S30675, S50675	UltraChrome® GS2	Solvent	✓	9740i, 9760LX, LX480
EPSON	SureColor® S70670, S70675	UltraChrome® GSX	Solvent	✓	9740i, 9760LX, LX480
HP	Latex 310, 315, 330, 335	HP 831 Latex	Latex	✓	9740i, SV480
HP	L25500	HP 789 Latex	Latex	✓	9740i, SV480
HP	8000, 9000, 10000	HP 790	Solvent	✓	9740i, 9760LX, LX480
HP Scitex	TJ8300	TJ100 Supreme	Solvent	✓	9760LX, LX480
HP Scitex	TJ8500	TJ200 UV	UV	✓	9760LX, 1920DR
HP Scitex	TJ8500, TJ8600	TJ210 UV	UV	✓	9760LX, 1920DR
HP Scitex	XL1200, XL1500	XL200, XL300 Supreme	Solvent	✓	9760LX, 1920DR, LX480
Mimaki	JV33, CJV30 Series	SS21 Series	Solvent	✓	9740i, 9760LX, LX480
Mimaki	JV150, CJV150 Series	SS21 Series	Solvent	✓	9740i, 9760LX, LX480
Mimaki	JV300, CJV300 Series	SS21 Series	Solvent	✓	9740i, 9760LX, LX480
Mimaki	JV400-LX Series	LX100 Latex	Latex	✓	9740i, SV480
Mimaki	JV400-LX Series	LX101 Latex	Latex	✓	9740i, SV480

Mimaki	JV5 Series	ES Series	Solvent	✓	9740i, 9760LX, LX480
Mimaki	JV5 Series	HS Series	Solvent	✓	9740i, 9760LX, LX480
Mutoh	Valuejet 1628X, 1638X	Eco-Ultra™ Series	Solvent	✓	9740i, 9760LX, LX480
Mutoh	Valuejet 1204,1304,1604,1614,1618	Eco-Ultra™ Series	Solvent	✓	9740i, 9760LX, LX480
Mutoh	Valuejet 1324, 1624, 1638	Eco-Ultra™ Series	Solvent	✓	9740i, 9760LX, LX480
Mutoh	Xperjet 1641SR, 1682SR	MS41	Solvent	✓	9740i, 9760LX, LX480
RICOH	RICOH Pro L4100	L4160	Latex	✓	9740i, SV480
RICOH	RICOH Pro L5160	AR	Latex	✓	9740i, SV480
Roland®	SOLJET EJ-640	EJ	Solvent	✓	9740i, 9760LX, LX480
Roland®	SOLJET PRO 4 XR/XF	ECO-SOL MAX 2	Solvent	✓	9740i, 9760LX, LX480
Roland®	SOLJET PRO II Series	ECO-SOL MAX	Solvent	✓	9740i, 9760LX, LX480
Roland®	SOLJET PRO III Series	ECO-SOL MAX	Solvent	✓	9740i, 9760LX, LX480
Roland®	VersaCAMM®	ECO-SOL MAX	Solvent	✓	9740i, 9760LX, LX480
OKI Data Infotech Corporation	ColorPainter™ 64S	EG-Outdoor	Solvent	✓	9740i, 9760LX, LX480
EFI™ VUTEk®	QS2000, 3200, 3220	QS Series 2 UV	UV	✓	9760LX, 1920DR
EFI™ VUTEk®	QS220	QS220 UV	UV	✓	9760LX, 1920DR
EFI™ VUTEk®	QS3200r, 3250r	QSr UV	UV	✓	9760LX, 1920DR
EFI™ VUTEk®	150, X300, X360	UltraVu Series 6	Solvent	✓	9740i, 9760LX, LX480
NOTES	LIMITATIONS: Always check the media and protection Product Bulletins for additional details and intended use.				
Total Ink Coverage	270% for most films and printers in a CMYK system. Exceptions: 250% for all Reflective Films and Mimaki JV5 Series with HS ink series.				
Limitation of Liability	With the exception of 3M branded products, 3M does not represent that any printer or printer accessory recommended in 3M literature will meet customer requirements, any federal, state or local regulations or any applicable safety standards. Such determination is the responsibility of the printer owner.				