



3M™ Performance Warranty Table

Jan 2025

The 3M™ Performance Warranty provides warranty coverage for approved combinations of 3M Graphics Products and OEM branded inks (“Performance Warranty Inks”). This warranty does not offer warranty protection against defects, failures or losses caused by, arising from, or related to Inks formally known as Finished Graphic Defects - Ink Related. The only remedy available is replacement of 3M Graphics Products used in the construction of the finished graphic. Refer to the current 3M Graphics Products Warranty Bulletin for complete details on warranty coverage and exclusions.

3M Graphic Films*

IJ180 Series, IJ280, SV480mC, LX480mC, IJ175Cv3, IJ3552C, IJ3690LF Series, IJ680-10, IJ680CR-10, 780mC-10R, IJ8150 Series, PL50mC, IJ3650 Series, IJ3630-20, IJ3730 Series, 8170 Series, 40 Series, 48 Series, IJ160 Series, 8173 Series, IJ3635 series

3M Graphic Protection Products

8518, 8519, 8520, 8915, 8428G, 8528, 8150, 8914, 8600M Series, 8418G, 8548G, 8549L, 8550M, 3619, 3620, 3658G, 3660M, 8588G, 8590M, 8993, 8995-124, 8900 Series, 8508, 8509, 8510, 8048G, 8050M, 9740i, 9760LX

Manufacturer	Printer Model	Performance Warranty Inks	Ink Type	Excluded 3M Graphics Products**
AGFA	Jeti Ceres RTR3200 LED	Anuvia 1550 RTR & 1050 UV	UV	SV480mC, LX480mC, IJ3635-210SV/LX, 9760LX
AGFA	Jeti Mira LED	Anuvia 1500 & 1050 UV	UV	SV480mC, LX480mC, IJ3635-210SV/LX, 9760LX
AGFA	Jeti Tauro H2500, H3300 LED	Anuvia 1551 UV	UV	IJ180mC-114, SV480mC, IJ3690LF-114, IJ8150 Series, IJ3650-114, IJ3630, IJ3730 Series, IJ3635-210SV/LX, 9740i, 9760LX
Durst	Rho 500R	Rho Roll v3 UV	UV	SV480mC, LX480mC, IJ3635-210SV/LX, 9760LX
Durst	Rho 312R, 512R, 520R	Rho Roll UV ink	UV	SV480mC, LX480mC, IJ3635-210SV/LX, 9760LX
EPSON	SureColor® S30670, S50670, S30675, S50675	UltraChrome® GS2	Solvent	LX480mC, PL50mC, IJ3635-210UV, 9740i, 9760LX
EPSON	SureColor® S70670, S70675	UltraChrome® GSX	Solvent	LX480mC, PL50mC, IJ3635-210UV, 9740i, 9760LX
EPSON	SureColor® R5070, R5070L	UltraChrome® RS	Resin	SV480mC, IJ3635-210UV, 8993, 9740i
HP	Latex 310, 315, 330, 335	HP 831 Latex	Latex	SV480mC, IJ3635-210UV, 8993, 9740i
Mimaki	JV5 Series	ES Series	Solvent	LX480mC, PL50mC, IJ3635-210UV, 9740i, 9760LX
Mimaki	JV5 Series	HS Series	Solvent	LX480mC, PL50mC, IJ3635-210UV, 9740i, 9760LX
Mimaki	JV33, CJV30 Series	SS21 Series	Solvent	LX480mC, PL50mC, IJ3635-210UV, 9740i, 9760LX
Mimaki	JV150, CJV150 Series	SS21 Series	Solvent	LX480mC, PL50mC, IJ3635-210UV, 9740i, 9760LX
Mimaki	JV300, CJV300 Series	SS21 Series	Solvent	LX480mC, PL50mC, IJ3635-210UV, 9740i, 9760LX
Mimaki	JV100 Series	SS21 Series	Solvent	LX480mC, PL50mC, IJ3635-210UV, 9740i, 9760LX
Mimaki	JV100 Series	AS5	Solvent	LX480mC, PL50mC, 40 Series, IJ160 Series, IJ3635-210UV, 9740i, 9760LX
Mimaki	JV100 Series	CS250	Solvent	LX480mC, PL50mC, 40 Series, IJ160 Series, IJ3635-210UV, 9740i, 9760LX
Mimaki	JV330 Series	SS21 Series	Solvent	IJ180mC-114, IJ180mC-10UR, LX480mC, IJ3552C, IJ3690LF-114, IJ8150, PL50mC, IJ3560-114, IJ3630, IJ3730 Series, 48 Series, IJ3635-210UV, 9740i, 9760LX
Mimaki	JV330 Series	BS4	Solvent	IJ180mC-114, IJ180mC-10UR, LX480mC, IJ3552C, IJ3690LF-114, IJ8150, PL50mC, IJ3560-114, IJ3630, IJ3730 Series, 48 Series, IJ3635-210UV, 9740i, 9760LX
Mimaki	UJV100	LUS-170	UV	SV480mC, LX480mC, IJ3635-210SV/LX, 9740i, 9760LX
Mimaki	UJV100	LUS-210	UV	SV480mC, LX480mC, IJ3635-210SV/LX, 9740i, 9760LX
Mimaki	JV400-LX Series	LX100 Latex	Latex	SV480mC, IJ3635-210UV, 8993, 9740i
Mimaki	JV400-LX Series	LX101 Latex	Latex	SV480mC, IJ3635-210UV, 8993, 9740i
Mutoh	ValueJet 1324, 1624, 1628X, 1604, 1638X, 2638X	MS31	Solvent	LX480mC, PL50mC, 40 Series, 48 Series, IJ3635-210UV, 9740i, 9760LX
Mutoh	XpertJet 1641SR, 1682SR	MS41	Solvent	LX480mC, PL50mC, 40 Series, 48 Series, IJ3635-210UV, 9740i, 9760LX

RICOH	RICOH Pro L4100	L4160	Latex	SV480mC, PL50mC, IJ3635-210UV, 8993, 9740i
RICOH	RICOH Pro L5160	AR	Latex	SV480mC, PL50mC, IJ3635-210UV, 8993, 9740i
Roland®	SOLJET EJ-640	EJ	Solvent	LX480mC, PL50mC, IJ3635-210UV, 9740i, 9760LX
Roland®	SOLJET PRO 4 XR/XF	ECO-SOL MAX 2	Solvent	LX480mC, PL50mC, IJ3635-210UV, 9740i, 9760LX
Roland®	SOLJET PRO II Series	ECO-SOL MAX	Solvent	LX480mC, PL50mC, IJ3635-210UV, 9740i, 9760LX
Roland®	SOLJET PRO III Series	ECO-SOL MAX	Solvent	LX480mC, PL50mC, IJ3635-210UV, 9740i, 9760LX
Roland®	VersaCAMM®	ECO-SOL MAX	Solvent	LX480mC, PL50mC, IJ3635-210UV, 9740i, 9760LX
*3M Graphic Films	<p>These 3M Graphic Films are included when referencing the following product series:</p> <p>IJ180 Series: IJ180mC-10, IJ180Cv3-10, IJ180C-10, IJ180-10, IJ180mC-114, IJ180mC-10LSE, IJ180mC-10SLS, IJ180mC-120 IJ3690LF Series: IJ3690LF-10, IJ3690LF-114 IJ8150 Series: IJ8150, 8150 IJ3650 Series: IJ3650-10, IJ3650-114 IJ3730 Series: IJ3730-50, IJ3730-60 8170 Series: 8170-P40, 8170-P50 40 Series: 40C-10R, 40C-20R, 40C-114R, IJ40-10, IJ40-10T, IJ40-10R, IJ40-20, IJ40-20R, 40C-10, 40C-20, IJ40-114, IJ40-124, IJ40-124R 48 Series: 48C-20R, 48-20R, 48-20, 48C-20 IJ160 Series: IJ160-10, IJ160C-10 8173 Series: 8173, 8173 for UV IJ3635 Series: IJ3635-210SV/LX, IJ3635-210UV 8900 Series: 8900-BR100, 8900-CF100 8600M Series: 8600M-401, 8600M-301</p>			
**Excluded 3M Graphics Products	The 3M Graphic Films and 3M Graphic Protection Products options listed in this column are not approved for 3M Performance Warranty coverage with the respective printer and ink platform.			
Notes	<p>With the exception of 3M branded products, 3M does not represent that any printer or printer accessory recommended in 3M Product and Instruction Bulletins will meet customer requirements, any federal, state or local regulations, or any applicable safety standards. Such determination is the responsibility of the printer owner.</p> <p>Some printer & ink platforms may not be approved for all listed 3M Graphic Films and 3M Graphic Protection Products. Refer to the 3M Performance Warranty Matrices for approved combinations of 3M Graphic Films and 3M Graphic Protection Products.</p> <p>3M requires the use of 3M Graphic Protection Products for all 3M Graphic Films covered under this warranty. Always check the 3M Product and Instruction Bulletins for additional details.</p>			
Maximum Allowable Ink Coverage	<p>3M requires the use of an appropriate printer profile with linearization to optimize the amount of ink on the 3M graphics product.</p> <p><i>The maximum total ink coverage for printers with a CMYK configuration on 3M Graphics Products are:</i></p> <ul style="list-style-type: none"> ●270% when printed with 3M approved solvent inkjet inks. ●280% when printed with 3M approved UV inkjet inks. ●280% when printed with 3M approved latex inkjet inks. ●250% when printed on the 3M reflective films and Mimaki JV5 Series printer with HS ink series <p><i>Cyan, Yellow, Magenta, Black, Light Cyan, Light Magenta, Light Black inks are in scope. Other ink colors are excluded.</i></p> <p><i>Do not exceed the maximum total ink coverage for the ink type used on 3M Graphics Products. Exceeding the maximum total ink coverage on 3M Graphics Products can result in media characteristic changes, incomplete drying, overlamine lifting, and/or poor graphic performance. For additional details about total ink coverage, refer to the 3M Product and Instruction Bulletins.</i></p>			

3M™ Performance Warranty Matrix

3M does not warrant any Finished Graphic Defects - Ink Related under the Performance Warranty. Only 3M Graphics Products listed below are covered. See the Performance Warranty Table for 3M Graphics Products exemptions with specific printer and ink combinations.

3M™ Performance Warranty - Zone 1														Release: Jan 2025			
Review the notes below the table and on the last page of this document. Product offering might vary from country to country. Local availability of selected graphics constructions should be clarified with your local 3M subsidiary.	Transportation				Exterior Signs				Interior Signs				Watercraft				
	Vehicles, Trailers, Rail, Personal recreational utility vehicles				Exterior Surface & Sign				Interior Surface & Sign				Inland and Seagoing Watercrafts				
	Good	Better	Best	Special	Good	Better	Best	Special	Good	Better	Best	Special	Good	Better	Best	Special	
IJ280	-	8/1	8/2	8/3	-	-	-	-	-	-	-	-	-	-	-	-	
LX480mC, SV480mC	6	8/1	8/2	8/3	4	5	7	7	5	8	8	8	-	3	3	-	
IJ180 Series (excl. UR), IJ175Cv3, IJ3690LF Series	6 (3yrs 9760LX)	8/1	8/2	8/3	4	5	7	7	5	8	8	8	-	3	3	-	
IJ680-10, IJ680CR-10, 780mC-10R	6 (3yrs 9760LX)	8/1	8/2	8/3	4	5	7	7	5	8	8	8	-	-	-	-	
IJ8150 Series	-	4	-	4/2	-	4	-	4	-	5	-	8	-	-	-	-	
IJ3552C	-	2	-	-	-	2	-	-	-	2	-	-	-	-	-	-	
PL50mC	-	2	2	-	-	2	2	-	-	2	2	-	-	-	-	-	
8170 Series, 8173 Series	-	1	-	-	-	2	-	-	-	5	-	-	-	-	-	-	
IJ3635 Series	-	-	-	-	-	-	6	-	-	-	5	-	-	-	-	-	
IJ3650 Series, IJ3630, IJ3730 Series	-	-	-	-	4	5	7	-	5	8	8	-	-	-	-	-	
40 Series	2	2	-	-	2	2	-	-	2	2	2	-	-	-	-	-	
IJ160 Series	2	2	-	-	2	2	-	-	2	2	-	-	-	-	-	-	
48 Series	2	-	-	-	2	-	-	-	2	-	-	-	-	-	-	-	

Graphic Protection options	Good	Better	Best	Special
IJ280	-	8428G, 8518, 8519, 8520, 8915, 8900 Series	8548G, 8549L, 8550M	8528
LX480mC, SV480mC	8993, 8995-124*	8518, 8519, 8520, 8428G, 8588G, 8590M, 8915, 8900 Series,*8600M Series	8548G, 8549L, 8550M	8528
IJ180 Series (excl. UR), IJ175Cv3, IJ3690LF Series	8418G, 8993, 8995-124*, 9740i, (9760LX)	8518, 8519, 8520, 8428G, 8588G, 8590M, 8915, 8900 Series,*8600M Series	8548G, 8549L, 8550M	8528
IJ680-10, IJ680CR-10, 780mC-10R	9740i, (9760LX)	8518, 8519, 8428G	8548G, 8549L	8528
IJ8150 Series	-	8150, 8518, 8914	-	8528
IJ3552C	-	8518, 8519, 8520, 8915	-	-
PL50mC	-	8518, 8519, 8520, 8428G	8548G, 8549L, 8550M	-
8170 Series, 8173 Series	-	8518, 8914	-	-
IJ3635 Series	-	-	3619, 3620, 3658G, 3660M	-
IJ3650 Series, IJ3630, IJ3730 Series	-	8518, 8519, 8520, 8915	3619, 3620, 3658G, 3660M	-
40C Series	8508, 8509, 8510	8518, 8519, 8520	8550M	-
IJ160 Series	9740i	8518, 8519, 8520, 8915	-	-
48 Series	8048G, 8050M	-	-	-

NOTES:

Warranty period is stated in YEARS

First number represents vertical exposure / second number non-vertical exposure warranty period of graphics. All boxes with one number only have a vertical exposure warranty period.

*For Interior Surface & Sign applications only, not warranted for other applications

Graphic Protection & Media Options:

Some printer & ink platforms may not be approved for all listed 3M Graphic Films or 3M Graphic Protection Products. 3M recommends graphic protection for all graphics. Before selecting a 3M Graphic Product, find the best combination of protection and film for your graphic application including conformability, gloss, adhesion to substrate and other attributes by reviewing 3M Product and Instruction Bulletins.

3M™ Performance Warranty Matrix

3M does not warrant any Finished Graphic Defects - Ink Related under the Performance Warranty. Only 3M Graphics Products listed below are covered. See the Performance Warranty Table for 3M Graphics Products exemptions with specific printer and ink combinations.

3M™ Performance Warranty - Zone 2														Release: Jan 2025			
Review the notes below the table and on the last page of this document. Product offering might vary from country to country. Local availability of selected graphics constructions should be clarified with your local 3M subsidiary.	Transportation				Exterior Signs				Interior Signs				Watercraft				
	Vehicles, Trailers, Rail, Personal recreational utility vehicles				Exterior Surface & Sign				Interior Surface & Sign				Inland and Seagoing Watercrafts				
	Good	Better	Best	Special	Good	Better	Best	Special	Good	Better	Best	Special	Good	Better	Best	Special	
IJ280	-	7/1	7/2	7/3	-	-	-	-	-	-	-	-	-	-	-	-	
LX480mC, SV480mC	5	7/1	7/2	7/3	3	4	6	6	5	8	8	8	-	2	2	-	
IJ180 Series (excl. UR), IJ175Cv3, IJ3690LF Series	5 (2yrs 9760LX)	7/1	7/2	7/3	3	4	6	6	5	8	8	8	-	2	2	-	
IJ680-10, IJ680CR-10, 780mC-10R	5 (2yrs 9760LX)	7/1	7/2	7/3	3	4	6	6	5	8	8	8	-	-	-	-	
IJ8150 Series	-	3	-	3/1	-	3	-	3	-	5	-	8	-	-	-	-	
IJ3552C	-	2	-	-	-	2	-	-	-	2	-	-	-	-	-	-	
PL50mC	-	2	2	-	-	2	2	-	-	2	2	-	-	-	-	-	
8170 Series, 8173 Series	-	1	-	-	-	2	-	-	-	5	-	-	-	-	-	-	
IJ3635 Series	-	-	-	-	-	-	5	-	-	-	5	-	-	-	-	-	
IJ3650 Series, IJ3630, IJ3730 Series	-	-	-	-	3	4	6	-	5	8	8	-	-	-	-	-	
40 Series	2	2	-	-	2	2	-	-	2	2	2	-	-	-	-	-	
IJ160 Series	2	2	-	-	2	2	-	-	2	2	-	-	-	-	-	-	
48 Series	2	-	-	-	2	-	-	-	2	-	-	-	-	-	-	-	

Graphic Protection options	Good	Better	Best	Special
IJ280	-	8428G, 8518, 8519, 8520, 8915, 8900 Series	8548G, 8549L, 8550M	8528
LX480mC, SV480mC	8993, 8995-124*	8518, 8519, 8520, 8428G, 8588G, 8590M, 8915, 8900 Series,*8600M Series	8548G, 8549L, 8550M	8528
IJ180 Series (excl. UR), IJ175Cv3, IJ3690LF Series	8418G, 8993, 8995-124*, 9740i, (9760LX)	8518, 8519, 8520, 8428G, 8588G, 8590M, 8915, 8900 Series,*8600M Series	8548G, 8549L, 8550M	8528
IJ680-10, IJ680CR-10, 780mC-10R	9740i, (9760LX)	8518, 8519, 8428G	8548G, 8549L	8528
IJ8150 Series	-	8150, 8518, 8914	-	8528
IJ3552C	-	8518, 8519, 8520, 8915	-	-
PL50mC	-	8518, 8519, 8520, 8428G	8548G, 8549L, 8550M	-
8170 Series, 8173 Series	-	8518, 8914	-	-
IJ3635 Series	-	-	3619, 3620, 3658G, 3660M	-
IJ3650 Series, IJ3630, IJ3730 Series	-	8518, 8519, 8520, 8915	3619, 3620, 3658G, 3660M	-
40 Series	8508, 8509, 8510	8518, 8519, 8520	8550M	-
IJ160 Series	9740i	8518, 8519, 8520, 8915	-	-
48 Series	8048G, 8050M	-	-	-

NOTES:

Warranty period is stated in YEARS

First number represents vertical exposure / second number non-vertical exposure warranty period of graphics. All boxes with one number only have a vertical exposure warranty period.

*For Interior Surface & Sign applications only, not warranted for other applications

Graphic Protection & Media Options:

Some printer & ink platforms may not be approved for all listed 3M Graphic Films or 3M Graphic Protection Products. 3M recommends graphic protection for all graphics. Before selecting a 3M Graphic Product, find the best combination of protection and film for your graphic application including conformability, gloss, adhesion to substrate and other attributes by reviewing 3M Product and Instruction Bulletins.

3M™ Performance Warranty Matrix

3M does not warrant any Finished Graphic Defects - Ink Related under the Performance Warranty. Only 3M Graphics Products listed below are covered. See the Performance Warranty Table for 3M Graphics Products exemptions with specific printer and ink combinations.

3M™ Performance Warranty - Zone 3														Release: Jan 2025			
Review the notes below the table and on the last page of this document. Product offering might vary from country to country. Local availability of selected graphics constructions should be clarified with your local 3M subsidiary.	Transportation				Exterior Signs				Interior Signs				Watercraft				
	Vehicles, Trailers, Rail, Personal recreational utility vehicles				Exterior Surface & Sign				Interior Surface & Sign				Inland and Seagoing Watercrafts				
	Good	Better	Best	Special	Good	Better	Best	Special	Good	Better	Best	Special	Good	Better	Best	Special	
IJ280	-	5	5/1.5	5/2	-	-	-	-	-	-	-	-	-	-	-	-	
LX480mC, SV480mC	3	5	5/1.5	5/2	2	3	4	4	5	8	8	8	-	1	1	-	
IJ180 Series (excl. UR), IJ175Cv3, IJ369OLF Series	3 (1yr 9760LX)	5	5/1.5	5/2	2	3	4	4	5	8	8	8	-	1	1	-	
IJ680-10, IJ680CR-10, 780mC-10R	3 (1yr 9760LX)	5	5/1.5	5/2	2	3	4	4	5	8	8	8	-	-	-	-	
IJ8150 Series	-	2	-	2	-	2	-	2	-	5	-	8	-	-	-	-	
IJ3552C	-	2	-	-	-	2	-	-	-	2	-	-	-	-	-	-	
PL50mC	-	2	2	-	-	2	2	-	-	2	2	-	-	-	-	-	
8170 Series, 8173 Series	-	1	-	-	-	1	-	-	-	5	-	-	-	-	-	-	
IJ3635 Series	-	-	-	-	-	-	4	-	-	-	5	-	-	-	-	-	
IJ3650 Series, IJ3630, IJ3730 Series	-	-	-	-	2	3	4	-	5	8	8	-	-	-	-	-	
40 Series	2	2	-	-	2	2	-	-	2	2	2	-	-	-	-	-	
IJ160 Series	2	2	-	-	2	2	-	-	2	2	-	-	-	-	-	-	
48 Series	2	-	-	-	2	-	-	-	2	-	-	-	-	-	-	-	

Graphic Protection options	Good	Better	Best	Special
IJ280	-	8428G, 8518, 8519, 8520, 8915, 8900 Series	8548G, 8549L, 8550M	8528
LX480mC, SV480mC	8993, 8995-124*	8518, 8519, 8520, 8428G, 8588G, 8590M, 8915, 8900 Series,*8600M Series	8548G, 8549L, 8550M	8528
IJ180 Series (excl. UR), IJ175Cv3, IJ369OLF Series	8418G, 8993, 8995-124*, 9740i, (9760LX)	8518, 8519, 8520, 8428G, 8588G, 8590M, 8915, 8900 Series,*8600M Series	8548G, 8549L, 8550M	8528
IJ680-10, IJ680CR-10, 780mC-10R	9740i, (9760LX)	8518, 8519, 8428G	8548G, 8549L	8528
IJ8150 Series	-	8150, 8518, 8914	-	8528
IJ3552C	-	8518, 8519, 8520, 8915	-	-
PL50mC	-	8518, 8519, 8520, 8428G	8548G, 8549L, 8550M	-
8170 Series, 8173 Series	-	8518, 8914	-	-
IJ3635 Series	-	-	3619, 3620, 3658G, 3660M	-
IJ3650 Series, IJ3630, IJ3730 Series	-	8518, 8519, 8520, 8915	3619, 3620, 3658G, 3660M	-
40 Series	8508, 8509, 8510	8518, 8519, 8520	8550M	-
IJ160 Series	9740i	8518, 8519, 8520, 8915	-	-
48 Series	8048G, 8050M	-	-	-

NOTES:

Warranty period is stated in YEARS

First number represents vertical exposure / second number non-vertical exposure warranty period of graphics. All boxes with one number only have a vertical exposure warranty period.

*For Interior Surface & Sign applications only, not warranted for other applications

Graphic Protection & Media Options:

Some printer & ink platforms may not be approved for all listed 3M Graphic Films or 3M Graphic Protection Products. 3M recommends graphic protection for all graphics. Before selecting a 3M Graphic Product, find the best combination of protection and film for your graphic application including conformability, gloss, adhesion to substrate and other attributes by reviewing 3M Product and Instruction Bulletins.

[Geographic Zones](#)

Zone 1:

Austria, Belarus, Belgium, Bosnia, Croatia, Czech Republic, Denmark, Estonia, Finland, France (except Corsica), Germany, Greenland, Hungary, Iceland, Ireland, Italy (north of Rome), Kazakhstan, Latvia, Liechtenstein, Lithuania, Luxembourg, Moldova, Mongolia, Montenegro, Netherlands, Norway, Poland, Romania, Serbia, Slovakia, Slovenia, Sweden, Switzerland, UK, Ukraine (except Crimea region)

Zone 2:

Albania, Armenia, Australia (south of Brisbane - Perth line), Azerbaijan, Benin, Brunei, Bulgaria, Burundi, Cambodia, Canada, Central African Republic, China, Congo, Crete, Cuba, Djibouti, Fiji, France (Corsica), Gabon, Georgia, Ghana, Gibraltar, Greece (except Crete), Guam, Guinea-Bissau, Hong Kong, Indonesia, Italy (south of Rome and Sardinia), Ivory Coast, Kenya, Kyrgyzstan, Laos, Lesotho, Liberia, Macedonia, Malawi, Malaysia, Malta, Marshall Islands, Mozambique, New Caledonia, New Zealand, Nigeria, North Vietnam, Papua New Guinea, Philippines, Portugal, Rwanda, Sierra Leone, Singapore, Solomon Islands, Somalia, South Africa (except of Kalahari desert and Namib dessert area), South Korea, South Vietnam, Spain (except Canary Islands), Sumatra, Taiwan, Tajikistan, Tanzania, Tasmania, Thailand, Togo, Tonga, Turkey, Turkmenistan, Tuvalu, Uganda, USA (except desert south west area), Uzbekistan, Zaire

Zone 3:


Afghanistan, Algeria, Angola, Antigua, Argentina (except Gran Chaco area), Aruba, Australia (north of Brisbane - Perth line), Bahamas, Bahrain, Bangladesh, Barbados, Barbuda, Belize, Bhutan, Bolivia, Botswana, Brazil, Burkina, Cameroon, Cayman Islands, Chad, Chile (except Atacama area), Colombia, Costa Rica, Curacao, Cyprus, Dominica, Dominican Republic, Dubai, Ecuador, Egypt, El Salvador, Equatorial Guinea, Eritrea, Ethiopia, Gambia, Greece (Crete), Guatemala, Guinea, Guyana, Haiti, Honduras, India, Iraq, Israel, Jamaica, Jordan, Kuwait, Lebanon, Libya, Madagascar, Maldives, Mali, Mauritania, Mauritius, México (except Sonora, Chihuahua, Baja California, Sur y Baja California area), Morocco, Myanmar, Namibia, Nepal, Netherland Antilles, Nicaragua, Niger, Oman, Pakistan, Panamá, Paraguay, Perú, Puerto Rico, Qatar, Sao Tome & Principe, Saudi Arabia, Senegal, Spain (Canary Islands), Sri Lanka, St. Martin, Sudan, Surinam, Swaziland, Trinidad and Tobago, Tunisia, United Arabic Emirates, Uruguay, USA (desert south west area), Venezuela, Virgin Islands, Western Sahara, Yemen, Zambia, Zimbabwe

[USA \(desert south west area\)](#)

Definitions

"Application(s)" is defined as an end-use application identified in the Warranty Matrices that defines warranty coverage including, but not limited to: i) "Interior Signs" (stationary graphics located indoors and not exposed to the elements); ii) "Exterior Signs" (stationary graphics located outdoors and exposed to the elements); iii) "Watercraft" (non-regulated, exterior surfaces on boats with an application above the water line; iv) "Transportation" (a) Rail (freight and passenger rail cars and locomotives); (b) Vehicles (buses, vans, passenger vehicles, delivery trucks, pickup trucks, straight trucks, and semi-tractors); (c) Trailers (semi-trailers, enclosed trailers and tankers used for commercial business purposes excluding air shields and soft-sided trailers); and (d) Personal recreational utility vehicles (snowmobiles, ATVs, UTVs, motorcycles, golf carts); v) OEM Graphics (OEM labels and decorative graphics produced for and used by original equipment manufacturers).

"Exposure" is defined by angle: a) vertical exposures (face of graphic is less than 15° from vertical) and b) non-vertical exposures (face of graphic is greater than 15° from vertical) and by location (global geographic zones). Angles and locations are described and located in the Warranty Matrices and in the Global Geographic Zones Map. Note that the Global Geographic Zones are based on a variety of environmental conditions.



Warranty and Limited Liability

Refer to the 3M Graphics Products Warranty Bulletin for complete information on warranty coverage under the 3M™ Basic Product Warranty and potential coverage under the 3M™ Performance Warranty and 3M™ MCS™ Warranty. Warranty coverage, warranty periods and warranty terms vary including, but not limited to, variations based on approved combinations of 3M Graphics Products, MCS Warranty Inks, Printers, Exposures, and Applications. Except for the limited remedies stated in the Warranty Bulletin and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract,