



PROTECTA

Fall Protection



3M™ Protecta® Comfort Belt Style
Fall Arrest Suspension Harness

**Designed to offer workers comfort
and versatility in rope access
and suspension work applications.**

The new generation of 3M™ Protecta® Fall Arrest harnesses has been further expanded to include a suspension model. Designed specifically to offer rope access and suspension workers comfort, reliability and versatility.

More comfort:


1. Extra large, comfortable, lightweight and breathable shoulder and back pads
2. Softer and more durable hip padding for extra comfort
3. Removable leg pads
4. Water and stain-resistant webbing
5. No sharp edges on the webbing
6. Double adjustment of leg straps (size and height) ensures perfect positioning during suspension

Easier donning and increased safety:

7. Large stand up rear fall arrest D-ring for easier reach
8. Large cranked suspension D-ring for easier connection
9. Twist-lock carabiner for safer, automatic connection between lower and upper part of the harness
10. Front and back impact indicators make it simple to inspect the harness for damage and help ensure it's safe to use
11. Front fall arrest D-ring for additional fall arrest connection options
12. Shoulder adjustment buckle
13. 2 x large cranked work positioning D-rings on belt
14. Quick-connect buckles on leg straps for quick closure

Designed to meet your tool and equipment carrying needs:

15. 2 x auto-resetting lanyard keepers provide easy parking and release of snap hooks and carabiners
16. 4 x gear tool loops to store and secure several tools



| Size | Reference |
|--------------------|-----------|
| Small (S) | 1161764 |
| Medium/Large (M/L) | 1161765 |
| Extra Large (XL) | 1161766 |

Specifications:

| | |
|-------------------------------|---|
| Webbing: | 45mm polyester – water and dirt-resistant |
| Thread: | Polyester |
| Buckles: | Quick connect buckles and pass through buckles. Steel, zinc-plated, black electro-deposition paint |
| Adjustments: | Torso, waist, legs (diameter and height) |
| Attachment D-rings: | Steel, zinc plated, black electro-deposition paint |
| Operating temperature: | -35°C to +57°C |
| Weight capacity: | 140kg |
| Weight: | 2.65kg (M/L size model) |
| Standards: | CE EN 361:2002 (Full body fall arrest harness) CE EN 358:2018 (Work positioning harness) CE EN 813:2008 (Sit harness) |

Important notice

The mounting and use of the product described within this document assumes that the user has previous experience of this type of product and that it will be assembled by a competent professional according to product documentation. Before using this product, 3M recommends that the user completes some trials to validate the performance of the product for the application intended by the user.

All information and specification details contained within this document are specific to this particular 3M product and cannot be applied to other products or environments. Any action or use of this product in violation of this document is at the risk of the user.

Compliance with the information and specifications regarding the particular product described in this document does not exempt the user from compliance with additional guidelines (e.g., safety rules, procedures). Compliance with operational requirements especially in respect to the environment and usage of tools with this product must be observed. 3M is not responsible for the consequences of any violation of these rules which are beyond its decision and control.

Warranty provisions are provided with the sales contract documents consistent with applicable law.

3M Fall Protection

Capital Safety (Northern Europe) Limited

3M Centre, Cain Road
Bracknell, Berkshire, RG12 8HT, UK

Phone: +33(0)4 83 58 08 08 Email: informationfallprotection@mmm.com Web: 3M.com/FallProtection

Capital Safety Group (EMEA)

Le Broc Center, Bâtiment A, Z.1. 1re Avenue – BP15
06511 Carros Le Broc, Cedex, FRANCE



Fall Protection