



Automotive Aftermarket Division

3M™ Perforated Trim Masking Tape

1) Part Numbers

06345	5 mm Hard Band, 50.8 mm x 10 m
06347	7 mm Hard Band, 50.8 mm x 10 m
06349	10 mm Hard Band, 50.8 mm x 10 m
06348	15 mm Hard Band, 50.8 mm x 10 m

2) Description and end uses

3M™ Trim Masking Tapes are special purpose automotive masking tapes, designed to lift and protect the rubber moulding from overspray. These mouldings found around the glass on modern vehicles with direct bonded windows, can be difficult and costly to remove.

The design of 3M™ Trim Masking Tape eliminates the need to remove the glass enabling the perfect finish.

3) Physical Properties

Thickness	:	0.12 mm	AFERA 4006
	:	0.260 mm	AFERA 4006
Adhesion to steel	:	13N/25 mm	AFERA 4001
Temperature performance	:	120°C	

4) Directions for Use

1. Make sure the area to be masked with the trim masking tape is clean, dry and free from any contaminates.
2. Feed the first length between the paint and the moulding using the clear plastic strip as the leading edge. Ensure the release paper is facing the glass.
3. Keep inserting to all of the plastic strip is behind the moulding, carefully remove the liner paper from the product taking care not to pull the strip back out again.
4. Gently pull the blue plastic backing towards the glass to generate a gap between the paint work and the moulding.



Technical Data Sheet

Effective: 08/04/2020 Supersedes: NEW

5. Once a small gap can be seen between the paint and the moulding, stick the adhesive face onto the glass to hold in place.
6. Using the gap generated by the first strip of TMT, insert the next strip behind the first sliding it along the aperture until it just overlaps the first strip by 2-3mm.
7. Repeat step 6 until the required area is masked.

Tip: To help to identify the appropriate size that is best suited to the job, put a short length (approx. 50 mm) from each roll size and insert behind the rubber.

5) Storage

Store in clean dry place. Temperature of 21°C and 50 percent relative humidity are recommended.

6) Safety

1. When using solvents etc. for cleaning the surface prior to the application of the Trim masking tape, care must be taken to avoid contact with the skin and eyes. The correct PPE must be worn at all times.
2. After removing the TMT from the vehicle, as it may now be contaminated with paint waste it should be disposed of in accordance to local authority / country legislation.

3M™ Perforated Trim Masking Tape is designed FOR PROFESSIONAL USE ONLY

7) Disclaimer

All statements, technical information and recommendations are based on tests we believe to be reliable as at the date of hereof, but the accuracy or completeness thereof is not guaranteed. Please ensure before using the product that it is suitable for your intended use. Since the conditions and methods of use of the product and of the information referred to herein are beyond our control, other than for fraudulent misrepresentation, 3M expressly disclaims any and all liability as to any results obtained or arising from any use of the product or reliance on such information.



Technical Data Sheet

Effective: 08/04/2020 Supersedes: NEW

For Additional Health and Safety Information

3M South Africa & Sub-Saharan Africa, 146A Kelvin Drive, Woodmead, Sandton, South Africa, Tel: (0861) 225536
3M (East) AG Representation Office Tirane, Rruga Sami Frasheri, Pallati i Ri Perxhola Kati 2 Ap2, 1000 Albania
3M Arabia, LLC, Building 24-25 3M Saudi Arabia Zone C, Business Gate, Airport Road, Riyadh, Saudi Arabia
3M Bulgaria, Mladost 4, Business Park, bl.4, 2nd floor, Sofia 1766, Bulgaria
3M Česko, spol. s r.o., V Parku 2343/24, 148 00 - Praha 4, Czech Republic
3M (East) AG, Branch office Croatia, Avenija Većeslava Holjevca 40, 10 000 Zagreb, Croatia, Tel: +385 1 2499750, www.3m.com.hr
3M Egypt, Finance Center , New Cairo , Plot 140 , Banking Sector , 5th settlement , Cairo , Egypt
3M Hellas MEPE, Automotive Aftermarket Division, 20 Kifisias Avenue, 151 25 Marousi, Greece, Phone: +30 210 68 85 300, innovation.gr@mmm.com, www.3M.gr
3M Hungária Kft, Neumann János u. 1/E, 1117 Budapest, Hungary
3M Israel, 91 Medinat Hayehudim St., Herzliya, Israel
3M Kenya Ltd, Victoria Towers, 3rd Floor, Kilimanjaro Av, Upperhill, Kenya
3M Gulf Limited, Ein El Mreisseh, Saint Charles City Center, 4th. Floor, P.O.Box: 11-5025, Riad el Solh, Beirut 1107 2180 Lebanon
3M Minnesota Mining & Manufacturing Nigeria Limited, No 2 Sheraton Opebi Link Road, Ikeja, Lagos Nigeria
3M Pakistan, Islamic Chamber of Commerce Building, ST-2/A, Block 9, KDA Scheme 5, Clifton, Karachi, Pakistan
3M Poland, Al. Katowicka 117, Kajetany, 05-830 Nadarzyn, Poland, Telefon: +48 22 739 60 00, www.3m.pl/kontakt
3M Gulf (Representation Office), Suhaim Bin Hamad St., Al Mana Towers Tower B, 2nd Floor, Office No.4, Doha Qatar, P.O.Box 14685
3M Romania, 12 Meneuțului St., Bucharest Business Park, Building D, District 1 013713 Bucharest, Romania
3M (East) AG, Representation Office Serbia, Airport City, Omladinskih brigada 90B, 11070 Belgrade, Serbia, Tel: +381 11 2209 400, www.3m.co.rs/3M/sr_RS/3m-south-east-europe/
3M Slovensko s.r.o., Polus Tower 2, Vajnorská 100/B, 83104 Bratislava
3M (East) AG, Branch office Slovenia, Cesta v Gorice 8, 1000, Ljubljana, Slovenia, Tel: +386 1 2003 630, www.3m.com/3M/sl_SI/3m-south-east-europe/
3M Sanayi ve Ticaret As, Barbaros Mah., Mor Sümbül Sok., No:7/3F, 27-51, Nidakule Ataşehir Güney, 34746 Ataşehir, İstanbul, Turkey
3M Gulf Limited, Dubai Internet City, Building No. 11, 3rd Floor, U.A.E

© 3M 2020. 3M is a trademark of the 3M company. All rights reserved