

Choose
your
features.



G5-03 E



G5-03 Pro



G5-02



G5-03 Pro Air



G5-01



9100 MP



M-407SG /
M-409SG

Welding filter options	G5VC, G5TW, G5NC, G5 Passive		G5-02	G5VC, G5TW, G5NC, G5 Passive		9100XXi, 9100 X, 9100 Passive	
Supports powered or supplied air				●	●	●	●
Approx. weight	500 g (1.10 lb)****	615 g (1.36 lb)***	535 g (1.18 lb)	865 g (1.91 lb)***	1000 g (2.20 lb)***	1209 g (2.67 lb)*****	M-407SG 1744 g (3.84 lb)***** M-409SG 2094 g (4.62 lb)*****
Side windows — shade 5 filters that widen your field of vision		●		●		●	●
High-comfort Speedglas™ headband with smooth ratchet for precise tightening		●		●	●		
Flip-up with clear visor					●	●	●
Eye and face protection — Welding helmet, welding filter and protection plates	ANSI Z87.1+ CSA Z94.3		ANSI Z87.1	ANSI Z87.1+ CSA Z94.3			ANSI Z87.1+
Head protection		Hard Hat adapters for H-700 Series and X5000 Series				ANSI Z89.1 Type 1, Class G	ANSI Z89.1 Type 1, Class G
Scrape Guard Compatible		●		●	●		
Respiratory protection	3M disposable or reusable respirators	3M disposable or reusable respirators	3M disposable or reusable respirators	APF 25 / APF 1000*	APF 25 / APF 1000*	APF 25 / APF 1000*	APF 1000
Powered and Supplied Air Solutions							
3M™ Adflo™ Air Purifying Respirator (PAPR)				●	●	●	●
3M™ Versaflo™ TR-300+ PAPR				●	●	●	●
3M™ Versaflo™ TR-600 PAPR				●	●	●	●
3M™ Versaflo™ TR-800 PAPR							●**
3M™ Versaflo™ V-Series Supplied Air Valves				●	●	●	●
Reusable Respirators							
3M™ Rugged Comfort Half Facepiece Reusable Respirator 6500QL/6500 Facepieces	●	●	●				
3M™ Advanced Particulate Filter, 2297, P100	●	●	●				
3M™ Particulate Filter, 2097, P100	●	●	●				
3M™ Hydrogen Fluoride Cartridge/Filter, 7093C, P100	●	●	●				
Disposable Respirators							
3M™ Particulate Respirator, 8214, N95	●	●	●				
3M™ Particulate Welding Respirator, 8212, N95	●	●	●				
3M™ Particulate Respirator, 8514, N95	●	●	●				
3M™ Particulate Welding Respirator, 8515, N95	●	●	●				
Earmuffs							
3M™ PELTOR™ Welding Earmuff, H505B	●	●	●	●	●		●
3M™ PELTOR™ Earmuff Assembly, M-985						●	
Earplugs							
3M™ E-A-R™ Classic Earplugs	●	●	●	●	●	●	●
3M™ E-A-R™ Ultrafit™ Earplugs	●	●	●	●	●	●	●
Communications							
3M™ PELTOR™ Electronic Earplugs EEP-100	●	●	●	●	●	●	●

*Requires additional shroud. See User Instructions for additional information.
**ADF is not intrinsically safe.
***With G5TW ADF
****With G5NC ADF
*****With 9100 XXi ADF