



PELTOR™
Protection & Communication

Communicate from a distance.



Need to clearly communicate from a distance? 3M™ PELTOR™ Two-way Radio and Bluetooth Headsets help workers clearly communicate in noisy environments.

Featuring:

- Hearing protection to help protect against hazardous noise
- Environmental microphones that help workers hear their surroundings without removing their hearing protection.
- Waterproof noise-cancelling speech microphone that enables clear speech transmission in noisy environments.



3M™ PELTOR™ WS™ LiteCom Pro III Headset, Navy Blue, Headband: MT73H7A4D10NA



WS ProTac XPI: MT15H7AWS6

3M™ PELTOR™ WS LiteCom Pro III Headset

With built-in analog and digital programmable two-way communication radio, level-dependent hearing protection, Bluetooth® functionality and a jack to connect to external devices.

- Integrated two-way radio
- Noise-cancelling waterproof speech mic
- Hands-free voice-operated transmission
- Environmental Listening Technology

3M™ PELTOR™ WS™ ProTac XPI Headsets

Featuring Bluetooth® wireless communication, the 3M™ PELTOR™ WS™ ProTac XPI Series Headsets allow you to connect to your smart device and have clear, hands-free conversations in noisy environments.

- Bluetooth® technology
- Noise-cancelling speech mic
- Environmental Listening Technology

A full range of accessories is available to help keep your equipment clean!



Mic Tape: HYM1000



Hygiene Kit: HY83



Hygiene pads: HY100A

Learn more by talking to a 3M Hearing & Communication Specialist. Visit <https://engage.3m.com/PELTORHeadsets> for more information.

3M PSD products are occupational use only.

Note: U.S. EPA specifies the NRR as the measure of hearing protector noise reduction. However, 3M makes no warranties as to the suitability of the NRR for this purpose. 3M strongly recommends personal fit testing of hearing protectors. Research suggests that users may receive less noise reduction than indicated by the attenuation label value(s) on the packaging due to variation in fit, fitting skill, and motivation of the user. Refer to applicable regulations for guidance on how to adjust attenuation label values. It is recommended that the NRR be reduced by 50% to better estimate typical protection.



3M Personal Safety Division
3M Center,
Building 235-2NW-70 St. Paul,
MN 55144-1000, 3M.com/Peltor

For more Information:
Technical Service 1-800-665-2942
Customer Service 1-800-328-1667

Always read and follow User Instructions.

© 3M 2020. All rights reserved. 3M, PELTOR, and all other trademarks used herein or hereon are trademarks of 3M Company, used under license in Canada. The Bluetooth wordmark and logos are registered trademarks owned by Bluetooth SIG, Inc. Please recycle. Printed in the U.S.A.