



Safety backed by science.

3M[™] SecureFit[™] Safety Glasses 3M[™] SecureFit[™] Safety Glasses



Performance. Style. Comfort.

3M[™] SecureFit[™] Safety Glasses

Protecting your vision on the job is important. But it doesn't have to mean sacrificing style or comfort. Get eyewear that performs and looks good doing it. Featuring a comfortable fit and a sleek profile designed to work with other personal protective equipment, 3M[™] SecureFit[™] Safety Glasses helps keep you safe and comfortable on the job.



3M[™] SecureFit[™] Safety Glasses









We collected data on head and face shapes around the world to develop a patented design that self-adjusts to individual head sizes and shapes. This design provides the same level of comfort to individuals across a diverse workforce.

Regardless of head size, from small heads to large heads, our 3M[™] SecureFit[™] Pressure Diffusion Temple Technology is designed to provide a secure and comfortable fit for an extended period of wear time.



The science of comfort.









Designed to perform.

Curved temples for enhanced security

Our design applies pressure on the less sensitive back of the head instead of the side of the head, achieving a comfortable fit even during rapid head movement.

3M[™] Pressure Diffusion Temple Technology

3M's innovative temple design features slotted ribs that provide comfortable pressure equalisation, allowing the temples to flex and self-adjust to the size and shape of the wearer's head.

The benefits are clear.

Fogged lenses can be frustrating and dangerous. But 3M[™] SecureFit[™] Safety Glasses models featuring 3M[™] Scotchgard[™] Protector Anti-Fog/Anti-Scratch Coating can help workers see clearly for longer, thanks to an active ingredient that bonds the coating to the lens.





3M[™] Scotchgard[™] Protector Anti-Fog/Anti-Scratch Coating

- Resists fogging longer than traditional anti-fog coatings through up to 25 washings with water.*
- Helps provide scratch resistance in tough work environments.
- Designed for working in challenging situations, such as hot and humid conditions, indoor/outdoor work, physically demanding tasks and climate-controlled areas.



*Based on 3M internal testing per EN168 test method when compared with traditional anti-fog coatings.

3M[™] SecureFit[™]

Family of Safety Glasses

There's a lot of variety to choose from in the 3M[™] SecureFit[™] family, all with the comfort, safety and style your workforce demands.

Find the series with the right mix of features and value for you.





Lightweight comfort at an affordable price.

500 Series

The right fit changes everything. 3M[™] SecureFit[™] 200 Safety Glasses feature temples that automatically self-adjust to help provide a secure, comfortable fit every time.



500 series





Product ID: SF201AS/AF Lens: Clear Frame: Clear Coating: Anti-Scratch/Anti-Fog





Product ID: SF202AS/AF Lens: Grey Frame: Grey Coating: Anti-Scratch/Anti-Fog



Product ID: SF203AS/AF Lens: Amber Frame: Amber Coating: Anti-Scratch/Anti-Fog



Product ID: SF201SGAF-BLU Lens: Clear Frame: Blue Coating: Scotchgard[™] Anti-Fog/Anti-Scratch

Available products

| Product I.D. | 3M I.D. | Description | Frame colour | Lens colour | Coating | Each/ case |
|---------------|-------------|--|-----------------|----------------|---------|---------------|
| SF201AS/AF | 70071695517 | 3M [™] SecureFit [™] 200 Safety Glasses, Clear frame, Anti-Scratch/Anti-Fog, Clear Lens | | Clear | AS/AF | 20 |
| SF201AS | 70071695541 | 3M™ SecureFit™ 200 Safety Glasses, Clear frame, Anti-Scratch, Clear Lens | Clear | Clear | AS | 20 |
| SF202AS/AF | 70071695525 | 3M [™] SecureFit [™] 200 Safety Glasses, Grey frame, Anti-Scratch/Anti-Fog, Grey Lens | Grey | Grey | AS/AF | 20 |
| SF203AS/AF | 70071695533 | 3M™ SecureFit™ 200 Safety Glasses, Amber frame, Anti-Scratch/Anti-Fog, Amber Lens | Amber | Amber | AS/AF | 20 |
| SF201SGAF-BLU | XA006509021 | 3M™ SecureFit™ 200 Safety Glasses, Blue frame, Scotchgard™ Anti-Fog/Anti-Scratch Coating (K&N), Clear Lens | Blue | Clear | SGAF | 20 |



Enhanced comfort and sleek design available in a variety of contemporary colours.

Take the next step in comfort with 3M[™] SecureFit[™] 400 Safety Glasses, featuring 3M[™] Pressure Diffusion Temple Technology, a soft one-piece nose bridge, dual-injected temples and a range of options, including lens colours, premium coatings, readers and more.





Product ID: SF401AS/AF Lens: Clear Frame: Green/Black Coating: Anti-Scratch/Anti-Fog



Product ID: SF402AS/AF Lens: Grey Frame: Green/Black Coating: Anti-Scratch/Anti-Fog



Product ID: SF403AS/AF Lens: Yellow Frame: Green/Black Coating: Anti-Scratch/Anti-Fog



Product ID: SF408AS Lens: Blue Mirror Frame: Green/Black Coating: Anti-Scratch



Product ID: SF400FI Foam Insert



Product ID: SF410AS Lens: Indoor/Outdoor Mirror Frame: Green/Black Coating: Anti-Scratch



Product ID: SF415AS/AF Lens: Clear Readers +1.5 Frame: Green/Black Coating: Anti-Scratch/Anti-Fog



Product ID: SF420AS/AF Lens: Clear Readers +2.0 Frame: Green/Black Coating: Anti-Scratch/Anti-Fog



Product ID: SF425AS/AF Lens: Clear Readers +2.5 Frame: Green/Black Coating: Anti-Scratch/Anti-Fog



Product ID: RX-SF400 RX Prescription Insert

3M[™] SecureFit[™] Safety Glasses

400 series

with 3M[™] Scotchgard[™] Protector Anti-Fog/Anti-Scratch Coating Advanced coating technology for premium performance.



Product ID: SF401SGAF-BLU Lens: Clear Frame: Blue/Grey Coating: Scotchgard" Anti-Fog/ Anti-Scratch



Product ID: SF401SGAF-BLU-F Lens: Clear w/ Foam Gasket Frame: Blue/Grey Coating: Scotchgard[®] Anti-Fog/ Anti-Scratch



Product ID: SF401SGAF-RED Lens: Clear Frame: Red/Grey Coating: Scotchgard" Anti-Fog/ Anti-Scratch



Product ID: SF405SGAF-BLA Lens: Brown Frame: Brown/Black Coating: Scotchgard" Anti-Fog/ Anti-Scratch



Product ID: SF406SGAF-BLA Lens: Orange Frame: Brown/Black Coating: Scotchgard[™] Anti-Fog/ Anti-Scratch



Product ID: SF407SGAF-BLU Lens: Indoor/Outdoor Grey Frame: Blue/Grey Coating: Scotchgard[™] Anti-Fog/ Anti-Scratch



Product ID: SF402SGAF-BLU Lens: Grey Frame: Blue/Grey Coating: Scotchgard" Anti-Fog/ Anti-Scratch



Product ID: SF403SGAF-YEL Lens: Amber Frame: Yellow/Black Coating: Scotchgard[™] Anti-Fog/ Anti-Scratch

400 X $\frac{1}{2}$

with Brow Guard

Helps provide additional coverage from particles.



Product ID: SF401XRAS-GRN Lens: Clear Frame: Green/Black Coating: Rugged Anti-Scratch

Lens: Amber

Anti-Scratch

Frame: Yellow/Black



Product ID: SF401XSGAF-BLU Lens: Clear Frame: Blue/Grey Coating: Scotchgard[™] Anti-Fog/ Anti-Scratch



Product ID: SF403XSGAF-YEL Product ID: SF407XSGAF-BLU Lens: Indoor/Outdoor Grey Frame: Blue/Grey Coating: Scotchgard[™] Anti-Fog/ Coating: Scotchgard[™] Anti-Fog/ Anti-Scratch



Product ID: SF401XSGAF-GRN Lens: Clear Frame: Hi-Vis Green/Clear Coating: Scotchgard[™] Anti-Fog/ Anti-Scratch



Product ID: SF416XAS-BLK Lens: Orange Mirror Frame: Grey/Black Coating: Anti-Scratch



Product ID: SF402XSGAF-BLU Lens: Grey Frame: Blue/Grey Coating: Scotchgard[™] Anti-Fog/ Anti-Scratch



Product ID: SF422XSGAF-BLK Lens: Vermillion Frame: Black/Black Coating: Scotchgard[™] Anti-Fog/ Anti-Scratch

Available products

400 series

| Product I.D. | 3M I.D. | Description | Frame colour | Lens colour | Coating | Each/case |
|-----------------|-------------|---|--------------|--------------------------|---------|-----------|
| SF400FI | 70071695343 | 3M [™] SecureFit [™] 400 Foam Insert n | | n/a | n/a | 5 |
| RX-SF400 | 70071731734 | 3M [™] SecureFit [™] 400 Prescription Insert | n/a | n/a | n/a | 10 |
| SF401AS/AF | UU003704788 | 3M [™] SecureFit [™] 400 Safety Glasses, Black/Green frame, Anti-Scratch/Anti-Fog, Clear Lens | Black/Green | Clear | AS/AF | 20 |
| SF402AS/AF | UU003683420 | 3M [™] SecureFit [™] 400 Safety Glasses, Black/Green frame, Anti-Scratch/Anti-Fog, Grey Lens | Black/Green | Grey | AS/AF | 20 |
| SF403AS/AF | UU003683412 | 3M [™] SecureFit [™] 400 Safety Glasses, Black/Green frame, Anti-Scratch/Anti-Fog, Amber Lens | Black/Green | Amber | AS/AF | 20 |
| SF408AS | UU003683446 | 3M [™] SecureFit [™] 400 Safety Glasses, Black/Green frame, Anti-Scratch, Blue Mirror Lens | Black/Green | Blue Mirror | AS | 20 |
| SF410AS | UU003683438 | 3M [™] SecureFit [™] 400 Safety Glasses, Black/Green frame, Anti-Scratch, Indoor/Outdoor Mirror Lens | Black/Green | Indoor/Outdoor Mirror | AS | 20 |
| SF415AS/AF | 70071676277 | 3M [™] SecureFit [™] 400 Reader Safety Glasses, Black/Green frame, Anti-Scratch/Anti-Fog, clear +1.5 Lens | Black/Green | Clear | AS/AF | 20 |
| SF420AS/AF | 70071695327 | 3M [™] SecureFit [™] 400 Reader Safety Glasses, Black/Green frame, Anti-Scratch/Anti-Fog, clear +2.0 Lens | Black/Green | Clear | AS/AF | 20 |
| SF425AS/AF | 70071695335 | 3M [™] SecureFit [™] 400 Reader Safety Glasses, Black/Green frame, Anti-Scratch/Anti-Fog, clear +2.5 Lens | Black/Green | Clear | AS/AF | 20 |
| SF401SGAF-BLU | 70071730330 | 3M [™] SecureFit [™] 400 Safety Glasses, Blue/Grey frame, Scotchgard [™] Anti-Fog/Anti-Scratch Coating (K&N), Clear Lens | Blue/Grey | Clear | SGAF | 20 |
| SF401-GAF-BLU-F | 70071730348 | 3M [™] SecureFit [™] 400 Safety Glasses, Blue/Grey frame, Foam, Scotchgard [™] Anti-Fog/Anti-Scratch Coating (K&N), Clear Lens | Blue/Grey | Clear | SGAF | 20 |
| SF401SGAF-RED | 70071730322 | 3M [™] SecureFit [™] 400 Safety Glasses, Red/Grey frame, Scotchgard [™] Anti-Fog/Anti-Scratch Coating (K&N), Clear Lens | Red/Grey | Clear | SGAF | 20 |
| SF407SGAF-BLU | 70071730355 | 3M [™] SecureFit [™] 400 Safety Glasses, Blue/Grey frame, Scotchgard [™] Anti-Fog/Anti-Scratch Coating (K&N), Indoor/Outdoor Grey Lens | Blue/Grey | Indoor/Outdoor Grey | SGAF | 20 |
| SF402SGAF-BLU | 70071730363 | 3M [™] SecureFit [™] 400 Safety Glasses, Blue/Grey frame, Scotchgard [™] Anti-Fog/Anti-Scratch Coating (K&N), Grey Lens | Blue/Grey | Grey | SGAF | 20 |
| SF403SGAF-YEL | 70071730371 | 3M [™] SecureFit [™] 400 Safety Glasses, Yellow/Black frame, Scotchgard [™] Anti-Fog/Anti-Scratch Coating (K&N), Amber Lens | Yellow/Black | Amber | SGAF | 20 |
| SF405SGAF-BLA | 70071730389 | 3M [™] SecureFit [™] 400 Safety Glasses, Black/Brown frame, Scotchgard [™] Anti-Fog/Anti-Scratch Coating (K&N), Brown Lens | Black/Brown | Brown | SGAF | 20 |
| SF406SGAF-BLA | 70071730397 | 3M [™] SecureFit [™] 400 Safety Glasses, Black/Brown frame, Scotchgard [™] Anti-Fog/Anti-Scratch Coating (K&N), Orange Lens | Black/Brown | Orange | SGAF | 20 |

3M[™] SecureFit[™] Safety Glasses

Available products

400X ^{serie}

| Product I.D. | 3M I.D. | Description | Frame colour | Lens colour | Coating | Each/ case |
|----------------|-------------|---|--------------|------------------------------|---------|---------------|
| SF401XRAS-GRN | XA006509096 | 3M [™] SecureFit [™] 400X Safety Glasses, Green/Black frame, Rugged Anti-Scratch (K), Clear Lens | Green/Black | Clear | RAS | 20 |
| SF401XSGAF-GRN | XA006509039 | 3M [™] SecureFit [™] 400X Safety Glasses, Green/Clear frame, Scotchgard [™] Anti-Fog/Anti-Scratch Coating (K&N), Clear Lens | Green/Clear | Clear | SGAF | 20 |
| SF401XSGAF-BLU | XA006509047 | 3M [™] SecureFit [™] 400X Safety Glasses, Blue/Grey frame, Scotchgard [™] Anti-Fog/Anti-Scratch Coating (K&N), Clear Lens | Blue/Grey | Clear | SGAF | 20 |
| SF402XSGAF-BLU | XA006509054 | 3M [™] SecureFit [™] 400X Safety Glasses, Blue/Grey frame, Scotchgard [™] Anti-Fog/Anti-Scratch Coating (K&N), Grey Lens | Blue/Grey | Grey | SGAF | 20 |
| SF403XSGAF-YEL | XA006509070 | 3M [™] SecureFit [™] 400X Safety Glasses, Yellow/Black frame, Scotchgard [™] Anti-Fog/Anti-Scratch Coating (K&N), Amber Lens | Yellow/Black | Amber | SGAF | 20 |
| SF407XSGAF-BLU | XA006509062 | 3M [™] SecureFit [™] 400X Safety Glasses, Blue/Grey frame, Scotchgard [™] Anti-Fog/Anti-Scratch Coating (K&N), Indoor/Outdoor Light Grey Lens | Blue/Grey | Indoor/Outdoor Light Grey | SGAF | 20 |
| SF416XAS-BLK | XA006509104 | 3M [™] SecureFit [™] 400X Safety Glasses, Black/Black frame, Anti-Scratch, Orange Mirror Lens | Black/Black | Orange Mirror | AS | 20 |
| SF422XSGAF-BLK | XA006509088 | 3M [™] SecureFit [™] 400X Safety Glasses, Black/Black frame, Scotchgard [™] Anti-Fog/Anti-Scratch Coating (K&N), Vermillion Lens | Black/Black | Vermillion | SGAF | 20 |

Series Series



Stylish dual-lens frame with a variety of lens options.

Get quality, durability and versatility all in one with 3M[™] SecureFit[™] 600 Safety Glasses. Choose from a variety of features, including 3M[™] Scotchgard[™] Protector Anti-Fog/Anti-Scratch Coating, multiple lens colours and a removable foam-lined gasket.



800 is



Product ID: SF601RAS Lens: Clear Rugged Frame: Grey Coating: Rugged Anti-Scratch



Product ID: SF610AS Lens: Indoor/Outdoor Mirror Lens Frame: Grey Coating: Anti-Scratch



Product ID: SF611AS Lens: Grey Polarised Frame: Grey Coating: Anti-Scratch



Product ID: **SF617AS** Lens: **Welding Shade 1.7** Frame: **Grey** Coating: **Anti-Scratch**



Product ID: SF630AS Lens: Welding Shade 3.0 Frame: Grey Coating: Anti-Scratch



Product ID: SF650AS Lens: Welding Shade 5.0 Frame: Grey Coating: Anti-Scratch



Product ID: SF601SGAF Lens: Clear Frame: Grey Coating: Scotchgard[™] Anti-Fog/ Anti-Scratch



Product ID: SF601SGAF/FI Lens: Clear w/Foam Gasket Frame: Grey Coating: Scotchgard[®] Anti-Fog/ Anti-Scratch



Product ID: SF602SGAF Lens: Grey Frame: Grey Coating: Scotchgard^{**} Anti-Fog/ Anti-Scratch



Product ID: SF603SGAF Lens: Amber Frame: Grey Coating: Scotchgard[™]Anti-Fog/ Anti-Scratch

Available products

| Product I.D. | 3M I.D. | Description | Frame colour | Lens colour | Coating | Each/case |
|--------------|-------------|---|--------------|-----------------------|---------|-----------|
| SF600FI | 70071695954 | 3M [™] SecureFit [™] 600 Foam Insert | n/a | n/a | n/a | 5 |
| SF601RAS | 70071695939 | 3M [™] SecureFit [™] 600 Safety Glasses, Grey frame, Rugged Anti-Scratch (K), Clear Lens | Grey | Clear | RAS | 20 |
| SF610AS | 70071695947 | 3M [™] SecureFit [™] 600 Safety Glasses, Grey frame, Anti-Scratch, Indoor/Outdoor Mirror Lens | Grey | Indoor/Outdoor Mirror | AS | 20 |
| SF611AS | 70071695921 | 3M™ SecureFit™ 600 Safety Glasses, Grey frame, Anti-Scratch, Grey Polarised Lens | Grey | Grey Polarised | AS | 20 |
| SF617AS | 70071695897 | 3M™ SecureFit™ 600 Safety Glasses, Grey frame, Anti-Scratch, Welding Shade 1,7 Lens | Grey | Welding Shade 1.7 | AS | 20 |
| SF630AS | 70071695905 | 3M [™] SecureFit [™] 600 Safety Glasses, Grey frame, Anti-Scratch, Welding Shade 3.0 Lens | Grey | Welding Shade 3.0 | AS | 20 |
| SF650AS | 70071695913 | 3M [™] SecureFit [™] 600 Safety Glasses, Grey frame, Anti-Scratch, Welding Shade 5.0 Lens | Grey | Welding Shade 5.0 | AS | 20 |
| SF601SGAF | 70071676830 | 3M [™] SecureFit [™] 600 Safety Glasses, Grey frame, Scotchgard [™] Anti-Fog/Anti-Scratch Coating (K&N), Clear Lens | Grey | Clear | SGAF | 20 |
| SF601SGAF/FI | 70071677713 | 3M [™] SecureFit [™] 600 Safety Glasses, Grey frame, Foam, Scotchgard [™] Anti-Fog/Anti-Scratch Coating (K&N), Clear Lens | Grey | Clear | SGAF | 20 |
| SF602SGAF | 70071695871 | 3M [™] SecureFit [™] 600 Safety Glasses, Grey frame, Scotchgard [™] Anti-Fog/Anti-Scratch Coating (K&N), Grey Lens | Grey | Grey | SGAF | 20 |
| SF603SGAF | 70071695889 | 3M [™] SecureFit [™] 600 Safety Glasses, Grey frame, Scotchgard [™] Anti-Fog/Anti-Scratch Coating (K&N), Amber Lens | Grey | Amber | SGAF | 20 |

Series 0028



Over-the-glass protection designed with self-adjusting temple technology for all-day wearability.

$3200 \, \text{series}$

3M[™] SecureFit[™] 3700 Overspectacles are designed to offer eye protection with all-day wearability for workers with prescription eyeglasses. Since prescription glasses may not be anti-fog coated, you can choose between an anti-scratch+ coating or 3M[™] Scotchgard[™] Protector Anti-Fog/Anti-Scratch Coating.



$3200\,\text{s}$



Product ID: SF370ASP-BLU Lens: Clear Frame: Blue/Blue Coating: Anti-Scratch+



Product ID: SF3701SGAF-BLU Lens: Clear Frame: Blue/Blue Coating: Scotchgard" Anti-Fog/ Anti-Scratch



Product ID: SF3707SGAF-BLU Lens: Indoor/Outdoor Grey Frame: Blue/Blue Coating: Scotchgard" Anti-Fog/ Anti-Scratch



Product ID: SF3701SGAF-GRN Lens: Clear Frame: Grey/Lime Green Coating: Scotchgard" Anti-Fog/ Anti-Scratch



Product ID: SF3717ASP-BLK Lens: IR Shade 1.7 Frame: Black/Green Coating: Anti-Scratch+



Product ID: SF3701SGAF-ORG Lens: Clear Frame: Grey/Orange Coating: Scotchgard" Anti-Fog/ Anti-Scratch



Product ID: SF3730ASP-BLK Lens: IR Shade 3.0 Frame: Black/Green Coating: Anti-Scratch+



Product ID: SF3702SGAF-BLU Lens: Grey Frame: Blue/Blue Coating: Scotchgard[™] Anti-Fog/ Anti-Scratch



Product ID: SF3750ASP-BLK Lens: IR Shade 5.0 Frame: Black/Green Coating: Anti-Scratch+



Product ID: SF3703SGAF-GRN Lens: Amber Frame: Grey/Lime Green Coating: Scotchgard" Anti-Fog/ Anti-Scratch

STOOX is with Brow Guard



Product ID: SF3701XSGAF-BLU Lens: Clear Frame: Grey/Blue Coating: Scotchgard[™] Anti-Fog/ Anti-Scratch



Product ID: SF3702XSGAF-BLU Lens: Grey Frame: Grey/Blue Coating: Scotchgard" Anti-Fog/ Anti-Scratch



Product ID: SF3707XSGAF-BLU Lens: Indoor/Outdoor Grey Frame: Grey/Blue Coating: Scotchgard" Anti-Fog/ Anti-Scratch

Available products

| Product I.D. | 3M I.D. | Description | Frame colour | Lens colour | Coating | Each/case |
|-----------------|-------------|---|--------------|------------------------------|---------|-----------|
| SF3701ASP-BLU | XA006510110 | 3M [™] SecureFit [™] 3700 Overspectacles, Blue Frame, Anti-Scratch+ (K), Clear Lens E | | Clear | ASP | 20 |
| SF3701SGAF-BLU | XA006510102 | 3M [™] SecureFit [™] 3700 Overspectacles, Blue Frame, Scotchgard [™] Anti-Fog/Anti-Scratch Coating (K&N), Clear Lens Bl | | Clear | SGAF | 20 |
| SF3701SGAF-GRN | XA006510136 | 3M [™] SecureFit [™] 3700 Overspectacles, Lime Green Frame, Scotchgard [™] Anti-Fog/Anti-Scratch Coating (K&N), Clear Lens | Lime Green | Clear | SGAF | 20 |
| SF3701SGAF-ORG | XA006510177 | 3M [™] SecureFit [™] 3700 Overspectacles, Orange Frame, Scotchgard [™] Anti-Fog/Anti-Scratch Coating (K&N), Clear Lens | Orange | Clear | SGAF | 20 |
| SF3702SGAF-BLU | XA006510128 | 3M [™] SecureFit [™] 3700 Overspectacles, Blue Frame, Scotchgard [™] Anti-Fog/Anti-Scratch Coating (K&N), Grey Lens | Blue | Grey | SGAF | 20 |
| SF3703SGAF-GRN | XA006510193 | 3M [™] SecureFit [™] 3700 Overspectacles, Lime Green Frame, Scotchgard [™] Anti-Fog/Anti-Scratch Coating (K&N), Amber Lens | Lime Green | Amber | SGAF | 20 |
| SF3707SGAF-BLU | XA006510169 | 3M [™] SecureFit [™] 3700 Overspectacles, Blue Frame, Scotchgard [™] Anti-Fog/Anti-Scratch Coating (K&N), Indoor/Outdoor Light Grey Lens | Blue | Indoor/Outdoor Light Grey | SGAF | 20 |
| SF3701XSGAF-BLU | XA006510847 | 3M [™] SecureFit [™] 3700 Overspectacles, Blue Frame, Brow Guard, Scotchgard [™] Anti-Fog/Anti-Scratch Coating (K&N), Clear Lens | Blue | Clear | SGAF | 20 |
| SF3702XSGAF-BLU | XA006510854 | 3M [™] SecureFit [™] 3700 Overspectacles, Blue Frame, Brow Guard, Scotchgard [™] Anti-Fog/Anti-Scratch Coating (K&N), Grey Lens | Blue | Grey | SGAF | 20 |
| SF3707XSGAF-BLU | XA006510862 | 3M [™] SecureFit [™] 3700 Overspectacles, Blue Frame, Brow Guard, Scotchgard [™] Anti-Fog/Anti-Scratch Coating (K&N), I/O Light Grey Lens | Blue | Indoor/Outdoor Light Grey | SGAF | 20 |
| SF3717ASP-BLK | XA006509823 | 3M [™] SecureFit [™] 3700 Safety Overspectacles, Black/Green frame, Anti-Scratch+ (K), IR 1.7 Grey Lens | Black/Green | Grey | ASP | 20 |
| SF3730ASP-BLK | XA006509831 | 3M™ SecureFit™ Safety Overspectacles, Black/Green frame, Anti-Scratch+ (K), IR 3.0 Grey Lens | Black/Green | Grey | ASP | 20 |
| SF3750ASP-BLK | XA006510227 | 3M [™] SecureFit [™] 3700 Safety Overspectacles, Black/Green frame, Anti-Scratch+ (K), IR 5.0 Grey Lens | Black/Green | Grey | ASP | 20 |

Series Comparison Chart

| Features | 200 Series | 400 Series | 400X Series | 600 Series | 3700 Series |
|---|------------|------------|-------------|------------|-------------|
| 3M [™] Pressure Diffusion Temple Technology | × | × | × | × | × |
| 3M [™] Scotchgard [™] Anti-Fog/Anti-Scratch Coating | × | × | × | × | × |
| Soft Temple Tips | | × | × | | |
| Rugged Anti-Scratch or Anti-Scratch+ (K) Coating | | | × | × | × |
| Soft Nose Bridge | | × | × | × | × |
| Brow Guard | | | × | | × |
| Removable Foam Gasket | | × | | × | |
| Dual Lens Design | | | | × | |
| Readers | | × | | | |
| Indoor/Outdoor (Mirror) Lens | | × | × | × | × |
| Orange and Brown Lens | | × | | | |
| IR Lens | | | | × | × |
| Sunglare Mirror Lens | | × | × | | |
| Vermillion Lens | | | × | | |
| Polarised Lens | | | | × | |

A difference you can see and feel.

Eyewear that's lightweight and comfortable — believe it. Contact your 3M sales rep to request trial wear samples of 3M[™] SecureFit[™] Safety Glasses and feel the difference the instant you put them on. See for yourself.

Visit 3M.co.uk/SecureFit

© 3M 2020. All rights reserved. 3M, SecureFit and Scotchgard are trademarks of 3M Company. OMG78950