

# 3M™ Performance Industrial Spray Gun

---

## Engineered for the industrial painter.

The 3M™ Performance Spray Gun is the industrial coating solution that can help reduce variability in your process and boost productivity by giving technicians a smarter way to spray.





# Throw down paint like a seasoned pro with a simple, intuitive design.

Lightweight and easy to use, the 3M™ Performance Spray Gun was built with the industrial painter in mind. Made from an advanced impact-resistant composite material, the spray gun is one of the lightest in the industry yet durable enough for the toughest industrial conditions. From the trigger to the body, the spray gun was optimized by kinesiologists to enhance comfort specifically for the high demands of all-day spraying.

With its versatile design, technicians can spray from either a pressurized source or a gravity cup. The pressure-fed hose and nozzles allow for continuous bulk spraying for larger jobs. Or for spot repairs and small areas, convert the spray gun to use the 3M™ PPS™ Series 2.0 Spray Cup System— so you use just the right amount of coating to match the size and finish of the job.

Simple, innovative design means fewer parts to maintain. With quick-change replaceable nozzles, paint never passes through the body of the spray gun. Cleanup can be as simple as wiping the tip of the needle and replacing the head – which means no more disassembling or soaking in solvent. It's like getting a brand new spray gun every time you put on a fresh nozzle. At sizes from 1.1 to 2.0, 3M™ Performance Atomizing Heads allow you to easily spray a wide range of coatings – from stains and primers to topcoats and even adhesives.



## Specifications

**Air Consumption:** 370 SLPM [13 SCFM]

**Recommended Air Inlet Pressure:** 1.24 Bar [18 psi]

**Maximum Operating Temperature:** 50 °C [122 °F]

**Maximum Operating Overpressure:** 10 Bar [145 psi]

**Weight:** 378 g [13.3 oz]

**Air Inlet:** 1/4 BSP/NPS

**Liquid Inlet:** 3/8 BSP/NPS

**Nozzle Orifice Sizes:** 1.1, 1.4, 1.8



## Lightweight and Durable

One of the lightest spray guns in the industry, the impact-resistant composite body is built to withstand demanding industrial environments.



## Low Maintenance and Easy

Simple, intuitive design means fewer parts to maintain or rebuild and can help achieve more consistent performance whether you're a beginner or a pro.



## Replaceable Nozzles

With quick-change replaceable atomizing heads ranging from 1.1 to 2.0, it's like getting a brand new spray gun with every new nozzle.



## Built for Versatility

Sprays a wide range of coatings, including, stains, primers, basecoats, topcoats, clearcoats, and adhesives – from either a pressure-fed system or with 3M™ PPS™ Series 2.0 Spray Cup System.



## Spray Gun and Systems

### Part No. Components

#### 3M™ Performance Industrial Spray Gun System

26878 Spray gun, air control valve, pressure whip, pressure and gravity atomizing heads, PPS Series 2.0

#### 3M™ Performance Spray Gun

26832 Spray gun and air control valve

## Replacement Parts and Accessories

### Part No. Product

#### 3M™ Performance Spray Gun

26833 Pressure Whip  
26839 Ball Valve  
26835 Locking Collar  
26840 Rebuild Kit  
26834 Whip Pin  
26838 Needle

## Atomizing Head Refill Kits

Part No.	Color	Size
<b>Pressure</b>		
26811	Yellow	1.1
26814	Orange	1.4
26818	Clear	1.8
26830	Variety Kit	3 sizes (1.1, 1.4, 1.8)
<b>Gravity</b>		
26712	Blue	1.2
26713	Green	1.3
26714	Orange	1.4
26716	Purple	1.6
26718	Clear	1.8
26720	Red	2.0
26730	Variety Kit	6 sizes (1.2, 1.3, 1.4, 1.6, 1.8, 2.0)

# Ditch the old systems.

The high-maintenance metal guns that require more fuss than they're worth, the spray cans, the paint brushes and rollers – try the new 3M™ Performance Spray Gun and help bring consistency and quality back into your paint operations.

For industrial/occupational use only.  
Not for consumer sale or use.



Automotive Aftermarket Division  
3M Center  
Building 223-06S-07  
St. Paul, MN 55144-1000  
1-877-666-2277

For more information, visit us at  
[3M.com/performancespraygun](https://3M.com/performancespraygun)

**Product Selection and Use:** Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for proper evaluation (including, but not limited to, fitness for purpose and suitability of application), selection, and use of 3M products. Safety products should always be selected and used in accordance with all applicable regulations and standards (e.g., OSHA, ANSI, and others), after conducting a proper hazard assessment. Failure to properly evaluate, select, and use a 3M product may result in injury, sickness, death, and/or harm to property.

**Warranty, Limited Remedy, and Disclaimer:** Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If the 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

**Limitation of Liability:** Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.

3M and PPS are trademarks of 3M Company. All other trademarks are property of their respective owners. Please recycle. Printed in USA. © 3M 2020. All rights reserved. 60-4405-0000-1