

3M[™] Paintshop Coverall 51850

Technical data sheet



Description

The 3M™ Paintshop Coverall 51850 is designed to help protect against certain light liquid splashes (Type 6) and hazardous dusts (Type 5). Product features include:

- EVA foam knee pads
- 3-panel hood
- Elasticated waist and ankles
- Wider ankle openings (versus other 3M Coveralls)
- Knitted cuffs with thumb loop
- Two-way zipper with sealable storm flap
- Low linting
- Reinforced gusset
- Large breathable back panel

Comfort and protection



Liquid protection

Type 6 - Light liquid splashes (EN 13034:2005 + A1:2009)



Dust protection Type 5 - Solid airborne particulates EN ISO 13982-1:2004 +A1:2010



Anti-static

Anti-static coating on inner side (white material)¹ (EN 1149-5:2008)



Nuclear

Radioactive particulates (EN 1073-2:2002) Class 1



Except EN863 puncture resistance. Does not offer protection against radiation.

¹All apparel must be suitably grounded for anti-static treatment to be effective. White material only.

Approvals

These products are type examined by SATRA Technology Europe Ltd., Notified body number 2777 and audited annually by SGS, Notified Body number 0598.

These products are CE marked to the requirements of the European Regulation (EU) 2016/425.

The applicable legislation can be determined by reviewing the Certificate and Declaration of Conformity at www.3m.com/Body/certs.



Materials	
Suit	Polypropylene & polyethylene laminate 60gsm (white)
Back panel	SMMMS Polypropylene 43gsm (green)
Zipper	Metal/nylon/polyester braid
Knee pads	EVA foam
Elastic	Synthetic rubber (non-latex)
Cuffs	Polyester
Thread	Polyester/cotton


This product does not contain components made from silicone or natural rubber latex.

Sizing²

An appropriate size garment should be selected to allow sufficient movement for the task whilst maintaining a secure fit.

Height		Chest		
S	64 – 67 in	164 – 170 cm	33 – 36 in	84 – 92 cm
М	66 – 69 in	167 – 176 cm	36 – 39 in	92 – 100 cm
L	69 – 71 in	174 – 181 cm	39 – 43 in	100 – 108 cm
XL	70 – 74 in	179 – 187 cm	43 – 45 in	108 – 115 cm
XXL	73 – 76 in	186 – 194 cm	45 – 49 in	115 – 124 cm
3XL	76 – 78 in	194 – 200 cm	49 – 52 in	124 – 132 cm
4XL	78 – 81 in	200 - 206 cm	52 – 55 in	132 – 140 cm

² The values above are the result of illustrative lab test measures and should not be considered as a commitment from 3M.



Storage and disposal

- Store in dry, clean conditions in original packaging, away from direct sunlight, sources of high temperature, and solvent vapours
- Store within the temperature range -20°C to +25°C (-4°F to +77°F) and with relative humidity below 80%
- Expected shelf life is five (5) years from date of manufacture when stored as stated³
- Replace garments if damaged, heavily contaminated or in accordance with local work practice or regulations
- Handle and dispose of contaminated garments with care and in accordance with applicable regulations

³The shelf life as defined above remains an indicative and maximum data, subject to many external and non-controllable factors. It may never be interpreted as a warranty.

Limited Use



Do not wash



Do not dry clean



Do not bleach



Flammable — keep away from sparks or flames



Do not iron



Single use do not re-use



Do not tumble dry

Warnings and limitations

Before use read and understand all user instructions and be sure that the product is suitable for the application and fitted correctly. Product must never be altered or modified.

Do not use for:

- Contact with heavy oils, sparks or flame, or combustible liquids;
- Exposure situations resulting in spray or liquid build-up on the suit;
- Environments with high mechanical risks (abrasions, tears, cuts);
- Contact with hazardous substances beyond Type 5/6 certification;
- Environments with conditions of excessive heat.

Applications and Performance

Yes	Hazardous liquid splash	Yes, if chemical is compatible with suit material ⁴
Yes	Hazardous liquid spray	No
Yes	Organic solvents	No
No	Acids/alkalis	Yes, if chemical is compatible with suit material ⁴
No		
	Yes Yes No	Yes liquid splash Hazardous liquid spray Organic solvents No Acids/alkalis

⁴ The chemicals against which the product has been tested and certified are listed in the user instructions and shown in the following table. For additional chemical penetration data, please call your local 3M Technical Service Representative or visit the 3M Chemical Test library at http://go.3M.com/CHTL.

In all cases, a risk assessment should be carried out. Always read product user information. Use limitations and performance data should be considered to ascertain the protection required. If in doubt, contact a safety professional.

For more information on 3M products and services please contact 3M.

3M™ Paintshop Coverall 51850

The tables show the performance of this product when tested under laboratory conditions in accordance with the referenced standard test method.

Note: The maximum Class is 6 unless otherwise noted.

Test	Standard/ test method	Class/result
Abrasion resistance (visual assessment)	EN 530:2010	Class 1
Flex cracking (visual assessment)	ISO 7854:1995	Class 6
Tear resistance	ISO 9073-4 :1997	Class 1
Tensile strength	EN ISO 13934-1:1999	Class 1
Puncture resistance	EN 863:1995	Class 1
Resistance to ignition	EN 13274-4:2001	Pass
Resistance to blocking	EN 25978:1990	No Blocking
Seam strength	EN ISO 13935-2:1999	Class 2

Test	Standard/ test method	Class/result
Repellency to liquids – 30% H ₂ SO ₄	EN ISO 6530:2005	Class 3 of 3
Liquid penetration resistance – 30% H ₂ SO ₄	EN ISO 6530:2005	Class 3 of 3
Repellency to liquids – 10% NaOH	EN ISO 6530:2005	Class 3 of 3
Liquid penetration resistance – 10% NaOH	EN ISO 6530:2005	Class 3 of 3
Anti-static coating on inner side (white material only)	EN 1149-1:2006	Pass
Radioactive particulates (TIL)	EN 1073-2:2002	Class 1 of 3



Visit the 3M Chemical Test Library for an online repository of available chemical data for 3M™ Protective Coveralls:

http://go.3M.com/CHTL



IMPORTANT NOTICE

www.3M.eu/safety

The use of the 3M product described within this document assumes that the user has previous experience of this type of product and that it will be used by a competent professional. Before any use of this product it is recommended to complete some trials to validate the performance of the product within its expected application.

All information and specification details contained within this document are inherent to this specific 3M product and would not be applied to other products or environment. Any action or usage of this product made in violation of this document is at the risk of the user.

Compliance to the information and specification relative to the 3M product contained within this document does not exempt the user from compliance with additional guidelines (safety rules, procedures). Compliance to operational requirements especially in respect to the environment and usage of tools with this product must be observed. The 3M group (which cannot verify or control those elements) would not be held responsible for the consequences of any violation of these rules which remain external to its decision and control.

Warranty conditions for 3M products are determined with the sales contract documents and with the mandatory and applicable clause, excluding any other warranty or compensation.

For more information on 3M products and services please contact 3M.





