



3M Science.
Applied to Life.™

Be ready to respond.

Solutions for Surge Planning Implementation



You need response resources you can rely on.

Responding to a crisis is a big responsibility with a lot of moving parts and details. From effective communications to cleaning, containment or repurposing facilities, your team is going to need to pull together many resources to implement your plan. That's why we've put together a selection of products to help you quickly find what you need to successfully stay on top of this evolving emergency.

Communications | Cleaning | Containment | Facility Repurposing

**In a crisis,
communication
is key.**



Post-it® Super Sticky Easel Pads

Stick securely without causing damage. Capture team messages permanently on ink bleed-through resistant paper. Reposition, remove or dispose in seconds.



7100159622

Post-it® Super Sticky Easel Pad, 4 Pack, 559 VAD 4PK, White, 25 in. x 30 in.



7100159630

Post-it® Super Sticky Easel Pad, 6 Pack, 559 VAD 6PK, White, 25 in. x 30 in.

Command Center

Turn any room into a command center with versatile Post-it® Brand Products. Make any wall a white board with Post-it® Flex Write Surface for sharing situational updates anywhere, anytime. Map plans, assign tasks, create to-do lists and more quickly and clearly with Post-it® Super Sticky Easel Pads and Post-it® Super Sticky Notes.

Post-it® Flex Write Surface

Create a whiteboard instantly for capturing daily team messages with dry erase markers (temporary) or permanent markers. Sticks securely, removes cleanly.



7100197625

Dry Erase 7100197625 - FWS3x2, Flex Write Surface, 2 ft. x 3 ft.



7100197624

Dry Erase 7100197624 - FWS4x3, Flex Write Surface, 4 ft. x 3 ft.



7100198315

Dry Erase 7100198315 - FWS6x4, Flex Write Surface, 4 ft. x 2 yd.

Post-it® Flex Write Surface (cont.)



7100198316

Dry Erase 7100198316 - FWS8×4,
Flex Write, 4 ft. x 2.66 yd.



7100195630

Dry Erase 7100195630 - FWS50×4,
16.6 yd. x 4 ft.

Post-it® Notes

Capture daily or updated messages amongst groups or teams or take quick notes. Post-it® Super Sticky Notes work best on walls or smooth surfaces. Post-it® Extreme Notes are water-resistant notes that stick in tough conditions where surfaces are rough, or might get wet, hot or cold.



7100104282

Post-it® Super Sticky Notes, 3 in.
x 3 in., Marrakesh collection, 24
Pads/Pack 654-24SSAN-CP



7100083624

Post-it® Super Sticky Notes, 3 in. x 3 in.,
Rio de Janeiro collection, 24 Pads/Pack
654-24SSAU-CP



7100113494

Post-it® Notes, 3 in. x 5 in., Canary
Yellow, 18 Pads/Pack 655-18CP



7100168673

Post-it® Extreme Notes, 3 in. x 3 in.,
Assorted Colors, 3 Pads/Pack
EXTRM33-3CTMX



7100156011

Post-it® Extreme Notes, 3 in. x 3 in.,
Assorted Colors, 12 Pads/Pack
EXTRM33-12TRYX



When cleaning goes beyond critical.

Facility Cleanliness Priorities

In times of emergency, cleaning and disinfecting is absolutely critical. All locations like hospitals, alternate care sites (ACS), critical manufacturing and warehouses, and grocery stores need to be kept clean. It's more important than ever to use proper cleaners and disinfectants during routine and daily cleaning, while sorbents can help with absorbing and cleaning up a variety of liquids.

3M™ Cleaners and Disinfectants

3M has an extensive array of products for facility cleanliness management.



7100034339

3M™ TB Quat Disinfectant Ready-to-Use Cleaner, Quart, 12/Case

Cleaning

3M™ Cleaners and Disinfectants (cont.)



7000052378
3M™ Quat Disinfectant Cleaner 5H,
2 Liter, 6/Case



70071126398
3M™ Quat Disinfectant Cleaner
Concentrate 5L, 2 Liter, 6/Case



7010342270
3M™ Neutral Quat Disinfectant Cleaner
Concentrate 23A, 0.5 Gallon, 4/Case



7000052529
3M™ Neutral Quat Disinfectant Cleaner
Concentrate 23H, 2 Liter, 6/Case



7100134549
3M™ Neutral Quat Disinfectant Cleaner
Concentrate 23L, 2 Liter, 6/Case



7010342249
3M™ Disinfectant Cleaner RCT
Concentrate 40A, 0.5 Gallon 4/Case



7100058966
3M™ Disinfectant Clean RCT
Concentrate 40L Gray Cap 2 Liter
6/Case



7010385951
3M™ Disinfectant Cleaner RCT
Concentrate, Gallon, 4/Case



7100135687
3M™ Twist & Fill™ System Dispenser,
Gray Cap, 1/Case

Cleaning

3M™ Cleaners and Disinfectants (cont.)



7010385975
3M™ Flow Control System, Wall Mount, Action Gap, 1 Each/Case

Liquid industrial cleaner and degreaser

Used to help dissolve and remove dirt, grease, tar and many non-curing adhesives.



7000028595
3M™ Citrus Base Cleaner Transparent, Net Wt 18.5 oz., 12/Case, Not for sale or use in California. Consult local air quality rules before use.

3M™ Sorbents

Absorb and clean up liquids and spills, from aggressive (hazardous), to non-aggressive or oil-only applications.



7000002024
3M™ Chemical Sorbent Folded C-FL550DD/P-F2001, Environmental Safety Product, High Capacity, 3 bx/Case



7000001951
3M™ Maintenance Sorbent Folded M-FL550DD/M-F2001/07172(AAD), Environmental Safety Product, High Capacity, 3 ea/Case




7000002025
3M™ Petroleum Sorbent Folded P-FL550DD/T-F2001/07173(AAD), Environmental Safety Product, High Capacity, 3 bx/Case

3M™ Floor Mops and Pads

Quickly switch between cleaning and finishing with floor protector application—or use disposable mop pads when laundry is unavailable or to help reduce cross-contamination for an effective clean every time.




7100172630
3M™ Scotch-Brite™ Professional 2-In-1 Flat Mop, Ergonomic Handle



7100179842
3M™ Scotch-Brite™ Professional 2-In-1 Flat Mop & Backpack Finish Applicator Kit, Ergonomic Handle




7100172627
3M™ Scotch-Brite™ Professional Standard Flat Mop




7100155486
3M™ Easy Clean Disposable Floor Mop Pad, 18 in. 30/Case




7000127862
3M™ Easy Scrub Mop White 18 in.



7000126855
3M™ Easy Scrub Mop Red 18 in.



7100135689
3M™ Easy Scrub Mop Green 18 in.



7000126856
3M™ Easy Scrub Mop Blue 18 in.

Cleaning

3M™ Easy Trap™ Dusters

Convenient disposable sheets allow for quick sweeping and dusting without requiring laundry services.



7100081547

3M™ Easy Trap™ Sweep & Dust Sheets; 5 in. x 6 in. Sheets; 60 Sheets/Roll; 8 Rolls/Case



7100081546

3M™ Easy Trap™ Sweep & Dust Sheets; 8 in. x 6 in. Sheets; 60 Sheets/Roll, 8 Rolls/Case



7100081545

3M™ Easy Trap™ Sweep & Dust Sheets; 5 in. x 6 in. Sheets, 250 Sheets/Roll, 1 Roll/Case



7100081544

3M™ Easy Trap™ Sweep & Dust Sheets; 5 in. x 6 in. Sheets; 250 Sheets/Roll, 2 Rolls/Case


Scotch-Brite® Disposable Toilet Scrubber

Keep toilets clean while helping reduce cross-contamination risks by disposing and refilling scrub pads between each use.



7100112800

Scotch-Brite® Disposable Toilet Scrubber



7100112739

Scotch-Brite® Disposable Toilet Scrubber Refills

Containment

Containment with confidence.


Containment

Help Reduce the Spread

Help create containment spaces to care for contagious patients. Remove dirt and contaminants from shoe soles, wheels, and other passing objects on contact with 3M™ Clean Walk Mats, and test surfaces for bacteria with 3M™ Clean Trace™ Surface ATP Swabs.

3M™ Clean Walk Mats

Place these on hard surfaces or carpeted floors in transition walkways to capture dirt from wheels, shoes and more.



7100010027

3M™ Clean-Walk Mat 5830, White, 18 in. x 46 in., 30 Sheets Per Mat, 4/Case

7000049618

3M™ Clean-Walk Mat 5830, White, 18 in. x 36 in., 30 Sheets Per Mat, 4/Case

7100010027

3M™ Clean-Walk Mat 5830, White, 18 in. x 46 in., 30 Sheets Per Mat, 4/Case

7000049620

3M™ Clean-Walk Mat 5830, White, 25 in. x 45 in., 60 Sheets Per Mat 4/Case




70006717048

3M™ Clean-Walk Framed Mat 5840 - 31.5 x 25.5 in. 1/Case

7000148412


3M™ Clean-Walk Framed Mat 5840, White On White, 31-1/2 in. x 25-1/2 in., 60 Sheets Per Mat

Containment



3M™ Tapes

Use for a variety of applications that require fast and easy-to-use permanent bonding strength without need for screws, mounting or attachment hardware.




7000028971
3M™ VHB™ Tape 5952,
1/2 in. x 36 yd. Black



7000124124
3M™ VHB™ Tape 5952,
1/2 in. x 36 yd. Black Small Pack



7000049237
3M™ VHB™ Tape 5952,
3/4 in. x 36 yd. Black



7000042794
3M™ VHB™ Tape 5952,
1 in. x 36 yd. Black



7000124123
3M™ VHB™ Tape 5952,
1 in. x 36 yd. Black Small Pack

Containment


3M™ Tapes (cont.)

These tapes are designed for lighter-duty applications like mounting interior sanitation devices in high traffic areas to promote hand hygiene.



7100091133

3M™ Double Coated Urethane Foam Tape 4026, 1 in. x 1 in., 1000 squares Natural



7000123338

3M™ Double Coated Urethane Foam Tape 4026, 1/2 in. x 36 yd. Natural



7000123340

3M™ Double Coated Urethane Foam Tape 4026, 1 in. x 36 yd. Natural



7000125247

3M™ Double Coated Urethane Foam Tape 4026, 2 in. x 36 yd. Natural

3M™ Clean-Trace™ Surface ATP Test Swab

Easy to use and simple to learn, these test swabs help you verify cleaning effectiveness, assess and improve hygienic performance and reduce risk.



7100067519

3M™ Clean-Trace™ Surface ATP Test Swab UXL100, 100/Case

Repurposing Facilities

Giving repurposed facilities functionality.

Temporarily Transforming and Repurposing Facilities

In times of crisis, it may be appropriate to transform a space into an alternate care site. Additionally, a critical infrastructure may require implementation of temporary safety measures, like directing the flow of customers or employees. With the right solutions from 3M, you can delineate spaces, mount and attach devices, help protect surfaces and unused equipment, route and protect vital cables and wires—and do it all without causing long-term damage. It's a smart and efficient way to temporarily transform a space in an emergency.

3M™ Tapes

Mount, bond and conform these tapes on irregular surfaces both indoors and outdoors.



7000123604

3M™ Double Coated Polyethylene Foam Tape
4496W 1/2 in. x 36 yd. White

7000123606


3M™ Double Coated Polyethylene Foam Tape
4496W 1 in. x 36 yd. White

7010312158

3M™ Double Coated Polyethylene Foam Tape
4496W 2 in. x 36 yd. White

Repurposing Facilities

3M™ Protection Fabric and Materials | Protect surfaces and unused equipment from liquids and dirt.



7100132342

3M™ Self-Stick Liquid Protection Fabric, 6 in. x 300 ft., Blue

7100224216

3M™ Self-Stick Liquid Protection Fabric, 14 in. x 300 ft., Blue

7100223606

3M™ Self-Stick Liquid Protection Fabric, 28 in. x 300 ft., Blue

7100224202

3M™ Self-Stick Liquid Protection Fabric, 56 in. x 300 ft., Blue




7100132343

3M™ Dirt Trap Protection Material, 28 in. x 300 ft., Gray (Dispenser sold separately)



7100132344

3M™ Dirt Trap Protection Material, 56 in. x 300 ft., Gray



7100003285

3M™ Dirt Trap Protection Material Dispenser, Magnetic, for 28 in. wide material



7000045517

3M™ Dirt Trap Protection Material Dispenser, Extendable wall applicator, for 28 in. wide material

7000045516

3M™ Dirt Trap Protection Material Dispenser, Versatile floor applicator, for 28 in. wide material



7000119908

3M™ Dirt Trap Protection Material Dispenser, Versatile floor applicator, for 56 in. wide material

Repurposing Facilities

3M™ Scotchcal™ Clear View Graphic Film

Help protect windows and glass surfaces with transparent, see-through films.



7000056243

3M™ Scotchcal™ Clear View Graphic Film
IJ8150, 60 in. x 50 yd., Transparent

7100006333

3M™ Scotchcal™ Clear View Graphic Film
IJ8150, 54 in. x 50 yd., Transparent

7100149475

3M™ Scotchcal™ Clear View Graphic Film
IJ8150, 8 in. x 10 in., Transparent

7100102665

3M™ Scotchcal™ Clear View Graphic Film
IJ8150, 54 in. x 25 yd., Transparent

75347217277

3M™ Scotchcal™ Clear View Graphic Film
IJ8150, 60 in. x 25 yd., Transparent

Command™ Hooks, Strips and Cord Bundlers

Make temporary placements, bundle cords and add convenient hooks for hanging bags, coats and other lightweight equipment with options rated up to 5 lbs.



7100144889

Command™ Large Designer Hooks (16 hooks, 24 foam strips) contract box



7100145191

Command™ Medium Wire Hooks (35 hooks, 40 foam strips) contract box



7100144878

Command™ Large Wire Hooks (14 hooks, 24 foam strips) contract box



7010300778

Command™ Poster Strips, (256 strips) contract box



7100205656

Command™ Large Picture Hanging Strips (120 total pairs/ 240 total strips) contract box



7100089521

Command™ Small Utility Hook Value Pack 17002-6ES

Repurposing Facilities

Command™ Hooks, Strips and Cord Bundlers (cont.)



7100217717
Command™ Small Wire Hooks



7100129501
Command™ Cord Bundlers, 17304-ES,
2 bundlers, 3 strips

3M™ Water Filtration

Achieve cleaner, clearer water for cooking and drinking by removing unpleasant taste and odor.



7000125866
3M™ Under Sink Full Flow Water Filter
System 3MFF100



7000125865
3M™ Under Sink Full Flow Water Filter Replacement
Cartridge 3MFF101, 5613432, 6/Case

3M™ Vinyl Floor Marking Tapes

Clearly delineate everything from aisles, walk-ways and traffic lanes, to work cells, temporary storage, product inspection locations or caution areas.



7100044478
3M™ Vinyl 471 Floor Marking Tape,
2 in. x 36 yd., Yellow



7000028854
3M™ Vinyl 471 Floor Marking Tape,
2 in. x 36 yd., Orange



7100044655
3M™ Vinyl 471 Floor Marking Tape,
2 in. x 36 yd., Red

Repurposing Facilities

3M™ Vinyl Floor Marking Tapes (cont.)



7100044652

3M™ Vinyl 471 Floor Marking Tape,
2 in. x 36 yd., Green



7100044656

3M™ Vinyl 471 Floor Marking Tape,
2 in. x 36 yd., Blue



7000048401

3M™ Vinyl 471 Floor Marking Tape,
2 in. x 36 yd., Black



7000028955

3M™ Hazard Warning Tape 766, Black/
Yellow, 2 in. x 36 yd., 5 mil

3M™ Masking and Marking Tapes

Use different colored masking tapes to immediately and temporarily label things and communicate clearly to identify different categorizations.



7000147263

3M™ Value Masking Tape 101+ Tan,
24 mm x 55 m 5.1 mil, 36/Case Bulk



7000147264

3M™ Value Masking Tape 101+ Tan,
48 mm x 55 m 5.1 mil, 24/Case Bulk



7000144751

3M™ General Use Masking Tape 201+ Tan,
24 mm x 55 m 4.4 mil, 36/Case Bulk

Repurposing Facilities

3M™ Masking and Marking Tapes (cont.)



7000144752

3M™ General Use Masking Tape 201+
Tan, 48 mm x 55 m 4.4 mil,
24/Case Bulk



7000124889

3M™ Performance Yellow Masking
Tape 301+, 24 mm x 55 m 6.3 mil,
36/Case Bulk



7000124891

3M™ Performance Yellow Masking
Tape 301+, 48 mm x 55 m 6.3 mil,
24/Case Bulk



7000124896

3M™ High Performance Green
Masking Tape 401+, 24 mm x 55 m
6.7 mil, 24/Case Bulk



7000124898

3M™ High Performance Green
Masking Tape 401+, 48 mm x 55 m
6.7 mil, 12/Case Bulk



7000028954

3M™ General Purpose Vinyl Tape
764 Yellow, 2 in. x 36 yd. 5.0 mil,
24/Case Bulk

3M™ Duct Tapes

Duct tape offers the versatility and holding strength you expect while helping protect surfaces.



7000001330

3M™ 8979, Slate Blue 48 mm x
54.8 m 24 Rolls/CTN



7000124266

3M™ 8979 Black 48 mm x 54.8 m
24/CV



7100140217

3M™ 8979 Duct Tape, Olive 48 mm x
55 m 24/CV

Repurposing Facilities

3M™ Duct Tapes (cont.)



7000001329

3M™ 8979 PERF PLUS 48 mm x 22.8 m Blue 12/Case



7000122540

Scotch® Tough 2420-A - No Residue Duct Tape 1.88 in. x 20 yd.



7000122558

Scotch® Tough 2245-A Heavy Duty All-Weather Duct Tape 1.88 in. x 45 yd.




7000122561

Scotch® Tough 2360-C Poly Hanging & Tarps Duct Tape, 60 yd.

Scotch® Strapping Tape

Hold items closed or in place temporarily and cleanly remove as needed.



7000028947

Scotch® Strapping Tape 8898, 48 mm x 55 m, Blue

7000048850

Scotch® Strapping Tape 8898, 24 mm x 55 m, Blue

7000042791

Scotch® Strapping Tape 8898, 12 mm x 55 m, Blue

7000028946

Scotch® Strapping Tape 8898, 18 mm x 55 m, Blue


7000123859

Scotch® Strapping Tape 8898, 72 mm x 55 m, Blue

Repurposing Facilities


3M™ Safety-Walk™

Create a slip-resistant surface with a low profile tread to help reduce tripping hazards and improve safety while walking.



7000126595

3M™ Safety-Walk™ Cushion Matting
3270, Anti-Fatigue, 3 ft. x 10 ft., Black



7000052387

3M™ Safety-Walk™ Cushion Matting
3270, Anti-Fatigue, 3 ft. x 20 ft., Black



7100017455

3M™ Safety-Walk™ Cushion Matting
3270E, Anti-Fatigue, 4 ft. x 10 ft., Black



7010340183

3M™ Safety-Walk™ Cushion Matting
3270E, Anti-Fatigue, 4 ft. x 6 ft., Black



7010340264

3M™ Safety-Walk™ Cushion Matting
5270E, Anti-Fatigue, 4 ft. x 6 ft., Black



7100095556

3M™ Safety-Walk™ Cushion Matting
5270E, Anti-Fatigue, 4 ft. x 20 ft., Black




7000052247

3M™ Safety-Walk™ General Purpose
Slip-Resistant Tread 630-B, Safety
Yellow, 1 in. x 60 ft.



7000028614

3M™ Safety-Walk Edge Sealing
Compound, 12/Case



7000048386

3M™ Safety Stripe Tape 5702
Black/Yellow, 3 in. x 36 yd. 5.4 mil,
12/Case Bulk

Repurposing Facilities

3M™ Electrical Tapes & Connectors

Make new electrical connections or repair existing ones to help set up temporary structures or repurposed facilities with generated power to keep things running.



7100002398

Scotch® Super 33+™ Vinyl Electrical Tape, 3/4 in. x 66 ft.



7000006095

Scotch® Vinyl Color Coding Electrical Tape 35, 3/4 in. x 66 ft., Blue



7000006094

Scotch® Vinyl Color Coding Electrical Tape 35, 3/4 in. x 66 ft., Red



7000006097

Scotch® Vinyl Color Coding Electrical Tape 35, 3/4 in. x 66 ft., White



7000006092

Scotch® Premium Vinyl Electrical Tape Super 88, 3/4 in. x 66 ft.



7000006085

Scotch® Linerless Rubber Splicing Tape 130C, 3/4 in. x 30 ft.



7000058872

3M™ Scotchlok Female QuickSlide Disconnect, T-Tap Nylon Insulated Self-Stripping 951X-Bottle, 22-18 AWG, 50 per bottle



7000058873

3M™ Scotchlok Female QuickSlide Disconnect, T-Tap Nylon Insulated Self-Stripping 952X-Bottle, 18-14 AWG, 50 per bottle



7000058874

3M™ Scotchlok Female Self-Stripping Disconnect, T-Tap Nylon Insulated Self-Stripping 953X, Bottle, 12 AWG, 50 per bottle

Repurposing Facilities

3M™ Electrical Tapes & Connectors (cont.)



7000058271

3M™ Scotchlok™ Electrical IDC 316IR, Pigtail, Self-Stripping, Irrigation Applications, Black/White, 22-16 AWG, 30/Carton, 300/Case



7010297609

Wire Terminal Kit, Terminal Type: Non-Insulated, Number of Pieces: 214, Number of Sizes: 4



7010398318

Wire Terminal Kit, Terminal Type: Vinyl Insulated, Number of Pieces: 134, Number of Sizes: 4



7010348677

Wire Terminal Kit, Terminal Type: Nylon Insulated, Number of Pieces: 96, Number of Sizes: 7



7000031598

3M™ Heat Shrink Tubing Assorted Black Kit FP-301-Black, 5 Kits/Case



7000031588

3M™ Heat Shrink Tubing FP-301-Color-Assortment: 5 Kits/Case

3M™ Dual Lock™ Reclosable Fasteners

Temporarily connect materials or use with tarps to create temporary reclosable “doorways” into re-entry rooms.



7000001980

3M™ Dual Lock™ Reclosable Fastener SJ3540 250 Black, 1 in. x 50 yd. 0.23 in. (5.8 mm), 2/Case Bulk



7000001960

3M™ Dual Lock™ Reclosable Fastener SJ3560 250 Clear, 1 in. x 50 yd. 0.23 in. (5.8 mm), 2/Case Bulk

Repurposing Facilities


3M™ Diamond Grade™ Conspicuity Marking Tape

In low light conditions or in-case of power outages, retroreflective adhesive marking tapes allow people to better see objects or obstructions improving safe movement and facilitating easier identification of critical resources.



7100139516

3M™ Diamond Grade™ Conspicuity Markings Series 983, 4 in. x 50 yd., White




7100137856

3M™ Diamond Grade™ Conspicuity Markings Series 983, 2 in. x 50 yd., Red



7100137855

3M™ Diamond Grade™ Conspicuity Markings Series 983, 1 in. x 50 yd., White



7010388922

3M™ Diamond Grade™ Conspicuity Markings Series 983, 6 in. x 150 ft., Red/White



7100137860

3M™ Diamond Grade™ Conspicuity Markings Series 983, 3 in. x 50 yd., Red



7100007190

3M™ Diamond Grade™ Conspicuity Markings Series 983, 4 in. x 50 yd., Red



7010343741

3M™ Diamond Grade™ Conspicuity Markings Series 983, 2 in. x 150 ft., Red/White



Let's get started.

To contact us or place an order,
please call 1-888-364-3577.



3M Government Markets

Building 225-4N-15

St. Paul, MN 55144-1000

Phone: 1-866-556-5712

Email: 3msupport.fsd-orders.us@mmm.com

© 3M 2020. All rights reserved.