

# Helping your facility reopen safely

3M Graphics solutions for distancing, wayfinding, and signage

## Interior Floors



Help keep everyone on the right path with floor graphics for social distancing and wayfinding. 3M graphics for floors and carpet are durable, removable, cleanable, and UL 410 approved for anti-slip.

- 3M™ Controltac™ Print Film 40C-10R with 3M™ Scotchcal™ Luster Overlamine 8509

## Exterior Sidewalks



Show customers the way with graphics for rough exterior surfaces. 3M graphics are UL 410 or NFSI approved and feature a sandpaper-like texture.

- 3M™ Scotchcal™ Graphic Film 3662 with 3M™ Scotchcal™ Matte Overlamine 3647
- 3M™ Safety-Walk™ Printable 588/688

## Windows & Glass



Display custom window signs or decals on your storefront windows, mirrors, and glass. Durable yet removable graphics come in white or clear with a protective overlamine.

- 3M™ Controltac™ Print Film 40C-10R (white) or 3M™ Controltac™ Print Film 40C-114R (clear) with 3M™ Scotchcal™ Gloss Overlamine 8508

## Walls & Signage



Enhance your customers' confidence by reassuring them you have established social distancing practices.

- 3M™ Controltac™ Print Film 40C-10R with 3M™ Scotchcal™ Matte Overlamine 8510M

Communicate important messages with affordable graphics for temporary signs.

- 3M™ Scotchcal™ Graphic Film IJ35C

## Ready to start your project?

Our network of graphics professionals can provide design, printing, and installation services to help you achieve your goals. Contact 3M to find one near you.

Contact 3M ▶