



3M™ Cubitron™ II Roloc™  
Durable Edge Disc 984F



# Faster cut. Longer life. More durable.


Boost productivity in grinding and refining.

When you're using a disc sander, you're relying on the edge of the abrasive disc to grind and refine. 3M™ Cubitron™ II Roloc™ Durable Edge Disc 984F delivers faster performance with fewer edge failures on most metals, including mild steel and stainless steel. The durable edge backing improves edge retention, preventing fraying and early wear-out. Meanwhile, 3M Precision-Shaped Ceramic Grain self-sharpenes for fast, consistent and continuous cutting with less pressure.

Check out the testing data on the right to see how 3M™ Cubitron™ II Durable Edge Disc 984F outperforms the competition.

## 984F Beats the Competition

When grinding stainless steel, our 3M™ Cubitron™ II Disc lasted longer and cut faster than two common competitor discs.



Cuts  
**51%**  
faster than  
Norton Blaze

Cuts nearly  
**132%**  
faster than  
Arc Predator

\* Results based on the initial 60 seconds of data on an automated, 4 minute test on 304 stainless steel using 3 inch Roloc™ discs on a servo motor.



Learn more at [3m.com/984Fdiscs](http://3m.com/984Fdiscs)