

3M Science.
Applied to Life.™

Back to Business Essentials

Solutions to Prepare you for a
Different Work Environment

United States



Solutions Index and Overview

After unprecedented shutdowns, workers are heading back to businesses that may not look like they remember. 3M can help with solutions to better equip you to a new normal work environment.



Marketing and Advertising Assets

- [Product List](#)
- [Line Card – Coming Soon!](#)
- [Digital and Advertising Assets](#)

Packaging Solutions

- [Scotch® Box Sealing Tape](#)
- [3M™ Masking Tape](#)

Floor Marking and Floor Safety Solutions

- [3M™ Safety-Walk™ Floor Safety Solutions](#)
- [Floor and Safety Marking Toolkit](#)

Cleaning and Disinfecting Solutions

- [3M™ Industrial Cleaner & Adhesive Remover](#)
- [3M™ Glass Cleaner](#)
- [3M™ Stainless Steel Cleaner](#)
- [3M™ TB Quat Disinfectant Ready-to-Use Cleaner and 3M™ Disinfectant Cleaner Concentrate RCT](#)
- [3M™ Easy Trap™ Sweep & Dust Sheets](#)

Personal Safety

- [Protective Eyewear](#)
- [Fall Protection](#)
- [Head and Face Protection](#)
- [Hearing Protection](#)
- [Welding Safety](#)

MRO and Additional Products

- [Electrical Tapes and Supplies](#)
- [3M™ Duct Tapes](#)
- [3M Abrasives Systems](#)
- [3M™ VHB™ Tape LSE Series](#)
- [Automotive Aftermarkets](#)
- [Scotch™ Flex & Seal Shipping Roll](#)

Social Distancing Toolkit

Product List



[Download product list](#)



Catalogue Category	Division	Category Description	SAP ID (US)	Marketplace Formal Name (EN)
MRO	Abrasives	Portable PSG	7100219761	3M™ Cut & Grind Wheel 06469, T27, 6 in x 1/8 in x 7/8 in (152.4 mm x 3.2 mm x 22.2 mm), 10/Inner, 20/Case
MRO	Abrasives	Portable PSG	7100219187	3M™ Cut & Grind Wheel 06470, T27, 7 in x 1/8 in x 7/8 in (177.8 mm x 3.2 mm x 22.2 mm), 10/Inner, 20/Case
MRO	Abrasives	Portable PSG	7100214086	3M™ Cut & Grind Wheel 06463, T27, 5 in x 1/8 in x 7/8 in (127 mm x 3.2 mm x 22.2 mm), 10/Inner, 20/Case
MRO	Abrasives	Portable PSG	7100214084	3M™ Cut & Grind Wheel 06462, T27, 4 1/2 in x 1/8 in x 7/8 in (114.3 mm x 3.2 mm x 22.2 mm), 10/Inner, 20/Case
MRO	Abrasives	Surface Conditioning	7100179815	Scotch-Brite™ Roloc™ Clean and Strip XT Pro Extra Cut Disc, TR, A XCS, 2 in (5.08 cm) x NH
MRO	Abrasives	Coated PSG	7100178130	3M™ Flap Disc, 769F, T29, 40+, 4 1/2 in x 7/8 in (114.3 mm x 22.2 mm)
MRO	Abrasives	Coated PSG	7100178127	3M™ Flap Disc, 769F, T29, 40+, 5 in x 7/8 in (127 mm x 22.2 mm)
MRO	Abrasives	Coated PSG	7100178126	3M™ Flap Disc, 769F, T29, 60+, 5 in x 7/8 in (127 mm x 22.2 mm)
MRO	Abrasives	Coated PSG	7100178125	3M™ Flap Disc, 769F, T27, 60+, 5 in x 7/8 in (127 mm x 22.2 mm)
MRO	Abrasives	Coated PSG	7100178124	3M™ Flap Disc, 769F, T27, 80+, 5 in x 7/8 in (127 mm x 22.2 mm)
MRO	Abrasives	Coated PSG	7100178123	3M™ Flap Disc, 769F, T29, 80+, 5 in x 7/8 in (127 mm x 22.2 mm)
MRO	Abrasives	Coated PSG	7100178092	3M™ Solus™ CCS Series, SCCS07SGAF-GRN, Scotchgard™ Anti-Fog Coating, I/O Gray AF-AS lens, 20ea/cs
MRO	Abrasives	Coated PSG	7100178091	3M™ Flap Disc, 769F, T29, 120+, 4 1/2 in x 7/8 in (114.3 mm x 22.2 mm)
MRO	Abrasives	Coated PSG	7100178088	3M™ Solus™ CCS Series, SCCS07SGAF-GRN, Scotchgard™ Anti-Fog Coating, I/O Gray AF-AS lens, 20ea/cs
MRO	Abrasives	Coated PSG	7100178028	3M™ Flap Disc, 769F, T29, 80+, 4 1/2 in x 7/8 in (114.3 mm x 22.2 mm)
MRO	Abrasives	Coated PSG	7100178027	3M™ Flap Disc, 769F, T29, 60+, 4 1/2 in x 7/8 in (114.3 mm x 22.2 mm)
MRO	Abrasives	Coated PSG	7100178023	3M™ Flap Disc, 769F, T27, 60+, 4 1/2 in x 7/8 in (114.3 mm x 22.2 mm)
MRO	Abrasives	Coated PSG	7100178016	3M™ Flap Disc, 769F, T27, 80+, 4 1/2 in x 7/8 in (114.3 mm x 22.2 mm)
MRO	Abrasives	Coated PSG	7100178012	3M™ Flap Disc, 769F, T27, 40+, 5 in x 7/8 in (127 mm x 22.2 mm)
MRO	Abrasives	Coated PSG	7100177972	3M™ Flap Disc, 769F, T29, 120+, 5 in x 7/8 in (127 mm x 22.2 mm)
MRO	Abrasives	Surface Conditioning	7100177492	Scotch-Brite™ Clean and Strip XT Pro Extra Cut Disc, T27, A XCS, Quick Change, 5 in x 5/8-11 in (127 mm x M18 x 2)
MRO	Abrasives	Surface Conditioning	7100177482	Scotch-Brite™ Clean and Strip XT Pro Disc, T27, S XCS, Quick Change, 5 in x 5/8-11 in (127 mm x M18 x 2)
MRO	Abrasives	Coated PSG	7100177446	3M™ Flap Disc, 769F, T27, 40+, 4 1/2 in x 7/8 in (114.3 mm x 22.2 mm)
MRO	Abrasives	Portable PSG	7100177170	3M™ Silver Cut-Off Wheel
MRO	Abrasives	Surface Conditioning	7100175521	Scotch-Brite™ Roloc™ Clean and Strip XT Pro Disc, TR, S XCS, 2 in (5.08 cm) x NH
MRO	Abrasives	Surface Conditioning	7100175520	Scotch-Brite™ Clean and Strip XT Pro Extra Cut Disc, T27, A XCS, Quick Change, 4 1/2 in x 5/8 in-11 (114.3 mm x M18 x 2)
MRO	Abrasives	Surface Conditioning	7100175252	Scotch-Brite™ Clean and Strip XT Pro Disc, T27S, XCS, Quick Change, 4 1/2 in x 5/8 in-11 (114.3 mm x M18 x 2)
MRO	Abrasives	Surface Conditioning	7100173795	Scotch-Brite™ Roloc™ Clean and Strip XT Pro Disc, TR, S XCS, 3 in (7.62 cm) x NH
MRO	Abrasives	Surface Conditioning	7100173790	Scotch-Brite™ Roloc™ Clean and Strip XT Pro Extra Cut Disc, TR, A XCS, 3 in (7.62 cm) x NH
MRO	Abrasives	Coated PSG	7100146282	3M™ Cubitron™ II Cloth Belt 784F fabric on 120+ XF-weight 1/2 in x 18 in

Line Card – Coming Soon!



Coming Soon!

Web Banners

300x250 pixels, 789x90 pixels, 120x600 pixels, 250x250 pixels




300x250 pixels



250x250 pixels



120x600 pixels




789x90 pixels




[Download Web Banners](#)

Social Media Ads

Facebook, LinkedIn, Instagram, Twitter



Facebook Ad



LinkedIn Ad



Twitter Ad



Instagram Ad



[Download Social Media Ads](#)

Packaging Solutions

The background of the image is an abstract geometric pattern composed of numerous triangles of varying sizes and orientations. The color palette is a range of blues, from deep navy blue to bright cyan, creating a dynamic and modern visual effect. The triangles are arranged in a way that suggests a crystalline or architectural structure.

Scotch® Box Sealing Tapes

Product guide, sell sheets, videos, photography



3M Packaging Solutions Guide



Scotch® High Tack Box Sealing Tape 371+ sell sheet



[link](#) | [link \(distributor enabled\)](#)

Scotch® Box Sealing Tapes

Product guide, sell sheet, videos, photography



Demonstration videos:



[link](#)



[link](#)



[link](#)



Moisture seal image



[link](#)



Application image



[link](#)




Cold temperature image



[link](#)

3M™ Masking Tapes

Reference guide, videos, photography



Reference guide



[link](#) | [link \(distributor enabled\)](#)

3M™ Masking Tapes

Reference guide, video, photography



Masking Made Simple Video 1



[link](#)



Masking Made Simple Video 2



[link](#)




Masking Made Simple Video 3



[link](#)

3M™ Masking Tapes

Reference guide, videos, photography



Application image



[link](#)



Application image



[link](#)



Application image



[link](#)



Application image



[link](#)



Application image



[link](#)

The background is a complex, abstract geometric pattern composed of numerous overlapping triangles in various shades of blue and cyan. The triangles vary in size and orientation, creating a dynamic, crystalline effect. The colors range from deep navy blue to bright cyan, with many intermediate tones. The overall composition is non-representational and modern.

Floor Marking and Floor Safety Solutions

3M™ Safety-Walk™ Floor Safety Solutions



3M™ Safety-Walk™ Slip-Resistant Tapes and Treads		Technical Data Sheet Revision K, March 2020
Product Description		
3M™ Safety-Walk™ Coarse Tapes and Treads - 700 Series		
The product consists of large abrasive particles bonded by a tough, durable polymer to a dimensionally stable plastic film. The reverse side is coated with a pressure-sensitive adhesive covered by a removable protective liner.		
Standard Sizes:		
Refer to Standard Product Chart (Page 2)		
• Colors: Black #710, Gray #770		
• Custom sizes: Available upon request		
3M™ Safety-Walk™ Slip-Resistant General Purpose Tapes and Treads - 600 Series		
The product consists of abrasive particles bonded by a tough, durable polymer to a dimensionally stable plastic film. The reverse side is coated with a pressure-sensitive adhesive covered by a removable protective liner.		
Standard Sizes:		
Refer to Standard Product Chart (Page 2)		
• Colors: Black #610, Clear #620, Safety Yellow #630, Safety Yellow/Black Stripes #613, White #688, and Black with Photo-luminescent (PL) strip #690		
• Custom sizes: Available upon request		
3M™ Safety-Walk™ Slip-Resistant Conformable Tapes and Treads - 500 Series		
The product consists of abrasive particles bonded by a tough, durable polymer to aluminum foil. The reverse side is coated with a pressure-sensitive adhesive covered by a removable protective liner. The product is designed to stretch and conform to irregular surfaces such as diamond plating or flat surfaces with rivets or screw heads, ladder rungs, etc.		
Standard Sizes:		
Refer to Standard Product Chart (Page 2)		
• Colors: Black #503, Safety Yellow #530, and White #588		
• Custom sizes: Available upon request		
3M™ Safety-Walk™ Slip-Resistant Medium Resilient Tapes and Treads - 300 Series		
The product consists of dimensionally stable plastic film coated with a textured resilient surface. The reverse side is coated with a pressure-sensitive adhesive covered by a removable protective liner.		
Standard Sizes:		
Refer to Standard Product Chart (Page 2)		
• Colors: Black #390 and Gray #370		
• Custom sizes and colors: Available upon request.		
3M™ Safety-Walk™ Slip-Resistant Fine Resilient Tapes and Treads - 200 Series		
The product consists of a fine textured resilient top surface. The reverse side is coated with a pressure-sensitive adhesive covered by a removable protective liner.		
Standard Sizes:		
Refer to Standard Product Chart (Page 2)		
• Colors: White #280 and Clear #220		
• Custom sizes: Available upon request		



Tech Data Sheet



[link](#)

Floor and Safety Marking



Floor and Safety Marking Tape Digital Toolkit



Index and Overview



Mark your floors with the power of 3M tapes.

Floors, walls, or loading docks — whatever you need, we've got a tape for the job. From heavy traffic and pallet drag to colors and patterns for pipe marking, our tapes give you power to optimize your workflow any time you need to — while helping make sure everyone stays safe.

3M™ Ultra Durable Floor Marking Tape 971: Tough traffic areas
3M™ Vinyl Tape 471: Everyday medium traffic areas
3M™ Vinyl Tape 764: Walls and pipes

For more information, please visit 3M.com/floormarking

**If your team would like any of the assets within this toolkit co-branded, please reach out to your channel representative

Training and Technical Materials

- [Video and Technical Bulletins](#)

Selling Tools

- [Sell Sheets and Brochure](#)
- [Video Overviews](#)
- [Sales Scripts and Guide](#)
- [Marking and Attachment Solutions for Social Distancing](#)

Marketing and Advertising Assets

- [Digital Banner Ads](#)
- [Application Photography](#)
- [Social Media Recommendations](#)
- [Additional Digital Campaign Resources \(CPC\)](#)



Toolkit



The background is a complex, abstract geometric pattern composed of numerous overlapping triangles in various shades of blue and cyan. The triangles vary in size and orientation, creating a dynamic, crystalline effect. The colors range from deep navy blue to bright cyan, with many intermediate tones. The overall composition is non-representational and modern.

Cleaning and Disinfecting Solutions

3M™ Industrial Cleaner and Adhesive Remover



Videos



3M™ Industrial Cleaner Application



Maintenance Application Solutions



3M™ Adhesive Remover Application
For 3M Authorized Distributors Only.




Flyer

**Includes Option to Add Distributor Part Numbers*



Banner Ads



Free Sample Request



Sales Guide



Application and Product Images




3M™ Glass Cleaner



Flyer




[link](#)



Safety Data Sheet



[link](#)



Tech Data Sheet




[link](#)


3M™ Stainless Steel Cleaner





Brochure
Cleaner and Protector
[link](#)




Safety Data Sheet
Cleaner and Protector
[link](#)





Technical Data
Cleaner and Protector
[link](#)




Safety Data Sheet
Cleaner and Polish
[link](#)

3M™ TB Quat Disinfectant Ready-to-Use Cleaner



Technical Data Sheet



[link](#)

3M™ Disinfectant Cleaner Concentrate RCT



Flyer



[link](#)

3M™ Easy Trap™ Sweep & Dust Sheets



Brochure



[link](#)

3M™ Easy Trap Duster - Sweep & Dust Sheets
Technical Data Sheet
TD 135, April 2017
(Supersedes March 2010)

Product Description

3M™ Easy Trap Duster - Sweep & Dust Sheets (the "Product") is a unique floor dusting material that captures and holds dust and dirt. The Product can be adapted to any flat mop system.

Special Features

- The dusting sheets can be used on both sides to increase your effective floor dusting area.
- The open construction of the sheet provides space for dirt and dust to be captured.
- The proprietary coating of the fibers helps capture and hold dirt, dust, hair and sand.
- The open construction helps reduce drag when floor dusting.
- The proprietary fibers pick up even when wet.
- Perforated rolls allow you to customize the sheet size in increments of 6 in. (152 mm).

General Use Directions

Preparation

- Tear off the needed amount of dust sheets to cover the width of the holder.
- Place the sheet on the floor and place the holder directly on it, or apply the sheet on the holder and then put the system on the floor. You are now ready to dust the floor.

NOTE: When the sheet no longer picks up debris, remove the cloth from the holder, flip the cloth over and reapply it to the holder. When both sides of the cloth are completely soiled, replace the cloth.

Clean-up & Disposal

Remove used dust sheet from the holder and place in an appropriate container for disposal.

Product Specifications and Packaging

3M™ Easy Trap Duster - Sweep & Dust Sheets

6 in. wide roll	8 in. wide roll
60 sheet box	5 in. x 30 ft. (152.4 cm x 9.14 m)
250 sheets/roll (2 rolls/box)	5 in. x 125 ft. (127 cm x 38.1 m)
8 in. wide roll	
60 sheet box	8 in. x 30 ft. (203.2 cm x 9.14 m)
250 sheets/roll (2 rolls/box)	8 in. x 125 ft. (203.2 cm x 38.1 m)

Commercial Solutions
3M Center, Building 220-01C-04
St. Paul, MN 55144
1-800-328-0333
3M.com/Factory

© 3M 2017. All rights reserved.
3M is a trademark of 3M. Used under license in Canada.
All other trademarks are property of their respective owners.
TD 135, April 2017 (Supersedes March 2010)
Please recycle.

Tech Data Sheet

[link](#)


For 3M Authorized Distributors Only.

21

Personal Safety

The background of the slide is an abstract geometric pattern composed of numerous triangles of varying sizes and orientations. The color palette is a range of blues, from deep navy blue to bright cyan, creating a dynamic and modern visual effect.

Protective Eyewear



3M™ SecureFit™ Protective Eyewear
Landing Page




[link](#)



3M™ SecureFit™ Protective
Eyewear Catalog



[link](#)



3M™ Scotchgard™ Anti-Fog Coating
Landing Page



[link](#)






3M™ Scotchgard™ Anti-Fog
Coating Brochure



[link](#)

Fall Protection



3M™ DBI-SALA® Full Line Catalog



[link](#)



3M™ PROTECTA® Full Line Catalog



[link](#)



Cleaning of Web in Fall Protection Products



[link](#)



Disinfecting Fall Protection Equipment



[link](#)




3M™ Fall Protection Landing Page



[link](#)

Head and Face Protection




 [3M™ Head and Face Protection Landing Page](#)
 [link](#)

3M Science. Applied to Life.™

Guide for 3M™ ANSI Hard Hats, Headgear, and Faceshields


Product	Hazard	Compatibility	Adapter Needed
Hard Hat	Impact	Yes	No Adapter Needed
	Penetration	Yes	No Adapter Needed
	Electrical	Yes	No Adapter Needed
	Thermal	Yes	No Adapter Needed
Headgear	Impact	Yes	No Adapter Needed
	Penetration	Yes	No Adapter Needed
	Electrical	Yes	No Adapter Needed
	Thermal	Yes	No Adapter Needed
Faceshield	Impact	Yes	No Adapter Needed
	Penetration	Yes	No Adapter Needed
	Electrical	Yes	No Adapter Needed
	Thermal	Yes	No Adapter Needed

 [Guide for 3M™ ANSI Hard Hats, Headgear, and Faceshields](#)
 [link](#)




 [3M™ Head Protection eBook](#)
 [link](#)

Hearing Protection




3M™ Center for Hearing Conservation



3M™ Hearing Protection Selector Tool



3M™ Hearing Solutions Catalog



Cleaning and Disinfecting 3M™ PELTOR™ Technical Bulletin



Welding Safety

3M™ Speedglas™ Heavy-Duty Welding Helmet G5-01

REQUEST A DEMO

Adjust your welding helmet, not yourself [Download the brochure \(PDF, 2.86 MB\)](#)

Developed with extensive input from welders working at high amperages who need to grind frequently, the 3M™ Speedglas™ Heavy-Duty Welding Helmet G5-01 was created to be adaptable to your unique needs and working environment.



Variable Color Technology

Both of the new G5-01 auto-darkening welding filters (ADFs) feature the popular 3M Speedglas Natural Color Technology for more realistic color in the light state. And the G5-01VC (Variable Color) model lets users select a warm, standard, or cool color preference in the dark state.

[Watch the variable color technology in action](#)



Adjustable airflow

With the helmet's new duct system, users can direct the airflow to either their face or visor, as well as the amount of air coming from the top outlet vs. the two side outlets. With greater control over personalized settings, users can balance the airflow's cooling effect while maintaining flows that might dry out their nose or eyes.

[See how the adjustable airflow works](#)



Task light

A new, optional helmet-mounted task light provides hours of powerful lighting and runs off of the Adflo battery pack.

[Explore the task light](#)

Metal Fabrication & Production Industries

3M Integrated Welding Solutions

Help Improve Worker Safety, Comfort & Productivity With Integrated Welding Equipment.

SAFETY

COMFORT

PRODUCTIVITY

Put Safety into Practice

Workers in the metal fabrication industry face numerous hazardous and potentially hazardous levels of exposure. In fact, met-fab has one of the highest rates of OSHA recordable injuries. With this backdrop, 3M has been hard at work to offer products that provide options for you as you work to ensure worker protection, and productivity among workers in met-fab, like welders.

When it comes to welder's personal safety, we want to help. We're proud that our Technical Service team has been helping customers get the right support for more than 35 years.

REQUEST A DEMO

Choosing the Right Welding Safety Equipment

Whether you are a welder or a safety manager, the need for eye and face protection is well known when it comes to welding. But other hazards – like welding fumes – are not so well known and can result in illnesses weeks, months or years later. We can assist you in identifying the proper gear to help keep you safe for your environment.



1. Identify the hazards and assess the risks

Make a list of all the risks in your welding environment (radiation, sparks, fumes, noise, trip hazards, falling objects, etc). 3M can help with hazard monitoring and measurement tools, such as air sampling equipment.

[Safety & Hazards](#)



2. Select the right type of equipment

Determine your protection based on relevant factors, such as the following:

- Equipment type (e.g., eye, face, head, hearing)
- The level of protection needed to work safely
- Personal preferences - a key to user acceptance - covers issues including comfort, style, and ease of maintenance.

[What do you need? \(Graphic\) \(PDF, 399 KB\)](#)



3. Training, motivation & maintenance

- [Mobile Online Training and Education Center with 3M Safety Roadshow](#)
- [3M eAcademy Online training for respiratory protection classes](#)
- [Webinars and how to videos](#)



3M™ Speedglas™ Heavy-Duty Welding Helmet G5-01 Landing Page

 [link](#)



3M™ Integrated Welding Solutions Landing Page

 [link](#)



Choosing the Right Welding Equipment Guide


 [link](#)

MRO and Additional Products

The background of the slide is an abstract geometric pattern composed of numerous overlapping triangles in various shades of blue and cyan. The triangles vary in size and orientation, creating a dynamic and modern visual effect. The text "MRO and Additional Products" is overlaid on the upper left portion of this pattern.

Electrical Tapes and Supplies


Guides, brochures



Barricades Tape Brochure



[link](#)



17-page Application Guide



[link](#)



Comfort Grip Brochure



[link](#)



12-page Product Selection Guide





[link](#)

Electrical Tapes and Supplies

Scotch® Super 33+™ Vinyl Electrical Tape

Videos, photography



Strength test video



[link](#)



Elasticity video



[link](#)



Endurance video



[link](#)




Product image



[link](#)

3M™ Duct Tapes

Brochures, sell sheet, videos, photography



3M™ DT Series brochure



[link](#)



3M™ DT Series “simplified” brochure



[link](#)



3M™ DT Series sell sheet



[link](#)

3M™ Duct Tapes

Brochures, sell sheet, videos, photography



Video series	
DT8	link
DT11	link
DT17	link



3M™ DT Series video



[link](#)

3M™ Duct Tapes

Brochure, video, webinar, sell sheet, blog article, photography



Application image



[link](#)



Application image



[link](#)



Application image



[link](#)



Application image



[link](#)



Product family image




[link](#)

Electrical Tapes and Supplies

Scotch® Linerless Rubber Splicing Tape 130C

Social ad, boomerang, 360° video



130C boomerang



130C 360° video




We have a solution social ad



Electrical Tapes and Supplies

3M™ Performance Plus™ Wire Connectors


Videos, boomerang, photography



3M™ Performance Plus™ Wire Connectors Video



[link](#)



3M™ Performance Plus™ Wire Connector Boomerang



[link](#)



[Arc Flash Protection Test Video](#)

Electrical Tapes and Supplies

3M™ Performance Plus™ Wire Connectors

Video, boomerangs, photography



Product family image



[link](#)



Technology image



[link](#)



Application image




[link](#)



Application image



[link](#)




Application image



[link](#)


3M Abrasives Systems



3M™ Abrasives for Right-Angle Systems



[link](#)



3M™ Industrial Products for Metalworking



[link](#)




3M™ Roloc™ Application Guide Metalworking




[link](#)



[Videos](#)




[link](#)



[link](#)

3M™ VHB™ LSE Tapes



Banner Ads



[link](#)



Sales Guide




[link](#)



Distributor Flyer




[link](#)



Video



[link](#)



Brochure



[link](#)



Product Images



[link](#)



Part Numbers



[link](#)


Automotive Aftermarket Cleaning Supplies

Product ID	Product Name	Asset Location 
7100006252	3M™ Detailing Spray Bottle, 37716, 32 fl oz (946 ml)	Product image 
7000045728	3M™ Spray Trigger Nozzle Head, 37717uyui	Product image 
7100145294	3M™ Wetordry™ Bucket, 02513	Product image 
7100100889	3M™ Detailing Cloth Yellow	Product image 
7000142673	3M™ Glass Cleaner, 08968, 19 oz (538.64 g)	Product image 
7000000457	3M™ Glass Cleaner, 08888, 19 oz.	Product image 
7010328094	3M™ Interior Protection Automotive Seat Cover, 36900	Product image 
7000125073	Marson® Kwikiee™ Disposable Plastic Seat Covers, 30200	Product image 
7010364272	3M™ Interior Protection Floor Mat, 39601, 19 in x 17 in	Product image 
7000142688	3M™ Leather and Vinyl Restorer, 39040, 16 oz (453.6 g)	Product image 
7100085658	38087, Interior Dressing, 5 GAL	Product image 

Products to help with cleaning applications and to ensure fewer contact points as you start to get back to business.



Scotch™ Flex & Seal Shipping Roll




Scotch™ Flex & Seal Shipping Landing Page



[link](#)



[Videos](#)



- Sustainability document
- Proof in Numbers document
- Sealing Benefit document




[link](#)

Social Distancing Toolkit


The background of the image is a complex, abstract geometric pattern composed of numerous overlapping triangles. The triangles are in various shades of blue and cyan, creating a dynamic and modern visual effect. The text 'Social Distancing Toolkit' is centered in the upper portion of the image, rendered in a clean, white, sans-serif font.

3M Social Distancing Product Solutions Toolkit



Overview


- [Personal Protective Equipment Solutions](#)
 - Communications From a Distance
 - Hearing Protection
 - Eye Protection
- [Floor Marking Solutions](#)
- [Other Product Solutions](#)
- [Helpful Resources](#)



© 3M 2020. All Rights Reserved.



Content intended for 3M Authorized Distributors only. 2



3M Social Distancing Production Solutions Toolkit



[link](#)

The background is a complex, abstract geometric pattern composed of numerous triangles of varying sizes and orientations. The color palette is a range of blues, from deep navy blue to bright cyan, creating a dynamic and modern visual effect.

Thank you!