

3M[™] Silicon Carbide – a Versatile Specialist

Formerly known as EKasic®

Practically experienced scientists develop ceramic-based solutions to your requirements. A broad range of silicon carbide materials, tailored to specific fields of application, continually opens up new opportunities. Parts made of 3M[™] Silicon Carbide have an excellent track record over decades in many industrial sectors. Our scientists translate the demands of technical systems into focused customer solutions and ensure that our innovations are economically feasible and logistically manageable.



3M[™] Silicon Carbide Pump Shafts



3M[™] Silicon Carbide Gas Sealing Rings used for compressors and stirrers in the oil and gas processing.



3M[™] Silicon Carbide Sliding Bearings used e.g. in quality chemical and industrial pumps as well as in stirrers and mixers for the chemical, pharmaceutical and food industry.



3M[™] Silicon Carbide Mechanical Seal Rings are particularly suitable for heavy-duty applications, i.e. the handling of contaminated fluids, abrasive fluids and/or extremely corrosive fluids.



3M[™] Silicon Carbide laserstructured Sliding Bearings (left: radial bearing, right: thrust bearings) used e.g. in highly-loaded chemical pumps, in magnetic couplings for hermetically sealed pumps and in stirrers for chemical and pharmaceutical processes.

3M Technical Ceramics provides the widest product portfolio of sintered silicon carbide material in the market. The key to performance of our 3M[™] Silicon Carbide material is microstructure.

Our materials develop applications for technical systems that meet very tough demands:

- Tribological performance under high load (pressure, sliding speed, temperature)
- High resistance to wear
- Resistance to corrosion in aggressive media
- Thermal shock resistance
- Low distortion under thermal loads

The all-rounder

3M[™] Silicon Carbide Grade F

Good chemical resistance, low specific density, high hardness and wear resistance, outstanding thermal conductivity properties and thermoshock resistance: 3M[™] Silicon Carbide Grade F combines all these specific advantages of sintered silicon carbide particularly for bearings and seals for use in pumps.



The corrosion-resistant grade

3M[™] Silicon Carbide Grade C

Resistance to corrosion is a particular problem where aggressive chemicals or hot water are being transferred e.g. by circulating pumps. 3M[™] Silicon Carbide Grade C has proved highly effective in corrosive environments.

The high-strength grades

3M[™] Silicon Carbide Grade F plus and Grade T plus

Two high-density materials achieve the optimum strength for silicon carbide. These non-porous, fine-grained grades guarantee very high mechanical strength and edge stability. 3M[™] Silicon Carbide Grade F plus and Grade T plus are the ideal materials for complex thermal and mechanical loads.

The tribological grades

3M[™] Silicon Carbide Grade P and Grade G

Improved dry run and mixed friction properties prove especially valuable in sliding and friction systems. The porous 3M[™] Silicon Carbide Grade P and the graphite-loaded 3M[™] Silicon Carbide Grade G.

Product is manufactured and sold by 3M Technical Ceramics, Zweigniederlassung der 3M Deutschland GmbH.

Warranty and Limitation of Liability: Many factors beyond our control and uniquely within user's knowledge and control can affect the use and performance of the product in a particular application. User is solely responsible for evaluating the product and determining whether it is fit for a particular purpose and suitable for user's method of application. User is solely responsible for evaluating third party intellectual property rights and for ensuring that user's use of the product does not violate any third party intellectual property rights. Unless a different warranty is specifically stated in the applicable product literature or packaging insert, we warrant that each product meets the applicable product specification at the time we ship the product.

WE MAKE NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OF NON-INFRINGEMENT OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE.

The quality of our products is warranted under our General Terms and Conditions of Sale as now are or hereafter may be in force.

Limitation of Liability: Except where prohibited by law, we will not be liable for any loss or damages arising from the product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability. We accept liability for intent and gross negligence. We are also liable for any culpable breach of major contractual obligations; however, if a breach of major contractual obligations is due to negligence, our liability is limited to the foreseeable damage associated with this type of contract. This does not affect our liability for culpable fatal or bodily injury or damage to health; this also applies to liability under the Product Liability Act (*Produkthaftungsgesetz*). Other claims for compensation are excluded.

Technical Information: Technical information, recommendations, and other statements contained in this document or provided by us are based on tests or experience that we believe are reliable, but the accuracy or completeness of such information is not guaranteed. Such information is intended for persons with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license under any of our or third party intellectual property rights is granted or implied with this information.



3M Technical Ceramics Zweigniederlassung der 3M Deutschland GmbH Max-Schaidhauf-Straße 25 87437 Kempten, Germany T +49 (0)831 5618-0 F +49 (0)831 5618-345 info.technical-ceramics@3M.com www.3M.de / Technical-Ceramics

The management system has been certified according to DIN EN ISO 9001, DIN EN ISO 50001, DIN EN ISO 14001.

Please recycle. Printed in Germany. © 3M 2015. All rights reserved. Issued: 09/15 3M is a trademark of 3M. Used under license by 3M subsidiaries and affiliates.