3M Data Sheet ScotchTM 33 Vinyl Electrical Tape

1. Product Description

Scotch[™] 33 Electrical Tape is a quality, general purpose vinyl insulating tape. It has excellent resistance to: abrasion, moisture, alkalies, acid, copper corrosion and varying weather conditions (including sunlight). It is a polyvinyl chloride (PVC) tape that has a high electric strength, is flame retardant and conformable, and provides excellent mechanical protection with minimum bulk. It is a UL Listed "Insulating Tape".

Product features are:

- UL Listed; UL 510 Standard "Insulating Tape" (product category OANZ), File E129200
- Polyvinyl chloride (PVC) backing
- Pressure-sensitive rubber based adhesive
- Inhibits corrosion of electrical conductors
- Complies with solid electric cable insulation

2. Applications

- Primary electrical insulation for all wire and cable splices rated up to 600 volts and 105°C
- Protective jacketing for high voltage cable splices and repairs
- Harnessing of wires and cables
- For indoor and outdoor applications
- For above or below grade applications

3. Typical Properties*

Electric Strength ¹	>39 KV/mm
Insulation Resistance ²	>10 ⁶ MΩ
Thickness ³	0.178 mm
Elongation ³	200%
Backing Strength ³	29.77 N/10 mm
Adhesion ³ To Steel To Backing	2.63 N/10 mm 2.41 N/10 mm
Temperature Rating ⁴	80°C
UL 510 Flame Retardant ³	Yes

Flagging³

<2.54 mm

Telescoping 24 h at 50°C

<2.54 mm

*These are typical properties and should not be used for specification purposes.

- ¹ IEC 60243
- ² IEC 60426
- ³ IEC 60454-2

⁴ UL-recognized for flame retardancy per UL 510, Product Category OANZ2, File E129200

4. Installation Techniques

The tape shall be applied in half-lapped layers with sufficient tension to conform and produce a uniform covering. In most applications, this tension will reduce the tape's width to approximately 5/8 of its original width. On pigtail splices, the tape should be wrapped beyond the end of the wires and then folded back, leaving a protective cushion to resist cut-through. Always wrap the tape "uphill", taping from a smaller diameter surface to a larger diameter surface. Apply the tape with no tension on the last wrap to prevent flagging.

5. Shelf Life

Scotch[™] 33 Vinyl Electrical Tape has a 5 years shelf life (from date of manufacture) when stored under the following recommended storage conditions. Store behind present stock in a clean dry place at a temperature of 21°C and 40-50% relative humidity. Good stock rotation is recommended.

6. Availability

Scotch[™] 33 Vinyl Electrical Tape is available from your local 3M authorized electrical distributor in the following standard roll sizes:

19 mm x 33 m

38 mm x 13.5 m

Other lengths and widths are available by special order.

IMPORTANT NOTICE

All statements, technical information and recommendations related to the Seller's products are based on information believed to be reliable, but the accuracy or completeness thereof is not guaranteed. Before utilizing the product, the user should determine the suitability of the product for its intended use. The user assumes all risks and liability whatsoever in connection with such use.

Any statements or recommendations of the Seller which are not contained in the Seller's current publications shall have no force or effect unless contained in an agreement signed by an authorized office of the Seller. The statements contained herein are made in lieu of all warranties, expressed or implied, including but not limited to the implied warranties of merchantability and fitness for a particular purpose which warranties are hereby expressly disclaimed.

SELLER SHALL NOT BE LIABLE TO THE USER OR ANY OTHER PERSON UNDER ANY LEGAL THEORY; INCLUDING BUT NOT LIMITED TO NEGLIGENCE OR STRICT LIABILITY; FOR ANY INJURY OR FOR ANY DIRECT; INDIRECT; INCIDENTAL OR CONSEQUENTIAL DAMAGES SUSTAINED OR INCURRED BY REASON OF THE USE OF ANY OF THE SELLER'S PRODUCTS.

> **3M** 2003 Issue: 1

ЗМ

Electro Product Division Carl-Schurz-Straße 1 D-41453 Neuss Germany Tel: +49 2131 – 14 0 Fax: +49 2131 – 14 3897